



Lenovo 4XC1K83390 network card Internal Ethernet 1000 Mbit/s

Brand : Lenovo
Product code: 4XC1K83390
Product name : 4XC1K83390



- Dual-port Gigabit Ethernet (GbE) Adapter
- IEEE 802.3ab 10/100/1000 Mb/s Gigabit Ethernetcompliant
- ThinkStation Broadcom BCM5720-2P Dual-port Gigabit Ethernet Adapter

Lenovo 4XC1K83390 network card Internal Ethernet 1000 Mbit/s:

ThinkStation Broadcom BCM5720-2P Dual-port Gigabit Ethernet Adapter is a dual-port 10/100/1000 Mb/s x1 PCI Express (PCIe) Ethernet adapter that supports offload technologies including Large Send, TCP segmentation, and TCP/UDP/IP checksum, and receive-side scaling (RSS) that deliver optimal network throughput, lower host processor utilisation and as a result improve system overall performance. Lenovo 4XC1K83390. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Maximum data transfer rate: 1000 Mbit/s

Ports & interfaces		Design	
Connectivity technology *	Wired	Certification	CE/FCC/IC/ACA/BSM/MSIP/VCCI
Host interface *	PCI Express	Compatible products	ThinkStation
Interface *	Ethernet	Operational conditions	
Ethernet LAN (RJ-45) ports	2	Operating temperature (T-T)	0 - 55 °C
Network		Operating relative humidity (H-H)	5 - 95%
Maximum data transfer rate *	1000 Mbit/s	Weight & dimensions	
Networking standards *	IEEE 802.3ab, IEEE 802.3az, IEEE 802.3x	Width	111.8 mm
Ethernet LAN	✓	Depth	65.6 mm
Ethernet interface type	Gigabit Ethernet	Weight	80 g
Ethernet LAN data rates	10,100,1000 Mbit/s	Packaging data	
Cabling technology	10/100/1000BaseT(X)	Package width	177 mm
Design		Package depth	144 mm
Component for *	Server	Package height	53 mm
Internal *	✓	Package weight	120 g



0195892084259



195892084259

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.