

Epson EB-760Wi 4100 ANSI lumens 3LCD WXGA (1280x800) White

Brand : Epson

Product code: V11HA80080

Product name : EB-760Wi

- Interactive HD display for any room 53-100" UST display for unrestricted viewing (no shadows/reflections)
 - Bright and energy efficient laser 4,100lm CLO with 3LCD technology for brighter colours at only 205W
 - Effortless connectivity options Auto-on, wired / wireless display with USB 2A output for smart sticks
 - Simple to use and built to last Virtually maintenance free with 5-year, 12,000hr warranty
 - Document camera compatibility Create and record a live, totally immersive lesson or presentation
- 4100 Lumen, WXGA, 3LCD, Laser, 53" - 100", LAN, WLAN, 356 x 395 x 133 mm



Projector		Network	
Smart projector *	✗	Wi-Fi *	✓
Screen size compatibility *	1346.2 - 2540 mm (53 - 100")	Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac)
Projector brightness *	4100 ANSI lumens	Miracast	✓
Projection technology *	3LCD	Storage	
Projector native resolution *	WXGA (1280x800)	Card reader integrated *	✗
Contrast ratio (typical) *	2500000:1	Features	
Native aspect ratio *	16:10	Interactive *	✓
Number of colours	1.07 billion colours	Noise level (economic mode)	27 dB
Projector brightness (economic mode)	2100 ANSI lumens	On Screen Display (OSD)	✓
Keystone correction, horizontal	-3 - 3°	Noise level *	37 dB
Keystone correction, vertical	-3 - 3°	Air filter	✓
Matrix size	1.5 cm (0.59")	Multimedia	
Light source		Built-in speaker(s) *	✓
Light source type *	Laser	RMS rated power	16 W
Service life of light source *	20000 h	Design	
Service life of light source (economic mode)	30000 h	Market positioning *	Presentation
Lens system		Product colour *	White
Focus *	Manual	Placement	Ceiling, Desktop, Wall
Fixed focal length	3.7 mm	Cable lock slot	✓
F-number (relative aperture)	1.6	Cable lock slot type	Kensington
Zoom ratio	1.35:1	Display	
Throw ratio	0.27 - 0.37:1	Built-in display *	✗
Video		Power	
Analog signal format system *	Not supported	Power source *	AC
Full HD *	✗	Power consumption (typical) *	197 W
3D *	✗	Power consumption (economy mode)	141 W
Ports & interfaces		AC input voltage	100 - 240 V
Service port type	USB Type-B	AC input frequency	50/60 Hz
USB 2.0 ports quantity	2		
Headphone outputs	3		

Ports & interfaces		Operational conditions	
Microphone in	✓	Operating relative humidity (H-H)	20 - 80%
Serial interface type *	RS-232C	Storage relative humidity (H-H)	-10 - 90%
VGA (D-Sub) ports quantity *	3	Weight & dimensions	
HDMI ports quantity *	3	Width	356 mm
Composite video in *	1	Depth	395 mm
DVI port *	✗	Height	133 mm
Network		Weight *	6 kg
Smart TV *	✗	Packaging content	
Ethernet LAN *	✓	Remote control included *	✓
Ethernet LAN data rates	10,100 Mbit/s	Batteries included	✓
		Cables included	AC, USB
		Interactive pen included	✓



8715946715261

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.