

ASUS ProArt PA278CV computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD LED Black

Brand : ASUS

Product family: ProArt

Product code: 90LM06Q1-B02370

Product name : PA278CV

- 27-inch WQHD (2560 x 1440) LED backlight display with IPS 178° wide viewing angle panel
 - International color standard 100% sRGB and 100% Rec. 709 wide color gamut
 - Calman Verified with factory calibrated for excellent Delta E < 2 color accuracy
 - Extensive connectivity including DP over USB-C™ with 65W Power Delivery, DisplayPort, HDMI, USB hub
 - 75Hz refresh rate and Adaptive-Sync technology (48~75Hz) to animated content with fast action and eliminate screen tearing
 - Daisy-chaining allows users to daisy chain up to four monitors for a multi-display workstation via DisplayPort
 - Ergonomic design with +35° ~ -5° tilt, ±45° swivel, ±90° pivot and 150mm height adjustments for a comfortable viewing experience
- 27", IPS, WQHD, 2560 x 1440, 100% sRGB, 5ms, 75Hz, HDCP, 2 x 2W, USB-C, 2 x DisplayPort, HDMI, 4 x USB Hub, Earphone, Power Delivery, 615 x (374 - 524) x 228 mm, 8.4 Kg



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	HDMI version	1.4
Display resolution *	2560 x 1440 pixels	DisplayPorts quantity	2
HD type *	Quad HD	DisplayPort version	1.2
Native aspect ratio *	16:9	Audio input	✗
Display technology *	LED	Headphone out *	✓
Panel type *	IPS	Headphone outputs	1
Touchscreen *	✗	Headphone connectivity	3.5 mm
Display brightness (typical)	350 cd/m²	HDCP	✓
Response time *	5 ms	Charging port type	USB Type-C
Screen shape *	Flat	Ergonomics	
Supported graphics resolutions	2560 x 1440	VESA mounting *	✓
Contrast ratio (typical) *	1000:1	Panel mounting interface	100 x 100 mm
Contrast ratio (dynamic)	100000000:1	Cable lock slot *	✓
Dynamic contrast ratio marketing name	SmartContrast	Cable lock slot type	Kensington
Maximum refresh rate *	75 Hz	Height adjustment *	✓
Viewing angle, horizontal	178°	Adjustable height (max)	15 cm
Viewing angle, vertical	178°	Pivot	✓
Display number of colours *	16.7 million colours	Pivot angle	-90 - 90°
Pixel pitch	0.233 x 0.233 mm	Swivelling	✓
Viewable size, horizontal	59.7 cm	Swivel angle range	-45 - 45°
Viewable size, vertical	33.6 cm	Tilt adjustment	✓
Digital horizontal frequency	30 - 112 kHz	Tilt angle range	-5 - 35°
Digital vertical frequency	46 - 75 Hz	Power	
sRGB coverage (typical)	100%	Energy efficiency class (SDR) *	G
Performance		Energy consumption (SDR) per 1000 hours *	32 kWh
AMD FreeSync *	✓	Power consumption (typical) *	21.28 W
VESA Adaptive Sync support	✓	Power consumption (off)	0 W
Flicker-free technology	✓	Power consumption (PowerSave)	0.5 W
Low Blue Light technology	✓		

Multimedia		Power	
Number of speakers	2	AC input voltage	100 - 240 V
RMS rated power	4 W	Energy efficiency scale	A to G
Built-in speaker(s) *	✓	Weight & dimensions	
Built-in camera *	✗	Width (with stand)	615 mm
Design		Depth (with stand)	228 mm
Market positioning *	Graphics design	Height (with stand)	524 mm
Product colour *	Black	Weight (with stand)	8.4 kg
Front bezel colour	Black	Width (without stand)	615 mm
Feet colour	Silver	Depth (without stand)	54 mm
Ports & interfaces		Height (without stand)	372 mm
Built-in USB hub *	✓	Packaging data	
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Package width	731 mm
USB upstream port type	USB Type-C	Package depth	227 mm
USB Type-A downstream ports quantity	4	Package height	456 mm
USB Power Delivery up to	65 W	Package weight	10.7 kg
DVI port	✗	Package type	Box
HDMI *	✓	Packaging content	
HDMI ports quantity	1	Cables included	AC, DisplayPort, HDMI, USB Type-C
Logistics data			
		Harmonized System (HS) code	85285210



4718017910040

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.