



Canon i-SENSYS MF542x Laser A4 1200 x 1200 DPI 43 ppm Wi-Fi

Brand : Canon

Product family: i-SENSYS

Product code: 3513C008

Product name : MF542x

1200 x 1200dpi, UFR II, PCL 5e, PCL6, Adobe PostScript, 72.9 dB, 1430W, 19.8Kg

[Canon i-SENSYS MF542x Laser A4 1200 x 1200 DPI 43 ppm Wi-Fi:](#)

Canon i-SENSYS MF540 Series

Get ultra-fast results and versatile multifunctionality from a space-saving black and white laser printer, ideal for hard-working businesses

A versatile black and white laser printer

Meet the needs of your business with the Canon i-SENSYS MF540 series: high-performance multifunctional laser printers with rapid print speeds, customisable controls and flexible mobile connectivity – perfect for those in need of a space-saving solution.

Canon i-SENSYS MF542x

Take black and white printing to the next level with the MF542x, a multifunctional laser printer with superior print speeds and versatile connectivity for workers on the move.

Canon i-SENSYS MF542x

Save space with a compact design boasting print, scan and copy functionality, a perfect fit for productive businesses in need of a high-performance black and white laser printer.



Printing		Paper handling	
Duplex printing mode	Auto	ISO A-series sizes (A0...A9) *	A4, A5
Print technology *	Laser	ISO B-series sizes (B0...B9)	B5
Printing *	Mono printing	Non-ISO print media sizes	Legal, Statement
Duplex printing *	✓	Envelopes sizes	C5, Com-10, DL, Monarch
Maximum resolution *	1200 x 1200 DPI	Paper tray media weight	60 - 120 g/m ²
Print speed (black, normal quality, A4/US Letter) *	43 ppm	Multi-Purpose Tray media weight	60 - 199 g/m ²
Warm-up time	14 s	Ports & interfaces	
Time to first page (black, normal)	5.7 s	Direct printing *	✓
Copying		USB port	✓
Duplex copying *	✓	USB 2.0 ports quantity	1
Copying *	Mono copying	Network	
Maximum copy resolution *	600 x 600 DPI	Wi-Fi *	✓
Copy speed (black, normal quality, A4)	43 cpm	Ethernet LAN *	✓
Time to first copy (black, normal)	6.4 s	Cabling technology	10/100/1000Base-T(X)
Maximum number of copies	999 copies	Ethernet LAN data rates	10,100,1000 Mbit/s
Copier resize	25 - 400%	Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)
Scanning		Security algorithms	64-bit WEP, 128-bit WEP, 802.1x RADIUS, AES, HTTPS, SNMPv3, SSL/TLS, TKIP, WPA-PSK, WPA2-PSK
Duplex scanning *	✓	Supported network protocols (IPv4)	LPD, RAW, Port9100, IPP, IPPS, WSD
Scanning *	Colour scanning	Supported network protocols (IPv6)	LPD, RAW, Port9100, IPP, IPPS, WSD
Optical scanning resolution *	600 x 600 DPI	Management protocols	SNMPv1, SNMPv3 (IPv4,IPv6)
Maximum scan resolution	9600 x 9600 DPI	Mobile printing technologies	Apple AirPrint, Canon PRINT Business, Google Cloud Print, Mopria Print Service
Scanner type *	Flatbed & ADF scanner	Performance	
Scan to	Cloud, E-mail, PC, USB	Card reader integrated	✗
Image formats supported	JPG, PNG, TIF	Internal memory *	1000 MB
Document formats supported	PDF	Processor frequency	800 MHz
Input colour depth	24 bit	Sound pressure level (printing)	72.9 dB
Output colour depth	24 bit		
Greyscale levels	256		
Scan drivers	ICA, TWAIN, WIA		

Fax		Design	
Duplex faxing	✓	Product colour *	White
Faxing *	Mono faxing	Market positioning *	Business
Fax resolution (black)	400 x 400 DPI	Built-in display *	✓
Fax transmission speed	3 sec/page	Display	LCD
Modem speed	33.6 Kbit/s	Display diagonal	12.7 cm (5")
Fax memory	512 pages	Control type	Touch
Auto-redialing	✓	Power	
Fax forwarding	✓	Power consumption (max)	1430 W
Error Correction Mode (ECM)	✓	Power consumption (standby)	13.6 W
Features		Power consumption (sleep)	0.9 W
Recommended duty cycle	2000 - 7500 pages per month	Energy Star Typical Electricity Consumption (TEC)	1.4 kWh/week
Maximum duty cycle *	150000 pages per month	AC input voltage	220 - 240 V
Digital sender	✓	AC input frequency	50 - 60 Hz
Page description languages	PCL 5e, PCL 6, PostScript 3, UFRII-LT	System requirements	
Printer fonts	PCL, PostScript	Windows operating systems supported	Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Vista
Input & output capacity		Mac operating systems supported	Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
Total number of input trays *	1	Linux operating systems supported	✓
Total input capacity *	550 sheets	Server operating systems supported	Windows Server 2003, Windows Server 2003 R2, Windows Server 2008, Windows Server 2008 R2, Windows Server 2012, Windows Server 2012 R2
Total output capacity *	150 sheets	Operational conditions	
Multi-Purpose tray	✓	Operating relative humidity (H-H)	20 - 80%
Multi-Purpose tray input capacity	100 sheets	Operating temperature (T-T)	10 - 30 °C
Auto document feeder (ADF)	✓	Weight & dimensions	
Auto document feeder (ADF) input capacity	50 sheets	Width	480 mm
Paper handling		Depth	464 mm
Maximum ISO A-series paper size *	A4	Height	452 mm
Maximum print size	215 x 355 mm	Weight	19.8 kg
Paper tray media types *	Envelopes, Heavy paper, Labels, Plain paper, Recycled paper	Logistics data	
		Harmonized System (HS) code	84433100



8714574663791

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.