

Brother BSS-1D300-060 printer ribbon Black

Brand : Brother

Product code: BSS-1D300-060

Product name : BSS-1D300-060



- High capacity at 300 metres length per ribbon
- 60mm in width
- High quality thermal transfer ink ribbon
- Ensure clear, durable results
- Standard wax/resin with black ink
- Requires compatible label roll

The BSS-1D300-060 standard wax/resin thermal transfer black ink ribbon, 300 metres in length and 60mm in width has been Certified by Brother International Europe.

Brother BSS-1D300-060 printer ribbon Black:

This high capacity standard wax/resin ribbon has been developed to meet your professional label printing needs. For use in retail, healthcare and logistics, you can use these 60mm wide ribbons for barcode printing and a variety of other applications. Wax/resin thermal transfer ribbons are the best of both worlds, combining the cost effectiveness of wax ribbons alongside the durability of resin labels. The BSS-1D300-060 ribbons are used in conjunction with compatible label rolls in your thermal transfer label printer. Wax/resin ribbons are best suited to coated paper labels.



Performance		Weight & dimensions	
Printing colours	Black	Depth	65 mm
Print technology	Thermal transfer	Height	60 mm
Product colour	Black	Weight	191 g
Country of origin	Spain	Ribbon width	6 cm
Brand compatibility	Brother	Ribbon length	300 m
Compatibility *	TD-4420TN, TD-4520TN, TD-4650TNWB, TD-4650TNWBR, TD-4750TNWB, TD-4750TNWBR	Packaging data	
Technical details		Package weight	2.62 kg
		Quantity per pack	1 pc(s)
Master (outer) cases per pallet layer	13 pc(s)	Logistics data	
Layers per pallet	8 pc(s)	Products per pallet	1248 pc(s)
Pallet type	800 x 1200 mm	Pallet gross weight	290.5 kg
Weight & dimensions		Pallet gross height	11.1 cm
Width	65 mm	Master (outer) cases per pallet	104 pc(s)
		Harmonized System (HS) code	84439990



5014047600364



5014047600401

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.