

Epson CO-W01 3000 ANSI lumens 3LCD WXGA (1200x800) Black, White



Brand : Epson

Product code: V11HA86040

Product name : CO-W01

- WXGA projector
 - 3,000 lumen brightness
 - Up to 378" screen size
 - 3LCD technology
- WXGA projector

Epson CO-W01 3000 ANSI lumens 3LCD WXGA (1200x800) Black, White:

Create the big screen experience with this high-quality, long-lasting and flexible projector for the home and office, with WXGA resolution.

Here's a projector the whole family can enjoy; from watching box sets to delivering sharp presentations, this WXGA projector has the tools for the job. There's no need to worry about ambient light; it produces a bright and clear display with 3,000 lumens and 3LCD technology. It's also easy to transport and set up. And its incredibly long lamp life means it's great value for money.

Projector		Features	
Screen size compatibility *	635 - 9601.2 mm (25 - 378")	Noise level (economic mode)	29 dB
Projection distance	0.9 - 10.4 m	Noise level *	38 dB
Projector brightness *	3000 ANSI lumens	Country of origin	Philippines
Projection technology *	3LCD	Multimedia	
Projector native resolution *	WXGA (1200x800)	Built-in speaker(s) *	✓
Native aspect ratio *	16:10	RMS rated power	5 W
Number of colours	16.7 million colours	Design	
Projector brightness (economic mode)	2000 ANSI lumens	Market positioning *	Presentation
Keystone correction, horizontal	-30 - 30°	Product colour *	Black, White
Keystone correction, vertical	-30 - 30°	Placement	Desktop
Matrix size	1.5 cm (0.59")	Cable lock slot	✓
Vertical synchronization (min)	100 kHz	Cable lock slot type	Kensington
Vertical synchronization (max)	120 kHz	Power	
Light source		Power source *	AC
Light source type *	Lamp	Power consumption (typical) *	270 W
Service life of light source *	6000 h	Power consumption (standby) *	0.5 W
Service life of light source (economic mode)	12000 h	Power consumption (economy mode)	214 W
Lamp type	UHE	AC input voltage	100 - 240 V
Lamp power	188 W	AC input frequency	50 - 60 Hz
Lens system		Operational conditions	
Focus *	Manual	Operating temperature (T-T)	5 - 40 °C
Zoom capability	✓	Storage temperature (T-T)	-10 - 60 °C
Throw ratio	1.27 - 1.71:1	Operating relative humidity (H-H)	20 - 80%
Video		Storage relative humidity (H-H)	10 - 90%
Analog signal format system *	Not supported	Weight & dimensions	
Full HD *	✗	Width	295 mm
3D *	✗	Depth	211 mm
Video colour modes	Cinema, Dynamic, Presentation, Vivid	Height	87 mm
Ports & interfaces		Weight *	2.4 kg
HDMI version	1.4	Package width	365 mm
USB 2.0 ports quantity	2	Package depth	322 mm
		Package height	165 mm

Ports & interfaces		Weight & dimensions	
USB 2.0 Type-A ports quantity	1	Package weight	3.68 kg
USB 2.0 Type-B ports quantity	1	Packaging content	
HDMI ports quantity *	1	Remote control included *	✓
Storage		Batteries included	✓
Card reader integrated *	✗	Cables included	AC
		Technical details	
		Commodity Classification Automated Tracking System (CCATS)	85286200000
		Logistics data	
		Harmonized System (HS) code	85286200000



8715946706849

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.