



APC APDU9981EU3 power distribution unit (PDU) 24 AC outlet(s) 0U Black

Brand : APC


Product code: APDU9981EU3

Product name : APDU9981EU3

- APC Rack PDU 9000 Switched, ZeroU, 11.0kW, 230V, (21) C13 & (3) C19
- With Industry leading reliability, manageability, and security, APC Switched Rack PDU's provide advanced load management plus on/off outlet level power cycling and sequencing control
- Includes: Installation guide, Rack mounting brackets, Safety guide, Serial configuration cable
Rack PDU 9000 Switched, ZeroU, 11.0kW, 230V, (21) C13 & (3) C19
APC APDU9981EU3. PDU types: Switched, Rack capacity: 0U, Type: Three-phase. AC outlets quantity: 24 AC outlet(s), AC outlet types: C13 coupler, C19 coupler, Power plug: IEC 60309. Cable length: 1.8 m.
Nominal input voltage: 400 V, Maximum current: 16 A, AC input frequency: 50 - 60 Hz. Certification: CUL listed, EN 55022 class A, EN 55024, EN 61000-3-2, EN 61000-3-3, FCC part 15 class A, ICES-003,...



Design		Power	
PDU types *	Switched	Maximum total current draw per phase	16 A
Type	Three-phase	Maximum power	11000 W
Rack capacity *	0U	Certificates	
Mounting	Vertical	Certification	CUL listed, EN 55022 class A, EN 55024, EN 61000-3-2, EN 61000-3-3, FCC part 15 class A, ICES-003, UL listed, VDE
Product colour	Black	Operational conditions	
Display	LCD	Operating temperature (T-T)	-5 - 45 °C
On/off switch	✓	Storage temperature (T-T)	-25 - 65 °C
Ports & interfaces		Operating relative humidity (H-H)	0 - 95%
AC outlets quantity *	24 AC outlet(s)	Storage relative humidity (H-H)	5 - 95%
Power plug	IEC 60309	Operating altitude	0 - 3048 m
AC outlet types *	C13 coupler, C19 coupler	Non-operating altitude	0 - 15240 m
Features		Weight & dimensions	
Daisy chain	✓	Width	55 mm
Reset button	✓	Depth	46 mm
Cable length	1.8 m	Height	1792 mm
Power		Weight	7 kg
Nominal input voltage *	400 V	Packaging data	
AC input frequency	50 - 60 Hz	Package weight	8.95 kg
Maximum current *	16 A	Package width	165 mm
Nominal output voltage	230 V	Package depth	114 mm
Output voltage	230 V	Package height	2002 mm
Load capacity	11040 VA		
Maximum input current per phase	16 A		



0731304404262



731304404262

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.