

Targus AMB586GL mouse Gaming Ambidextrous Bluetooth Optical 4000 DPI

Brand : Targus

Product code: AMB586GL

Product name : AMB586GL

Wireless, 4.33"x2.95"x1.77", Black
Targus AMB586GL. Form factor: Ambidextrous. Movement detection technology: Optical, Device interface: Bluetooth, Movement resolution: 4000 DPI, Buttons type: Pressed buttons, Buttons quantity: 6, Scroll type: Wheel. Power source: Batteries. Product colour: Black




Mouse		Design	
Number of scroll wheels	1	Product colour *	Black
Scrolling directions	Vertical	Surface coloration	Monochromatic
Purpose *	Gaming	Power	
Device interface *	Bluetooth	Power source *	Batteries
Movement detection technology *	Optical	Number of batteries supported	1
Movement resolution *	4000 DPI	Battery type	AA
Buttons type	Pressed buttons	System requirements	
Scroll type *	Wheel	Windows operating systems supported	✓
Programmable mouse buttons	✗	Mac operating systems supported	✓
Buttons quantity *	6	Other operating systems supported	ChromeOS
Button functions	Forward	Weight & dimensions	
Silent click	✗	Width	45 mm
Customizable movement resolution	✓	Depth	110 mm
Multi-device support	✗	Height	74.9 mm
Bluetooth version	5.0	Weight	136.08 g
Bluetooth Low Energy (BLE)	✓	Packaging data	
Design		Quantity per pack *	1 pc(s)
Form factor *	Ambidextrous		
Ergonomic design	✓		



0092636353117



092636353117



5063194000176

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.