

Epson EB-810E Ultra short throw projector 5000 ANSI lumens 3LCD 1080p (1920x1080) White

Brand : Epson

Product code: V11HA99080

Product name : EB-810E



Super UST 4KE laser display

Epson EB-810E. Projector brightness: 5000 ANSI lumens, Projection technology: 3LCD, Projector native resolution: 1080p (1920x1080). Light source type: Laser, Service life of light source: 20000 h, Service life of light source (economic mode): 30000 h. Focus: Manual, Fixed focal length: 2.3 mm, Zoom ratio: 1.35:1. Video colour modes: Blackboard, Cinema, DICOM simulation mode, Dynamic, Multi-projection, Natural, Presentation. Serial interface type: RS-232C, Service port type: USB Type-B



Projector		Features	
Smart projector *	✗	Interactive *	✗
Screen size compatibility *	2032 - 4064 mm (80 - 160")	Noise level (economic mode)	26 dB
Projector brightness *	5000 ANSI lumens	Noise level *	35 dB
Projection technology *	3LCD	High Dynamic Range (HDR) supported	✓
Projector native resolution *	1080p (1920x1080)	High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10), Hybrid Log-Gamma (HLG)
Contrast ratio (typical) *	2500000:1	Password protection	✓
Native aspect ratio *	16:9		
Vertical scan range	192 - 240 Hz		
Light source		Multimedia	
Light source type *	Laser	Built-in speaker(s) *	✗
Service life of light source *	20000 h		
Service life of light source (economic mode)	30000 h		
Lens system		Design	
Focus *	Manual	Market positioning *	Business
Fixed focal length	2.3 mm	Product type *	Ultra short throw projector
F-number (relative aperture)	1.8	Product colour *	White
Zoom ratio	1.35:1	Placement	Ceiling, Desktop, Wall
Throw ratio	0.16 - 0.40:1	Cable lock slot	✓
		Cable lock slot type	Kensington
Video		Display	
Analog signal format system *	Not supported	Built-in display *	✗
Full HD *	✓		
3D *	✗		
Video colour modes	Blackboard, Cinema, DICOM simulation mode, Dynamic, Multi-projection, Natural, Presentation		
Ports & interfaces		Power	
HDBaseT port	✓	Power source *	AC
Service port type	USB Type-B	Power consumption (typical) *	290 W
USB 2.0 ports quantity	2	Power consumption (max)	380 W
USB 2.0 Type-A ports quantity	2	Power consumption (PowerSave)	0.4 W
Serial interface type *	RS-232C	Power consumption (economy mode)	286 W
HDMI ports quantity *	3	AC input voltage	100 - 240 V
DVI port *	✗	AC input frequency	50/60 Hz
		Operational conditions	
		Operating temperature (T-T)	-10 - 60 °C
		Operating relative humidity (H-H)	20 - 80%
		Storage relative humidity (H-H)	10 - 90%

Network		Weight & dimensions	
Smart TV *	✗	Width	695 mm
Ethernet LAN *	✓	Depth	341 mm
Ethernet LAN (RJ-45) ports	1	Height	156 mm
Ethernet LAN data rates	10,100 Mbit/s	Weight *	12.5 kg
Wi-Fi *	✓	Packaging content	
Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac)	Remote control included *	✓
Miracast	✓	Batteries included	✓
Storage		Cables included	AC
Card reader integrated *	✗		



8715946718156

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.