

dbramante1928 Iceland - iPhone 13 Pro Max - Clear Hard case

Brand : dbramante1928

Product code: IL67CL001360

Product name : Iceland - iPhone 13 Pro Max - Clear Hard case

- Guided by WWF, dbramante1928 is becoming a Climate Positive Company
 - Made from 100% recycled plastic
 - The equivalent recycled material weight of a 2L plastic bottle is used to make each case
 - Slim, impact protection case with non-slip grip and easy-to-press buttons
 - Compatible with wireless charging in case
 - Raised edges protect camera and screen
- Iceland, iPhone 13 Pro Max, Clear Hard case

dbramante1928 Iceland - iPhone 13 Pro Max - Clear Hard case:

Made from 100% recycled plastic and 'ice' clear, protect your phone and the planet at the same time with this all-around, slim, snap-on impact protection case. Designed in Denmark by a Climate Positive Company, and eco-friendly without compromising quality, protection, design or functionality, this case feels great in your hand. It is ideal for those looking to bring effortless style to their everyday lives.



Features		Packaging data	
Maximum screen size *	17 cm (6.7")	Package weight	90 g
Surface coloration	Monochromatic	Logistics data	
Compatibility *	iPhone 13 Pro Max	Harmonized System (HS) code	85177900
Case type *	Cover	Country of origin	China
Material *	Recycled plastic	Shipping (inner) case net weight	59 g
Product colour *	Transparent	Shipping (inner) case gross weight	90 g
Brand compatibility *	Apple	Quantity outer carton	30 pc(s)
Protection features	Impact resistant	Master (outer) case width	395 mm
Weight & dimensions		Master (outer) case length	245 mm
Width	82 mm	Master (outer) case height	230 mm
Depth	11 mm	Master (outer) case net weight	740 g
Height	164 mm	Master (outer) case gross weight	740 g
Weight	31 g	Master (outer) case volume	22258.25 cm ³
Packaging content		Master (outer) cases per pallet layer (EU)	48 pc(s)
Quantity per pack	30 pc(s)	Products per pallet (EU)	1440 pc(s)
Sustainability		Pallet gross weight	3.71 kg
Sustainability compliance	✓	Packaging data	
Package width	117 mm	Package width	117 mm
Package depth	20 mm	Package depth	20 mm
Package height	207 mm	Package height	207 mm



5711428013606

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.