


Epson Fine Art Cotton Textured Bright A4 25 Sheets

Brand : EpsonProduct code: C13S450288

Product name : Fine Art Cotton Textured Bright A4 25 Sheets

Fine Art Cotton Textured Bright A4 25 Sheets
Epson Fine Art Cotton Textured Bright A4 25 Sheets. Type: Art paper, Sheets quantity: 25 sheets, Media weight: 300 g/m². Sheet width: 21 cm, Sheet length: 29.7 cm, Roll width: 21 cm. Package width: 220 mm, Package depth: 305 mm, Package height: 20 mm. Doesn't contain: Acid. Products per master (outer) case: 10 pc(s), Country of origin: United Kingdom



Features		Packaging data	
Type *	Art paper	Package width	220 mm
Sheets quantity *	25 sheets	Package depth	305 mm
Media weight	300 g/m²	Package height	20 mm
Cover material	Cotton	Package weight	680 g
Surface texture	Textured	Package type	Box
Printing media thickness	515 µm	Sustainability	
Finish type	Matt	Doesn't contain	Acid
Print type	Inkjet	Logistics data	
Format	A4	Master (outer) case gross weight	0 g
Printing media gloss level	95	Products per master (outer) case	10 pc(s)
Quantity per pack	1 pc(s)	Master (outer) case GTIN (EAN/UPC)	8715946661988
Weight & dimensions		Country of origin	United Kingdom
Sheet width	21 cm		
Sheet length	29.7 cm		
Roll width	21 cm		



8715946661391

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.