

ASUS Chromebox CHROMEBOX5-GC029UN Intel® Celeron® 7305 4 GB DDR4-SDRAM 128 GB SSD ChromeOS Mini PC Black

Brand : ASUS

Product family: Chromebox

Product code: 90MS02N1-M00290

Product name :
CHROMEBOX5-GC029UN



Chromebox 5 (Intel Celeron 7305, 4GB RAM, 128GB SSD, Wi-Fi 6E + BT5.0, CHROMEBOX5-GC029UN)

[ASUS Chromebox CHROMEBOX5-GC029UN Intel® Celeron® 7305 4 GB DDR4-SDRAM 128 GB SSD ChromeOS Mini PC Black:](#)

ASUS Chromebox 5 offers outstanding performance and instantaneous response for incredible productivity. It's powered by up to a 12th Gen Intel® Core™ i7 processor that delivers blistering processing speeds to cater to the most demanding tasks. And with up to 32 GB DDR4 memory, ASUS Chromebox 5 enables easy multitasking without slowdowns.

In addition, Intel Iris® Xe graphics deliver unmatched processing power for stunning, supersmooth visuals. A PCIe® Gen 4 x4 M.2 SSD provides ultrafast data transfers and app launches.

Overall, ASUS Chromebox 5 offers an exceptional user experience that combines superior performance and cutting-edge features for next-level productivity.



Processor		Network	
Processor manufacturer *	Intel	Ethernet LAN *	✓
Processor family *	Intel® Celeron®	Ethernet LAN data rates	10,100,1000,2500 Mbit/s
Processor model *	7305	Cabling technology	10/100/1000Base-T(X)
Processor cores	5	Wi-Fi *	✓
Processor threads	5	Top Wi-Fi standard	Wi-Fi 6E (802.11ax)
Performance cores	1	Wi-Fi standards	Wi-Fi 6E (802.11ax)
Efficient cores	4	Antenna type	2x2
Processor cache	8 MB	Bluetooth	✓
Processor cache type	Smart Cache	Bluetooth version	5.3
Processor base power	15 W	Ports & interfaces	
Maximum turbo power	55 W	USB 3.2 Gen 2 (3.1 Gen 2) Type-A ports quantity *	4
Memory		Intel® Thunderbolt 4	✓
Internal memory *	4 GB	Thunderbolt 4 ports quantity	1
Maximum internal memory *	16 GB	DisplayPorts quantity	1
Internal memory type	DDR4-SDRAM	DisplayPort version	1.4
Memory clock speed	3200 MHz	Ethernet LAN (RJ-45) ports	1
Storage		Combo headphone/mic port	✓
Total storage capacity *	128 GB	DC-in jack	✓
Storage media *	SSD	Power	
Optical drive type *	✗	Power supply *	65 W
Total SSDs capacity	128 GB	Design	
Number of SSDs installed	1	Chassis type *	Mini PC
SSD capacity	128 GB	Colour name	ECO Black
SSD interface	PCI Express 4.0	Cable lock slot	✓
NVMe	✓	Cable lock slot type	Kensington
SSD form factor	M.2	Product colour *	Black
Card reader integrated	✓		
Compatible memory cards	MicroSD (TransFlash)		

Graphics		Software	
Discrete graphics card *	✗	Operating system installed *	ChromeOS
On-board graphics card *	✓	Display	
Discrete graphics card model *	Not available	Display included *	✗
On-board GPU manufacturer	Intel	Weight & dimensions	
On-board graphics card family	Intel® UHD Graphics	Width *	166.5 mm
On-board graphics card model *	Intel® UHD Graphics	Depth *	165.8 mm
Performance		Height *	45.9 mm
Product type *	Mini PC	Weight *	800 g
		Packaging content	
		Cables included	AC



4711387161272

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.