

Philips 2000 series SPT6207BL/40 keyboard Mouse included
Universal USB QWERTY English Black

Brand : Philips Product family: 2000 series Product code: SPT6207BL/40

Product name : SPT6207BL/40



2000 series SPT6207BL Wired keyboard-mouse combo

Philips 2000 series SPT6207BL/40 keyboard Mouse included Universal USB QWERTY English Black:

This keyboard and mouse duo is equipped with responsive keys, an ambidextrous mouse design, and durability that last millions of keystrokes for a combo that is made to last.
Philips 2000 series SPT6207BL/40. Keyboard form factor: Full-size (100%). Keyboard style: Straight.
Connectivity technology: Wired, Device interface: USB, Keyboard layout: QWERTY. Cable length: 1.6 m.
Recommended usage: Universal. Product colour: Black. Mouse included



Keyboard		Mouse	
Recommended usage *	Universal	Buttons type	Pressed buttons
Connectivity technology *	Wired	Scroll	✓
Device interface *	USB	Scroll type	Wheel
Keyboard layout *	QWERTY	Scrolling directions	Vertical
Keyboard language *	English	Mouse cable length	1.5 m
Pointing device *	✗	Buttons durability (million clicks)	8
Keyboard form factor *	Full-size (100%)	Headset	
Numeric keypad *	✓	Headset included	✗
Keyboard keys operating life	8 million characters	System requirements	
Windows keys	✓	Windows operating systems supported	✓
Multimedia keys	✓	Mac operating systems supported	✓
Design		Linux operating systems supported	✓
Backlight *	✗	Mobile operating systems supported	Android 10, Android 10.0, Android 11.0, Android 12.0, Android 3.2, Android 4.0, Android 4.1, Android 4.2, Android 4.2.1, Android 4.2.2, Android 4.3, Android 4.4, Android 5.0, Android 5.1, Android 6.0, Android 7.0, Android 7.1, Android 7.1.2, Android 8.0, Android 8.1, Android 9.0
Keyboard style	Straight		
Ergonomic design	✓	Operational conditions	
Product colour *	Black	Operating temperature (T-T)	0 - 40 °C
Material	Plastic	Operating relative humidity (H-H)	10 - 85%
Features		Weight & dimensions	
USB connector type	USB Type-A	Keyboard dimensions (WxDxH)	443 x 152 x 31 mm
Cable length	1.6 m	Keyboard weight	505 g
Plug and Play	✓	Mouse dimensions (WxDxH)	110 x 65 x 35 mm
Power		Mouse weight	78 g
Power source type *	USB	Packaging content	
Mouse		Number of products included *	2 pc(s)
Mouse included *	✓	Manual	✓
Form factor	Ambidextrous		
Movement detection technology	Optical		
Movement resolution	1200 DPI		
Buttons quantity	3		



8712581801816

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.