

ASUS ProArt Projector A1 Standard throw projector 3000 ANSI lumens DLP 1080p (1920x1080) 3D Black

Brand : ASUS

Product code: 90LJ00G0-B00270

Product name : ProArt Projector A1

- Exceptional color accuracy: World's 1st Calman Verified projector, factory pre-calibrated for Delta E(ΔE) < 2 color difference
 - Wide color gamut: Covers 98% sRGB and REC.709 color spaces
 - Bright FHD visuals: 3000-lumen LED light source with up to 30,000-hour lifespan
 - Wireless mirroring: Seamless streaming with iOS, Android, and Windows 10 device support
 - Versatile controls: Four corner and 2D keystone correction, plus 1.2X zoom ratio for large projections in confined spaces
 - Easy color management: ASUS ProArt Preset and ProArt Palette software enable quick access to programmed settings and color parameters
- ASUS ProArt A1 LED professional projector- World's first Calman Verified projector, $\Delta E < 2$, 98% sRGB and Rec. 709, FHD (1920 x 1080), 3000 lumens, Four corner and 2D keystone correction, 1.2X zoom ratio, wireless mirroring



Projector		Features	
Supported aspect ratios	4:3, 16:10, 16:9	HDCP	✓
Projection distance	1.15 - 5.7 m	Screen mirroring	✓
Projector brightness *	3000 ANSI lumens	Noise level *	32 dB
Projection technology *	DLP	Multimedia	
Projector native resolution *	1080p (1920x1080)	Built-in speaker(s) *	✓
Contrast ratio (typical) *	800:1	RMS rated power	10 W
Native aspect ratio *	4:3	Design	
Number of colours	1.07 billion colours	Market positioning *	Presentation
Colour gamut	98%	Product type *	Standard throw projector
Light source		Product colour *	Black
Light source type *	LED	Placement	Ceiling, Desktop
Service life of light source *	30000 h	Cable lock slot	✓
Lamps quantity	1 lamp(s)	Display	
Lens system		Built-in display *	✗
Focus *	Manual	Power	
Zoom capability	✓	Power source *	AC
Zoom type	Manual	Power consumption (typical) *	370 W
Throw ratio	1.3:1 ~ 1.56:1	Power consumption (standby) *	0.5 W
Video		Power consumption (max)	370 W
Full HD *	✓	Operational conditions	
3D *	✓	Operating temperature (T-T)	0 - 40 °C
Ports & interfaces		Operating relative humidity (H-H)	10 - 90%
HDMI connector type	Full-size	Weight & dimensions	
HDMI version	2.0	Width	405 mm
USB 2.0 ports quantity	2	Depth	283 mm
Audio (L/R) in *	1		
Audio (L/R) out	1		

Ports & interfaces		Weight & dimensions	
Serial interface type *	RS-232	Height	99 mm
VGA (D-Sub) ports quantity *	1	Weight *	5.7 kg
HDMI ports quantity *	2	Package width	560 mm
DVI port *	×	Package depth	430 mm
Network		Package height	274 mm
Smart TV *	×	Package weight	8.1 kg
Ethernet LAN *	×	Packaging content	
Wi-Fi *	✓	Remote control included *	✓
Storage		Cables included	AC, HDMI
Card reader integrated *	×	Carrying case	✓
Features		Packaging content	Carrying Bag HDMI Cable Power Cord Adaptor Warranty Card QSG Remote Control WiFi Dongle
Noise level (economic mode)	28 dB	Logistics data	
		Harmonized System (HS) code	85286200



4718017816120

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.