

StarTech.com Bi-Directional SATA IDE Adapter Converter

Brand : StarTech.comProduct code: PATA2SATA3

Product name : Bi-Directional SATA IDE Adapter Converter



StarTech.com Bi-Directional SATA IDE Adapter Converter

StarTech.com Bi-Directional SATA IDE Adapter Converter:

Bi-directional adapter converts IDE to SATA or SATA to IDE

The PATA2SATA3 is a bi-directional SATA IDE adapter/converter that lets you connect a Serial ATA drive to a legacy IDE port, or an IDE drive to a SATA motherboard port.

A cost-effective solution for upgrading existing IDE systems to support SATA hard drives or optical drives, the SATA/IDE adapter eliminates the expense of having to purchase a controller card while saving the expansion slot that would be required for card installation.



In addition to SATA hard drive installation, the adapter can be reversed in order to connect older IDE drives to a newer SATA-enabled motherboard, making it easy to retrieve old files from a previous system.

The StarTech.com Advantage
StarTech.com Bi-Directional SATA IDE Adapter Converter. Connector 1: 2 x SATA Data 7 pin M/1 x IDE 40 pin F, Connector 2: SP4 M. Product colour: Black

Ports & interfaces		Packaging data	
Connector 1 *	2 x SATA Data 7 pin M/1 x IDE 40 pin F	Package width	173 mm
Connector 2 *	SP4 M	Package depth	142 mm
Connector 1 gender	Male	Package height	32 mm
Connector 2 gender	Female	Package weight	102 g
Performance		Other features	
Product colour *	Black	Dimensions (WxDxH)	50 x 61 x 11 mm
Housing material	Plastic	Logistics data	
Compatible products	2.5" SATA 3.5" EIDE 3.5" SATA 5.25" SATA 5.25" EIDE	Quantity per box	40 pc(s)
Weight & dimensions		Products per master (outer) case	50 pc(s)
Weight	20 g	Master (outer) case width	402 mm
		Master (outer) case length	467 mm
		Master (outer) case height	279 mm



0065030836982



065030836982



9789792336405

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.