



DELL SFP LC MM network transceiver module Fiber optic 1000 Mbit/s 850 nm

Brand : DELL

Product code: 407-10933

Product name : SFP LC MM



Networking Transceiver SFP 1000BASE-SX 850nm Wavelength 550m Reach - Kit


DELL SFP LC MM network transceiver module Fiber optic 1000 Mbit/s 850 nm:

The Dell Transceiver delivers fiber connectivity to extend the range of your network. Additionally, it provides a unique enhanced digital diagnostic monitoring interface, which allows real-time access to device operating parameters such as transceiver temperature, laser bias current, transmitted optical power, received optical power, and transceiver supply voltage. This product has been tested and validated on Dell systems. It is supported by Dell Technical Support when used with a Dell system. DELL SFP LC MM. SFP transceiver type: Fiber optic, Maximum data transfer rate: 1000 Mbit/s, Interface type: SFP. Quantity per pack: 1 pc(s)

Performance		Performance	
SFP transceiver type *	Fiber optic	Maximum transfer distance	550 m
Maximum data transfer rate *	1000 Mbit/s	Wavelength	850 nm
Interface type *	SFP	Packaging content	
Multi-mode fiber (MMF) supported	✓	Quantity per pack	1 pc(s)
Fiber optic connector	LC	Logistics data	
		Harmonized System (HS) code	85369010



5742220535904



3540260132846



5397063819485

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.