

Targus TED011EU backpack Black/Grey Polyurethane

Brand : Targus

Product code: TED011EU

Product name : TED011EU



- Durable Materials
 - Luminous integrated raincover
 - 2 Large Stash Pockets on Front
 - Reinforced top handle
 - Sternum strap for more comfort
 - Reflective panels on main body of backpack and shoulder straps
 - Large, flexible compartments
 - Water repellent base
- 15.6", PU, Black/Grey

Targus TED011EU backpack Black/Grey Polyurethane:

A fully featured backpack with highly durable materials and flexible storage

Targus TED011EU. Product main colour: Black/Grey, Coloration: Monochromatic, Maximum screen size: 39.6 cm (15.6"). Width: 120 mm, Depth: 370 mm, Height: 500 mm. Package width: 125 mm, Package depth: 340 mm, Package height: 490 mm. Material: Polyurethane. Products per pallet: 45 pc(s), Master (outer) case width: 505 mm, Master (outer) case length: 620 mm

Features		Packaging data	
Product main colour *	Black/Grey	Package depth	340 mm
Coloration	Monochromatic	Package height	490 mm
Notebook compartment	✓	Package weight	810 g
Maximum screen size	39.6 cm (15.6")	Material	
Exterior pockets	Front pocket	Material *	Polyurethane
Zipper pocket(s)	✓	Logistics data	
Handle(s)	✓	Products per pallet	45 pc(s)
Carrying handle(s)	✓	Harmonized System (HS) code	42029291
Weight & dimensions		Master (outer) case width	505 mm
Width *	120 mm	Master (outer) case length	620 mm
Depth *	370 mm	Master (outer) case height	345 mm
Height *	500 mm	Master (outer) case gross weight	5.36 kg
Weight	800 g	Products per master (outer) case	5 pc(s)
Packaging data			
Package width	125 mm		



5051794022650

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date