




Lenovo 7ZT7A00544 network card Internal Ethernet 1000 Mbit/s

Brand : Lenovo


Product code: 7ZT7A00544

Product name : 7ZT7A00544



ThinkSystem 1Gb 2-port RJ45 LOM
Lenovo 7ZT7A00544. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Maximum data transfer rate: 1000 Mbit/s. Product colour: Green, Metallic

Ports & interfaces		Design	
Connectivity technology *	Wired	Chipset	Intel® C624
Host interface *	PCI Express	Certification	UL recognized to UL60950-1 2nd Edition FCC Rules, Part 15, Class A
Interface *	Ethernet		Australian EMC Framework (RCM)
Ethernet LAN (RJ-45) ports	2		Japan VCCI, Class A Industry
Network		Compatible products	Canada, ICES-003, Class A EU (CE Mark) Korea KC-RRA, Class A
Maximum data transfer rate *	1000 Mbit/s		SR630 SR650 SR850 SR860 SR950
Networking standards *	IEEE 802.1Q, IEEE 802.1Qbg, IEEE 802.1p, IEEE 802.3ad, IEEE 802.3x	System requirements	
Ethernet LAN	✓	Other operating systems supported	VMware vSphere ESXi
Ethernet interface type	Gigabit Ethernet	Server operating systems supported	SUSE Linux Enterprise Server 11,
Ethernet LAN data rates	10000 Mbit/s		SUSE Linux Enterprise Server 12,
Cabling technology	10/100/1000BaseT(X)	Windows Server 2012 R2, Windows Server 2016	
Security algorithms	SNMP	Technical details	
Jumbo frames support	✓	Compliance certificates	RoHS
Jumbo frames	9728	Logistics data	
Supported network protocols	TCP/UDP/IP/SCTP, IPv4/IPv6	Harmonized System (HS) code	85176990
Quality of Service (QoS) support	✓	Other features	
VLAN tagging	✓	Flow control support	✓
LAN controller	Marvell 88E1514	Intel Virtual Machine Device Queues (VMDq)	✓
Design		PCI-SIG* SR-IOV Capable	✓
Product colour	Green, Metallic	Intel Data Direct I/O Technology	✓
Internal *	✓	Receive Side Scaling (RSS)	✓



0889488438587



889488438587

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.