

StarTech.com 2 Port HDMI Switch w/ Automatic and Priority Switching - 1080p

Brand : StarTech.com

Product code: VS221HDQ

Product name : 2 Port HDMI Switch w/ Automatic and Priority Switching - 1080p



StarTech.com 2 Port HDMI Switch w/ Automatic and Priority Switching - 2 In 1 Out HDMI Selector with Automatic Priority Switching - 1080p
StarTech.com 2 Port HDMI Switch w/ Automatic and Priority Switching - 1080p. Video port type: HDMI. Material: Aluminium, Plastic, Product colour: Black, Maximum operating distance: 10 m. AC input voltage: 100 - 240 V, AC adapter input current: 0.6 A, AC adapter output voltage: 12 V. Certification: CE, FCC, TAA, REACH. Width: 65 mm, Depth: 156 mm, Height: 20 mm




Ports & interfaces		Certificates	
Video port type *	HDMI	Certification	CE, FCC, TAA, REACH
HDMI ports quantity	3	Weight & dimensions	
HDMI in	1	Width	65 mm
Number of HDMI outputs	2	Depth	156 mm
Features		Height	20 mm
Material	Aluminium, Plastic	Weight	290 g
Product colour	Black	Packaging data	
Extended display identification data (EDID)	✓	Package width	197 mm
Plug and Play	✓	Package depth	294 mm
HDCP	✓	Package height	72 mm
Maximum operating distance	10 m	Package weight	853 g
Rack mounting	Yes	Packaging content	
Supported graphics resolutions	1280 x 720 (HD 720), 1920 x 1080 (HD 1080), 1920 x 1200 (WUXGA)	Mounting kit	✓
Supported video modes	1080p, 720p	Remote control included	✓
LED indicators	✓	Manual	✓
Maximum resolution	1920 x 1200 pixels	Plug adapter type	NA, EU, UK, AU
Audio output channels	7.1 channels	Operational conditions	
Power		Operating temperature (T-T)	0 - 40 °C
AC input voltage	100 - 240 V	Storage temperature (T-T)	-20 - 60 °C
AC adapter input current	0.6 A	Operating relative humidity (H-H)	0 - 80%
AC adapter output voltage	12 V	Technical details	
AC adapter output current	1.5 A	Compliance certificates	RoHS
Power consumption (typical)	18 W	Logistics data	
Power plug type	Type M	Harmonized System (HS) code	85176990



0065030855020



065030855020



7426801735775

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.