



Everyday™ Magenta Remanufactured Toner by Xerox compatible with Brother TN245M, High capacity

Brand : Xerox

Product family: Everyday
Remanufactured

Product code: 006R03263




Product name : Everyday™
Magenta Remanufactured Toner
by Xerox compatible with
Brother TN245M, High capacity

Everyday™ Magenta Remanufactured Toner by Xerox compatible with Brother TN245M, High capacity

Everyday™ Magenta Remanufactured Toner by Xerox compatible with Brother TN245M, High capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Magenta Remanufactured Toner by compatible with Brother TN245M, High capacity. Colour toner page yield: 2200 pages, Black toner page yield: 2200 pages, Printing colours: Magenta, Quantity per pack: 1 pc(s)



Features		Operational conditions	
Compatibility *	DCP-9020 HL-3140 HL-3150 HL-3170 HL-3180 MFC-9130 MFC-9140 MFC-9330 MFC-9340	Storage relative humidity (H-H)	35 - 85%
Quantity per pack *	1 pc(s)	Weight & dimensions	
Black toner page yield *	2200 pages	Weight	550 g
Colour toner page yield *	2200 pages	Packaging data	
Type *	Compatible	Package width	160 mm
Printing colours *	Magenta	Package depth	370 mm
Brand compatibility *	Brother	Package height	120 mm
Supply type *	Single pack	Package weight	760 g
Cartridge capacity	High (XL) Yield	Package type	Box
OEM code	TN245M	Other features	
Country of origin	Serbia	Certification	RoHS, REACH SVHC, CE MARK STMC, ISO 9001:2015, ISO 14001:2015
Operational conditions		Logistics data	
Operating temperature (T-T)	17 - 25 °C	Harmonized System (HS) code	8443.99.1000
Operating relative humidity (H-H)	30 - 70%	Products per master (outer) case	15 pc(s)
Storage temperature (T-T)	0 - 35 °C		



0095205827880



095205827880

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date