

NETGEAR 10GBASE-LR Lite SFP+ network transceiver module
Fiber optic 10000 Mbit/s SFP+

Brand : NETGEAR

Product code: AXM764-10000S

Product name : 10GBASE-LR Lite SFP+

10GBASE-LR Lite SFP+ Transceiver

NETGEAR 10GBASE-LR Lite SFP+ network transceiver module Fiber optic 10000 Mbit/s SFP+:

AXM764 is NETGEAR 10GBASE-LR “Lite” SFP+ Transceiver, a new class of SMF 10G transmitter with LC duplex connector. While not a standard yet, 10GBASE-LR LITE has a specified reach of 2 km (1.24 mile) over standard 9/125µm single mode fiber. 10GBASE-LR LITE isn’t a replacement for standard 10GBASE-LR optics: it is just relevant alternative for “shorter” reach SMF applications.
NETGEAR 10GBASE-LR Lite SFP+. SFP transceiver type: Fiber optic, Maximum data transfer rate: 10000 Mbit/s, Interface type: SFP+. Compatible products: NETGEAR M5300, M6100, M7100, M7300. Quantity per pack: 1 pc(s)

Performance		Features	
SFP transceiver type *	Fiber optic	Hot-Plug support	✓
Maximum data transfer rate *	10000 Mbit/s	Compatible products	NETGEAR M5300, M6100, M7100, M7300
Interface type *	SFP+	Operational conditions	
Single-mode fiber (SMF) supported	✓	Operating temperature (T-T)	0 - 70 °C
Fiber optic connector	LC	Storage temperature (T-T)	-40 - 85 °C
Fiber cable diameters supported (core/cladding)	9/125 µm	Operating relative humidity (H-H)	10 - 80%
SFP transceiver standard	LR	Storage relative humidity (H-H)	10 - 85%
Maximum transfer distance	2000 m	Packaging content	
Networking standards	IEEE 802.3, IEEE 802.3ab, IEEE 802.3ae, IEEE 802.3u	Quantity per pack	1 pc(s)
Cabling technology	10GBASE-LR	Logistics data	
Auto MDI/MDI-X	✓	Harmonized System (HS) code	85369010



0606449108767



606449108767



4058829194017

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.