

Philips 3000 series SPT6307B/39 keyboard Mouse included Home RF Wireless UK English Black

Brand : Philips Product family: 3000 series Product code: SPT6307B/39
Product name : SPT6307B/39



3000 series SPT6307B Wireless keyboard-mouse combo

Philips 3000 series SPT6307B/39 keyboard Mouse included Home RF Wireless UK English Black:

Work without worrying about cable management; this keyboard is equipped with a 2.4G wireless connection. Not to mention, the keyboard has a low-profile design and the mouse can operate at up to 1600 DPI for the most efficient combo yet.
Philips 3000 series SPT6307B/39. Keyboard form factor: Full-size (100%), Connectivity technology: Wireless, Device interface: RF Wireless, Keyboard key switch: Mechanical, Keyboard number of keys: 110, Recommended usage: Home. Product colour: Black. Mouse included

Keyboard		Mouse	
Recommended usage *	Home	Mouse included *	✓
Connectivity technology *	Wireless	Form factor	Ambidextrous
Device interface *	RF Wireless	Movement detection technology	Optical
Keyboard key switch *	Mechanical	Movement resolution	1600 DPI
Keyboard language *	UK English	System requirements	
Pointing device *	✗	Windows operating systems supported	✓
Keyboard form factor *	Full-size (100%)	Mac operating systems supported	✓
Numeric keypad *	✓	Linux operating systems supported	✓
Keyboard number of keys	110	Weight & dimensions	
Frequency band	2.4 GHz	Keyboard dimensions (WxDxH)	433 x 136 x 22 mm
Design		Keyboard weight	566 g
Backlight *	✗	Mouse dimensions (WxDxH)	110 x 65 x 35 mm
Product colour *	Black	Mouse weight	83 g
Surface coloration	Monochromatic	Packaging content	
Material	Plastic	Number of products included *	2 pc(s)
Power			
Power source type *	USB		



8712581779283



8712581779290

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.