



## TP-Link AX3000 Whole Home Mesh WiFi 6 System, 3-Pack

**Brand :** TP-Link

**Product code:** DECO X50(3-PACK)

**Product name :** AX3000 Whole Home Mesh WiFi 6 System, 3-Pack

- AX3000 Dual Band WiFi - Super-fast WiFi 6 with speeds up to 3.0 Gbps
  - 4 Streams, Less Lag - 2x2/HE160 2402 Mbps + 2x2 574 Mbps
  - Gigabit Wired Speed - 3x Gigabit ports provide sufficient connectivity
  - Boosted Seamless Coverage - Seamless mesh WiFi coverage up to 6,500 ft2 (3-pack)
  - TP-Link HomeShield - Provides comprehensive network protection, robust parental controls, and real-time IoT protection
- Wi-Fi 6, AX3000, 2.4/5 GHz, 2x2 MU-MIMO, 3x 1G RJ-45, 12V, 110x110x114 mm, 3-pack

TP-Link AX3000 Whole Home Mesh WiFi 6 System, 3-Pack:

### Superior Mesh WiFi, Everywhere.

AX3000 Whole Home Mesh WiFi 6 System

- Superb Wired and Wireless Connectivity

Enjoy smooth 4K streaming, online gaming, and video calls throughout your home. Get super-fast WiFi 6 with speeds of up to 3.0 Gbps and 3 x Gigabit Ethernet ports providing wired warp speeds.

- Superior WiFi Performance

Deco X50 features higher WiFi speeds, larger device capacity, and nearly no lag with broader HE160 channel bandwidth.



| Design                                |                                                                                      | Features                                    |                                                        |
|---------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------|--------------------------------------------------------|
| Product colour *                      | White                                                                                | Parental control                            | ✓                                                      |
| Antenna type *                        | Internal                                                                             | Parental control features                   | Custom profiles, Time controls, Weekly/monthly reports |
| Antennas quantity                     | 2                                                                                    | Firmware upgradeable via MU-MIMO technology | ✓                                                      |
| Transmit power                        | CE: <20 dBm (2.4 GHz) <23 dBm (5 GHz) FCC: <30 dBm (2.4 GHz) <30 dBm (5 GHz)         | <b>Ports &amp; interfaces</b>               |                                                        |
| Reset button                          | ✓                                                                                    | Ethernet LAN (RJ-45) ports *                | 3                                                      |
| <b>Wireless LAN features</b>          |                                                                                      | DC-in jack                                  | ✓                                                      |
| Wi-Fi band *                          | Dual-band (2.4 GHz / 5 GHz)                                                          | <b>Power</b>                                |                                                        |
| Top Wi-Fi standard *                  | Wi-Fi 6 (802.11ax)                                                                   | AC adapter output voltage                   | 12 V                                                   |
| Wi-Fi standards                       | 802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac), Wi-Fi 6 (802.11ax) | AC adapter output current                   | 1.5 A                                                  |
| WLAN data transfer rate (first band)  | 574 Mbit/s                                                                           | <b>Certificates</b>                         |                                                        |
| WLAN data transfer rate (second band) | 2402 Mbit/s                                                                          | Compliance certificates                     | CE, RoHS                                               |
| Networking standards                  | IEEE 802.11n, IEEE 802.11a, IEEE 802.11ac, IEEE 802.11b, IEEE 802.11g                | <b>Operational conditions</b>               |                                                        |
| Security algorithms                   | WPA-PSK, WPA2-PSK, WPA3-PSK                                                          | Operating temperature (T-T)                 | 0 - 40 °C                                              |
| Number of guest networks (5 GHz)      | 1                                                                                    | Storage temperature (T-T)                   | -40 - 70 °C                                            |
| Number of guest networks (2.4 GHz)    | 1                                                                                    | Operating relative humidity (H-H)           | 10 - 90%                                               |
| IGMP proxy                            | ✓                                                                                    | Storage relative humidity (H-H)             | 5 - 90%                                                |
| IGMP snooping                         | ✓                                                                                    | <b>Weight &amp; dimensions</b>              |                                                        |
| Tagged VLAN                           | ✓                                                                                    | Width                                       | 110 mm                                                 |
| Dynamic DNS (DDNS)                    | ✓                                                                                    | Depth                                       | 110 mm                                                 |
| <b>Features</b>                       |                                                                                      | Height                                      | 114 mm                                                 |
| Built-in processor                    | ✓                                                                                    | <b>Packaging content</b>                    |                                                        |
|                                       |                                                                                      | Number of products included                 | 3 pc(s)                                                |
|                                       |                                                                                      | AC adapter included                         | ✓                                                      |
|                                       |                                                                                      | Number of units included                    | 3 pc(s)                                                |


| Features                         |       | Packaging content           |          |
|----------------------------------|-------|-----------------------------|----------|
| Processor cores                  | 2     | Ethernet cable              | ✓        |
| Processor frequency              | 1 GHz | Packaging data              |          |
| Quality of Service (QoS) support | ✓     | Package width               | 369 mm   |
| Port forwarding                  | ✓     | Package depth               | 276.5 mm |
| Firewall security                | SPI   | Package height              | 125 mm   |
| BeamForming                      | ✓     | Package weight              | 2.18 kg  |
| DHCP client                      | ✓     | Logistics data              |          |
| Universal Plug and Play (UPnP)   | ✓     | Harmonized System (HS) code | 85171800 |



4897098681732



4897098687086



0840030707087



840030707087

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.