



Lenovo ThinkVision S28u-10 computer monitor 71.1 cm (28") 3840 x 2160 pixels 4K Ultra HD LED Black

Brand : Lenovo

Product family: ThinkVision

Product code: 61E6GAR2UK


Product name : S28u-10

- Crystal-clear visuals on the 4K UHD In-Plane Switching panel means no detail is too small
 - Colors are vivid and bright with the >99% sRGB and 90% DCI-P3 color gamut providing 1.07 Billion colors for impeccable accuracy
 - Easily work for long hours on the S28u-10 that is TÜV Rheinland Eye Comfort Certified with flicker-free technology and reduced reflections
 - Eyestrain is minimized thanks to the natural low blue light solution that reduces blue light emission without compromising color accuracy, brightness, or power efficiency
 - The monitor has HDMI 2.0 and a DisplayPort 1.2 that provide improved connectivity required for modern businesses
 - The 100 x 100 mm VESA Mount makes the ThinkVision S28u-10 monitor easily deployable in a variety of scenarios
 - Additionally, the quick release tilt stand ensures the monitor is easy to set up and flexible to use
- 71.1cm (28") 4K Ultra HD 3840 x 2160 W-LED IPS, 16:9, 300cd/m², 1.07B, 6ms, 178°/178°, 1000:1



Display		Ergonomics	
Display diagonal *	71.1 cm (28")	VESA mounting *	✓
Display resolution *	3840 x 2160 pixels	Panel mounting interface	100 x 100 mm
HD type *	4K Ultra HD	Cable lock slot *	✓
Native aspect ratio *	16:9	Cable lock slot type	Kensington
Display technology *	LED	Height adjustment *	✗
Panel type *	IPS	Tilt adjustment	✓
Backlight type	W-LED	Tilt angle range	-5 - 22°
Touchscreen *	✗	On Screen Display (OSD)	✓
Display brightness (typical)	300 cd/m ²	Number of OSD languages	8
Response time *	6 ms	Power	
Anti-glare screen	✓	Energy efficiency class (SDR) *	F
Screen shape *	Flat	Energy consumption (SDR) per 1000 hours *	26 kWh
Supported graphics resolutions	3840 x 2160	Power consumption (typical) *	31 W
Contrast ratio (typical) *	1000:1	Power consumption (max)	48 W
Contrast ratio (dynamic)	3000000:1	Power consumption (off)	0.3 W
Maximum refresh rate *	60 Hz	AC input voltage	90 - 264 V
Viewing angle, horizontal	178°	AC input frequency	50 - 60 Hz
Viewing angle, vertical	178°	Power supply type	Internal
Display number of colours *	1.07 billion colours	Energy efficiency scale	A to G
Response time (fast)	4 ms	Weight & dimensions	
Pixel pitch	0.1617 x 0.158 mm	Width (with stand)	636.9 mm
Pixel density	157.35 ppi	Depth (with stand)	230 mm
Viewable size, horizontal	63.2 cm	Height (with stand)	450.8 mm
Viewable size, vertical	36 cm	Weight (with stand)	5.24 kg
Colour depth	10 bit	Width (without stand)	636.9 mm
Colour gamut standard	sRGB	Depth (without stand)	49.2 mm
sRGB coverage (typical)	99%	Height (without stand)	373.7 mm
DCI-P3 coverage	90%	Weight (without stand)	4.58 kg
Performance		Bezel width (side)	2 mm
Flicker-free technology	✓	Bezel width (top)	2 mm
Multimedia		Bezel width (bottom)	2.28 cm
Built-in speaker(s) *	✗		

Multimedia		Packaging data	
Built-in camera *	✗	Package width	452 mm
Design		Package depth	127 mm
Market positioning *	Business	Package height	723 mm
Product colour *	Black	Package weight	7 kg
Colour name	Raven Black	Packaging content	
Front bezel colour	Black	Stand included	✓
Feet colour	Black	Cables included	AC, HDMI
Ports & interfaces		HDMI cable length	1.8 m
Built-in USB hub *	✗	Sustainability	
HDMI *	✓	Sustainability certificates	ENERGY STAR
HDMI ports quantity	1	Other features	
HDMI version	2.0	Introduction year	2020
DisplayPorts quantity	1	Compatible operating systems	Windows 7, Windows 10
DisplayPort version	1.2	Warranty period	3 year(s)
Headphone out *	✓	Compliance certificates	RoHS
Headphone outputs	1	Certification	Energy Star Certified, TCO 7.0, TCO Edge 2.0, EPEAT Gold, RoHS
Headphone connectivity	3.5 mm		Eyesafe Display, TÜV Rheinland Low Blue Light



0193638462712



193638462712

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.