

Epson Pen and crossword Singlepack Cyan16 DURABrite Ultra Ink

Brand : Epson

Product family: Pen and crossword

Product code: C13T16224022

Product name : Singlepack Cyan16 DURABrite Ultra Ink

Singlepack Cyan16 DURABrite Ultra Ink

Epson Pen and crossword Singlepack Cyan16 DURABrite Ultra Ink:

Save up to 30% ink¹ with Epson's individual ink cartridges

With Epson's individual inks, you only replace the colour used, saving you up to 30% ink¹ compared to competitors' tri-colour cartridges.

Reduce your printing costs with XL inks

Epson offers a choice of standard or extra large (XL) ink cartridges across its latest ink ranges. XL inks are ideal if you print high volumes and can reduce your printing costs by up to 25%²

Epson inks are optimised for Epson printers

Epson inks and papers have been developed to work hand-in-hand with Epson printers to produce the best results time and time again.

Epson Pen and crossword Singlepack Cyan16 DURABrite Ultra Ink. Colour ink page yield: 165 pages, Colour ink volume: 3.1 ml, Printing colours: Cyan, Quantity per pack: 1 pc(s)



Features		Packaging data	
Print technology	Inkjet printing	Package height	102 mm
Compatibility *	- WorkForce WF-2760DWF -	Package type	Blister
	WorkForce WF-2750DWF -	Other features	
	WorkForce WF-2660DWF -	Certification	CE
	WorkForce WF-2650DWF -	Logistics data	
	WorkForce WF-2630WF - WorkForce	Pallet gross width	80 cm
Quantity per pack *	WF-2540WF - WorkForce	Pallet gross length	120 cm
	WF-2530WF - WorkForce	Pallet gross height	60 cm
	WF-2520NF - WorkForce	Products per pallet	3400 pc(s)
	WF-2510WF - WorkForce WF-2010WF	Master (outer) case width	102 mm
	1 pc(s)	Master (outer) case length	260 mm
Colour ink cartridges quantity	1	Master (outer) case height	146 mm
Colour ink volume	3.1 ml	Products per master (outer) case	10 pc(s)
Colour ink page yield *	165 pages	Harmonized System (HS) code	84439990
Type *	Original	Products per pallet (UK)	3400 pc(s)
Printing colours *	Cyan	Products per pallet layer	340 pc(s)
Brand compatibility *	Epson	Products per pallet layer (UK)	340 pc(s)
OEM code	C13T16224022	Minimum order quantity	10 pc(s)
Country of origin	China		
Operational conditions			
Storage temperature (T-T)	-20 - 40 °C		
Packaging data			
Package width	145 mm		
Package depth	26 mm		



8715946624914



8715946627182

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.