

Epson Padlock Singlepack Black 35XL DURABrite Ultra Ink

Brand : Epson Product family: Padlock Product code: C13T35914010

Product name : Singlepack
Black 35XL DURABrite Ultra Ink

Singlepack Black 35XL DURABrite Ultra Ink
Epson Padlock Singlepack Black 35XL DURABrite Ultra Ink. Cartridge capacity: High (XL) Yield, Black ink type: Pigment-based ink, Black ink volume: 41.2 ml, Printing colours: Black, Quantity per pack: 1 pc(s), Black ink page yield: 2600 pages



Features		Packaging data	
Black ink type	Pigment-based ink	Package type	Blister
Print technology	Inkjet printing	Other features	
Compatibility *	- WorkForce Pro WF-4740DTWF -	Certification	CE
	- WorkForce Pro WF-4730DTWF -	Logistics data	
Quantity per pack *	- WorkForce Pro WF-4725DWF -	Products per pallet	1800 pc(s)
	- WorkForce Pro WF-4720DWF	Pallet gross weight	0 g
Black ink cartridges quantity	1	Master (outer) case width	120 mm
Black ink volume	41.2 ml	Master (outer) case length	260 mm
Black ink page yield *	2600 pages	Master (outer) case height	146 mm
Type *	Original	Products per master (outer) case	6 pc(s)
Cartridge capacity	High (XL) Yield	Master (outer) case gross weight	0 g
Ink type	Pigment-based ink	Master (outer) case GTIN (EAN/UPC)	8715946632797
Printing colours *	Black	Harmonized System (HS) code	84439990
Brand compatibility *	Epson	Pallet weight (UK)	0 g
OEM code	C13T35914010	Products per pallet (UK)	1800 pc(s)
Country of origin	Indonesia	Products per pallet layer	180 pc(s)
Packaging data		Products per pallet layer (UK)	180 pc(s)
Package width	120 mm	Minimum order quantity	6 pc(s)
Package depth	43 mm		
Package height	145 mm		
Package weight	114 g		



8715946632353



4058154209196



5057454723639

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.