



Jabra Evolve 30 II Replacement Headset Mono

Brand : Jabra **Product code:** 14401-20

Product name : Evolve 30 II Replacement Headset Mono

Evolve 30 II Replacement Headset Mono

[Jabra Evolve 30 II Replacement Headset Mono:](#)

One mono replacement headset for Jabra Evolve 30 II. The headset includes headband, ear cushion and 3.5mm jack.

Jabra Evolve 30 II Replacement Headset Mono. Product type: Headset. Connectivity technology: Wired. Recommended usage: Office/Call center. Headphone frequency: 150 - 7000 Hz. Cable length: 0.95 m. Weight: 171.1 g. Product colour: Black



Performance		Operational conditions	
Product type *	Headset	Operating temperature (T-T)	-10 - 50 °C
Wearing style *	Head-band	Storage temperature (T-T)	-30 - 80 °C
Recommended usage *	Office/Call center	Weight & dimensions	
Headset type *	Monaural	Weight	171.1 g
Product colour *	Black	Packaging data	
Cable length	0.95 m	Package width	180 mm
Plug and Play	✓	Package depth	35 mm
Country of origin	China	Package height	230 mm
Certification	CE, FCC, KCC, RCM	Package weight	110 g
Ports & interfaces		Packaging content	
Connectivity technology *	Wired	Quick start guide	✓
3.5 mm connector	✓	Quantity	1
USB connectivity	✓	Logistics data	
Bluetooth	✗	Harmonized System (HS) code	85183000
Headphones		Master (outer) case width	226 mm
Ear coupling *	Supraaural	Master (outer) case length	564 mm
Headphone frequency	150 - 7000 Hz	Master (outer) case height	496 mm
Impedance	32 Ω	Master (outer) case gross weight	6.34 kg
Headphone sensitivity	93.6 dB	Products per master (outer) case	48 pc(s)
Driver unit	2.8 cm	Other features	
Microphone		Travel pouch	✓
Microphone type *	Boom		
Microphone frequency	100 - 10000 Hz		
Microphone noise-canceling	✓		



5706991020458



0706487017943



706487017943

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.