



Recommended P.C.Board Layout

SPECIFICATIONS

Current Rating: 3.0 Amp

Dielectric Withstanding: 1000V AC

Insulation Resistance: 5000MΩ Min

Contact Resistance: 4mΩ Max.

Operating Temperature:

Gold Plated: -55°C to +125°C

Tin Plated: -40°C to +105°C

Soldering Temperature: 260°C for 10 seconds

MATERIALS

Insulation Material: PPS, UL 94V-0

Contact Material: Brass

All materials must be RoHS compliant.

Datenblatt passend zu folgenden Artikelnummern

10120536 / 10120538 / 10120540