

Specification:

- ErP Level VI Efficiency Rating
- 50,000 Hour MTBF
- UL & CE Approved
- 1 Years Warranty

Output:

Output Voltage:	5.1V DC
Output Current:	2500mA
Output Power:	12.75 watt
Short Circuit Protection:	Automatic Recovery
Over Current Protection:	Automatic Recovery
Ripple & Noise:	240mVp-p max
Turn On Time:	3S Max
Line Regulation:	1% max
Output Regulation:	5% +/-
Output Cable:	1500mm Micro USB B 5Pin



Input:

Input Voltage:	90~264V AC
Input Frequency:	47~63Hz
Input Current:	1.2A Max
Inrush Current:	40A Max

Other:

Weight:	Approx. 138g
Operating Temperature:	0°C~40°C
Storage Temperature:	-20°C~+80°C
Humidity:	5~95%RH (non-condensing)
MTBF:	50,000 Hours

