



4mm Plug with the caged spring and tapering sleeve providing protection against kinking for self-assembly of test lead.

Material:

- Plug body: brass
- Spring: steel
- Surface treatment: gold or nickel
- Insulation: PE

Ratings:

- Rated voltage & current: 30V AC - 60V DC/max. 32A
- Max. cable diameter: 3.5mm
- Connection type: solder or screw in

Order code	Colour
17-2646	Black 4mm plug
17-2647	Blue 4mm plug
17-2648	Green 4mm plug
17-2649	Red 4mm plug
17-2650	Yellow 4mm plug