

Order code	Manufacturer code	Description
85-2908	SW3346	36W VOLT ADJUSTABLE MULTI OUTPUT PSU RC

	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

36 watt maximum multi output switch mode power supply

PowerPax part number SW3346

This plug top switch mode power supply provides a choice of 20 fully regulated output voltages. The voltage cannot be changed by mistake by the end user as there is no selector switch. The voltage is chosen by way of a resistor which pushes into side of the power supply. The table below shows the complete choice of outputs which step up in 1vdc increments and range between 5vdc and 24vdc

The unit is also supplied with UK, European, USA and Australian push on input pins and a choice of 6 output connectors. The standard output connector pack includes the following types but any dedicated connector, including those not shown, can be fitted on request

Type A) 2.5mm male

Type B) 3.5mm male

Type D) 2.1 x 5.5 x 12mm female

Type G) 2.5 x 5.5 x 12mm female

Type H) 1.3 x 3.5 x 10mm female

Type N) 1.5 x 5.5 x 12mm female

The connectors can be pushed on either way round to provide either + or – centre polarity



Input: 100 – 240vac 50/60Hz

Safety approvals include CE, CB GS approved

Output Voltage & Current:

Output Voltage	Output Current	Output Voltage	Output Current
5.0V	3800mA	15.0V	2400mA
6.0V	3700mA	16.0V	2200mA
7.0V	3600mA	17.0V	2100mA
8.0V	3500mA	18.0V	2000mA
9.0V	3400mA	19.0V	1880mA
10.0V	3300mA	20.0V	1800mA
11.0V	3200mA	21.0V	1700mA
12.0V	3000mA	22.0V	1630mA
13.0V	2700mA	23.0V	1560mA
14.0V	2500mA	24.0V	1500mA