UNITED KINGDOM 3-PIN PLUG-IN POWER SUPPLY 9VDC 6WATT



T6352ST

Features:

- United Kingdom Fixed AC Head
- 1 Year Warranty
- Level VI Efficiency
- CE Approved



Description:

The Stontronics Range of Class II 6 watt AC/DC United Kingdom plug-in power supplies provide 6 watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications.

Specification	
Part Number	T6352ST
Input Voltage Range	90-264Vac
Input Frequency Range	47-63Hz
Input Current Rated	No Damage
Output Voltage Rating	+9V
Output Current Range	0.66A
Output Min Current	0A
Output Connection Type	2.1x5.5x12mm Centre Positive – Right Angle
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 2%
Ripple & Noise	300mVp-p
Efficiency	78.81% Min
Over Voltage Protection	25VDC Maximum
Over Load Protection	2.5A max with auto-recovery function
Operating Temperature	0°C to 40°C
Storage Temperature	-20°C to +60°C
Operating Humidity	20% to 85%
Storage Humidity	5% to 95%
Hi-Pot	3000VAC 4mA 1min
Leakage Current	0.25mA max
Safety Standard	BS EN60950-1:2006+A2
EMI Standard	EN55022:2010/AC:2011 EN61000-3-2:2014 EN61000-3-3:2013 EN55024:2010 IEC61000-4-2:2008 IEC61000-4-3:2006/A1:2007/A2:2010 IEC61000-4-4:2012 IEC61000-4-5:2014 IEC61000-4-6:2013 IEC61000-4-8:2009 IEC61000-4-11:2004
MTBF	50K Hours
Size mm max.	55 (L) x 49.5 (W) x 42.5(H) mm
Weight	139g
Regulator Type	Switched Mode Power Supply

UNITED KINGDOM 3-PIN PLUG-IN POWER SUPPLY 9VDC 6WATT



T6352ST

Diagrams

