JET.T7GM3 JET+ 7-drawer mobile workbenches - 3 modules per drawer



Description:

- 7 drawers (useful dimensions): 18 modules distributed in the 60 and 130 mm high drawers:
- 5 drawers 60 mm high = 15 modules.
- 1 drawers 130 mm high = 3 modules.
- 1 drawer 200 mm high.
- Supplied with 6 partitions for 60 mm drawers and 2 partitions for 130 mm drawers.
- The 200 and 270 mm drawers can also be fitted with modules.
- Total load in the drawers: 155 kg.
- High storage capacity: 155 litres.
- 1 full-length closed compartment for storing long tools:
- Door with key lock.
- Identical key for the drawers and the compartment.
- Supplied with the plastic slider.
- For the wood top version, just add wood top JET.A14M5.
- Can be fitted with a JET.C4GM5 chest
- Compatible with the JET+ and JET.XL range of accessories.
 4 very high performance wheels 160 mm diameter 2
- castors (including 2 with brakes) and 2 fixed.

 \bullet Overall dimensions (including wheels and worktop): L.1154 x D.546 x H.1000 mm.

- Drawer useful size: L.569 x D.421 x H.60/130/200 mm.
- Compartment dimensions: L.378 x D.430 x H. 679 mm

(passage width with door open 310 mm).

Color:	Black 9004
[kg]:	103

2015 **EACOM**