




**SPECIFICATION  
CONTROL DRAWING  
Crystal Resonator**

FREQUENCY
32.768000kHz



Holder Style	2x6 Cyl
Mode	Fundamental
Adjustment Tolerance	± 10PPM at 25°C
Operating Temp. Range	-10°C to +60°C
Load Capacitance	12.5 pF
ESR	35000 Ohm
Marking	Mark Std

Amdt Date	Change Note	AEL Code		
		X32K768L025		
		<table border="1"> <tr> <th align="left">Issue Ref</th> <td align="center">A</td> </tr> </table>	Issue Ref	A
Issue Ref	A			