

Table of Contents

1.	SAFETY PRECAUTIONS AND WARNINGS.....	1
2.	GENERAL INFORMATION.....	2
2.1	TPMS SYSTEM REVIEW	2
2.2	TPMS LEGISLATION	2
2.3	TPMS TELL-TALE LIGHT	2
2.4	BENEFITS OF TPMS.....	3
3.	TOOL INFORMATION.....	4
3.1	TOOL DESCRIPTION	4
3.2	SPECIFICATIONS.....	5
3.3	ACCESSORIES INCLUDED.....	5
3.4	ICONS	6
3.5	KEYBOARD	6
3.6	BATTERY CHARGING	7
3.7	SETTINGS	7
4.	TPMS ACTIVATION.....	18
4.1	VEHICLE SELECTION	18
4.2	LATEST SCAN.....	26
4.3	AUDIT REPORT.....	27
4.4	RKE & RF MONITOR.....	28
5.	SOFTWARE UPDATE.....	30
6.	WARRANTY AND SERVICE.....	32
6.1	LIMITED ONE YEAR WARRANTY	32
6.2	SERVICE	32

1. Safety Precautions and Warnings

To prevent personal injury or damage to vehicles and/or the scan tool, read this instruction manual first and observe the following safety precautions at a minimum whenever working on a vehicle:

- Always perform diagnosis or service in a safe environment. Wear safety eye protection that meets ANSI standards.
- Wear safety eye protection that meets ANSI standards.
- Keep clothing, hair, hands, tools, test equipment, etc. away from all moving or hot engine parts.
- Operate the vehicle in a well ventilated work area: Exhaust gases are poisonous.
- Put blocks in front of the drive wheels and never leave the vehicle unattended while running tests.
- Use extreme caution when working around the ignition coil, distributor cap, ignition wires and spark plugs. These components create hazardous voltages when the engine is running.
- Keep a fire extinguisher suitable for gasoline/chemical/electrical fires nearby.
- Put the transmission in PARK (for automatic transmission) or NEUTRAL (for manual transmission) and make sure the parking brake is engaged.
- Refer to the user's manual for the vehicle being serviced and adhere to all diagnostic procedures and precautions. Otherwise personal injury or unneeded repairs may result.
- Keep the scan tool dry, clean, free from oil/water or grease. Use a mild detergent on a clean cloth to clean the outside of the scan tool, when necessary.
- Keep the TPMS tool dry, clean, free from oil, water and grease. Use a mild detergent on a clean cloth to clean the outside of the TPMS tool when necessary.

2. General Information

2.1 TPMS system review

A tire pressure monitoring system (**TPMS**) is an electronic system designed to monitor the air pressure inside the pneumatic tires on various types of vehicles. TPMS report real-time tire-pressure information to the driver of the vehicle, either via a gauge, a pictogram display, or a simple low-pressure warning light. TPMS can be divided into two different types — direct (dTPMS) and indirect (iTPMS). TPMS are provided both at an OEM (factory) level as well as an aftermarket solution.

2.2 TPMS Legislation

In the United States, the United States Department of Transportation (NHTSA) released the FMVSS No. 138, which requires an installation of a Tire Pressure Monitoring System to all new passenger cars, multipurpose passenger vehicles, trucks, and buses that have a gross vehicle weight rating (GVWR) of 4,536 kg (10,000 lbs.) or less, except those vehicles with dual wheels on an axle, as of 2007. In the European Union, starting November 1, 2012, all new models of passenger cars must be equipped with a TPMS, with even tighter specifications that will be defined by the UNECE Vehicle Regulations (Regulation No. 64). From November 1, 2014, all new passenger cars sold in the European Union must be equipped with TPMS. On July 13, 2010, the South Korean Ministry of Land, Transport and Maritime Affairs announced a pending partial-revision to the Korea Motor Vehicle Safety Standards (KMOVSS), specifying that "TPMS shall be installed to passenger vehicles and vehicles of GVW 3.5 tons or less, ... [effective] on January 1, 2013 for new models and on June 30, 2014 for existing models". Japan is expected to adopt European Union legislation approximately one year after European Union implementation. Further countries to make TPMS mandatory include Russia, Indonesia, the Philippines, Israel, Malaysia and Turkey.

2.3 TPMS tell-tale light

When diagnosing TPMS systems, you should understand what the TPMS tell-tale light means.

When turning the ignition OFF to ON, the TPMS tell-tale should come on, and then go off, which indicates the system is working fine. If the light stays on, there would be a pressure problem. If the light flashes, there would be a system problem, which can range from faulty sensors to sensors on the vehicle that haven't been learned to that vehicle.

2.4 Benefits of TPMS

The significant advantages of TPMS are summarized as follows:

- Fuel saving.
- Extended tire life.
- Decreased downtime and maintenance.
- Improved safety.
- Environmental efficiency.

3. Tool Information

3.1 Tool Description



- 1) **Rubber BOOT** – Protects the TPMS tool from drop, abrasion, and etc.
- 2) **LCD DISPLAY** – Indicates test results. Backlit 128*64 pixel display with contrast adjustment.
- 3)  **UP SCROLL BUTTON** – Moves up through menu and submenu items in menu mode. When more than one set of data are retrieved, use this button to move down to next screens for additional data.

- 4)  **N BUTTON** – Cancels a selection (or action) from a menu or return to previous menu.
- 5)  **DOWN SCROLL BUTTON** – Moves down through menu and submenu items in menu mode. When more than one set of data are retrieved, use this button to move down to next screens for additional data.
- 6)  **HELP BUTTON** – Provides help information.
- 7)  **POWER BUTTON** – Turns on/off the tool.
- 8)  **Y BUTTON** – Confirms a selection (or action) from a menu or return to previous menu.
- 9)  **TEST BUTTON** – Commences a TPMS test.
- 10) **USB PORT** – Connects the TPMS tool to computer with the USB cable supplied to update the device or for charging.
- 11) **POWER PORT** – Connects the TPMS tool to the mains with the charger supplied for battery charging.

3.2 Specifications

- 1) Display: Backlit 128*64 pixel display with contrast adjustment
- 2) Power: 3.7V Li-polymer battery
- 3) Operating Temperature: 0 to 50 °C (32 to 122 °F)
- 4) Storage Temperature: -20 to 70 °C (-4 to 158 °F)
- 5) Dimensions:
- 6)

Length	Width	Height
195.5 mm (7.7")	104 mm (4.09")	37.5 mm (1.48")
- 7) Weight: 0.37kg (0.82lb)

3.3 Accessories Included

- 1) **User's Manual** -- Instructions on tool operations.

- 2) **USB Cable** -- Allows easy update through PC via internet connection.
- 3) **Carry Case** – A case to store the tool when not in use.
- 4) **Magnet** -- Used to trigger magnetically activated sensors (early model TPMS sensors)
- 5) **Power Adapter** – Charges the built-in battery.
- 6) **CD** – Includes user's manual, MaxilinkII Kit, etc.

3.4 Icons

- 1) “▶” -- Indicates current selection.
- 2) “X/X” -- Indicates total items in a menu and their sequence.
- 3) “ ” -- Indicates there is data stored in the tool.
- 4) “ ” -- Indicates battery volume.
- 5) “ ” -- Indicates USB communication with the computer is established.
- 6) “? ” -- Indicates there is tip for relevant item. Press  **HELP BUTTON** to view the details for help information.
- 7) “...”-- Indicates the item is too long for the display. Press  **HELP BUTTON** to view the full text.
- 8) “ ” -- Indicates magnet is required to activate TPMS sensor.
- 9) “P↓”-- Indicates deflation is required to activate TPMS sensor.
- 10) “ ” -- Indicates test mode **One Wheel of Wheels to Test** in the system setting is selected.
- 11) “ ” -- Indicates test mode **ALL Wheels of Wheels to Test** in the system setting is selected.
- 12) “ ” – Indicates the TPMS tool is sending signals to the tire sensor for activation and test.

3.5 Keyboard

No solvents such as alcohol are allowed to clean the keypad or display. Use a mild nonabrasive detergent and a soft cotton cloth. Do not soak the keypad as the keypad is not waterproof.

3.6 Battery Charging

The tool has a 3.7v built-in lithium-ion polymer rechargeable battery. There are two means of battery charging:

- 1) To charge battery by power adapter.
 - Locate the power port of the device.
 - Connect the device and the power source with the adapter.
- 2) To charge battery by USB cable
 - Locate the USB port of the device.
 - Connect the device and the computer with the USB cable.

For optimum performance, always keep your tool sufficiently charged. It is recommended that you charge the tool for over 2 hours before the first use.

 **NOTE:** Only use the power adaptor or USB cable that is included in our pack to charge this tool. The use of un-approved power supplies may damage your tool and void the tool warranty.

3.7 Settings

The tool allows you to make the following adjustments and settings.

- 1) **Language:** Selects the desired language.
- 2) **ID Format:** Sets the ID displaying in Hexadecimal or Decimal.
- 3) **Pressure Unit:** Sets the pressure unit in kPa, Psi or Bar.
- 4) **Temperature Unit:** Sets the temperature unit in degree Celsius or Fahrenheit.
- 5) **Beep Set:** Turns on/off key-press beep.
- 6) **Wheels to Test:** Gives the operator the choice to test One wheel or All wheels.

- 7) **Auto Power-off:** Sets the time to power off automatically.
 - 8) **Contrast:** Adjusts the contrast of the LCD display.
 - 9) **Backlight Set:** Turns on/off the backlight.
 - 10) **Tool Information:** Views the important information of the tool.
- *Settings of the unit will remain until change to the existing settings is made.*

To enter the Setup menu

When the scan tool is powered on, it displays a **Main Menu**. (Figure 3.1) Use the **UP/DOWN** scroll button to select **Settings** from **Main Menu**, and press the **Y** button.




Figure 3.1

Language

- 1) From **System Settings** screen, use the **UP/DOWN SCROLL** button to select **Language**, and press the **Y** button.




Figure 3.2

- 2) Use the **UP/DOWN SCROLL** button to select the desired language and press the **Y** button to save your selection and return to the previous screen. We provide three language options currently.



Figure 3.3

ID Format

- 1) From **System Settings** screen, use the **UP/DOWN SCROLL** button to select **ID Format**, and press the **Y** button.




Figure 3.4

- 2) From **ID Format** screen, use the **UP/DOWN SCROLL** button to select the desired format of ID.




Figure 3.5

- 3) Press the **Y** button to save your settings and return to previous menu, or press the **N** button to exit without change.

Pressure Unit

- 1) From **System Settings** screen, use the **UP/DOWN SCROLL** button to select **Pressure Unit**, and press the **Y** button.




Figure 3.6

- 2) From **Pressure Unit** screen, use the **UP/DOWN SCROLL** button to select the desired unit: Kpa, Psi or Bar. (Figure 3.7)
- 3) Press the **Y** button to save your settings and return to previous menu, or press the **N** button to exit without change.




Figure 3.7

Temperature Unit

- 1) From **System Settings** screen, use the **UP/DOWN SCROLL** button to select **Temperature Unit**, and press the **Y** button.




Figure 3.8

- 2) From **Temperature Unit** screen, use the **UP/DOWN SCROLL** button to select the desired unit of temperature. (Figure 3.9)
- 3) Press the **Y** button to save your settings and return to the previous menu, or press the **N** button to exit without change.




Figure 3.9

Beep Set

This function allows you to turn on/off the build-in speaker for key pressing.

- 1) From **System Settings** screen, use the **UP/DOWN SCROLL** button to select **Beep Set**, and press the **Y** button.




Figure 3.10

- 2) From **Beep Set** menu, use the **UP/DOWN SCROLL** button to select **Beep ON** or **Beep OFF** to turn on/off the beep. (Figure 3.11)
- 3) Press the **Y** button to save your selection or the **N** button to cancel and return to the previous menu.




Figure 3.11

Wheels to Test

This function gives you choice to test TPMS sensors in ALL Wheels mode or One Wheel mode.

- 1) From **System Settings** screen, use the **UP/DOWN SCROLL** button to select **Wheels to Test**, and press the **Y** button.




Figure 3.12

- 2) From **Test Unit** menu, use the **UP/DOWN SCROLL** button to select **All Wheels** or **One Wheel** mode for TPMS sensor testing.




Figure 3.13

- 3) Press the **Y** button to save your selection or the **N** button to cancel and return to the previous menu.

 **NOTE:** In **All Wheels** mode, the tool will determine if a duplicate sensor ID has been read. In this case, the tool will display a message “**Sensor ID Duplicate.**” In **One Wheel** mode, the tool will not check the duplicate sensor ID.

Auto Power-off

- 1) From **System Settings** screen, use the **UP/DOWN SCROLL** button to select **Auto Power-off**, and press the **Y** button.




Figure 3.14

- 2) Press the **UP/DOWN SCROLL** button to increase or decrease the time to auto power-off the tool, and then press the **Y** button to confirm your change or the **N** button to cancel and return to the previous menu.




Figure 3.15

- 🔍 **NOTE:** Before the tool powers off automatically, it will save all the TPMS test data. Next time when the tool is powered on, you may retrieve the recorded data. If the tool automatically powers off during a test operation, next time when the tool is powered on, it will automatically turn to the previous operation screen.
- 🔍 **NOTE:** When using external power, the scan tool stays on until you turn it off. When using internal battery power, the scan tool turns off automatically after a set time of inactivity.

Contrast

- 1) From **System Settings** screen, use the **UP/DOWN SCROLL** button to select **Contrast**, and press the **Y** button.




Figure 3.16

- 2) Press the **UP/DOWN SCROLL** button to adjust the screen display contrast, and then press the **Y** button to confirm your change or the **N** button to cancel and return to previous menu.




Figure 3.17

Backlight Set

The Backlight function allows you to adjust the screen backlighting.

NOTE: Temperature or lighting may affect the brightness of the scan tool screen. If necessary, use the Contrast Adjust function to adjust the screen for working conditions.

- 1) From **System Settings** screen, use the **UP/DOWN SCROLL** button to select **Backlight Set**, and press the **Y** button.




Figure 3.18

- 2) From **Backlight Set** menu, use the **UP/DOWN SCROLL** button to select **Backlight ON** or **Backlight OFF** to turn on/off the backlight.




Figure 3.19

- 3) Press the **Y** button to save your selection or the **N** button to cancel and return to previous menu.

Tool Information

This function allows user to view some important information about the tool, such as serial number, software version and hardware version.

- 1) From **System Settings** screen, use the **UP/DOWN SCROLL** button to select **Tool Information**, and press the **Y** button; wait for the **Tool Information** screen to appear.

- 2) View tool information on screen.

Tool Information	
Serial NO :	Ts40000005
Date :	06/28/12
S/W Ver :	V1.0
H/W Ver :	V2.00

Figure 3.20

4. TPMS Activation

The MaxiTPMS[®] TS401 is a hand held tool used to activate all magnetic, frequency, and tire deflation triggered sensors used on vehicle tire pressure monitoring systems to get information such as sensor ID, tire pressure, tire temperature, sensor battery, and frequency. It also sends the sensor data to vehicle's ECU to let the ECU learn the positions of sensors whenever tires and wheels are rotated or sensors are replaced.

There are two means of activating a TPM sensor:

- A. **Vehicle Selection**--To activate the sensor by selecting vehicle make, model and year.
 - B. **Latest Scan**--The TPMS tool automatically records the latest activated sensor and it activates the sensor by using the wave signal of the latest trigger event. So Latest Scan is very useful for technicians to wake up sensors of the same vehicle.
- *All software screens shown in this manual are examples. Actual test screens may vary for each vehicle being tested.*

4.1 Vehicle Selection

- 1) Use the **UP/DOWN SCROLL** button to select **Vehicle Selection** from **Main Menu** (Figure 4.1), and press the **Y** button to confirm.
- 2) Observe the menu title and use the **UP/DOWN SCROLL** button to select by make, model and year to identify the vehicle being tested, place the device alongside the valve stem and press the **Y** button. (Taking Mitsubishi as an example.)




Figure 4.1

- *The selected vehicle is remembered by the tool when a test is commenced.*

Select by Make




Figure 4.2

Select by Model



Figure 4.3

Select by Year




Figure 4.4

- 3) Depending upon the reading mode (**All Wheels** or **One Wheel**), results are displayed in different manners.

All Wheels Mode

In this mode, the screen will display as below (Figure 4.5). The tool will do TPMS test in a sequence of FL (Left Front), FR (Right Front), RR (Right Rear), RL (Left Rear) and SPARE, if the vehicle has the option for the spare. Use the **UP/DOWN SCROLL** button to move to the desired wheel for testing. Place the tool alongside the valve stem and point toward the sensor location and then press **TEST** button.




Figure 4.5

Once the first sensor test is completed, the screen will hold for 3 seconds for viewing and then switch to the next sensor test. Follow

the same procedure for the rest of the three or four wheels by pressing the **UP/DOWN SCROLL** button and then **TEST** button.

The tool will send LF signal to trigger the sensor. Depending on the sensor type, the tool will activate the sensor on the first or last step. Once the sensor is successfully activated and decoded, the tool will display as below with an audible beep. (Figure 4.6)



Figure 4.6

After the sensor is activated, a test result icon, “√”, “x”, “D”, will display alongside the wheel, indicating the wheel test is completed, otherwise there's no result icon displayed.

The figure by the side of the result icon (Figure 4.6) indicates the specific tire pressure value.

- ✓ Press **Y** button to read all sensor data, including sensor ID, tire pressure, temperature, battery condition and modulation.
- ✓ Hollow wheel indicates wheel test has not been carried out.
- ✓ Solid wheel indicates wheel test has completed.

One Wheel Mode

The screen will show as below.



Figure 4.7

In this mode, the tool will do TPMS test for each single wheel. Place the tool alongside the valve stem and point toward the sensor location and then press **TEST** button. Wait for test result before moving the tool.

The tool will send LF signal to trigger the sensor. Depending on the sensor type, the tool will activate the sensor on the first or last step. Once the sensor is successfully activated and decoded, the tool will display as below with an audible beep. (Figure 4.8)



Figure 4.8

Once the first sensor test is completed, the screen will hold for 3 seconds for data viewing and then switch to next sensor test. Follow the same procedure for the other sensor tests.

The tool can save up to 5 TPMS sensor data records at each time. Press the **UP/DOWN** or **LEFT/RIGHT** scroll button to turn over data screens while viewing. If more than five records are stored, the latest record will overwrite the first one.

TABLE 1 POSSIBLE RESULTS FOR TESTING

Icon	Test Results	Description
✓	Successful Sensor Read	TPMS sensor is successfully activated and decoded. The tool displays the sensor information.
X	Failed Sensor Read	If the search period expires and no sensor activation or decode, it may be wrong sensor fitting or non-functioning sensor. The tool displays a message “No sensor detected.”. In this case, repeat test to confirm the TPMS failure.
X	Wrong Sensor Type	A TPMS sensor is activated and decoded, but does not match the protocol for the Make, Model or Year that the tool was set-up for. The tool displays a message “Sensor triggered but cannot be known.”. In this case, verify the Make, Model or Year you have selected as well as the sensor part number that was fitted.
D	Duplicate ID (only checked in All Wheels mode)	A sensor with a duplicate ID has been read. The tool displays a message “Sensor ID Duplicate.”. In this case, clear data and re-read again.

NOTE: With Ford Banded sensors, the tool should be held 180 degree away from the stem. Please refer to vehicle user's manual.

- If the TPMS sensor requires a magnet, place the magnet over the stem and then place the tool alongside the stem, and press **TEST** button.




Figure 4.9

- If the TPMS sensor requires tire deflation (of the order of 10PSI), then deflate the tire and place the tool alongside the stem while pressing **TEST** button.




Figure 4.10

- Anytime while doing the TPMS test, press **? BUTTON** to read the sensor make, OEM part no., and relearn information for the vehicle being tested.




Figure 4.11

- Sensor activation can be aborted at any time by pressing the **N** button. When the activation is aborted, the tool will return to the previous menu.
- By pressing the **Y** button, you may review information of all sensors tested. The screen will switch every five seconds.

Pos	ID-H	Kpa	° F
FL	7C076A80	240	78.0
FR	7C076A80	240	77.0
RR	7C076A80	240	78.0
RL	7C076A80	240	78.0

[N]=exit 1/2

Figure 4.12

Pos	BAT	Mode	MDT
FL	OK	NA	433FM
FR	OK	NA	433FM
RR	OK	NA	433FM
RL	OK	NA	433FM

[N]=exit 2/2

Figure 4.13

[Pos] – Indicates the wheel sensor position.

[ID-H/D] – Shows sensor ID data.

[KPa/Psi/Bar] – Indicates wheel pressure.

[°C/°F] – Indicates wheel temperature.

[BAT] – Indicates battery condition.

[Mode] – Defines tire sensor working mode or status.

[MDT] – Indicates sensor signal frequency.

NOTE: Different ID format, pressure and temperature units will display at the title bar according to the device's system setting, please refer to 2.7 Settings for detailed guidance.

4.2 Latest Scan

This function allows you to review the last tested sensor data and activate the sensor by using the wave signal of the latest trigger event, which is very useful for technicians to wake up sensors of the same vehicle.

- ***Once the tool has been used to test a vehicle, this item will change to the name of vehicle being tested.***
- 1) Use the **UP/DOWN SCROLL** button to select **Latest Scan** (In our example, this is **Mitsubishi Lance**) from **Main Menu** (Figure 4.14), place the device alongside the valve stem and press the **Y** button to confirm.




Figure 4.14

- 2) A prompt comes up asking for your confirmation.




Figure 4.15

- 3) Press the **N** button to playback the historical records. (Figure 4.16) Use the **UP/DOWN SCROLL** button to view additional information or press the **N** button to exit.

Pos	BAT	Mode	MDT
FL	OK	NA	433FM
FR	OK	NA	433FM
RR	OK	NA	433FM
RL	OK	NA	433FM
[N]=exit 2/2			

Figure 4.16

- 4) Press the **Y** button to delete test records and enter test mode. For detailed procedure, please refer to section **4.1 Vehicle Selection**.

4.3 Audit Report

After the user finished the TPMS test, the tool is capable of presenting all of its stored TPMS data in a HTML file when connected to a PC via an USB cable.

The tool will automatically pop up a explorer window in PC screen when connected to an active USB port on the PC. Make sure the tool

is powered on. Otherwise, there will be no communication between the tool and computer.

Once the explorer window is open, you may view a file by double-clicking on the file. If this explorer window does not automatically pop up, the user may browse for the newly connected device manually.

The data presented is in a HTML form format that displays not only information regarding the TPMS, but also automatically updates with the date. It also provides data entry areas for other tester and vehicle data.

MaxiTPMS TS601

Vehicle Make Tested: Honda Odyssey Touring 2005-2007

Test Performed by:

Owners Name:

License Plate No:

Model and Year:

Comments:

Wheel	BCM ID Hex	BCM ID Dec	ID Hex	ID Dec	Pressure	Temperature	Battery State	Modulation	OEM Part #:
FL	8D657ACF	2374335183	B8220764	30892378600	240kpa	25	OK	315AM	06421-S3V-A04
FR	Untested	Untested	Untested	Untested	Untested	Untested	Untested	Untested	Untested
RR	Untested	Untested	Untested	Untested	Untested	Untested	Untested	Untested	Untested
RL	Untested	Untested	Untested	Untested	Untested	Untested	Untested	Untested	Untested
SP	Untested	Untested	Untested	Untested	Untested	Untested	Untested	Untested	Untested

Figure 4.17

4.4 RKE & RF Monitor

Today's keyless remotes -- also known as key fobs -- make life easier. But when your key fob stops working or starts to perform sporadically, it will be particularly frustrating. Check your key fob to make sure it is in top condition so it will work when you really need it.

Since a key fob is attuned to a special frequency that is only detected by the car for which it was issued, you will need to have your vehicle to test the fob. Otherwise you will have to take it to a dealership or an automotive locksmith to have them tested for the right frequency. But with our TPMS tool, the key fob testing becomes easy and

convenient.

- 1) Use the **UP/DOWN SCROLL** button to select **RKE & RF Monitor** from **Main Menu** (Figure 4.18), and press the **Y** button to confirm.




Figure 4.18

- 2) Hold the key fob very close to the tool and press the function buttons on key fob to test. If the button works and the key fob is sending a signal, the tool will beep and the screen will show as below. If the button does not work, the tool will do nothing. To make sure each button is working properly, please follow the process to test each button in turn.




Figure 4.19

- The progress bar indicates the approximate power level of the key fob.
 - The stronger the signal, the higher the beep tone.
 - The tool only tests 315MHz and 433MHz key fobs.
- 3) Press the **N** button to return to previous menu.

5. Software Update

The tool allows user to update software. It works on computers running Windows systems (XP/2000/Vista/Windows7).

To update software, you will need the followings:

- ✓ TS401
- ✓ CD with update tool
- ✓ PC or laptop with USB ports
- ✓ USB cable

CAUTION: DO NOT try to update the tool when the battery is low. Data will be lost if the device is out of power while updating.

- 1) Download the latest update files from our website: www.auteltech.com, and save in your computer.
- 2) Connect the TPMS tool to the computer with the USB cable.
- 3) Use the **UP/DOWN SCROLL** button to select **Update Mode** from **Main Menu** (Figure 5.1), and press the **Y** button to confirm.




Figure 5.1

NOTE: When you made a wrong choice and the tool is unable to work properly, you may need to update the programs. To hold the **N** button and power on the scan tool, you will enter

the Update Mode forcibly. Then follow the update procedure to refresh the program.

- 4) Run the Maxi-link II Kit in your computer. (Figure 5.2)




Figure 5.2

- 5) Click **Select File** button to locate the latest update file you have recently downloaded.
- 6) Click **Update** to start updating.
- 7) Once the update is complete, the tool is updated and ready to go.

6. Warranty and Service

6.1 Limited One Year Warranty

Autel warrants to its customers that this product will be free from all defects in materials and workmanship for a period of one (1) year from the date of the original purchase, subject to the following terms and conditions:

- 1) The sole responsibility of Autel under the Warranty is limited to either the repair or, at the option of Autel, replacement of the TPMS tool at no charge with Proof of Purchase. The sales receipt may be used for this purpose.
- 2) This warranty does not apply to damage due directly or indirectly, to misuse, abuse, negligence or accidents, repairs or alterations outside our Service Center or facilities, criminal activity, improper installation, normal wear and tear, or to lack of maintenance.
- 3) Autel shall not be liable for any incidental or consequential damages arising from the use, misuse, or mounting of the TPMS tool. Some states do not allow limitations on how long an implied warranty lasts, so the above limitations may not apply to you.
- 4) All information in this manual is based on the latest information available at the time of publication and no warranty can be made for its accuracy or completeness. Autel reserves the right to make changes at any time without notice.

6.2 Service

If you have any questions, please contact your local distributor or visit our website at www.auteltech.com.

If it becomes necessary to return the tool for repair, contact your local distributor for more information.

Autel TS401 09-01-14

Make	Model	Year	Type
Acura	CSX	2008 - 2012	
Acura	ILX	2013	
Acura	MDX	2004 - 2013	
Acura	RDX	2007 - 2013	
Acura	RL	2005 - 2012	
Acura	TL	2005 - 2013	
Acura	TSX	2007 - 2013	
Acura	ZDX	2010 - 2013	
Audi	A3	2006 - 2012	
Audi	A4	2002 - 2012	
Audi	A4 Cabriolet	2003 - 2012	
Audi	A5	2008 - 2012	
Audi	A6	2002 - 2004	
Audi	A6	2005 - 2009	
Audi	A6	2010 - 2012	
Audi	A6 Allroad	2001 - 2011	
Audi	A8	2000 - 2002	
Audi	A8	2003	315
Audi	A8	2003	433
Audi	A8	2004 - 2012	
Audi	Q5	2009 - 2012	
Audi	Q7	2005 - 2012	
Audi	R8	2008 - 2012	
Audi	RS4	2007 - 2008	
Audi	RS4 Cabriolet	2008 - 2009	
Audi	RS6	2000 - 2005	315
Audi	RS6	2000 - 2005	433
Audi	S4	2002 - 2012	
Audi	S5	2008 - 2012	
Audi	S6	2004 - 2011	
Audi	S8	2000 - 2009	
Audi	S8	2003	315
Audi	S8	2003	433
Audi	TT	2007 - 2012	
Bentley	Arnage	2008	433
Bentley	Azure	2007 - 2009	
Bentley	Continental GT	2003 - 2011	
Bentley	Continental GT(614)	2005	
Bentley	Flying Spur	2005 - 2010	
Bentley	Mulsanne	2011 - 2012	
BMW	1 Series	2007 - 2013	
BMW	3 Series	1999	
BMW	3 Series	2000 - 2002	315
BMW	3 Series	2000 - 2002	433
BMW	3 Series	2003 - 2013	
BMW	5 Series	2000 - 2013	
BMW	5 Series	2002	315
BMW	5 Series	2002	433
BMW	6 Series	2006 - 2013	
BMW	7 Series	2000 - 2001	315
BMW	7 Series	2000 - 2001	433

BMW	7 Series	2002 - 2012	
BMW	Alpina	2004 - 2013	
BMW	M1	2011 - 2012	
BMW	M3	2008 - 2013	
BMW	M5	2006 - 2013	
BMW	M6	2006 - 2013	
BMW	X1	2012 - 2013	
BMW	X3	2006 - 2013	
BMW	X5	2000 - 2013	
BMW	X6	2008 - 2013	
BMW	X6 HYBRID	2009 - 2011	
BMW	Z Series	2006 - 2013	
Buick	Allure	2007 - 2011	
Buick	Enclave	2008 - 2013	
Buick	LaCrosse	2007 - 2013	
Buick	LeSabre	2007	
Buick	Lucerne	2007 - 2011	
Buick	Rainier	2007	
Buick	Rainier	2006	315
Buick	Rainier	2006	433
Buick	Regal	2011 - 2013	
Buick	Verano	2012 - 2013	
Cadillac	CTS	2004 - 2013	
Cadillac	CTS-V	2009 - 2013	
Cadillac	Deville	2001 - 2005	
Cadillac	DTS	2006 - 2011	
Cadillac	Escalade	2004 - 2013	
Cadillac	Escalade	2007	Clamp In
Cadillac	Escalade	2007	Snap In
Cadillac	Seville	2001 - 2004	
Cadillac	SRX	2004 - 2013	
Cadillac	STS	2005 - 2011	
Cadillac	STS	2009	Clamp In
Cadillac	STS	2009	Snap In
Cadillac	XLR	2004 - 2011	
Cadillac	XTS	2013	
Chevrolet	Avalanche	2004 - 2013	
Chevrolet	Avalanche	2007	Clamp In
Chevrolet	Avalanche	2007	Snap In
Chevrolet	Aveo	2007 - 2011	
Chevrolet	Camaro	2010 - 2013	
Chevrolet	Camaro ZL1	2012 - 2013	
Chevrolet	Captiva sport	2012 - 2013	
Chevrolet	Cobalt	2008 - 2009	Clamp In
Chevrolet	Cobalt	2008 - 2009	Snap In
Chevrolet	Cobalt	2010 - 2012	
Chevrolet	Colorado	2007 - 2012	
Chevrolet	Corvette	1997 - 2013	
Chevrolet	Corvette C5	2001 - 2004	
Chevrolet	Corvette C6	2005 - 2009	
Chevrolet	Corvette Z06	2001 - 2012	
Chevrolet	Cruze	2011 - 2013	
Chevrolet	Equinox	2007 - 2013	

Chevrolet	Express Series	2008 - 2012	
Chevrolet	G Series	2008 - 2011	
Chevrolet	HHR	2008 - 2011	
Chevrolet	HHR	2009	Clamp In
Chevrolet	HHR	2009	Snap In
Chevrolet	Impala	2006 - 2013	
Chevrolet	Impala	2007	Clamp In
Chevrolet	Impala	2007	Snap In
Chevrolet	Malibu	2008	Clamp In
Chevrolet	Malibu	2008	Snap In
Chevrolet	Malibu	2009 - 2013	
Chevrolet	Monte Carlo	2006	
Chevrolet	Monte Carlo	2007	Clamp In
Chevrolet	Monte Carlo	2007	Snap In
Chevrolet	ORLANDO	2012	
Chevrolet	Silverado	2004 - 2013	
Chevrolet	Silverado	2007	Snap In
Chevrolet	Silverado	2007	Trw Clamp In
Chevrolet	Sonic	2012 - 2013	
Chevrolet	Spark	2013	
Chevrolet	SSR	2006 - 2007	
Chevrolet	Suburban	2004 - 2012	
Chevrolet	Suburban	2007	Snap In
Chevrolet	Suburban	2007	Trw Clamp In
Chevrolet	Tahoe	2004 - 2013	
Chevrolet	Tahoe	2007	Snap In
Chevrolet	Tahoe	2007	Trw Clamp In
Chevrolet	Trailblazer	2006 - 2009	
Chevrolet	Traverse	2009 - 2012	
Chevrolet	Uplander	2008 - 2009	
Chevrolet	Van	2008 - Onwards	
Chevrolet	Volt	2010 - 2013	
Chrysler	200	2011 - 2013	
Chrysler	300	2005 - 2013	
Chrysler	300	2007	315
Chrysler	300	2007	433
Chrysler	300 SRT	2010 - 2011	
Chrysler	300M	2002 - 2004	
Chrysler	Aspen	2007 - 2011	
Chrysler	Concorde	2002 - 2004	
Chrysler	Crossfire	2004	
Chrysler	Crossfire	2005 - Onwards	Conti
Chrysler	Crossfire	2005 - 2011	Sch
Chrysler	Intrepid	2002 - 2004	
Chrysler	Pacifica	2003 - 2008	
Chrysler	Pacifica	2004	Conti
Chrysler	Pacifica	2004	Sch
Chrysler	Prowler	2002	
Chrysler	PT Cruiser	2008 - 2010	
Chrysler	Sebring	2007 - 2012	
Chrysler	Sebring	2008 - 2009	315
Chrysler	Sebring	2008 - 2009	433
Chrysler	Town & Country	2002 - 2013	

Chrysler	Town & Country	2008	315
Chrysler	Town & Country	2008	433
Chrysler	Voyager	2002 - 2003	
Citroen	C4	2008 - Onwards	
Citroen	C4	2005 - 2007	39417
Citroen	C4 Coupe	2005 - 2007	39417
Citroen	Picasso C4	2006 - 2008	
Citroen	Picasso C4 Restyle	2008 - Onwards	
Citroen	C5 I	2001 - 2004	38169
Citroen	C5 II	2004 - 2008	
Citroen	C5 III	2008 - Onwards	
Citroen	C6	2005 - Onwards	
Citroen	C8	2002 - 2005	38596
Citroen	C8	2005 - Onwards	
Dodge	Avenger	2007 - 2013	
Dodge	Caliber	2007 - 2012	
Dodge	Caravan	2002 - 2007	
Dodge	Challenger	2008 - 2013	
Dodge	Charger	2005 - 2013	
Dodge	Charger SRT	2009 - 2012	
Dodge	C/V	2012	
Dodge	Dakota	2008 - 2011	
Dodge	Dart	2013	
Dodge	Durango	2007 - 2013	
Dodge	Grand Caravan	2002 - 2013	
Dodge	Intrepid	2002 - 2004	
Dodge	Journey	2009 - 2013	
Dodge	Magnum	2005 - 2011	
Dodge	Nitro	2007 - 2012	
Dodge	Raider	2009	
Dodge	Ram	2008 - 2013	
Dodge	Ram	2009	315
Dodge	Ram	2009	433
Dodge	Ram 250	2009	
Dodge	Sprinter	2007 - 2010	
Dodge	Stratus	2007	
Dodge	Viper	2003 - 2011	
Ferrari	430	2006 - 2011	
Ferrari	458	2009 - 2011	
Ferrari	550	2002 - 2010	
Ferrari	575	2002 - 2006	315
Ferrari	575	2002 - 2006	433
Ferrari	612	2002 - 2011	
Ferrari	California	2010 - 2011	
Ferrari	Enzo	2003	
Ferrari	FXX	2003	
Ferrari	Spider	2002	
Fiat	500	2011 - 2013	
Ford	C-Max	2012 - 2013	
Ford	Crown Victoria	2006 - 2011	
Ford	E-150	2007 - 2013	
Ford	E-250	2007 - 2013	
Ford	E-350 SD	2007 - 2013	
Ford	Edge	2007 - 2013	
Ford	Escape	2005 - 2013	

Ford	Expedition	2003 - 2013	
Ford	Explorer	2002 - 2013	
Ford	Explorer Sport Trac	2006 - 2010	
Ford	F-150	2007 - 2013	
Ford	F-250 SD	2008 - 2013	
Ford	F-350 SD	2008 - 2013	
Ford	F450/550	2008 - 2013	
Ford	Fiesta	2011 - 2013	
Ford	Five Hundred	2006 - 2009	
Ford	Flex	2009 - 2013	
Ford	Focus	2007 - 2013	
Ford	Freestar	2004 - 2007	
Ford	Fusion	2007 - 2013	
Ford	Grand Marquis	2007 - 2011	
Ford	Mustang	2007 - 2013	
Ford	Ranger	2007 - 2011	
Ford	Shelby GT	2012	
Ford	Taurus	2008 - 2013	
Ford	Taurus X	2008 - 2009	
Ford	Transit	2010 - 2013	
GMC	Acadia	2007 - 2012	
GMC	Canyon	2007 - 2012	
GMC	Envoy	2005 - 2006	
GMC	Envoy	2007 - 2009	1820
GMC	Envoy	2007	Sch Clamp In
GMC	Envoy	2007	Trw Clamp In
GMC	Envoy	2008 - 2009	Snap In
GMC	Savana	2008 - 2009	Conti
GMC	Savana	2010 - 2013	
GMC	Sierra All	2004 - 2013	
GMC	Sierra All	2007	Sch Clamp In
GMC	Sierra All	2007	Snap In
GMC	Sierra All	2007	Trw Clamp In
GMC	Terrain	2010 - 2013	
GMC	Yukon All	2004 - 2013	
GMC	Yukon All	2007	Snap In
GMC	Yukon All	2007	Trw Clamp In
Honda	Accord	2008 - 2012	
Honda	Civic	2008 - 2013	
Honda	Crosstour	2010 - 2013	
Honda	CR-V	2007 - 2011	Alloy
Honda	CR-V	2007 - 2011	Steel
Honda	CR-V	2012 - 2013	
Honda	CR-Z	2011 - 2013	
Honda	Element	2006 - 2011	
Honda	Fit	2008 - 2013	
Honda	Insight	2010 - 2013	
Honda	Odyssey	2006 - 2013	
Honda	Odyssey Touring	2005 - 2012	
Honda	Pilot	2005	Alloy
Honda	Pilot	2005	Steel
Honda	Pilot	2006 - 2008	
Honda	Pilot	2009 - 2013	Alloy
Honda	Pilot	2009 - 2013	Steel
Honda	Pilot Touring	2009 - 2012	

Honda	Ridgeline	2006 - 2013	Alloy
Honda	Ridgeline	2006 - 2012	Steel
Honda	Ridgeline RTL	2009 - 2012	
Honda	S2000	2008 - 2009	
Hummer	H2	2008 - 2010	
Hummer	H3	2006 - 2010	
Hummer	H3T	2006 - 2010	
Hyundai	Accent	2008 - 2013	
Hyundai	Azera	2007 - 2013	
Hyundai	Elantra	2007 - 2013	
Hyundai	Elantra Touring	2010 - 2012	
Hyundai	Entourage	2007 - 2010	
Hyundai	Equus	2011 - 2012	
Hyundai	Genesis	2009 - 2012	
Hyundai	Genesis Coupe	2010 - 2013	
Hyundai	Genesis Sedan	2009 - 2012	
Hyundai	Santa Fe	2007 - 2013	
Hyundai	Santa Fe	2008	Lo Line
Hyundai	Santa Fe	2008	Hi Line
Hyundai	Sonata	2007 - 2013	
Hyundai	Sonata	2008	Am
Hyundai	Sonata	2008	Fm
Hyundai	Tiburon	2007 - 2008	
Hyundai	Tucson	2007 - 2012	
Hyundai	Veloster	2012 - 2013	
Hyundai	Veracruz	2006 - 2012	
Hyundai	Veracruz	2008	Hi Line
Hyundai	Veracruz	2008	Lo Line
Infiniti	EX35	2008 - 2010	
Infiniti	EX35	2010 - 2013	41395
Infiniti	EX37	2013	
Infiniti	FX35	2003 - 2010	
Infiniti	FX35	2010 - 2012	41978
Infiniti	FX37	2013	
Infiniti	FX45	2003 - 2008	
Infiniti	FX50	2009 - 2010	
Infiniti	FX50	2010 - 2013	41395
Infiniti	G25	2011 - 2012	
Infiniti	G35	2003 - 2008	
Infiniti	G37	2008 - 2010	
Infiniti	G37	2010 - 2013	41395
Infiniti	JX35	2013	
Infiniti	M35	2006 - 2012	
Infiniti	M35h	2012	
Infiniti	M37	2011 - 2012	
Infiniti	M45	2003 - 2010	
Infiniti	M56	2011 - 2013	
Infiniti	Q45	2003 - 2006 Onwards	
Infiniti	QX4	2003	
Infiniti	QX56	2004 - 2012	
Infiniti	QX56	2005 - 2006	Alloy
Infiniti	QX56	2005 - 2006	Steel
Isuzu	Ascender	2006 - 2011	
Isuzu	I-290	2007 - 2011	
Isuzu	I-370	2007 - 2011	

Isuzu	Rodeo	2004	
Jaguar	S Type	2005 - 2007	315
Jaguar	S Type	2005 - 2007	433
Jaguar	S Type	2008 - 2011	
Jaguar	X Type	2007 - 2011	
Jaguar	XF	2009 - 2013	315
Jaguar	XF	2009 - 2012	433
Jaguar	XJ	2004 - 2011	315
Jaguar	XJ	2004 - 2011	433
Jaguar	XJ	2012	
Jaguar	XJR	2006 - 2011	
Jaguar	XK	2006 - 2013	315
Jaguar	XK	2006 - 2012	433
Jaguar	XKR	2007 - 2013	
Jeep	Commander	2006 - 2011	
Jeep	Compass	2007 - 2013	
Jeep	Grand Cherokee	2002 - 2013	
Jeep	Liberty	2002 - 2012	
Jeep	Liberty	2009	315
Jeep	Liberty	2009	433
Jeep	Patriot	2007 - 2013	
Jeep	Wrangler	2007 - 2013	
Jeep	Wrangler	2009	Clamp In
Jeep	Wrangler	2009	Snap In
Kia	Amanti	2007 - 2012	
Kia	Borrego	2009 - 2011	
Kia	Forte	2010 - 2013	
Kia	Magentis	2008 - 2010	
Kia	Mohave	2009 - 2011	
Kia	Optima	2006 - 2013	
Kia	Rio	2007 - 2013	
Kia	Rondo	2006 - 2011	
Kia	Sedona	2006 - 2012	
Kia	Sorento	2007 - 2013	
Kia	Soul	2010 - 2013	
Kia	Spectra	2007 - 2011	
Kia	Sportage	2005 - 2013	
Kia	Tuscany	2007 - 2008	
Lamborghini	Murcielago	2008 - 2010	
Lamborghini	Gallardo	2008 - 2012	
Land Rover	LR2	2008 - 2009	315
Land Rover	LR2	2008 - 2009	433
Land Rover	LR2	2010 - 2012	
Land Rover	LR3	2002 - 2005	
Land Rover	LR3	2006 - 2009	315
Land Rover	LR3	2006 - 2009	433
Land Rover	LR4	2010 - 2013	
Land Rover	Range Rover	2006 - 2012	315
Land Rover	Range Rover	2006 - 2012	433
Land Rover	Range Rover Evoque	2012 - 2013	
Land Rover	Range Rover Sport	2006 - 2013	315
Land Rover	Range Rover Sport	2006 - 2011	433
Lexus	CT 200H	2011 - 2013	
Lexus	ES 350	2007 - 2013	
Lexus	GS 300	2005 - 2012	

Lexus	GS 350	2007 - 2013	
Lexus	GS 430	2005 - 2007	
Lexus	GS 450H	2007 - 2013	
Lexus	GS 460	2008 - 2012	
Lexus	GX 460	2010 - 2013	
Lexus	GX 470	2004 - 2009	
Lexus	HS Series	2010 - 2012	
Lexus	IS Series	2006 - 2013	
Lexus	LFA	2012 - 2013	
Lexus	LS	2007 - 2013	
Lexus	LX	2006 - 2013	
Lexus	RX	2006 - 2013	
Lexus	SC	2007 - 2011	
Lexus	SC430	2002 - 2007	
Lincoln	Aviator	2003 - 2005	
Lincoln	Mark LT	2007 - 2009	
Lincoln	MKS	2009 - 2013	
Lincoln	MKT	2010 - 2013	
Lincoln	MKX	2007 - 2013	
Lincoln	MKZ	2007 - 2013	
Lincoln	Navigator	2003 - 2013	
Lincoln	Town Car	2006 - 2011	
Lotus	Elise	2008 - 2011	
Lotus	Evora	2010 - 2011	
Lotus	Exige	2008 - 2011	
Maserati	Coupe	2007 - 2011	
Maserati	Quattroporte	2004 - 2011	
Maybach	Landaulet	2009 - 2012	
Maybach	Maybach 57	2003 - 2011	
Maybach	Maybach 57 S	2006 - 2012	
Maybach	Maybach 62	2003 - 2011	
Maybach	Maybach 62 S	2003 - 2012	
Mazda	B Pickup	2007 - 2009 Onwards	
Mazda	CX-7	2007 - 2012	
Mazda	CX-9	2007 - 2013	
Mazda	Mazda 2	2011 - 2013	
Mazda	Mazda 3	2004 - 2013	
Mazda	Mazda 5	2006 - 2013	
Mazda	Mazda 6	2005 - 2013	
Mazda	MX-5 Miata	2006 - 2013	
Mazda	RX-8	2004 - 2011	
Mazda	Speed 3	2010 - 2012	
Mazda	Speed 6	2007 - 2008	
Mazda	Tribute	2006 - 2011	
Mercedes	C Class	2007 - 2013	
Mercedes	CL Class	2000 - 2009	US 315
Mercedes	CL Class	2000 - 2009	EU 433
Mercedes	CL Class	2010 - 2013	
Mercedes	CLK Class	2006 - 2009	
Mercedes	CLS Class	2012 - 2013	
Mercedes	CLS Class	2006 - 2011	US 315
Mercedes	CLS Class	2006 - 2011	EU433
Mercedes	E Class	2000 - 2010	US 315
Mercedes	E Class	2000 - 2010	EU 433

Mercedes	E Class	2011 - 2013	
Mercedes	E Class	2010	SCH
Mercedes	G Class	2007 - 2013	
Mercedes	GL Class	2010 - 2013	
Mercedes	GL Class	2007 - 2009	US 315
Mercedes	GL Class	2007 - 2009	EU 433
Mercedes	GLK	2010 - 2013	
Mercedes	ML Class	2006 - 2010	315
Mercedes	ML Class	2006 - 2010	433
Mercedes	ML Class	2010	SCH
Mercedes	ML Class	2011 - 2013	
Mercedes	R Class	2006 - 2009	315
Mercedes	R Class	2006 - 2009	433
Mercedes	R Class	2010 - 2012	
Mercedes	S Class	2000 - 2012	US 315
Mercedes	S Class	2000 - 2009	EU 433
Mercedes	S Class	2010 - 2013	433
Mercedes	SL Class	2000 - 2012	US 315
Mercedes	SL Class	2000 - 2009	EU 433
Mercedes	SL Class	2013	
Mercedes	SLK Class	2008 - 2013	
Mercedes	SLR Class	2001 - 2009	US 315
Mercedes	SLR Class	2001 - 2009	EU 433
Mercedes	SLR McLaren	2005 - 2006	
Mercedes	SLS	2011 - 2012	
Mercury	Grand Marquis	2006 - 2011	
Mercury	Mariner	2006 - 2011	
Mercury	Milan	2008 - 2011	
Mercury	Montego	2006 - 2007	
Mercury	Monterey	2004 - 2007	
Mercury	Mountaineer	2002 - 2010	
Mercury	Sable	2008 - 2009	
Mini	All	2007 - 2013	
Mitsubishi	Conti Set To Park	ALL	
Mitsubishi	Eclipse	2006 - 2012	Alloy
Mitsubishi	Eclipse	2006 - 2012	Steel
Mitsubishi	Endeavor	2003 - 2010	
Mitsubishi	Endeavor	2007	315
Mitsubishi	Endeavor	2007	433
Mitsubishi	Endeavor	2011 - 2012	Alloy
Mitsubishi	Endeavor	2011 - 2012	Steel
Mitsubishi	Galant	2004 - 2010	
Mitsubishi	Galant	2007 - 2012	Alloy
Mitsubishi	Galant	2007 - 2012	Steel
Mitsubishi	i-MiEV	2012	
Mitsubishi	Lancer	2008 - 2013	
Mitsubishi	Montero	2003 - 2006	
Mitsubishi	Outlander	2007 - 2013	
Mitsubishi	Raider	2008 - 2009	
Nissan	350XV	2006	
Nissan	350Z	2003 - 2009	
Nissan	370Z	2009 - 2013	
Nissan	Altima	2006 - 2012	
Nissan	Altima Coupe	2013	
Nissan	Altima Sedan	2013	

Nissan	Armada	2005 - 2006	Alloy
Nissan	Armada	2005 - 2006	Steel
Nissan	Armada	2007 - 2012	
Nissan	Armada-LE	2008 - 2012	
Nissan	Cube	2009 - 2010	
Nissan	Cube	2011 - 2013	With Ikey
Nissan	Cube	2011 - 2013	Non Ikey
Nissan	Frontier	2003 - 2013	
Nissan	Frontier	2005 - 2008	Alloy
Nissan	Frontier	2005 - 2008	Steel
Nissan	GT-R	2009 - 2013	
Nissan	Juke	2011 - 2013	With Ikey
Nissan	Juke	2011 - 2013	Non Ikey
Nissan	Leaf	2011 - 2013	
Nissan	Maxima	2006 - 2013	
Nissan	Maxima	2007	Alloy
Nissan	Maxima	2007	Steel
Nissan	Murano	2003 - 2013	
Nissan	NV1500	2012	
Nissan	NV2500HD	2012	
Nissan	NV3500HD	2012	
Nissan	Pathfinder	2003 - 2013	
Nissan	Pathfinder	2004	Alloy
Nissan	Pathfinder	2004	Steel
Nissan	Quest	2004 - 2013	
Nissan	Quest	2005 - 2007	Alloy
Nissan	Quest	2005 - 2007	Steel
Nissan	Rogue	2008 - 2012	
Nissan	Sentra	2007 - 2008	Alloy
Nissan	Sentra	2007 - 2008	Steel
Nissan	Sentra	2009 - 2012	
Nissan	Titan	2004 - 2013	
Nissan	Titan	2005 - 2008	Alloy
Nissan	Titan	2005 - 2008	Steel
Nissan	Versa	2007 - 2008	Alloy
Nissan	Versa	2007 - 2008	Steel
Nissan	Versa	2009 - 2012	
Nissan	Versa	2013	With Ikey
Nissan	Versa	2013	Non Ikey
Nissan	Xterra	2003 - 2012	
Nissan	Xterra	2006	Alloy
Nissan	Xterra	2006	Steel
Opel	Astra H	2004 - 2009	
Opel	Insignia	2008 - Onwards	
Opel	Signum	2002 - 2009	
Opel	Vectra	2002 - 2008	
Opel	Vectra Estate	2009	
Opel	Zafira	2004 - 2009	
Peugeot	207	2006 - Onwards	
Peugeot	307	2007	
Peugeot	308	2007 - Onwards	
Peugeot	308 SW	2008 - Onwards	
Peugeot	3008	2009 - Onwards	
Peugeot	5008	2009 - Onwards	
Peugeot	407	2004 - Onwards	
Peugeot	407 SW	2004 - Onwards	

Peugeot	407 Coupe	2005 - Onwards	
Peugeot	607	2000 - 2004	
Peugeot	607 II	2004 - Onwards	
Peugeot	807	2002 - 2005	
Peugeot	807	2005 - Onwards	
Plymouth	Prowler	1997 - 2002	
Pontiac	G3	2009 - 2010	
Pontiac	G5	2008 - 2010	
Pontiac	G6	2008	Clamp In
Pontiac	G6	2008	Snap In
Pontiac	G6	2009 - 2010	
Pontiac	G8	2008 - 2009	
Pontiac	Grand Prix	2007	
Pontiac	Grand Prix	2008	Clamp In
Pontiac	Grand Prix	2008	Snap In
Pontiac	Montana	2008 - 2009	
Pontiac	Solstice	2008 - 2010	
Pontiac	Torrent	2007 - 2009	
Pontiac	Vibe	2008 - 2010	
Pontiac	Wave	2008 - 2009	
Porsche	911	2005 - 2013	
Porsche	911 Turbo	2006 - 2008	
Porsche	997 GT3	2007 - 2012	
Porsche	Boxster	2006 - 2008	315
Porsche	Boxster	2005 - 2008	433
Porsche	Boxster	2009 - 2012	
Porsche	Carerra GT	2003 - 2011	
Porsche	Cayenne	2002 - 2012	
Porsche	Cayenne	2009 - 2010	315
Porsche	Cayman	2005 - 2012	
Porsche	Panamera	2010 - 2012	315
Porsche	Panamera	2010 - 2013	433
Renault	Clio III	2005 - Onwards	
Renault	Espace IV	2002 - Onwards	
Renault	Koleos	2008 - Onwards	
Renault	Laguna II	2002 - Onwards	
Renault	Laguna III	2007 - Onwards	
Renault	Megane I	2001 - 2003	
Renault	Megane II	2003 - Onwards	
Renault	Megane III	2008 - Onwards	
Renault	Modus	2005 - Onwards	
Renault	Scenic I	2001 - 2004	
Renault	Scenic II	2004 - Onwards	
Renault	Scenic II	2006 - Onwards	
Renault	Scenic III	2009 - Onwards	
Renault	Scenic RX4	2001 - Onwards	
Renault	Vel Satis	2002 - Onwards	
Saab	9-3	2004 - 2012	
Saab	9-5	2004 - 2012	
Saab	9-4X	2012	
Saab	9-7X	2005 - 2009	
Saturn	Astra	2008 - 2010	
Saturn	Aura	2007 - 2010	
Saturn	Aura	2008	Clamp In
Saturn	Aura	2008	Snap In

Saturn	Lamda Crossover	2007 - 2008	
Saturn	Outlook	2007 - 2010	
Saturn	Sky	2008 - 2009	
Saturn	Vue	2007 - 2010	
Scion	FR-S	2013	
Scion	iQ	2012 - 2013	
Scion	TC	2006 - 2013	
Scion	XB	2007 - 2013	
Scion	XD	2008 - 2013	
Smart	Fortwo	2008	CONTI
Smart	Fortwo	2008	SCH
Smart	Fortwo	2009 - 2013	
Subaru	B9 Tribeca	2006 - 2011	
Subaru	BRZ	2013	
Subaru	Forester	2008 - 2013	
Subaru	Impreza	2008 - 2013	
Subaru	Legacy	2004 - 2013	
Subaru	Outback	2004 - 2013	
Subaru	Tribeca	2008 - 2013	
Subaru	XV Crosstrek	2013	
Suzuki	Equator	2009 - 2013	
Suzuki	Forenza	2007 - 2008	
Suzuki	Grand Vitara	2007 - 2013	
Suzuki	Kizashi	2010 - 2013	
Suzuki	Reno	2007 - 2008	
Suzuki	SX4	2007 - 2013	
Suzuki	Verona	2005 - 2006	
Suzuki	XL-7	2005 - 2011	
Toyota	4 Runner	2003 - 2013	
Toyota	Avalon	2007 - 2012	Japan Made
Toyota	Avalon	2007 - 2012	USA Made
Toyota	Avalon	2013	
Toyota	Camry	2007 - 2011	Japan Made
Toyota	Camry	2007 - 2011	USA Made
Toyota	Camry	2012 - 2013	
Toyota	Camry Hybrid	2008 - 2013	
Toyota	Corolla	2006 - 2013	Japan Made
Toyota	Corolla	2006 - 2013	USA Made
Toyota	FJ Cruiser	2008 - 2013	
Toyota	Highlander	2007 - 2013	
Toyota	Highlander Hybrid	2008 - 2012	
Toyota	Land Cruiser	2005 - 2007	
Toyota	Land Cruiser	2013	
Toyota	Matrix	2007 - 2013	Japan Made
Toyota	Matrix	2007 - 2013	USA Made
Toyota	Prius	2006 - 2013	
Toyota	Prius C	2012	
Toyota	Prius V	2012	
Toyota	RAV4	2006 - 2013	
Toyota	RAV4 EV	2012	

Toyota	Sequoia	2004 - 2008	Alloy
Toyota	Sequoia	2004 - 2008	Steel
Toyota	Sequoia	2009 - 2013	
Toyota	Sienna	2006 - 2013	
Toyota	Solara	2006 - 2011	
Toyota	Tacoma	2005 - 2013	Alloy
Toyota	Tacoma	2005 - 2013	Steel
Toyota	Tundra	2005 - 2013	Alloy
Toyota	Tundra	2005 - 2013	Steel
Toyota	Tundra	2006	Alloy PAC
Toyota	Tundra	2006	Alloy TRW
Toyota	Tundra	2006	Steel PAC
Toyota	Tundra	2006	Steel TRW
Toyota	Venza	2009 - 2013	
Toyota	Yaris	2007 - 2013	
Toyota	Land Cruiser	2008 - 2011	
Volkswagen	Beetle	2007 - 2011	
Volkswagen	CC	2009 - 2013	
Volkswagen	EOS	2007 - 2013	
Volkswagen	GLI	2008 - 2011	
Volkswagen	Golf	2010 - 2011	
Volkswagen	GTI	2006 - 2012	
Volkswagen	Jetta	2006 - 2012	
Volkswagen	Passat	2006 - 2011	
Volkswagen	Phaeton	2003 - 2007	315
Volkswagen	Phaeton	2003 - 2007	433
Volkswagen	Phaeton	2008 - 2011	
Volkswagen	R32	2008 - 2011	
Volkswagen	Rabbit	2006 - 2009	
Volkswagen	Routan	2009 - 2012	
Volkswagen	Tiguan	2009 - 2011	
Volkswagen	Touareg	2002 - 2006	
Volkswagen	Touareg 2	2007 - 2013	
Volvo	C30	2007 - 2013	
Volvo	C70	2007 - 2013	
Volvo	S40	2007 - 2012	
Volvo	S60	2004 - 2013	
Volvo	S60	2008	Clamp In
Volvo	S60	2008	Snap In
Volvo	S80	2004 - 2013	
Volvo	V50	2007 - 2012	
Volvo	V70	2004 - 2010	
Volvo	XC60	2009 - 2013	
Volvo	XC70	2004 - 2013	
Volvo	XC90	2005 - 2006	315
Volvo	XC90	2007 - 2013	US 315
Volvo	XC90	2008 - 2012	Eu 433

Autel TS401 01-06-15

Make	Model	Year
ALFA ROMEO	159	2005 - 11
ALFA ROMEO	4C	2013 - 2021
ALFA ROMEO	Alfa 8C	2007-09
ALFA ROMEO	Brera	2005 - 10
ALFA ROMEO	MiTo	08/13 - 06/2016
ALFA ROMEO	MiTo	2008 - 07/13
ALFA ROMEO	MiTo(LCV)	2014 - EOL
ALFA ROMEO	SPIDER	2006 - 10
Alpina	Alpina 3	01/2013 - 2017
Alpina	Alpina 3	03/2007 - 09/2009
Alpina	Alpina 3	09/2009 - 12/2012
Alpina	Alpina 5	01/2010 - 2017
Alpina	Alpina 6	03/2006 - 11/2010
Alpina	Alpina 6	12/2010 - 2018
Alpina	Alpina 7	09/2010 - EOL
Alpina	XD3	09/2010 - EOL
ASTON MARTIN	DB9	2004 - EOL
ASTON MARTIN	DBS	2007 - EOL
ASTON MARTIN	Rapide	2010 - EOL
ASTON MARTIN	V8/Vantage/Volante	2012 - 06/2014
ASTON MARTIN	Vanquish	2012 - EOL
AUDI	A3	06/2012 - 2014
AUDI	A4	2004 - 08
AUDI	A5	12/2006 - 09/2016
AUDI	A6 Allroad	2000 - 05
AUDI	A6 Allroad	2006 - 09
AUDI	A6 Allroad	2009 - EOL
AUDI	A6 Quattro	01/2011 - EOL
AUDI	A6 Quattro	06/2009 - 03/2011
AUDI	A6 Quattro	2004 -09
AUDI	A7	09/2010 - 09/2017
AUDI	A8	11/2009 - 09/2016(Series 3)
AUDI	A8	1999 - 2002
AUDI	A8	2002 - 12/2010
AUDI	Q5	09/2008 - 12/2015
AUDI	Q7	06/2014 - 2021
AUDI	Q7	2005 - 05/2009
AUDI	Q7	2009 - 05/2014
AUDI	R8	06/2009 - 03/2015
AUDI	R8	2007 - 06/2009
AUDI	RS4	2006 - 2008
AUDI	RS6	2000 - 2010
AUDI	RS6	2013 - 2014
AUDI	RS7	2013 - 2014
AUDI	S4	2004 - 07
AUDI	S6	2004 - 09
AUDI	S6	2009 - 2011
AUDI	S8	1999 - 2002
AUDI	S8	2002 - 2008

Autel TS401 01-06-15

AUDI	S8(D4)	2009 - 2014
AUDI	TT	02/2014 - 2020
BENTLEY	Azure	2007 - 2020
BENTLEY	Continental Flying Spur	2005 - EOL
BENTLEY	Continental GT	06/2005 - EOL
BENTLEY	Continental GT	2003 - 05/2005
BENTLEY	Mulsanne	2011 - 2018
BMW	1 Series	09/2010 - 2013
BMW	1 Series	2006 - 08/2010
BMW	1 Series(F20/F45)	07/2011 - 2018
BMW	2 Series(F22)	11/2013 - EOL
BMW	3 Series	03/1999 - 12/2004
BMW	3 Series	09/2009 - 09/2011
BMW	3 Series	2006 - 08/2009
BMW	3 Series(F classic)	11/2011 - 2018
BMW	4 Series	10/2013 - EOL
BMW	5 Series	03/2014 - 12/2014
BMW	5 Series	09/2010 - 02/2014
BMW	5 Series	1998 - 03
BMW	5 Series	2006 - 08/2010
BMW	6 Series	03/2014 - 12/2014
BMW	6 Series	2006 - 09
BMW	6 Series	2010 - 02/2014
BMW	7 Series	1998 - 05
BMW	7 Series(E classic)	2006 - 2010
BMW	7 Series(F classic)	03/2014 - 12/2014
BMW	7 Series(F classic)	09/2010 - 02/2014
BMW	7 Series(F classic)	2008 - 08/2010
BMW	i3	09/2013 - 2020
BMW	i8	01/2014 - 2020
BMW	X1	03/2014 - 12/2014
BMW	X1	10/2009 - 02/2014
BMW	X3	03/2014 - 12/2014
BMW	X3	11/2010 - 02/2014
BMW	X3	2003 - 08/2010
BMW	X4(F26)	04/2014-12/2014
BMW	X5(E53)	1999-09/2006
BMW	X5(E70)	01/2011-06/2013
BMW	X5(E70)	11/2006-12/2010
BMW	X5(F classic)	07/2013 - 2020
BMW	X6	12/2007 - 10/2011
BMW	X6	12/2011 - 07/2014
BMW	Z4	03/2006 - 08/2010
BMW	Z4	03/2014 - 09/2016
BMW	Z4	09/2010 - 02/2014
Buick	Allure(US)	2007
Buick	Allure(US)	2008
Buick	Allure(US)	2009
Buick	Allure(US)	2010
Buick	Allure(US)	2011

Autel TS401 01-06-15

Buick	Enclave(US)	2008
Buick	Enclave(US)	2009-14
Buick	Encore(US)	2013
Buick	LaCrosse(US)	2007-08
Buick	LaCrosse(US)	2009
Buick	LaCrosse(US)	2010
Buick	LaCrosse(US)	2011
Buick	LaCrosse(US)	2012
Buick	LaCrosse(US)	2013
Buick	LaCrosse(US)	2014
Buick	LeSabre(US)	2007
Buick	Lucerne(US)	2007
Buick	Lucerne(US)	2008
Buick	Lucerne(US)	2009
Buick	Lucerne(US)	2010
Buick	Lucerne(US)	2011
BUICK	Parc avenue	1997 - 2005
BUICK	Rainier	2007
Buick	Rainier(US)	2007
Buick	Rainier(US)	2006(315)
Buick	Regal(US)	2011
Buick	Regal(US)	2012
Buick	Regal(US)	2013-14
Buick	Verano(US)	2012-14
CADILLAC	ATS	2012 - 2013
CADILLAC	ATS	2014
Cadillac	ATS(US)	2013
Cadillac	ATS(US)	2014
CADILLAC	CTS	2006
CADILLAC	CTS	2007
CADILLAC	CTS	2008 - 2014
Cadillac	CTS(US)	2004-05
Cadillac	CTS(US)	2006
Cadillac	CTS(US)	2007
Cadillac	CTS(US)	2008
Cadillac	CTS(US)	2009-11
Cadillac	CTS(US)	2012-13
Cadillac	CTS-V(US)	2009-13
Cadillac	Deville(US)	2001-03
Cadillac	Deville(US)	2004
Cadillac	Deville(US)	2005
CADILLAC	DTS	2005 - 2011
Cadillac	DTS(US)	2006
Cadillac	DTS(US)	2007
Cadillac	DTS(US)	2008
Cadillac	DTS(US)	2009-11
CADILLAC	Escalade	2005 - 2006
CADILLAC	Escalade	2007 - 2008
CADILLAC	Escalade	2009 - 2011
CADILLAC	Escalade	2012 - EOL

Autel TS401 01-06-15

Cadillac	Escalade(US)	2004
Cadillac	Escalade(US)	2005-06
Cadillac	Escalade(US)	2007(clampin)
Cadillac	Escalade(US)	2007(snapin)
Cadillac	Escalade(US)	2008
Cadillac	Escalade(US)	2009-11
Cadillac	Escalade(US)	2012-14
Cadillac	Seville(US)	2001-03
Cadillac	Seville(US)	2004
CADILLAC	SRX	2005 - 2014
Cadillac	SRX(US)	2004-06
Cadillac	SRX(US)	2007-08
Cadillac	SRX(US)	2009
Cadillac	SRX(US)	2010-11
Cadillac	SRX(US)	2012-14
CADILLAC	STS	2005 - 2011
Cadillac	STS(US)	2005-07
Cadillac	STS(US)	2008
Cadillac	STS(US)	2009(clamp in)
Cadillac	STS(US)	2010-11
Cadillac	STS(US)	2009(snap in)
CADILLAC	XLR	2004 - 09
Cadillac	XLR(US)	2004-05
Cadillac	XLR(US)	2006-09
Cadillac	XLR(US)	2010-11
CADILLAC	XTS	05/2012 - 03/2018
Cadillac	XTS(US)	2013-14
Chevrolet	Avalanche(US)	2004
Chevrolet	Avalanche(US)	2005-06
Chevrolet	Avalanche(US)	2007(clamp in)
Chevrolet	Avalanche(US)	2007(snap in)
Chevrolet	Avalanche(US)	2008
Chevrolet	Avalanche(US)	2009-11
Chevrolet	Avalanche(US)	2012-13
CHEVROLET	Aveo	11/2011 - 2016
Chevrolet	Aveo(US)	2007
Chevrolet	Aveo(US)	2008-11
CHEVROLET	Camaro	2009 - 2014
Chevrolet	Camaro ZL1(US)	2012-14
Chevrolet	Camaro(US)	2010
Chevrolet	Camaro(US)	2011
Chevrolet	Camaro(US)	2012-13
Chevrolet	Camaro(US)	2014
Chevrolet	Caprice	2013-14
CHEVROLET	Captiva	2006 - 2014
Chevrolet	Captiva sport(US)	2012-13
CHEVROLET	Cobalt	02/2013 - EOL
Chevrolet	Cobalt(US)	2008(clamp in)
Chevrolet	Cobalt(US)	2008(snap in)
Chevrolet	Cobalt(US)	2009(clamp in)

Autel TS401 01-06-15

Chevrolet	Cobalt(US)	2009(snap in)
Chevrolet	Cobalt(US)	2010
Chevrolet	Cobalt(US)	2011-12
CHEVROLET	Colorado	2011 - 2014
CHEVROLET	Colorado(LCV)	2013 - 2014
Chevrolet	Colorado(US)	2007-10
Chevrolet	Colorado(US)	2011
Chevrolet	Colorado(US)	2012
CHEVROLET	Corvette	01/2010 - 01/2013
CHEVROLET	Corvette	07/2004 - 01/2010
Chevrolet	Corvette C5(US)	2001-02
Chevrolet	Corvette C5(US)	2003-04
Chevrolet	Corvette C6(US)	2005-09
Chevrolet	Corvette Z06(US)	2001-02
Chevrolet	Corvette Z06(US)	2003-04
Chevrolet	Corvette Z06(US)	2005-09
Chevrolet	Corvette Z06(US)	2010-11
Chevrolet	Corvette Z06(US)	2012
Chevrolet	Corvette(US)	1997-00
Chevrolet	Corvette(US)	2001-02
Chevrolet	Corvette(US)	2003-04
Chevrolet	Corvette(US)	2005
Chevrolet	Corvette(US)	2006-09
Chevrolet	Corvette(US)	2010-11
Chevrolet	Corvette(US)	2012-13
CHEVROLET	Cruze	10/2008 - 12/2014
Chevrolet	Cruze(US)	2011
Chevrolet	Cruze(US)	2012-14
Chevrolet	Equinox(US)	2007
Chevrolet	Equinox(US)	2008
Chevrolet	Equinox(US)	2009
Chevrolet	Equinox(US)	2010-11
Chevrolet	Equinox(US)	2012-14
Chevrolet	Express Series(US)	2008
Chevrolet	Express Series(US)	2009
Chevrolet	Express Series(US)	2010-11
Chevrolet	Express Series(US)	2012-14
CHEVROLET	Express(PC)	07/2002 - 12/2014
Chevrolet	G Series(US)	2008-11
Chevrolet	HHR(US)	2008
Chevrolet	HHR(US)	2009(clamp in)
Chevrolet	HHR(US)	2009(snap in)
Chevrolet	HHR(US)	2010-11
Chevrolet	Impala(US)	2006
Chevrolet	Impala(US)	2007(clamp in)
Chevrolet	Impala(US)	2007(snap in)
Chevrolet	Impala(US)	2008
Chevrolet	Impala(US)	2009-11
Chevrolet	Impala(US)	2012-13
CHEVROLET	Malibu	07/2011 - 12/2017

Autel TS401 01-06-15

Chevrolet	Malibu(US)	2008(clamp in)
Chevrolet	Malibu(US)	2008(snap in)
Chevrolet	Malibu(US)	2009
Chevrolet	Malibu(US)	2010-11
Chevrolet	Malibu(US)	2012-13
Chevrolet	Malibu(US)	2014
CHEVROLET	Matiz	06/2014 - EOL
Chevrolet	Monte Carlo(US)	2006
Chevrolet	Monte Carlo(US)	2007(clamp in)
Chevrolet	Monte Carlo(US)	2007(snap in)
CHEVROLET	Orlando	09/2010 - 12/2017
Chevrolet	ORLANDO(US)	2012
Chevrolet	Sonic(US)	2012-14
CHEVROLET	Spark	07/2009 - 06/2015
Chevrolet	Spark(US)	2013-14
CHEVROLET	Suburban	2006 - 08
Chevrolet	Suburban(US)	2004
Chevrolet	Suburban(US)	2005-06
Chevrolet	Suburban(US)	2007(snap in)
Chevrolet	Suburban(US)	2007(TRW clamp in)
Chevrolet	Suburban(US)	2008
Chevrolet	Suburban(US)	2009-13
Chevrolet	Suburban(US)	2014
Chevrolet	Tahoe(US)	2004
Chevrolet	Tahoe(US)	2005-06
Chevrolet	Tahoe(US)	2007(snap in)
Chevrolet	Tahoe(US)	2007(TRW clamp in)
Chevrolet	Tahoe(US)	2008
Chevrolet	Tahoe(US)	2009-13
Chevrolet	Tahoe(US)	2014
CHEVROLET	Trailblazer	2007 - 08
Chevrolet	Trailblazer(US)	2006
Chevrolet	Trailblazer(US)	2007-09
CHEVROLET	Trax	03/2012 - 12/2017
Chevrolet	Uplander(US)	2008-09
Chevrolet	Van(US)	2008+
CHEVROLET	Volt	11/2010 - 05/2015
Chevrolet	Volt(US)	2010
Chevrolet	Volt(US)	2011
Chevrolet	Volt(US)	2012-13
Chevrolet	Volt(US)	2014
Chrysler	200(US)	2011-14
Chrysler	200(US)	2011-14
CHRYSLER	300	2009 - 10
CHRYSLER	300	2011 - 2014
Chrysler	300 SRT(US)	2010-11
Chrysler	300 SRT(US)	2010-11
Chrysler	300(US)	2005-06
Chrysler	300(US)	2005-06
Chrysler	300(US)	2007(315)

Autel TS401 01-06-15

Chrysler	300(US)	2007(315)
Chrysler	300(US)	2007(433)
Chrysler	300(US)	2007(433)
Chrysler	300(US)	2008
Chrysler	300(US)	2008
Chrysler	300(US)	2009
Chrysler	300(US)	2009
Chrysler	300(US)	2010
Chrysler	300(US)	2010
Chrysler	300(US)	2011-14
Chrysler	300(US)	2011-14
CHRYSLER	300C	2005 - 2010
CHRYSLER	300C	2011 - 2014
Chrysler	300M(US)	2002-04
Chrysler	300M(US)	2002-04
Chrysler	Aspen(US)	2008-11
Chrysler	Aspen(US)	2008-11
Chrysler	Aspen(US)	2007
Chrysler	Aspen(US)	2007
Chrysler	Concorde(US)	2002-04
Chrysler	Concorde(US)	2002-04
Chrysler	Crossfire(US)	2004
Chrysler	Crossfire(US)	2004
Chrysler	Crossfire(US)	2005+(CONTI)
Chrysler	Crossfire(US)	2005+(CONTI)
Chrysler	Crossfire(US)	2005-11(SCH)
Chrysler	Crossfire(US)	2005-11(SCH)
CHRYSLER	Delta	2011 - 2014
CHRYSLER	Grand Voyager	2007 - 10
CHRYSLER	Grand Voyager	2011 - 17
Chrysler	Intrepid(US)	2002-04
Chrysler	Intrepid(US)	2002-04
CHRYSLER	Pacifica	2005 - 2006
Chrysler	Pacifica(US)	2003
Chrysler	Pacifica(US)	2003
Chrysler	Pacifica(US)	2004(CONTI)
Chrysler	Pacifica(US)	2005
Chrysler	Pacifica(US)	2005
Chrysler	Pacifica(US)	2006-08
Chrysler	Pacifica(US)	2006-08
Chrysler	Pacifica(US)	2004(CONTI)
Chrysler	Pacifica(US)	2004(SCH)
Chrysler	Pacifica(US)	2004(SCH)
Chrysler	Prowler(US)	2002
Chrysler	Prowler(US)	2002
Chrysler	PT Cruiser(US)	2008-10
Chrysler	PT Cruiser(US)	2008-10
CHRYSLER	Sebring	06/2006 - 12/2014
CHRYSLER	Sebring	2005 -05/2006
Chrysler	Sebring(US)	2007

Autel TS401 01-06-15

Chrysler	Sebring(US)	2007
Chrysler	Sebring(US)	2008-09(315)
Chrysler	Sebring(US)	2008-09(315)
Chrysler	Sebring(US)	2008-09(433)
Chrysler	Sebring(US)	2008-09(433)
Chrysler	Sebring(US)	2010-12
Chrysler	Sebring(US)	2010-12
Chrysler	Town & Country(US)	2002-03
Chrysler	Town & Country(US)	2002-03
Chrysler	Town & Country(US)	2004-05
Chrysler	Town & Country(US)	2004-05
Chrysler	Town & Country(US)	2006-07
Chrysler	Town & Country(US)	2006-07
Chrysler	Town & Country(US)	2009-10
Chrysler	Town & Country(US)	2009-10
Chrysler	Town & Country(US)	2011-14
Chrysler	Town & Country(US)	2011-14
Chrysler	Town & Country(US)	2008(315)
Chrysler	Town & Country(US)	2008(315)
Chrysler	Town & Country(US)	2008(433)
Chrysler	Town & Country(US)	2008(433)
CHRYSLER	Town&Country	2007 - 2011
CHRYSLER	Town&Country	2011 - 2014
CHRYSLER	Viper	2012 - 2014
CHRYSLER	Voyager	2007 - 10
CHRYSLER	Voyager	2011 - 17
Chrysler	Voyager(US)	2002-03
Chrysler	Voyager(US)	2002-03
CHRYSLER	Ypsilon	2011 - 18
CITROEN	Berlingo	05/2008 - 09/2013
CITROEN	Berlingo	10/2013 - 2014
CITROEN	Berlingo(LCV)	2008 - 2013
CITROEN	C3	2013 - 2014
CITROEN	C4	10/2010 - 09/2013
CITROEN	C4	10/2013 - 2015
CITROEN	C4	2004 - 09/2010
CITROEN	C5	08/2004 - 09/2013
CITROEN	C5	09/2013 - 2016
CITROEN	C5	2001 - 07/2004
CITROEN	C5(LCV)	10/2007 - EOL
CITROEN	C6	2005 - 2012
CITROEN	C8	10/2005 - 06/2014
CITROEN	C8	2002 - 09/2005
CITROEN	C-Cactus	2014 - 2020
CITROEN	C-Elysee	2012 - 2019
CITROEN	DS3	2009 - 2017
CITROEN	DS4	01/2014 - 2017
CITROEN	DS4	2010 - 01/2014
CITROEN	DS4(LCV)	10/2010 - EOL
CITROEN	DS5	01/2014 - 2018

Autel TS401 01-06-15

CITROEN	DS5	2011 - 01/2014
CITROEN	DS5(LCV)	06/2011 - EOL
CITROEN	Jumper	06/2014 - 2015
CITROEN	Jumpy	06/2014 - 2015
CITROEN	Jumpy	2011 - 05/2014
CITROEN	Nemo	2007 - 2015
CITROEN	Picasso C4	2006 - 2013
Dacia	Duster	02/2010 - 09/2017
Dacia	Lodgy	01/2012 - 12/2017
Dacia	Logan	11/2012 - 12/2019
Dacia	Logan MCV	04/2013 - 09/2020
Dacia	Sandero	10/2012 - 09/2019
Dacia	Sandero Pro	10/2012 - EOL
Daewo	Gentra	08/2013 - EOL
Daewo	Nexia	06/2014 - EOL
DODGE	AVENGER	2006 - 2013
Dodge	Avenger(US)	2007-14
Dodge	Avenger(US)	2007-14
Dodge	C/V(US)	2012
Dodge	C/V(US)	2012
DODGE	Caliber	2007 - 2011
Dodge	Caliber(US)	2007
Dodge	Caliber(US)	2007
Dodge	Caliber(US)	2008-09
Dodge	Caliber(US)	2008-09
Dodge	Caliber(US)	2010
Dodge	Caliber(US)	2010
Dodge	Caliber(US)	2011-12
Dodge	Caliber(US)	2011-12
DODGE	Caravan	2011 - 2014
Dodge	Caravan(US)	2002-03
Dodge	Caravan(US)	2002-03
Dodge	Caravan(US)	2004-05
Dodge	Caravan(US)	2004-05
Dodge	Caravan(US)	2006-07
Dodge	Caravan(US)	2006-07
DODGE	Challenger	2008 - 09
DODGE	Challenger	2010 - 2017
Dodge	Challenger(US)	2008
Dodge	Challenger(US)	2011-14
Dodge	Challenger(US)	2011-14
Dodge	Challenger(US)	2008
Dodge	Challenger(US)	2009
Dodge	Challenger(US)	2009
Dodge	Challenger(US)	2010
Dodge	Challenger(US)	2010
DODGE	Charger	2009
DODGE	Charger	2010 - 2016
Dodge	Charger SRT(US)	2009
Dodge	Charger SRT(US)	2009

Autel TS401 01-06-15

Dodge	Charger SRT(US)	2010
Dodge	Charger SRT(US)	2010
Dodge	Charger SRT(US)	2011-12
Dodge	Charger SRT(US)	2011-12
Dodge	Charger(US)	2005-06
Dodge	Charger(US)	2005-06
Dodge	Charger(US)	2007
Dodge	Charger(US)	2007
Dodge	Charger(US)	2008
Dodge	Charger(US)	2008
Dodge	Charger(US)	2009
Dodge	Charger(US)	2009
Dodge	Charger(US)	2010
Dodge	Charger(US)	2010
Dodge	Charger(US)	2011-14
Dodge	Charger(US)	2011-14
DODGE	Dakota	2009 - 2014
Dodge	Dakota(US)	2008-10
Dodge	Dakota(US)	2008-10
Dodge	Dakota(US)	2011
Dodge	Dakota(US)	2011
Dodge	Dart(US)	2013-14
Dodge	Dart(US)	2013-14
DODGE	Durango	2011 - 2016
Dodge	Durango(US)	2007-08
Dodge	Durango(US)	2007-08
Dodge	Durango(US)	2011-14
Dodge	Durango(US)	2011-14
Dodge	Durango(US)	2009-10
Dodge	Durango(US)	2009-10
Dodge	Grand Caravan(US)	2002-03
Dodge	Grand Caravan(US)	2002-03
Dodge	Grand Caravan(US)	2004-05
Dodge	Grand Caravan(US)	2004-05
Dodge	Grand Caravan(US)	2006
Dodge	Grand Caravan(US)	2006
Dodge	Grand Caravan(US)	2007
Dodge	Grand Caravan(US)	2007
Dodge	Grand Caravan(US)	2008-10
Dodge	Grand Caravan(US)	2008-10
Dodge	Grand Caravan(US)	2011-14
Dodge	Grand Caravan(US)	2011-14
DODGE	Grand carvan	2011 - 2014
Dodge	Intrepid(US)	2002-04
Dodge	Intrepid(US)	2002-04
DODGE	Journey	2010
DODGE	Journey	2011 - 09/2015
Dodge	Journey(US)	2009
Dodge	Journey(US)	2009
Dodge	Journey(US)	2010

Autel TS401 01-06-15

Dodge	Journey(US)	2010
Dodge	Journey(US)	2011-14
Dodge	Journey(US)	2011-14
Dodge	Magnum(US)	2005-06
Dodge	Magnum(US)	2005-06
Dodge	Magnum(US)	2007
Dodge	Magnum(US)	2007
Dodge	Magnum(US)	2008
Dodge	Magnum(US)	2008
Dodge	Magnum(US)	2009
Dodge	Magnum(US)	2009
Dodge	Magnum(US)	2010
Dodge	Magnum(US)	2010
Dodge	Magnum(US)	2011
Dodge	Magnum(US)	2011
DODGE	Nitro	2007 - 2011
Dodge	Nitro(US)	2007-08
Dodge	Nitro(US)	2007-08
Dodge	Nitro(US)	2009-11
Dodge	Nitro(US)	2009-11
Dodge	Nitro(US)	2012
Dodge	Nitro(US)	2012
Dodge	Raider(US)	2009
Dodge	Raider(US)	2009
DODGE	Ram	2010 - 2013
DODGE	Ram	2014
Dodge	Ram 250(US)	2009
Dodge	Ram 250(US)	2009
Dodge	Ram(US)	2008
Dodge	Ram(US)	2008
Dodge	Ram(US)	2010
Dodge	Ram(US)	2010
Dodge	Ram(US)	2011-14
Dodge	Ram(US)	2011-14
Dodge	Ram(US)	2009(315)
Dodge	Ram(US)	2009(315)
Dodge	Ram(US)	2009(433)
Dodge	Ram(US)	2009(433)
Dodge	Sprinter(US)	2007-10
Dodge	Sprinter(US)	2007-10
Dodge	Stratus(US)	2007
Dodge	Stratus(US)	2007
DODGE	Viper	2013 - 15
Dodge	Viper(US)	2003-11
Dodge	Viper(US)	2003-11
FERRARI	458 Italia	2009 - 10/2015
FERRARI	550 Maranello Evoluzione	2002 - 2014
FERRARI	575 M-Maranello	2002 - 06
FERRARI	599 GTB	2006 - 2012
FERRARI	612 Scaglietti	2004 - 2010

Autel TS401 01-06-15

FERRARI	California	10/2008 - 10/2014
FERRARI	Enzo	2003 - 04
FERRARI	F12	2012 - 2014
FERRARI	F430	07/2007 - 10/2009
FERRARI	F430	2005 - 06/2007
FERRARI	FF	2011 - 2018
FERRARI	FXX	2005 - 06
FIAT	500	2007 - 2015
FIAT	500L	2012 - 2014
FIAT	Bravo	2007 - 14
FIAT	Croma	2005 - 2014
FIAT	Doblo	2012 - 2014
FIAT	Ducato	2014 - 2015
FIAT	Freemont	2011 - 2014
FIAT	Grande Punto	2005 - 2014
FIAT	Linea	2007 - 2016
FIAT	Punto	2005 - 2015
FIAT	Punto Evo	2009 - 2012
FIAT	Qubo	2007 - EOL
FIAT	Scudo	2006 - 2015
FIAT	Strada	2012 - 2014
FIAT	Ulysse	2002 - 09/2005
FIAT	Ulysse Nuovo 2F	10/2005 - 10
FORD	B-MAX	06/2014 - 01/2019
FORD	C-MAX	04/2014 - 2016
Ford	C-Max(US)	2012-14
Ford	Crown Victoria(US)	2006
Ford	Crown Victoria(US)	2007
Ford	Crown Victoria(US)	2008
Ford	Crown Victoria(US)	2009
Ford	Crown Victoria(US)	2010
Ford	Crown Victoria(US)	2011
Ford	E-150(US)	2007
Ford	E-150(US)	2008
Ford	E-150(US)	2009
Ford	E-150(US)	2010-14
Ford	E-250(US)	2007
Ford	E-250(US)	2008
Ford	E-250(US)	2009
Ford	E-250(US)	2010-14
Ford	E-350 SD(US)	2007
Ford	E-350 SD(US)	2008
Ford	E-350 SD(US)	2009
Ford	E-350 SD(US)	2010-14
FORD	Econoline	2006 - EOL
FORD	Ecosport	10/2014 - 2015
FORD	Ecosport	2012 - 09/2014
Ford	Edge(US)	2007-10(W Chrome rims)
Ford	Edge(US)	2011
Ford	Edge(US)	2012-14

Autel TS401 01-06-15

Ford	Edge(US)	2007-10 (W/O Chrome)
FORD	Escape	01/2009 - 04/2012
FORD	Escape	05/2012 - 2017
Ford	Escape(US)	2005
Ford	Escape(US)	2006
Ford	Escape(US)	2007
Ford	Escape(US)	2008
Ford	Escape(US)	2009
Ford	Escape(US)	2010
Ford	Escape(US)	2011
Ford	Escape(US)	2012-14
Ford	Expedition(US)	2003
Ford	Expedition(US)	2004
Ford	Expedition(US)	2005-06
Ford	Expedition(US)	2007 W Chrome rims
Ford	Expedition(US)	2008 W Chrome rims
Ford	Expedition(US)	2009 W Chrome rims
Ford	Expedition(US)	2010 W Chrome rims
Ford	Expedition(US)	2011
Ford	Expedition(US)	2012-14
Ford	Expedition(US)	2007 W/O Chrome
Ford	Expedition(US)	2008 W/O Chrome
Ford	Expedition(US)	2009 W/O Chrome
Ford	Expedition(US)	2010 W/O Chrome
FORD	Explorer	2011 - 2017
Ford	Explorer Sport Trac(US)	2006
Ford	Explorer Sport Trac(US)	2007
Ford	Explorer Sport Trac(US)	2008
Ford	Explorer Sport Trac(US)	2009
Ford	Explorer Sport Trac(US)	2010
Ford	Explorer(US)	2002
Ford	Explorer(US)	2003
Ford	Explorer(US)	2004
Ford	Explorer(US)	2005
Ford	Explorer(US)	2006
Ford	Explorer(US)	2007
Ford	Explorer(US)	2008
Ford	Explorer(US)	2009
Ford	Explorer(US)	2010
Ford	Explorer(US)	2011
Ford	Explorer(US)	2012-14
Ford	F-150(US)	2007-08
Ford	F-150(US)	2009-10
Ford	F-150(US)	2011
Ford	F-150(US)	2012-14
Ford	F-250 SD(US)	2008
Ford	F-250 SD(US)	2009
Ford	F-250 SD(US)	2010-11
Ford	F-250 SD(US)	2012-14
Ford	F-350 SD(US)	2008

Autel TS401 01-06-15

Ford	F-350 SD(US)	2009
Ford	F-350 SD(US)	2010-11
Ford	F-350 SD(US)	2012-14
Ford	F-450/550(US)	2008-09
Ford	F-450/550(US)	2010-11
Ford	F-450/550(US)	2012-14
FORD	Fiesta	2014 - 2015
Ford	Fiesta(US)	2011-14
Ford	Five Hundred(US)	2006-07
Ford	Five Hundred(US)	2008-09
Ford	Flex(US)	2009-10
Ford	Flex(US)	2011
Ford	Flex(US)	2012-14
FORD	Focus	12/2010 - 2017
Ford	Focus(US)	2007
Ford	Focus(US)	2008-09
Ford	Focus(US)	2010-11
Ford	Focus(US)	2012-14
Ford	Freestar(US)	2004
Ford	Freestar(US)	2005
Ford	Freestar(US)	2006-07
FORD	F-Series	2008 - EOL
Ford	Fusion(US)	2007
Ford	Fusion(US)	2008
Ford	Fusion(US)	2009
Ford	Fusion(US)	2010-11
Ford	Fusion(US)	2012-14
FORD	Galaxy	2006 - 2014
Ford	Grand Marquis(US)	2007
Ford	Grand Marquis(US)	2008
Ford	Grand Marquis(US)	2009-11
FORD	Ka	2008 - 2015
FORD	Kuga	11/2012 - 2019
FORD	Mondeo	10/2014 - 2019
FORD	Mondeo IV	2007 - 09/2014
FORD	Mustang	05/2014 - 2020
FORD	Mustang	2004 - 04/2014
Ford	Mustang(US)	2007
Ford	Mustang(US)	2008
Ford	Mustang(US)	2009
Ford	Mustang(US)	2010-11
Ford	Mustang(US)	2012-14
FORD	Navigator	2011 - 2014
Ford	Ranger(US)	2007
Ford	Ranger(US)	2008-11
Ford	Shelby GT(US)	2012
FORD	S-Max	2006 - 2014
Ford	Taurus X(US)	2008-09
Ford	Taurus(US)	2008-10
Ford	Taurus(US)	2011

Autel TS401 01-06-15

Ford	Taurus(US)	2012-14
FORD	Transit	2013 - 2021
Ford	Transit(US)	2010-11
Ford	Transit(US)	2012-14
GMC	Acadia(US)	2007-08
GMC	Acadia(US)	2009-14
GMC	Canyon(US)	2007-10
GMC	Canyon(US)	2011-12
GMC	Envoy(US)	2005
GMC	Envoy(US)	2006
GMC	Envoy(US)	2007(1820)
GMC	Envoy(US)	2007(SCH clamp in)
GMC	Envoy(US)	2007(TRW clamp in)
GMC	Envoy(US)	2008-09(1820)
GMC	Envoy(US)	2008-09(snap in)
GMC	Savana(US)	2008-09(CONTI)
GMC	Savana(US)	2010-14
GMC	Sierra	04/2013 - 2019
GMC	Sierra All(US)	2004
GMC	Sierra All(US)	2005-06
GMC	Sierra All(US)	2007(SCH clamp in)
GMC	Sierra All(US)	2007(snap in)
GMC	Sierra All(US)	2007(TRW clamp in)
GMC	Sierra All(US)	2008
GMC	Sierra All(US)	2009-13
GMC	Sierra All(US)	2014
GMC	Terrain(US)	2010-2011
GMC	Terrain(US)	2012-14
GMC	Yukon	2005 - 2013
GMC	Yukon All(US)	2004
GMC	Yukon All(US)	2005-06
GMC	Yukon All(US)	2007(snap in)
GMC	Yukon All(US)	2007(TRW clamp in)
GMC	Yukon All(US)	2008
GMC	Yukon All(US)	2009-13
GMC	Yukon All(US)	2014
HOLDEN	WM Caprice	2007 - 12
HONDA	Accord	2014
HONDA	Civic	2014 - EOL
HONDA	Jazz	2014 - EOL
HSV	Gange	2007 - 12
HSV	GTS	2007 - 12
HSV	GXP	2010
HSV	R8	2007 - 12
HSV	Senator	2007 - 12
HUMMER	H2	2002 - 2008
HUMMER	H3	2005 - 06
HUMMER	H3	2007 - 12
Hummer	H2(US)	2008
Hummer	H2(US)	2008

Autel TS401 01-06-15

Hummer	H2(US)	2009-10
Hummer	H2(US)	2009-10
Hummer	H3(US)	2006
Hummer	H3(US)	2006
Hummer	H3(US)	2007-10
Hummer	H3(US)	2007-10
Hummer	H3T(US)	2006-10
Hummer	H3T(US)	2006-10
HYUNDAI	Azera	2011 - 2014
HYUNDAI	Elantra	2014 - EOL
HYUNDAI	Equus	2014 - EOL
HYUNDAI	Genesis	2014 - EOL
HYUNDAI	Grandeur	2014 - EOL
HYUNDAI	i10	2011 - EOL
HYUNDAI	i10(LCV)	2014 - EOL
HYUNDAI	i20	2008 - 2014
HYUNDAI	i30	2007 - 01/2013
HYUNDAI	i30 CW	2009 ->
HYUNDAI	i30 GD	2011 - EOL
HYUNDAI	i40	2011 - EOL
HYUNDAI	ix20	09/2010 - 2014
HYUNDAI	ix20	2008 - 09/2010
HYUNDAI	ix35	2010-2012(Lo Line)
HYUNDAI	ix35	2013 - 14(Hi Line)
HYUNDAI	ix35	2013 - 14(Lo Line)
HYUNDAI	ix55	2006 - 2008
HYUNDAI	ix55	2009 - 2013
HYUNDAI	ix55	2014 - EOL
HYUNDAI	Santa Fe CM	2005 - 2009
HYUNDAI	Santa Fe CM	2010 - 2012
HYUNDAI	Santa Fe DM	2012 - EOL
HYUNDAI	Santa Fe(LCV)	03/2014 - EOL
HYUNDAI	Solaris	2014 ->
HYUNDAI	Sonata	2014 ->
HYUNDAI	Tucson	2006 - 2010
HYUNDAI	Veloster	2011 - 2013
HYUNDAI	Veloster	2014
INFINITI	EX	2008 - 2014
INFINITI	FX	2008 - 2014
INFINITI	G37 Coupe	2008 - 2014
INFINITI	G37 Sedan	2008 - 2013
INFINITI	M30D	2010 - 11
INFINITI	M35H	2012 - 14
INFINITI	Q50	2014
INFINITI	Q60	2014
INFINITI	Q70	2014
INFINITI	QX50	2014
INFINITI	QX56	2004 - 2012
INFINITI	QX57	2004 - 2012
INFINITI	QX70	2014

Autel TS401 01-06-15

JAGUAR	F	2013 - 2014
JAGUAR	XF	2007 - 2014
JAGUAR	XJ	2005 - 09
JAGUAR	XJ	2010 - 2014
JAGUAR	XK	2006 - 2014
JAGUAR	X-Type	2007 - 2014
JEEP	Cherokee	2007 - 2012
JEEP	Cherokee	2014
JEEP	Commander	2006 - 10
JEEP	Commander(US)	2006
JEEP	Commander(US)	2006
JEEP	Commander(US)	2007
JEEP	Commander(US)	2007
JEEP	Commander(US)	2008-11
JEEP	Commander(US)	2008-11
JEEP	Compass	2011 - 2014
JEEP	Compass(US)	2007
JEEP	Compass(US)	2007
JEEP	Compass(US)	2008-09
JEEP	Compass(US)	2008-09
JEEP	Compass(US)	2010
JEEP	Compass(US)	2010
JEEP	Compass(US)	2011-14
JEEP	Compass(US)	2011-14
JEEP	Grand Cherokee	2006 - 10
JEEP	Grand Cherokee	2011 - 06/2015
JEEP	Grand Cherokee(US)	2005-06
JEEP	Grand Cherokee(US)	2005-06
JEEP	Grand Cherokee(US)	2011-14
JEEP	Grand Cherokee(US)	2011-14
JEEP	Grand Cherokee(US)	2002-04
JEEP	Grand Cherokee(US)	2002-04
JEEP	Grand Cherokee(US)	2007
JEEP	Grand Cherokee(US)	2007
JEEP	Grand Cherokee(US)	2008-10
JEEP	Grand Cherokee(US)	2008-10
JEEP	Liberty	2005 - 2006
JEEP	Liberty	2007 - 2012
JEEP	Liberty(US)	2002-04
JEEP	Liberty(US)	2002-04
JEEP	Liberty(US)	2005-06
JEEP	Liberty(US)	2005-06
JEEP	Liberty(US)	2007-08
JEEP	Liberty(US)	2007-08
JEEP	Liberty(US)	2009(315)
JEEP	Liberty(US)	2009(315)
JEEP	Liberty(US)	2009(433)
JEEP	Liberty(US)	2009(433)
JEEP	Liberty(US)	2010-12
JEEP	Liberty(US)	2010-12

Autel TS401 01-06-15

JEEP	Patriot	2006 - 2014
JEEP	Patriot(US)	2007-14
JEEP	Patriot(US)	2007-14
JEEP	Wrangler	09/2010 - EOL
JEEP	Wrangler	2007 - 08/2010
JEEP	Wrangler(US)	2007-08
JEEP	Wrangler(US)	2007-08
JEEP	Wrangler(US)	2009(snap in)
JEEP	Wrangler(US)	2010-12
JEEP	Wrangler(US)	2010-12
JEEP	Wrangler(US)	2013-14
JEEP	Wrangler(US)	2013-14
JEEP	Wrangler(US)	2009(clamp in)
JEEP	Wrangler(US)	2009(clamp in)
JEEP	Wrangler(US)	2009(snap in)
KIA	Cadenza	2013 - EOL
KIA	Carens RP	2012 - 2013
KIA	Carens RP	2014 - EOL
KIA	Ceed-ED	2006 - 2012
KIA	Ceed-JD	03/2012 - EOL
KIA	Optima	08/2013 - 2014
KIA	Optima 11/Optima hybrid	2011 - 2014
KIA	Picanto	06/2014 - EOL
KIA	Quons	2013 - EOL
KIA	RIO	07/2014 - 2015 (Low line)
KIA	RIO	07/2014 - 2015(High line)
KIA	RIO	2012 - 06/2014
KIA	Sorento	2009 - 2012
KIA	Sorento	2012 - 2014
KIA	Soul	2008 - 09/2013
KIA	Soul(PS)	10/2013 - EOL
KIA	Sportage	2010 - 13(Hi Line)
KIA	Sportage	2012 - 13(Low Line)
KIA	Sportage	2014
KIA	Venga	2010 ->
LAMBORGHINI	Aventador	2011 - 2019
LAMBORGHINI	Gallardo	2007 - 2021
LAMBORGHINI	Murcielago LP640	2007 - EOL
LANCIA	Delta	2008 - EOL
LANCIA	Flavia	10/2010 - 2013
LANCIA	Phedra	10/2005 - 10
LANCIA	Phedra	2002 - 09/2005
LANCIA	Thema	2011 - 2014
LANCIA	Voyager	2011 - 2014
LAND ROVER	Discovery 3	2005 - 09
LAND ROVER	Discovery 4	2010 - 2014
LAND ROVER	Evoque	2011 - 2014
LAND ROVER	FreeLander	2005 - 2014
LAND ROVER	Ranger Rover	2002 - 03
LAND ROVER	Ranger Rover	2005 - 12

Autel TS401 01-06-15

LAND ROVER	Ranger Rover	2013
LAND ROVER	Ranger Rover Sports	06/2014 - EOL
LAND ROVER	Ranger Rover Vogue	2005 - 2013
LEXUS	C-CUV	11/2014 - EOL
LEXUS	CT	06/2014 - EOL
LEXUS	ES	06/2014 - EOL
LEXUS	ES	2007 - 10
LEXUS	GS	06/2014 - EOL
LEXUS	GS 300	07/2006 - 2013
LEXUS	GS 350	07/2009 - 2013
LEXUS	GS 430	07/2006 - 2013
LEXUS	GS 450	2/2006 - 12/2012
LEXUS	GS 450	2013
LEXUS	GS 460	09/2007 - 2013
LEXUS	GX	06/2014 - EOL
LEXUS	GX	2006 - 09
LEXUS	IS	07/2013 - EOL
LEXUS	IS200	2006 - 2012
LEXUS	IS220	2006 - 2012
LEXUS	IS250	2006 - 2012
LEXUS	IS300	2006 - 12
LEXUS	LFA	2010 - 12
LEXUS	LS	2014 - EOL
LEXUS	LS 460	8/2006 - 2009
LEXUS	LS 600	4/2007 - 2009
LEXUS	LX	06/2014 - EOL
LEXUS	LX	2005 - 10
LEXUS	RX	06/2014 - EOL
LEXUS	RX	2006 - 10
LEXUS	SC 430	8/2006 - 7/2010
Lincoln	Aviator(US)	2003
Lincoln	Aviator(US)	2004-05
Lincoln	Mark LT(US)	2007-08
Lincoln	Mark LT(US)	2009
Lincoln	MKS(US)	2009-10
Lincoln	MKS(US)	2011
Lincoln	MKS(US)	2012-14
Lincoln	MKT(US)	2010
Lincoln	MKT(US)	2011
Lincoln	MKT(US)	2012-14
Lincoln	MKX(US)	2007 W Chrome rims
Lincoln	MKX(US)	2007 W/O Chrome rims
Lincoln	MKX(US)	2008-10 W Chrome rims
Lincoln	MKX(US)	2008-10 W/O Chrome rims
Lincoln	MKX(US)	2011
Lincoln	MKX(US)	2012-14
Lincoln	MKZ(US)	2007
Lincoln	MKZ(US)	2008-09
Lincoln	MKZ(US)	2010-11
Lincoln	MKZ(US)	2012-14

Autel TS401 01-06-15

Lincoln	Navigator(US)	2003
Lincoln	Navigator(US)	2004
Lincoln	Navigator(US)	2005-06
Lincoln	Navigator(US)	2007
Lincoln	Navigator(US)	2008-10
Lincoln	Navigator(US)	2011
Lincoln	Navigator(US)	2012-14
Lincoln	Town Car(US)	2006-07
Lincoln	Town Car(US)	2008
Lincoln	Town Car(US)	2009
Lincoln	Town Car(US)	2010-11
LOTUS	Elise	2008 - EOL
LOTUS	Evora	2010 - EOL
LOTUS	Exige	2008 - EOL
MASERATI	Coupe	07/2009 - 2013
MASERATI	Coupe	2004 - 06/2009
MASERATI	Ghibli	11/2013 - EOL
MASERATI	Gran turismo	2004 - 10
MASERATI	Gran turismo	2011 - 12
MASERATI	Quattroporte	2004 - 09
MASERATI	Quattroporte	2010 - 2012
MASERATI	Quattroporte	2013 - EOL
MAYBACH	Landaulet	2008 - 2014
MAYBACH	Maybach 57	2002 - 2012
MAYBACH	Maybach 62	2002 - 2012
MAZDA	2	2007 - EOL
MAZDA	3	2009 - EOL
MAZDA	5	2010 - EOL
MAZDA	6	2008 - 2018
MAZDA	BT-50	2011 - EOL
MAZDA	CX5	2011 - EOL
MAZDA	CX7	2009 - EOL
MAZDA	CX9	2011 - EOL
MAZDA	MX5	06/2005 - 03/2015
MERCEDES	A-Class	04/2014 - EOL
MERCEDES	AMG	2010 - 2014
MERCEDES	AMG E-Class	1999 - 02
MERCEDES	C-Class(W204)	2008 - 02/2014
MERCEDES	C-Class(W205)	01/2014 - 2021
MERCEDES	Citan	09/2012 - EOL
MERCEDES	CLA	06/2014 - 04/2020
MERCEDES	CLC-Class	2008 - 11
MERCEDES	CL-Class	2009 - 12
MERCEDES	CLK	2007 - 09
MERCEDES	CLK	2009 - 2014
MERCEDES	CLS(218)	09/2010 - 10/2017
MERCEDES	CLS(219)	01/2005 - 08/2010
MERCEDES	CLS(219)	06/2004 - 01/2005
MERCEDES	E-Class	06/2005 -> 06/2009
MERCEDES	E-Class	1999 -> 05/2005

Autel TS401 01-06-15

MERCEDES	E-Class(C207)	06/2014 - EOL
MERCEDES	E-Class(W212)	07/2009 - 10/2015
MERCEDES	G-Class	2007 - 2018
MERCEDES	GLA	2014 - 2019
MERCEDES	GL-Class	06/2009 - EOL
MERCEDES	GL-Class	2006 - 06/2009
MERCEDES	GLK-Class	2008 - 2015
MERCEDES	M-Class	08/2009 - 2014
MERCEDES	M-Class	2005 - 07/2009
MERCEDES	ML-Class	2011 - 2014
MERCEDES	R-Class	08/2009 - 2016
MERCEDES	R-Class	2006 - 07/2009
MERCEDES	S-Class	06/2009 - EOL
MERCEDES	S-Class	10/2005 - 05/2009
MERCEDES	S-Class	1999 - 09/2005
MERCEDES	SL	2005 - 11
MERCEDES	SL	2012 - 2014
MERCEDES	SLK	2012 - 2017
MERCEDES	SLR	2002 - 2007
MERCEDES	SL-Roadster	2001 - 05
MERCEDES	SLS	2010 - 03/2016
MERCEDES	Sprinter	06/2014 - EOL
MERCEDES	Sprinter Combi	11/2011 - 2014
MERCEDES	Sprinter Combi	2006 - 10/2011
MERCEDES	Viano	2007 - 2014
MERCEDES	Vito Combi	12/2012 - 2014
MERCEDES	Vito NVC	2006 - 2014
Mercury	Grand Marquis(US)	2006-07
Mercury	Grand Marquis(US)	2008
Mercury	Grand Marquis(US)	2009-11
Mercury	Mariner(US)	2006-07
Mercury	Mariner(US)	2008
Mercury	Mariner(US)	2009
Mercury	Mariner(US)	2010
Mercury	Mariner(US)	2011
Mercury	Milan(US)	2008-09
Mercury	Milan(US)	2010-11
Mercury	Montego(US)	2006-07
Mercury	Monterey(US)	2004
Mercury	Monterey(US)	2005
Mercury	Monterey(US)	2006-07
Mercury	Mountaineer(US)	2002-03
Mercury	Mountaineer(US)	2004-05
Mercury	Mountaineer(US)	2006-07
Mercury	Mountaineer(US)	2008-10
Mercury	Sable(US)	2008-09
MINI	ALL Models	2007 - 09
MINI	ALL Models	2010 - 13
MINI	ALL Models	2014 ->
MINI	Cabrio(R57)	07/2014 - 2015

Autel TS401 01-06-15

MINI	Clubman(R55)	08/2007 - 09/2009
MINI	Clubman(R55)	08/2009 - 2015
MINI	Clubvan(R55)	07/2012 - 06/2015
MINI	Countrymen(R60)	08/2010 - 2017
MINI	Coupe(R58)	07/2011 - 08/2015
MINI	Mini	2010 - 2013
MINI	Mini	2014 - 2015
MINI	Paceman(R61)	11/2012 - 06/2018
MINI	Roadster(R59)	12/2011 - 08/2015
MITSUBISHI	ASX	2014
MITSUBISHI	Attrage	2014
MITSUBISHI	i-Miev	2014
MITSUBISHI	L200 CR	2014
MITSUBISHI	Lancer	2014
MITSUBISHI	Mirage	2014
MITSUBISHI	Outlander	2014
MITSUBISHI	Pajero	2014
MITSUBISHI	Shogun	2014
MITSUBISHI	Spacestar	2014
NISSAN	370Z	2008 - EOL
NISSAN	Almera	05/2013 - EOL
NISSAN	B-EV	2014
NISSAN	C-Hatch	10/2014 - EOL
NISSAN	Cube	2008 - 14
NISSAN	GTR	2007 - 2014
NISSAN	GTR	2014
NISSAN	Juke	06/2014 - 2015
NISSAN	Leaf	05/2014 - 2015
NISSAN	Micra	03/2010 - 2016
NISSAN	Murano	10/2007 - 03/2015
NISSAN	Navara	2004 - 14
NISSAN	Note	2013 - 2014
NISSAN	NV200	2014
NISSAN	Pathfinder	2004 - 2006
NISSAN	Patrol	2010
NISSAN	Pixo	01/2009 - 12/2014
NISSAN	PRIMERA	2002 - 2007
NISSAN	Qashqai	2013 - 2014
NISSAN	Sentra	08/2014 - EOL
NISSAN	Teana	2014 - EOL
NISSAN	Tida	2014
NISSAN	X-Trail	2013 - 2014
OPEL/VAUXHALL	Adam	08/2014 - 08/2015
OPEL/VAUXHALL	Adam	2012 - 07/2014
OPEL/VAUXHALL	Ampera	09/2011 - 2015
OPEL/VAUXHALL	Antara	06/2014 - 2015
OPEL/VAUXHALL	Antara	2006 - 10
OPEL/VAUXHALL	Antara	2011 - 05/2014
OPEL/VAUXHALL	Astra(A3300)	2004 - 2010
OPEL/VAUXHALL	Astra(P3400)	06/2014 - EOL

Autel TS401 01-06-15

OPEL/VAUXHALL	Astra(P3400)	09/2011 - 05/2014
OPEL/VAUXHALL	Astra(P3400)	10/2009 - 09/2011
OPEL/VAUXHALL	Cascada	06/2014 - EOL
OPEL/VAUXHALL	Cascada	2013 - 05/2014
OPEL/VAUXHALL	Corsa	06/2014 - 10/2014
OPEL/VAUXHALL	Corsa	11/2014 - EOL
OPEL/VAUXHALL	Insigna	05/2014 - 2015
OPEL/VAUXHALL	Insigna	2008 - 09/2011
OPEL/VAUXHALL	Meriva	08/2014 - EOL
OPEL/VAUXHALL	Mokka	06/2012 - 08/2015
OPEL/VAUXHALL	Signum	2002 - 09
OPEL/VAUXHALL	Vectra	2002 - 08
OPEL/VAUXHALL	Vectra Estate	2002 - 09
OPEL/VAUXHALL	Zafira B	06/2014 - 2015
OPEL/VAUXHALL	Zafira B	2004 - 2009
OPEL/VAUXHALL	Zafira C	06/2014 - 2015
OPEL/VAUXHALL	Zafira C	2009 - 05/2014
OPEL/VAUXHALL	Zafira tourer	09/2011 - 05/2014
PEUGEOT	1007	2005 - 09
PEUGEOT	108	08/2014 - EOL
PEUGEOT	207	09/2013 - 06/2016
PEUGEOT	207	2006 - 09/2013
PEUGEOT	3008	09/2013 - 09/2016
PEUGEOT	3008	2008 - 09/2013
PEUGEOT	3008(LCV)	2008 - EOL
PEUGEOT	301	2012 - 2019
PEUGEOT	307	03/2007 - 12/2007
PEUGEOT	307	2003 - 02/2007
PEUGEOT	308	09/2013 - 01/2015
PEUGEOT	308	2007 - 09/2013
PEUGEOT	407 & 407SW	2004 - 2011
PEUGEOT	407 Coupe	2005 - 2010
PEUGEOT	408	06/2014 - EOL
PEUGEOT	5008	09/2013 - 06/2017
PEUGEOT	5008	2009 - 09/2013
PEUGEOT	5008(LCV)	09/2009 ->
PEUGEOT	508	09/2013 - 06/2017
PEUGEOT	508	2011 - 09/2013
PEUGEOT	508(LCV)	09/2010 ->
PEUGEOT	607	2000 - 09/2004
PEUGEOT	607 II	10/2004 - 10
PEUGEOT	807	10/2005 - 2014
PEUGEOT	807	2002 - 09/2005
PEUGEOT	Boxer Combi	2014 - 2015
PEUGEOT	Expert	2014 - 2015
PEUGEOT	Partner	06/2014 - EOL
PEUGEOT	Partner	2008 - 05/2014
PEUGEOT	RCZ	09/2013 - 2016
PEUGEOT	RCZ	2010 - 09/2013
Pontiac	G3(US)	2009-10

Autel TS401 01-06-15

Pontiac	G5(US)	2008
Pontiac	G5(US)	2009-10
Pontiac	G6(US)	2008(clamp in)
Pontiac	G6(US)	2008(snap in)
Pontiac	G6(US)	2009-10
Pontiac	G8(US)	2008-09
Pontiac	Grand Prix(US)	2007
Pontiac	Grand Prix(US)	2008(clamp in)
Pontiac	Grand Prix(US)	2008(snap in)
Pontiac	Montana(US)	2008-09
Pontiac	Solstice(US)	2008
Pontiac	Solstice(US)	2009
Pontiac	Solstice(US)	2010
Pontiac	Torrent(US)	2007-08
Pontiac	Torrent(US)	2009
Pontiac	Vibe(US)	2008-10
Pontiac	Wave(US)	2008-09
PORSCHE	911(997-1 Carrera)	2005 - 08
PORSCHE	911(997-2 Carrera)	2009 - 11
PORSCHE	911(997T2-Turbo)	2010 - 2015
PORSCHE	911(997T-Turbo)	2007 - 09
PORSCHE	918 Spyder	2013 - 14
PORSCHE	991	2012 - 2014
PORSCHE	997(GT3)	2007 - 09
PORSCHE	997(GT3-2)	2010 - 2014
PORSCHE	Boxster	11/2008 - 2018
PORSCHE	Boxster(987)	2005 - 10/2008
PORSCHE	Carrera GT	2003 - 06
PORSCHE	Cayenne(955-92A)	2009 - 2014
PORSCHE	Cayenne(955-9PA)	2002 - 06
PORSCHE	Cayenne(955-9PA1)	2007 - 2010
PORSCHE	Cayman(987C)	2005 - 08
PORSCHE	Cayman(987C2)	2009 - 2014
PORSCHE	Macan	2013 - 2019
PORSCHE	Panamera Turbo	07/2013 - 2014
PORSCHE	Panamera(970)	2009 - 06/2013
RENAULT	Captur	2013 - 10/2019
RENAULT	Clio III	06/2014 - EOL
RENAULT	Clio III	2005 - 05/2014
RENAULT	Clio Van	07/2012 - EOL
RENAULT	Espace IV	2002 - 06/2014
RENAULT	Kangoo	10/2007 - 09/2017
RENAULT	Koleos	2008 - 12/2013
RENAULT	Koleos	2014
RENAULT	Laguna II	2002 - 03/2005
RENAULT	Laguna II	04/2005 - 06/2007
RENAULT	Laguna III	06/2007 - 03/2015
RENAULT	Latitude	2011 - 2015
RENAULT	Master	11/2009 - 09/2020
RENAULT	Megane 1	2001 - 08/2002

Autel TS401 01-06-15

RENAULT	Megane II	09/2002 - 12/2007
RENAULT	Megane III	09/2008 - 09/2015
RENAULT	Modus	05/2004 - 2012
RENAULT	Scenic 1	2001 - 04/2003
RENAULT	Scenic II	05/2003 - 08
RENAULT	Scenic II restyle	2006 - 08
RENAULT	Scenic III	2009 - 2014
RENAULT	Scenic RX4	2001 - 03
RENAULT	Symbol/Thalia	04/2013 - 03/2020
RENAULT	Trafic	2014 - 2015
RENAULT	Twingo	2007 - 2015
RENAULT	Vel Satis	09/2001 - 11/2009
RENAULT	Wind	06/2010 - 09/2016
RENAULT	Zoe	09/2012 - 03/2019
ROLLS ROYCE	Cabrio	2009 - 11
ROLLS ROYCE	Ghost	2009 - 2018
ROLLS ROYCE	Phantom	2007 - 11
ROLLS ROYCE	Phantom	2012 - 2014
ROLLS ROYCE	Wraith	08/2013 - EOL
SAAB	9.3	2003 - 06
SAAB	9.3	2006 - 09
SAAB	9.3	2009 - 12
SAAB	9.4	2011 - 2014
SAAB	9.5	2003 - 06
SAAB	9.5	2006 - 09
SAAB	9.5	2009 - 12
SAAB	9.7	2007 - 08
Saturn	Astra(US)	2008-09
Saturn	Astra(US)	2010
Saturn	Aura(US)	2007
Saturn	Aura(US)	2008(clamp in)
Saturn	Aura(US)	2008(snap in)
Saturn	Aura(US)	2009-10
Saturn	Lamda Crossover(US)	2007-08
Saturn	Outlook(US)	2007-08
Saturn	Outlook(US)	2009-10
Saturn	Sky(US)	2008
Saturn	Sky(US)	2009
Saturn	Vue(US)	2007
Saturn	Vue(US)	2008
Saturn	Vue(US)	2009-10
SKODA	Citigo	2011 - 09/2018
SKODA	Fabia	2013 - 04/2019
SKODA	Octavia	2012 - 06/2019
SKODA	Rapid	2012 - 04/2020
SKODA	Roomster	2012 - 2014
SKODA	Superb	2008 - 09/2014
SKODA	Yeti	2009 - 2015
SMART	Forfour	07/2014 - 09/2020
SMART	Fortwo	03/2014 - 03/2021

Autel TS401 01-06-15

SMART	Fortwo	2007 - 03/2014
SUBARU	BRZ	2014
SUBARU	C-Concept	2014
SUBARU	Forester	2014
SUBARU	Impreza	2014
SUBARU	Justy	2014
SUBARU	Legacy	2014
SUBARU	Outback	2014
SUBARU	Trezia	2014
SUBARU	Tribeca	2014
SUBARU	XV	2014
SUZUKI	Alto	2014
SUZUKI	Swift	2014
SUZUKI	SX-4	2013 - 2014
TESLA	Model S	2013 - 2014
TOYOTA	Alphard	2014 - 2015
TOYOTA	Auris	2014 - 2015
TOYOTA	Avensis	2014 - 2015
TOYOTA	Aygo	2014 - 2015
TOYOTA	Camry	2014 - 2015
TOYOTA	Corolla	2013 - 2015
TOYOTA	Landcruiser	2005 - 10
TOYOTA	Landcruiser	2013 - 14
TOYOTA	Prius	2014 - 2015
TOYOTA	Proace	2013 - 2014
TOYOTA	RAV4 III	9/2006 - 3/2013
TOYOTA	RAV4 IV	12/2012 - 2014
TOYOTA	Verso	2013 - 14
TOYOTA	Yaris	2014 - 2015
VOLKSWAGEN	Caravelle	2012 - 2014
VOLKSWAGEN	Crafter	2006 - 2016
VOLKSWAGEN	EOS	2006 - 2015
VOLKSWAGEN	Golf	2009 - 2015
VOLKSWAGEN	Jetta	2013 - 2015
VOLKSWAGEN	New Beetle	08/2011 - 2017
VOLKSWAGEN	New Beetle	2006 - 2010
VOLKSWAGEN	Passat	09/2010 - 09/2013
VOLKSWAGEN	Passat	09/2013 - 2014
VOLKSWAGEN	Passat	2006 - 2010
VOLKSWAGEN	Passat cc	09/2014 - 06/2015
VOLKSWAGEN	Passat cc	2008 - 09/2014
VOLKSWAGEN	Passat VI	2005 - 11/2010
VOLKSWAGEN	Phaeton	2002 - 05/2007
VOLKSWAGEN	Phaeton(2011)	06/2010 - 2015
VOLKSWAGEN	Phaeton(3D)	06/2007 - 05/2010
VOLKSWAGEN	Scirocco	2008 - 2015
VOLKSWAGEN	Sharan	2008 - 2015
VOLKSWAGEN	Tiguan	09/2013 - 12/2014
VOLKSWAGEN	Tiguan	2009 - 09/2013
VOLKSWAGEN	Touareg	09/2013 - 2015

Autel TS401 01-06-15

VOLKSWAGEN	Touareg	2002 - 06
VOLKSWAGEN	Touareg	2011 - 09/2013
VOLKSWAGEN	Touareg	2007 - 10
VOLKSWAGEN	Touran	07/2010 - 12/2014
VOLKSWAGEN	Touran(LCV)	07/2010 - EOL
VOLKSWAGEN	Transporter	2012 - 2016
VOLVO	C30	2007
VOLVO	C30	2008
VOLVO	C30	2009
VOLVO	C30	2010
VOLVO	C30	2011
VOLVO	C30	2012 - 06/2014
VOLVO	C70	2006-2007
VOLVO	C70	2008
VOLVO	C70	2009
VOLVO	C70	2010
VOLVO	C70	2011
VOLVO	C70	2012 - 06/2014
VOLVO	S40	2004 - 2007
VOLVO	S40	2008
VOLVO	S40	2009
VOLVO	S40	2010
VOLVO	S40	2011
VOLVO	S40	2012 - 06/2014
VOLVO	S60	03/2010 - 06/2014
VOLVO	S60	07/2014 - 2015
VOLVO	S60	2006
VOLVO	S60	2007 - 02/2010
VOLVO	S80	07/2014 - 2015
VOLVO	S80	2006
VOLVO	S80	2007
VOLVO	S80	2008
VOLVO	S80	2009
VOLVO	S80	2010
VOLVO	S80	2011
VOLVO	S80	2012 - 06/2014
VOLVO	V40	07/2014 - 2015
VOLVO	V50	2004 - 2007
VOLVO	V50	2008
VOLVO	V50	2009
VOLVO	V50	2010
VOLVO	V50	2011
VOLVO	V50	2012 - 06/2014
VOLVO	V60	07/2014 - 2015
VOLVO	V60	2010
VOLVO	V60	2011
VOLVO	V60	2012 - 06/2014
VOLVO	V70	07/2014 - 2015
VOLVO	V70 II	2006
VOLVO	V70 III	2007

Autel TS401 01-06-15

VOLVO	V70 III	2008
VOLVO	V70 III	2009
VOLVO	V70 III	2010
VOLVO	V70 III	2011
VOLVO	V70 III	2012 - 06/2014
VOLVO	XC60	07/2014 - 2015
VOLVO	XC60	2008
VOLVO	XC60	2009
VOLVO	XC60	2010
VOLVO	XC60	2011
VOLVO	XC60	2012 - 06/2014
VOLVO	XC70	07/2014 - 2015
VOLVO	XC70	2006
VOLVO	XC70	2007
VOLVO	XC70	2008
VOLVO	XC70	2009
VOLVO	XC70	2010
VOLVO	XC70	2011
VOLVO	XC70	2012 - 06/2014
VOLVO	XC90	2006
VOLVO	XC90	2007 - 2009
VOLVO	XC90	2011 - 2014

(This Free update increases the applications for European vehicles. The update will wipe the current applications off your TS401 and replace them with the above applications ONLY. To update you will also need the MaxiLinkII driver from the CD supplied with the tool or download from the Autel website. When saving the two software files from the Sealey website they MUST be saved onto the desktop. Please see instructions manual for details).