



General Laboratory Equipment

| | | | | | |
|----------------------|----------|----------------------|-----|-----------------------------|-----|
| Beakers | 218 | Flasks | 219 | Pipettes & Pipette Fillers | 233 |
| Bottles | 226, 230 | Fume Extraction | 242 | Plastic Measuring Cylinders | 230 |
| Burettes | 232 | Funnels & Holders | 228 | Polypropylene Tubes | 230 |
| Burners & Stands | 236 | Gas Washing Bottles | 227 | Polypropylene Coplin Jars | 230 |
| Calorimeters | 240 | Glass Filter Funnels | 227 | Reduction Adapters | 224 |
| Chromatography | 234 | Glass Tubing | 226 | Retort Stands & Clamps | 238 |
| Containers | 230 | Health & Safety | 241 | Reusable Syringes | 229 |
| Coplin Jars | 227 | Heating Mantles | 244 | Spatulas, Spoons & Scoops | 235 |
| Cork Borers | 229 | Hot Stirrer | 244 | Stoppers & Bungs | 229 |
| Cotton Wool | 235 | Indicator Test Paper | 235 | Stirring Rods | 236 |
| Crucibles | 228 | Jointed Flasks | 225 | Test Tubes | 223 |
| Crystallising Dishes | 227 | Jointed Glassware | 226 | Test Tube Brushes | 223 |
| Cylinders | 222 | Laboratory Jacks | 237 | Test Tube Holders | 223 |
| Drying Tubes | 223 | Measuring | 240 | Tongs & Holders | 235 |
| Evaporating Dishes | 228 | Measuring Beakers | 230 | Tweezers | 236 |
| Expansion Adapters | 224 | Pestle & Mortars | 228 | Watch Glass | 227 |
| Filter Paper | 234 | Petri Dishes & Racks | 234 | | |

Full range of General Laboratory Equipment available at:

www.rapidonline.com

Tall Form Beakers

| Capacity | ALL NEW PRODUCTS | | | | ALL NEW PRODUCTS | | | |
|----------|------------------|------------|-----------|--------|------------------|------------|-----------|--------|
| | Academy | | | | LabGlass | | | |
| | Order code | Unit price | Pack size | Price | Order code | Unit price | Pack size | Price |
| 25ml | | | | | 52-4051 | £0.69 | 12 | £8.28 |
| 50ml | 52-2242 | £0.59 | 12 | £7.13 | 52-4054 | £0.88 | 12 | £10.50 |
| 100ml | 52-2243 | £0.68 | 12 | £8.10 | 52-4048 | £1.21 | 12 | £11.43 |
| 150ml | 52-2244 | £0.73 | 12 | £8.75 | 52-4049 | £1.08 | 12 | £12.94 |
| 250ml | 52-2245 | £0.97 | 12 | £11.66 | 52-4050 | £1.13 | 12 | £13.58 |
| 400ml | 52-2246 | £1.23 | 12 | £14.74 | 52-4052 | £1.31 | 6 | £7.83 |
| 500ml | | | | | 52-4053 | £1.59 | 6 | £9.54 |
| 600ml | 52-2247 | £1.65 | 6 | £9.88 | 52-4055 | £1.73 | 6 | £10.40 |
| 800ml | 52-2248 | £2.11 | 6 | £12.64 | | | | |
| 1000ml | 52-2249 | £2.39 | 6 | £14.34 | 52-4047 | £2.58 | 6 | £15.49 |
| 2000ml | 52-2250 | £7.25 | 4 | £29.00 | | | | |
| 3000ml | 52-2251 | £10.72 | 1 | £10.72 | | | | |

ACADEMY[™]
Science ProductsSIMAX[®] LAB CLASS[®]
KIMBLE CHASENEW LINES
ADDED

Tall Form Beaker

Low Form Heavy Wall Beakers

| Capacity | ALL NEW PRODUCTS | | | | Kimble Chase | | | |
|----------|------------------|------------|-----------|--------|--------------|------------|-----------|-------|
| | Academy | | | | | | | |
| | Order code | Unit price | Pack size | Price | Order code | Unit price | Pack size | Price |
| 150ml | 52-1063 | £1.50 | 12 | £17.99 | | | | |
| 250ml | 52-1065 | £1.80 | 12 | £21.59 | | | | |
| 400ml | 52-1067 | £2.28 | 12 | £27.36 | | | | |
| 600ml | 52-1069 | £3.42 | 6 | £20.56 | 52-1898 | 6.92 | 1 | £6.92 |
| 1000ml | 52-1071 | £4.33 | 6 | £25.96 | | | | |
| 2000ml | 52-1073 | £6.93 | 4 | £27.70 | | | | |



Low Form Beaker



Low Form Heavy Wall Beaker

Low Form Beakers

| Capacity | ALL NEW PRODUCTS | | | | ALL NEW PRODUCTS | | | | Simax | | | | Kimble Chase | | | |
|----------|------------------|------------|-----------|--------|------------------|------------|-----------|--------|------------|------------|-----------|--------|--------------|------------|-----------|--------|
| | Academy | | | | LabGlass | | | | | | | | | | | |
| | Order code | Unit price | Pack size | Price | Order code | Unit price | Pack size | Price | Order code | Unit price | Pack size | Price | Order code | Unit price | Pack size | Price |
| 5ml | | | | | 52-4044 | £0.72 | 10 | £7.18 | | | | | | | | |
| 10ml | | | | | 52-4034 | £0.66 | 12 | £7.95 | | | | | | | | |
| 25ml | N 52-1088 | £0.34 | 12 | £4.11 | 52-4038 | £0.70 | 12 | £8.38 | | | | | | | | |
| 50ml | 52-0949 | £0.54 | 12 | £6.42 | 52-4043 | £0.85 | 12 | £10.19 | 52-0202 | £0.84 | 10 | £8.43 | 52-2264 | £3.01 | 12 | £36.15 |
| 100ml | 52-0951 | £0.54 | 12 | £6.52 | 52-4033 | £0.87 | 12 | £10.41 | 52-0204 | £0.88 | 10 | £8.78 | 52-2265 | £3.29 | 12 | £39.45 |
| 150ml | | | | | 52-4035 | £0.88 | 12 | £10.50 | | | | | | | | |
| 250ml | 52-0953 | £0.63 | 12 | £7.50 | 52-4037 | £0.93 | 12 | £11.13 | 52-0206 | £0.91 | 10 | £9.12 | 52-2266 | £3.59 | 12 | £43.12 |
| 400ml | | | | | 52-4040 | £1.15 | 6 | £6.88 | 52-0208 | £1.26 | 10 | £12.58 | 52-2267 | £4.29 | 12 | £51.42 |
| 500ml | | | | | 52-4042 | £1.39 | 6 | £8.36 | | | | | | | | |
| 600ml | 52-0955 | £1.01 | 6 | £6.04 | 52-4045 | £1.68 | 6 | £10.07 | 52-0210 | £1.51 | 10 | £15.07 | 52-2268 | £5.46 | 6 | £32.78 |
| 800ml | | | | | 52-4046 | £2.01 | 6 | £12.03 | | | | | 52-2269 | £9.48 | 6 | £56.88 |
| 1000ml | 52-0959 | £1.32 | 6 | £7.93 | 52-4032 | £2.20 | 6 | £13.18 | 52-0212 | £2.21 | 10 | £22.06 | | | | |
| 2000ml | N 52-1089 | £4.12 | 4 | £16.46 | 52-4036 | £4.85 | 1 | £4.85 | | | | | | | | |
| 3000ml | | | | | 52-4039 | £11.86 | 1 | £11.86 | | | | | | | | |
| 5000ml | N 52-1091 | £14.31 | 1 | £14.31 | 52-4041 | £18.23 | 1 | £18.23 | | | | | | | | |
| 10,000ml | | | | | 52-4031 | £50.99 | 1 | £50.99 | | | | | | | | |

Conical Flasks – Narrow Neck

ACADEMY



SIMAX®

| Capacity | Academy | | | |
|----------|------------|------------|-----------|--------|
| | Order code | Unit price | Pack size | Price |
| 10ml | | | | |
| 25ml | | | | |
| 50ml | | | | |
| 100ml | 52-0969 | £0.67 | 12 | £8.08 |
| 250ml | 52-0971 | £0.87 | 6 | £5.23 |
| 500ml | 52-0973 | £1.56 | 6 | £9.38 |
| 1000ml | N 52-1075 | £2.67 | 6 | £16.01 |
| 2000ml | N 52-1077 | £8.24 | 1 | £8.24 |
| 3000ml | | | | |
| 5000ml | | | | |

| ALL NEW PRODUCTS | | | | |
|------------------|------------|-----------|--------|--|
| LabGlass | | | | |
| Order code | Unit price | Pack size | Price | |
| 52-4155 | £0.79 | 12 | £9.48 | |
| 52-4158 | £0.92 | 12 | £11.06 | |
| 52-4162 | £0.72 | 12 | £8.60 | |
| 52-4154 | £1.21 | 12 | £14.47 | |
| 52-4157 | £0.92 | 12 | £11.06 | |
| 52-4161 | £1.63 | 6 | £9.75 | |
| 52-4153 | £2.41 | 6 | £14.47 | |
| 52-4156 | £9.32 | 1 | £9.32 | |
| 52-4159 | £9.58 | 1 | £9.58 | |
| 52-4160 | £18.50 | 1 | £18.50 | |

| Simax | | | |
|------------|------------|-----------|--------|
| Order code | Unit price | Pack size | Price |
| N 52-1189 | £2.58 | 10 | £25.80 |
| 52-0214 | £1.07 | 10 | £10.73 |
| 52-0216 | £1.13 | 10 | £11.28 |
| N 52-1191 | £1.76 | 10 | £17.62 |
| N 52-1193 | £3.25 | 10 | £32.48 |
| N 52-1201 | £9.67 | 6 | £57.99 |



NEW LINES ADDED



Conical Flasks – Wide Neck

SIMAX®

| ALL NEW PRODUCTS | | | | |
|------------------|------------|------------|-----------|--------|
| Simax | | | | |
| Capacity | Order code | Unit price | Pack size | Price |
| 25ml | 52-1246 | £3.89 | 10 | £38.85 |
| 50ml | 52-1247 | £6.55 | 10 | £65.45 |
| 100ml | 52-1248 | £1.29 | 10 | £12.86 |
| 250ml | 52-1249 | £1.59 | 10 | £15.85 |
| 300ml | 52-1250 | £2.99 | 10 | £29.85 |
| 500ml | 52-1251 | £2.29 | 10 | £22.85 |
| 1000ml | 52-1252 | £6.42 | 10 | £64.19 |
| 2000ml | 52-1253 | £10.98 | 6 | £65.90 |

Volumetric Flasks with Stopper Class A



Volumetric flasks from LabGlass fitted with a chemical resistant polypropylene stopper.

- Available in a range of sizes
- Made from borosilicate glass with one graduation mark
- Blue graduation
- Conforms to DIN ISO 1042 standard

| ALL NEW PRODUCTS | | | | | |
|------------------|------------|------------|-----------|-------------|--------|
| LabGlass | | | | | |
| Capacity | Order code | Unit price | Pack size | Socket size | Price |
| 5ml | 52-4177 | £1.43 | 2 | 10/19 | £2.86 |
| 10ml | 52-4171 | £1.43 | 2 | 10/19 | £2.86 |
| 25ml | 52-4174 | £1.57 | 2 | 10/19 | £3.13 |
| 50ml | 52-4176 | £1.77 | 2 | 12/21 | £3.53 |
| 100ml | 52-4170 | £2.03 | 2 | 14/23 | £4.05 |
| 250ml | 52-4173 | £3.13 | 2 | 14/23 | £6.26 |
| 500ml | 52-4175 | £4.00 | 2 | 19/26 | £8.00 |
| 1000ml | 52-4169 | £5.56 | 2 | 24/29 | £11.12 |
| 2000ml | 52-4172 | £10.00 | 1 | 29/32 | £10.00 |



Volumetric Flask Class B



| ALL NEW PRODUCTS | | | |
|-----------------------|------------|------------|--------|
| LabGlass | | | |
| Capacity/ socket size | Order code | Unit price | Price |
| 10ml 10/19 | 52-4180 | £1.31 | £2.61 |
| 20ml 10/19 | 52-4182 | £1.15 | £11.50 |
| 25ml 10/19 | 52-4184 | £1.67 | £3.33 |
| 50ml 12/21 | 52-4186 | £1.93 | £3.86 |
| 100ml 14/23 | 52-4179 | £1.90 | £3.79 |
| 200ml 14/23 | 52-4181 | £2.55 | £5.09 |
| 250ml 14/23 | 52-4183 | £2.87 | £5.74 |
| 500ml 19/26 | 52-4185 | £3.53 | £7.05 |
| 1000ml 24/29 | 52-4178 | £4.83 | £9.66 |

| Glassco | | | |
|------------|------------|-----------|--------|
| Order code | Unit price | Pack size | Price |
| 52-0998 | £3.46 | 2 | £6.92 |
| 52-0999 | £4.64 | 2 | £9.27 |
| N 52-1455 | £6.34 | 2 | £12.68 |
| N 52-1457 | £10.73 | 2 | £21.45 |

Round Bottom Boiling Flasks, Narrow Neck

ACADEMY



SIMAX

| Capacity | Academy | | | | LabGlass | | | | Simax | | | |
|----------|------------|------------|-----------|--------|------------|------------|-----------|--------|------------|------------|-----------|--------|
| | Order code | Unit price | Pack size | Price | Order code | Unit price | Pack size | Price | Order code | Unit price | Pack size | Price |
| 25ml | | | | | 52-4146 | £0.95 | 12 | £11.41 | | | | |
| 50ml | 52-2252 | £1.05 | 12 | £12.56 | 52-4148 | £1.19 | 12 | £14.30 | 52-1990 | £3.91 | 10 | £39.15 |
| 100ml | 52-2253 | £1.20 | 12 | £14.45 | 52-4143 | £1.92 | 12 | £23.01 | 52-1991 | £7.91 | 10 | £79.11 |
| 150ml | | | | | 52-4144 | £2.00 | 12 | £23.99 | | | | |
| 250ml | 52-2254 | £2.66 | 12 | £31.97 | 52-4145 | £2.67 | 12 | £32.05 | 52-1992 | £5.75 | 10 | £57.51 |
| 500ml | 52-2255 | £3.86 | 8 | £30.89 | 52-4147 | £3.48 | 6 | £20.88 | 52-1993 | £6.97 | 10 | £69.66 |
| 1000ml | 52-2256 | £5.06 | 6 | £30.35 | 52-4142 | £4.84 | 6 | £29.02 | 52-1994 | £9.44 | 10 | £94.37 |



Round Bottom Boiling Flasks, Wide Neck



| Capacity | LabGlass | | | |
|----------|------------|------------|-----------|--------|
| | Order code | Unit price | Pack size | Price |
| 25ml | 52-4149 | £1.32 | 12 | £15.81 |
| 50ml | 52-4150 | £1.73 | 12 | £20.77 |
| 100ml | 52-4151 | £2.16 | 12 | £25.89 |
| 150ml | 52-4152 | £1.99 | 12 | £23.82 |



Boiling Flasks, Flat Bottom, Wide Neck



| Capacity | LabGlass | | | |
|----------|------------|------------|-----------|--------|
| | Order code | Unit price | Pack size | Price |
| 50ml | 52-4141 | £1.13 | 12 | £13.59 |
| 100ml | 52-4138 | £1.49 | 12 | £17.90 |
| 250ml | 52-4139 | £2.60 | 12 | £31.18 |
| 500ml | 52-4140 | £4.13 | 6 | £24.78 |
| 1000ml | 52-4137 | £6.33 | 6 | £37.97 |



Boiling Flasks, Flat Bottom, Narrow Neck

ACADEMY



SIMAX

| Capacity | Academy | | | | LabGlass | | | | Simax | | | |
|----------|------------|------------|-----------|--------|------------|------------|-----------|--------|------------|------------|-----------|---------|
| | Order code | Unit price | Pack size | Price | Order code | Unit price | Pack size | Price | Order code | Unit price | Pack size | Price |
| 25ml | | | | | 52-4134 | £0.95 | 12 | £11.35 | | | | |
| 50ml | 52-2257 | £1.07 | 12 | £12.89 | 52-4136 | £1.14 | 12 | £13.72 | 52-1995 | 3.51 | 10 | £35.10 |
| 100ml | 52-2258 | £1.12 | 12 | £13.46 | 52-4131 | £1.26 | 12 | £15.16 | 52-1996 | 1.54 | 10 | £15.39 |
| 150ml | | | | | 52-4132 | £1.42 | 12 | £17.03 | | | | |
| 250ml | 52-2259 | £1.47 | 12 | £17.60 | 52-4133 | £1.60 | 12 | £19.19 | 52-1997 | 6.26 | 10 | £62.64 |
| 500ml | 52-2260 | £2.10 | 12 | £25.15 | 52-4135 | £2.30 | 6 | £13.82 | 52-1998 | 2.77 | 10 | £27.70 |
| 1000ml | 52-2261 | £3.35 | 6 | £20.09 | 52-4130 | £5.78 | 6 | £34.67 | 52-1999 | 12.46 | 10 | £124.61 |





Round Bottom Flasks with Two Necks

Round bottomed **borosilicate glass flasks** from **Glassco** with **two necks** - one jointed in the centre and one angled at the side. Ideal for use in a range of laboratory applications.

- Available in a range of sizes



| Capacity | Centre socket | Side socket | Order code | Price |
|----------|---------------|-------------|------------|--------|
| 100ml | 14/23 | 14/23 | 52-1545 | £8.78 |
| 100ml | 24/29 | 14/23 | 52-1547 | £10.76 |
| 100ml | 24/29 | 19/26 | 52-1549 | £12.20 |
| 250ml | 24/29 | 14/23 | 52-1551 | £9.53 |
| 250ml | 24/29 | 19/26 | 52-1553 | £10.23 |
| 500ml | 24/29 | 14/23 | 52-1555 | £10.54 |
| 500ml | 24/29 | 19/26 | 52-1557 | £11.92 |
| 1000ml | 24/29 | 14/23 | 52-1559 | £12.57 |
| 1000ml | 24/29 | 19/26 | 52-1561 | £22.57 |

567986



Round Bottom Flasks with Three Necks

Round bottomed **borosilicate glass flasks** from **Glassco** with **three jointed necks** - one in the centre and two angled at the side. Ideal for use in a range of laboratory applications.

- Available in a range of sizes



| Capacity | Centre socket | Side socket | Order code | Price |
|----------|---------------|-------------|------------|--------|
| 100ml | 19/26 | 14/23 | 52-1563 | £13.41 |
| 100ml | 24/29 | 14/23 | 52-1565 | £13.41 |
| 100ml | 24/29 | 19/26 | 52-1567 | £15.30 |
| 250ml | 19/26 | 14/23 | 52-1569 | £13.41 |
| 250ml | 19/26 | 19/26 | 52-1571 | £16.62 |
| 250ml | 24/29 | 14/23 | 52-1573 | £16.62 |
| 250ml | 24/29 | 19/26 | 52-1575 | £16.62 |
| 500ml | 24/29 | 14/23 | 52-1577 | £14.05 |
| 500ml | 24/29 | 19/26 | 52-1579 | £17.25 |
| 500ml | 29/32 | 14/23 | 52-1581 | £15.53 |
| 1000ml | 24/29 | 19/26 | 52-1583 | £23.15 |
| 1000ml | 24/29 | 19/26 | 52-1585 | £23.44 |
| 1000ml | 34/35 | 19/26 | 52-1587 | £25.73 |
| 2000ml | 24/29 | 19/26 | 52-1589 | £35.87 |
| 2000ml | 343/35 | 19/26 | 52-1591 | £37.42 |

567987



Wide Neck Flat Bottom Flasks

These **flat-bottomed flasks** from **Simax** have a **wide neck** with a rim and are suitable for use in a range of laboratory applications.

- Made from borosilicate glass
- Meets ISO 24450 standard
- Available in range of sizes
- Supplied in **packs of 10**



| Capacity | Overall dia. | Neck dia. | Height | Order code | Price |
|----------|--------------|-----------|--------|------------|---------|
| 50ml | 51mm | 34mm | 100mm | 52-2001 | £55.76 |
| 100ml | 64mm | 34mm | 110mm | 52-2003 | £83.97 |
| 250ml | 85mm | 50mm | 140mm | 52-2005 | £67.91 |
| 500ml | 105mm | 50mm | 170mm | 52-2007 | £80.33 |
| 1000ml | 131mm | 50mm | 200mm | 52-2009 | £104.09 |

568014



Pear Shape Single Neck Flasks

Pear-shaped **flasks** from **Glassco** with a **single neck** suitable for use in a number of laboratory applications.

- Made from borosilicate glass
- Available in a choice of sizes
- Supplied in **packs of 10**



| Capacity | Socket size | Height | Diameter | Order code | Price |
|----------|-------------|--------|----------|------------|--------|
| 50ml | 14/23 | 115mm | 50mm | 52-1803 | £36.18 |
| 50ml | 19/26 | 130mm | 50mm | 52-1805 | £83.30 |
| 100ml | 14/23 | 135mm | 60mm | 52-1809 | £36.99 |
| 100ml | 19/26 | 140mm | 60mm | 52-1827 | £36.64 |

567998



Round Bottom Distilling Flasks with Side Arm

These **distilling flasks** from **LabGlass** have a **round bottom** and a side arm.

- Available in a choice of sizes
- Made from borosilicate glass



| Capacity | Diameter | Height | Arm length | Order code | Price |
|----------|----------|--------|------------|------------|-------|
| 100ml | 64mm | 215mm | 100mm | 52-4163 | £3.04 |
| 250ml | 250mm | 225mm | 125mm | 52-4164 | £3.78 |
| 500ml | 105mm | 240mm | 140mm | 52-4165 | £4.99 |

567998

ALL NEW PRODUCTS



Conical Filtering Flasks with Plastic Screw and Integral Side Arm

These conical **filtering flasks** from **LabGlass** have an integral **plastic screw thread** side arm.

- Available in a choice of sizes
- Made from borosilicate glass



| Capacity | Order code | Price |
|----------|------------|-------|
| 250ml | 52-4167 | £4.79 |
| 500ml | 52-4168 | £6.37 |
| 1000ml | 52-4166 | £7.10 |

568068



Rapid We bring STEM to life
education

Round Base Cylinder Class B

ACADEMY

| Capacity | Academy | | | |
|----------|------------|------------|-----------|-------|
| | Order code | Unit Price | Pack Size | Price |
| 10ml | 52-1431 | £0.96 | 1 | £0.96 |
| 25ml | 52-1433 | £1.06 | 1 | £1.06 |
| 50ml | 52-1435 | £1.16 | 1 | £1.16 |
| 100ml | 52-1437 | £1.51 | 1 | £1.51 |
| 250ml | 52-1439 | £2.51 | 1 | £2.51 |
| 500ml | | | | |
| 1000ml | | | | |

| ALL NEW PRODUCTS | | | |
|------------------|------------|-----------|--------|
| LabGlass | | | |
| Order code | Unit Price | Pack Size | Price |
| 52-4122 | £0.85 | 10 | £8.52 |
| 52-4125 | £1.10 | 2 | £2.19 |
| 52-4127 | £1.26 | 2 | £2.52 |
| 52-4121 | £1.56 | 2 | £3.12 |
| 52-4124 | £2.44 | 2 | £4.87 |
| 52-4126 | £3.60 | 2 | £7.19 |
| 52-4123 | £6.45 | 2 | £12.89 |




Hexagonal Base Cylinder Class B

SIMAX®

| ALL NEW PRODUCTS | | | | |
|------------------|------------|------------|-----------|--------|
| LabGlass | | | | |
| Capacity | Order code | Unit Price | Pack Size | Price |
| 5ml | 52-4116 | £1.22 | 2 | £2.44 |
| 10ml | 52-4117 | £1.33 | 2 | £2.65 |
| 25ml | 52-4120 | £2.34 | 2 | £4.68 |
| 50ml | 52-4115 | £2.86 | 2 | £5.71 |
| 100ml | 52-4114 | £2.65 | 2 | £5.30 |
| 250ml | 52-4119 | £4.02 | 2 | £8.04 |
| 500ml | 52-4113 | £6.05 | 2 | £12.10 |
| 2000ml | 52-4118 | £15.44 | 1 | £15.44 |

| Simax | | | |
|------------|------------|-----------|--------|
| Order code | Unit Price | Pack Size | Price |
| 52-0192 | £3.88 | 1 | £3.88 |
| 52-0196 | £3.95 | 1 | £3.95 |
| 52-0198 | £4.75 | 1 | £4.75 |
| 52-0200 | £6.01 | 1 | £6.01 |
| N 52-1205 | £10.19 | 1 | £10.19 |



Round Base

Hexagonal Base

NEW LINES ADDED



Hexagonal Base Cylinder with Spout Class A

These measuring cylinders from LabGlass have a hexagonal base and spout.

- Available in a choice of sizes
- White graduation
- Made from borosilicate glass
- Class A
- Complies with DIN EN ISO 4788 standard
- Supplied in packs of 2 (except 2 litre version)



| ALL NEW PRODUCTS | | | | | |
|------------------|------------|--------------|------------|-----------|--------|
| Capacity | Order code | Sub-division | Unit price | Pack size | Price |
| 5ml | 52-4108 | 0.1ml | £2.33 | 2 | £4.66 |
| 10ml | 52-4109 | 0.2ml | £2.24 | 2 | £4.47 |
| 25ml | 52-4110 | 0.25ml | £3.66 | 2 | £7.31 |
| 50ml | 52-4107 | 1ml | £4.30 | 2 | £8.59 |
| 100ml | 52-4099 | 1ml | £4.96 | 2 | £9.92 |
| 250ml | 52-4111 | 2ml | £6.86 | 2 | £13.71 |
| 500ml | 52-4098 | 5ml | £10.49 | 2 | £20.97 |
| 1000ml | 52-4097 | 10ml | £12.79 | 2 | £25.58 |
| 2000ml | 52-4112 | 20ml | £20.10 | 1 | £20.10 |

568061



Squat Form Hexagonal Base Cylinder with Spout Class B

Squat form measuring cylinders from LabGlass with a hexagonal base and spout.

- Available in a choice of sizes
- White graduation
- Made from borosilicate glass
- Class B
- Supplied in packs of 2



| ALL NEW PRODUCTS | | | | | |
|------------------|------------|--------------|------------|-----------|--------|
| Capacity | Order code | Sub-division | Unit price | Pack size | Price |
| 50ml | 52-4096 | 1ml | £3.80 | 2 | £7.59 |
| 100ml | 52-4094 | 2ml | £4.77 | 2 | £9.53 |
| 250ml | 52-4095 | 5ml | £5.48 | 2 | £10.96 |

568060



SIMAX®

Desiccator

Desiccator from Simax with a knobbed lid and a perforated ceramic disc ideal for laboratory use.

- Made from borosilicate glass
- Size 200mm
- Overall diameter 269mm
- Base diameter 190mm
- Manufacturer's part 262D/200

Order code
52-1987
200mm

£82.28

Test Tubes



Test Tubes and Boiling Tubes with Rims

These **test tubes** from **Kimble Chase** are manufactured from borosilicate glass tubing and can be used for a wide range of applications. They are designed for **maximum heat transfer** and chemical resistance.

- Wall thickness between 0.8 to 1.0mm
- Smaller tubes are supplied in **packs of 100**
- 24 x 150mm tubes are supplied in **packs of 50**

| Size | Quantity | Order code | 1+ |
|------------|----------|----------------|-------|
| 10 x 75mm | 100 | 52-1895 | 15.64 |
| 12 x 75mm | 100 | 52-1254 | 14.78 |
| 16 x 100mm | 100 | 52-1255 | 23.98 |
| 16 x 125mm | 100 | 52-1900 | 31.62 |
| 16 x 150mm | 100 | 52-1897 | 31.04 |
| 24 x 150mm | 50 | 52-1902 | 24.83 |



Test Tubes with Side Arms

These test tubes are made from Borosilicate glass and feature a side arm.

- Available in various sizes

| Length/dia. | Order code | 1+ |
|-------------|----------------|-------|
| 125 x 17mm | 52-1282 | 0.889 |
| 150 x 19mm | 52-1284 | 1.11 |
| 150 x 24mm | 52-1286 | 1.56 |



Plain Disposable Culture Tubes

These plain disposable **culture tubes** from **Kimble Chase** have a rim top and are made from borosilicate glass.

- Available in a range of sizes
- Supplied in **packs of 1000** (500 for 18 x 150mm)

| Size | Quantity | Order code | 1+ |
|------------|----------|----------------|-------|
| 10 x 75mm | 1000 | 52-1257 | 33.19 |
| 12 x 75mm | 1000 | 52-1259 | 35.45 |
| 13 x 100mm | 1000 | 52-1261 | 49.31 |
| 16 x 125mm | 1000 | 52-1263 | 74.93 |
| 16 x 150mm | 1000 | 52-1276 | 76.95 |
| 18 x 150mm | 500 | 52-1279 | 88.16 |



Absorption Tubes 150 x 20mm (Pack of 2)

A borosilicate glass U-form absorption tube, with strong walls and side tubes. Absorption tubes are commonly used with calcium chloride or other desiccants to remove moisture from gases passed through them.



- Length 150mm
- Diameter 20mm
- Supplied in **packs of 2**
- **Eisco type CH0042C**

| Type | Order code | 1+ |
|-----------------|----------------|------|
| Absorption tube | 52-3432 | 4.78 |

Test Tube Brushes



Test Tube Brushes



Brushes for cleaning test tubes and other tubular equipment.

- High quality bristles mounted in heavy gauge twisted galvanised wire
- Wire handles can be bent to clean awkward shapes
- Available in a range of sizes
- Supplied **singly**

| Type | Overall length | Brush area size | Order code | MOQ 4 |
|-------|----------------|-----------------|----------------|-------|
| Small | 150mm | 50x17mm dia. | 52-8048 | 0.257 |

| Type | Order code | MOQ 3 |
|--------|----------------|-------|
| Medium | 52-8050 | 0.413 |

| Type | Order code | MOQ 2 |
|-------|----------------|-------|
| Large | 52-8052 | 0.498 |



Cleaning Brushes for Laboratory Glassware and Plasticware

Cleaning brushes for beakers, burettes, test tubes, measuring cylinders and many other items of other laboratory glassware and plasticware. The hard nylon bristles are mounted in twisted galvanised iron wire.



- Suitable for beakers, burettes, test tubes, measuring cylinders and many other items of other laboratory glassware and plasticware
- Hard nylon bristles, mounted in twisted galvanised iron wire

| Type | Order code | MOQ 2 |
|--------------|----------------|-------|
| Beaker Brush | 52-8053 | 0.592 |

| Type | Order code | Price each |
|---------------|----------------|------------|
| Burette Brush | 52-8055 | 0.549 |

| Type | Order code | MOQ 2 |
|-----------------|----------------|-------|
| Test Tube Brush | 52-8057 | 0.75 |



Flask, Bottle, Burette and Beaker Brushes

A range of brushes for cleaning laboratory equipment.

| Type | Order code | 1+ |
|----------------------|----------------|-------|
| Flask / bottle brush | 52-3451 | 0.802 |
| Burette brush | 52-3452 | 0.712 |
| Economy beaker brush | 52-3524 | 5.40 |
| Nylon beaker brush | 52-3525 | 1.43 |



Drying Tubes



Angled Glass Drying Tubes

These **angled drying tubes** from **Glassco** are suitable for use with other laboratory equipment.

- Made from borosilicate glass
- Available in a range of sizes



| Size | Order code | 1+ |
|-------|----------------|------|
| 10/19 | 52-1873 | 5.66 |
| 14/23 | 52-1877 | 5.66 |
| 19/26 | 52-1879 | 6.43 |
| 24/29 | 52-1881 | 7.07 |
| 29/32 | 52-1883 | 7.07 |

Test Tube Holders



Wooden Test Tubes Holders with Spring (Pack of 10)

A 180mm long clothes peg-style, wooden test tube holder.

- Accepts 11 to 19mm diameter test tubes
- Jaws open to 32mm
- Made from wood with a metal spring
- Supplied in **packs of 10**
- **Eisco type CH0726A**

Test tube not included.



| Type | Order code | 1+ |
|-------------------|----------------|------|
| Test tube holders | 52-3386 | 3.99 |



Metal Test Tube Holder

A Stoddard's pattern test tube holder ideal for students.



- Spring action clamps tubes in place
- Finger grips for safe holding
- Holds tubes up to 25mm diameter
- Nickel plated steel construction
- Overall length 130mm

| Type | Order code | MOQ 2 |
|------------------|----------------|-------|
| Test tube holder | 52-8040 | 0.35 |

Order online

Save time, and place your order at:
www.rapidonline.com

Expansion Adapters



| Glassco | | | | |
|--------------|------------|------------|-----------|---------------|
| Joints Size | Order code | Unit Price | Pack Size | Price |
| 14/23, 10/19 | 52-1611 | £8.114 | 10 | £81.14 |
| 19/26, 14/23 | 52-1613 | £4.361 | 10 | £43.61 |
| 24/29, 14/23 | 52-1615 | £4.361 | 10 | £43.61 |
| 24/29, 19/26 | 52-1617 | £4.361 | 10 | £43.61 |
| 29/32, 14/23 | 52-1619 | £5.279 | 10 | £52.79 |
| 29/32, 19/26 | 52-1629 | £5.279 | 10 | £52.79 |
| 29/32, 24/29 | 52-1631 | £5.279 | 10 | £52.79 |
| 34/35, 19/26 | 52-1633 | £5.93 | 1 | £5.93 |
| 34/35, 24/29 | 52-1635 | £5.93 | 1 | £5.93 |
| 34/35, 29/32 | 52-1637 | £8.19 | 1 | £8.19 |
| 40/38, 29/32 | 52-1639 | £11.21 | 1 | £11.21 |

| A PLUS | | | |
|------------|------------|-----------|---------------|
| Order code | Unit Price | Pack Size | Price |
| 52-1349 | £9.50 | 1 | £9.50 |
| 52-1387 | £8.68 | 1 | £8.68 |
| 52-1388 | £8.68 | 1 | £8.68 |
| 52-1389 | £11.69 | 1 | £11.69 |
| 52-1390 | £11.87 | 1 | £11.87 |



Reduction Adapters



| Glassco | | | | |
|--------------|------------|------------|-----------|----------------|
| Joints Size | Order code | Unit Price | Pack Size | Price |
| 10/19, 14/23 | 52-1641 | £5.02 | 10 | £50.22 |
| 14/23, 19/26 | 52-1643 | £4.47 | 10 | £44.69 |
| 14/23, 24/29 | 52-1645 | £4.47 | 10 | £44.69 |
| 14/23, 29/32 | 52-1647 | £4.47 | 10 | £44.69 |
| 19/26, 24/29 | 52-1649 | £4.47 | 10 | £44.69 |
| 19/26, 29/32 | 52-1651 | £4.67 | 10 | £46.71 |
| 19/26, 34/35 | 52-1653 | £5.83 | 10 | £58.32 |
| 19/26, 40/38 | 52-1655 | £7.02 | 10 | £70.20 |
| 19/26, 45/40 | 52-1657 | £7.79 | 10 | £77.90 |
| 24/29, 29/32 | 52-1659 | £4.67 | 10 | £46.71 |
| 24/29, 34/35 | 52-1661 | £5.95 | 10 | £59.54 |
| 24/29, 40/38 | 52-1663 | £7.02 | 10 | £70.20 |
| 24/29, 45/40 | 52-1665 | £8.07 | 10 | £80.73 |
| 24/29, 50/42 | 52-1667 | £7.66 | 10 | £76.55 |
| 29/32, 34/35 | 52-1669 | £5.66 | 10 | £56.57 |
| 29/32, 45/40 | 52-1671 | £10.14 | 10 | £101.39 |
| 34/35, 40/38 | 52-1673 | £8.84 | 10 | £88.43 |
| 34/35, 45/40 | 52-1675 | £12.38 | 10 | £123.80 |
| 34/35, 50/42 | 52-1677 | £12.38 | 10 | £123.80 |

| A PLUS | | | |
|------------|------------|-----------|--------------|
| Order code | Unit Price | Pack Size | Price |
| 52-1391 | £6.73 | 1 | £6.73 |
| 52-1392 | £6.73 | 1 | £6.73 |
| 52-1393 | £6.73 | 1 | £6.73 |
| 52-1394 | £6.73 | 1 | £6.73 |



ALL NEW PRODUCTS



Jointed Adaptors with Drying Tube

Jointed glass adaptors from A PLUS with a drying tube set at a 75° angle.

- Available in choice of sizes



| Joint | Order code | 1+ |
|-------|------------|---------------|
| 14/23 | 52-1427 | £10.66 |
| 19/26 | 52-1429 | £11.38 |

For full details visit
www.rapidonline.com



Jointed Liebig Condensers and Connectors

These glass Liebig condensers from A PLUS have removable hose connections and can be used to cool and condense hot vapour as part of a laboratory distilling apparatus.

- Available in a choice of sizes




| Overall height | Order code | 1+ |
|----------------|------------|---------------|
| 200mm | 52-1398 | £22.00 |
| 280mm | 52-1397 | £20.66 |
| 300mm | 52-1399 | £23.36 |



Liebig Condensers

These glass Liebig condensers from A PLUS are suitable for use to cool and condense hot vapour as part of a laboratory distilling apparatus.

- Available in a choice of sizes



| Overall height | Order code | 1+ |
|----------------|------------|---------------|
| 280mm | 52-1395 | £19.30 |
| 330mm | 52-1396 | £19.76 |



Glass Still Head Adaptors

These glass still head adaptors from A PLUS are suitable for use in connecting a flask with a condenser in a laboratory distillation assembly.

- Available in a choice of sizes



| Technical specification | | | |
|-------------------------|-----------|--------------|------------|
| Order code | Top joint | Bottom joint | Side joint |
| 52-1401 | 14/23 | 14/23 | 14/23 |
| 52-1403 | 19/26 | 19/26 | 19/26 |
| 52-1405 | 24/29 | 24/29 | 24/29 |
| 52-1407 | 14/23 | 24/29 | 19/26 |

| Top joint | Bottom joint | Order code | 1+ |
|-----------|--------------|------------|---------------|
| 14/23 | 14/23 | 52-1401 | £13.00 |
| 19/26 | 19/26 | 52-1403 | £14.27 |
| 24/29 | 24/29 | 52-1405 | £15.47 |
| 14/23 | 24/29 | 52-1407 | £16.47 |



Vacuum/Inert Gas Adaptors

These glass vacuum/inert gas adaptors from A PLUS are ideal for use in a number of laboratory applications.

- Available in a choice of sizes



| Technical specification | | | |
|-------------------------|--------------------|------------|--|
| Order code | Hose diameter (OD) | Joint size | |
| 52-1346 | 8mm | 14/23 | |
| 52-1347 | 8mm | 19/26 | |
| 52-1348 | 10mm | 24/29 | |

| Joint | Hose diameter | Order code | 1+ |
|-------|---------------|------------|--------------|
| 14/23 | 8mm | 52-1346 | £9.11 |
| 19/26 | 8mm | 52-1347 | £8.63 |
| 24/29 | 10mm | 52-1348 | £8.70 |

Jointed Round Bottom Flask Single Neck

| Capacity | Joint Size | Glassco | | | | A PLUS | | | |
|----------|------------|------------|------------|-----------|---------|------------|------------|-----------|--------|
| | | Order code | Unit Price | Pack Size | Price | Order code | Unit Price | Pack Size | Price |
| 5ml | 14/23 | 52-1467 | £3.58 | 10 | £35.75 | 52-1281 | £6.40 | 1 | £6.40 |
| 10ml | 10/19 | 52-1469 | £4.05 | 10 | £40.50 | | | | |
| 10ml | 14/23 | 52-1471 | £4.05 | 10 | £40.50 | 52-1283 | £6.40 | 1 | £6.40 |
| 25ml | 14/23 | 52-1473 | £4.17 | 10 | £41.72 | 52-1285 | £6.26 | 1 | £6.26 |
| 25ml | 19/26 | 52-1475 | £4.17 | 10 | £41.72 | 52-1287 | £6.26 | 1 | £6.26 |
| 25ml | 24/29 | 52-1477 | £4.17 | 10 | £41.72 | 52-1289 | £6.26 | 1 | £6.26 |
| 50ml | 14/23 | 52-1479 | £4.64 | 10 | £46.44 | 52-1291 | £6.70 | 1 | £6.70 |
| 50ml | 19/26 | 52-1481 | £4.64 | 10 | £46.44 | 52-1293 | £7.78 | 1 | £7.78 |
| 50ml | 24/29 | 52-1483 | £4.64 | 10 | £46.44 | 52-1295 | £7.78 | 1 | £7.78 |
| 50ml | 34/35 | 52-1485 | £5.95 | 10 | £59.54 | | | | |
| 100ml | 14/23 | 52-1487 | £4.19 | 10 | £41.85 | 52-1297 | £8.32 | 1 | £8.32 |
| 100ml | 19/26 | 52-1489 | £4.19 | 10 | £41.85 | 52-1299 | £8.32 | 1 | £8.32 |
| 100ml | 24/29 | 52-1491 | £4.19 | 10 | £41.85 | 52-1301 | £8.32 | 1 | £8.32 |
| 100ml | 29/32 | 52-1493 | £5.10 | 10 | £51.03 | 52-1303 | £8.32 | 1 | £8.32 |
| 100ml | 34/35 | 52-1495 | £5.54 | 10 | £55.35 | | | | |
| 150ml | 19/26 | 52-1497 | £5.16 | 10 | £51.57 | | | | |
| 150ml | 24/29 | 52-1499 | £5.16 | 10 | £51.57 | | | | |
| 250ml | 14/23 | 52-1501 | £5.13 | 10 | £51.30 | | | | |
| 250ml | 19/26 | 52-1503 | £5.13 | 10 | £51.30 | 52-1309 | £9.80 | 1 | £9.80 |
| 250ml | 24/29 | 52-1505 | £5.13 | 10 | £51.30 | 52-1311 | £9.80 | 1 | £9.80 |
| 250ml | 29/32 | 52-1507 | £5.13 | 10 | £51.30 | 52-1313 | £10.89 | 1 | £10.89 |
| 250ml | 34/35 | 52-1509 | £7.02 | 10 | £70.20 | | | | |
| 500ml | 19/26 | 52-1511 | £7.07 | 10 | £70.74 | 52-1315 | £12.38 | 1 | £12.38 |
| 500ml | 24/29 | 52-1513 | £7.07 | 10 | £70.74 | 52-1317 | £12.38 | 1 | £12.38 |
| 500ml | 29/32 | 52-1515 | £7.07 | 10 | £70.74 | 52-1319 | £12.38 | 1 | £12.38 |
| 500ml | 34/35 | 52-1517 | £7.63 | 10 | £76.28 | | | | |
| 500ml | 45/40 | 52-1519 | £10.23 | 10 | £102.33 | | | | |
| 1000ml | 19/26 | 52-1521 | £9.77 | 10 | £97.74 | | | | |
| 1000ml | 24/29 | 52-1523 | £9.77 | 10 | £97.74 | | | | |
| 1000ml | 29/32 | 52-1525 | £9.91 | 10 | £99.09 | | | | |
| 1000ml | 34/35 | 52-1527 | £10.76 | 10 | £107.60 | | | | |
| 2000ml | 24/29 | 52-1529 | £17.24 | 10 | £172.40 | | | | |
| 2000ml | 29/32 | 52-1531 | £17.47 | 10 | £174.69 | | | | |
| 2000ml | 34/35 | 52-1533 | £18.12 | 10 | £181.17 | | | | |
| 3000ml | 24/29 | 52-1535 | £29.32 | 1 | £29.32 | | | | |
| 3000ml | 34/35 | 52-1537 | £29.92 | 1 | £29.92 | | | | |
| 5000ml | 29/32 | 52-1539 | £38.62 | 1 | £38.62 | | | | |
| 5000ml | 34/35 | 52-1541 | £39.38 | 1 | £39.38 | | | | |
| 5000ml | 45/40 | 52-1543 | £39.81 | 1 | £39.81 | | | | |



ALL NEW PRODUCTS



Jointed Round Bottom Flask Two Necks

| Capacity | Centre Joint | Side Joint | Glassco | | | | A PLUS | | | |
|----------|--------------|------------|------------|------------|-----------|--------|------------|------------|-----------|--------|
| | | | Order code | Unit Price | Pack Size | Price | Order code | Unit Price | Pack Size | Price |
| 100ml | 14/23 | 14/23 | | | | | 52-1321 | £17.00 | 1 | £17.00 |
| 100ml | 14/23 | 14/23 | 52-1545 | £8.78 | 1 | £8.78 | 52-1323 | £17.06 | 1 | £17.06 |
| 100ml | 24/29 | 14/23 | 52-1547 | £10.76 | 1 | £10.76 | 52-1325 | £17.06 | 1 | £17.06 |
| 100ml | 24/29 | 19/26 | 52-1549 | £12.20 | 1 | £12.20 | 52-1327 | £17.06 | 1 | £17.06 |
| 250ml | 24/29 | 14/23 | 52-1551 | £9.53 | 1 | £9.53 | | | | |
| 250ml | 24/29 | 19/26 | 52-1553 | £10.23 | 1 | £10.23 | 52-1329 | £17.14 | 1 | £17.14 |
| 500ml | 24/29 | 14/23 | 52-1555 | £10.54 | 1 | £10.54 | | | | |
| 500ml | 24/29 | 19/26 | 52-1557 | £11.92 | 1 | £11.92 | | | | |
| 1000ml | 24/29 | 14/23 | 52-1559 | £12.57 | 1 | £12.57 | | | | |
| 1000ml | 24/29 | 19/26 | 52-1561 | £22.57 | 1 | £22.57 | | | | |



Jointed Glassware



Glassware Joint Clips

These plastic **joint clips** from **Eisco** are resistant to both temperature and chemicals and are ideal for holding together jointed laboratory glassware, reducing the need for **clamping**.

- Colour: yellow
- Joint size 14/23
- Recommended maximum temperature through joint 80°C
- Supplied in **packs of 10**
- Manufacturer's part **CH0869B**

| Type | Order code | 1+ |
|-------------|----------------|-------|
| Joint clips | 52-4187 | 10.22 |

568093



Plastic Joint Clips

Conical **joint clips** from **Glassco** designed to hold laboratory equipment in place.

- Available in a range of colours
- Supplied in **packs of 10**

| Colour | Size | Order code | 1+ |
|--------|-------|----------------|-------|
| Black | 10/19 | 52-1917 | 14.58 |
| Violet | 12/21 | 52-1919 | 14.58 |
| Yellow | 14/23 | 52-1921 | 14.58 |
| Blue | 19/26 | 52-1923 | 14.04 |
| Green | 24/29 | 52-1925 | 14.58 |
| Red | 29/32 | 52-1927 | 14.58 |
| Orange | 34/35 | 52-1929 | 16.07 |

568003



Organic Chemistry Sets



These **organic chemistry** sets from **Glassco** include the glassware and other equipment required to conduct increasingly complex experiments, ranging from basic preparations to **advanced** level.

- Equipment made from borosilicate glass
- Visit www.rapidonline.com for full list of contents

| Type | Order code | 1+ |
|--------|----------------|-------|
| Set 1 | 52-1931 | 32.36 |
| Set 2 | 52-1933 | 58.09 |
| Set 7 | 52-1935 | 98.09 |
| Set 27 | 52-1947 | 58.81 |

568004



Interchangeable Glassware Organic Chemistry Kit

A 9-piece set of borosilicate 3.3 glassware for organic chemistry experiments. All items use an ISO 383 standard taper 14/23 joint size for maximum versatility. The set is housed in a die-cut foam-lined storage box.



Kit contains:

- 1x flask, pear shaped, 50ml
- 1x still head
- 1x Liebig condenser
- 1x screw-cap adapter
- 1x receiver adaptor
- 1x air leak / steam inlet tube
- 1x dropping funnel 50ml with GP rota-flow tap
- 1x stopper
- 1x -10 to +110°C thermometer
- Supplied as a **set**
- Borosilicate 3.3 glass
- ISO 383 standard taper 14/23 joint size
- **Eisco type CH0876**

| Type | Order code | 1+ |
|---------------|----------------|-------|
| Glassware kit | 52-3439 | 38.99 |

565588

Glass Tubing



Glass Tubing Cutter

This rugged laboratory glass tube cutter is made from nickel-plated, die-cast metal.

It is fitted with a spring-loaded steel wheel and can cut glass tubes up to 40mm in diameter.

- Nickel-plated, die-cast metal
- Spring-loaded steel wheel
- Cuts glass tubes up to 40mm dia.
- **Eisco type CH0759SUP**

| Type | Order code | 1+ |
|---------------------|----------------|------|
| Glass tubing cutter | 52-3569 | 5.42 |

565632



Soda Glass Tubing

This **soda glass tubing** is ideal for use in the science laboratory.

- Available in 5mm and 6mm diameter
- Length 0.5m
- Supplied in **packs of 30**

| Diameter | Order code | 1+ |
|----------|----------------|-------|
| 5mm | 52-2751 | 14.99 |
| 6mm | 52-2752 | 15.84 |

565637



Polypropylene Cross Tubing Connectors

This 4-way cross-shaped **connector** from **Eisco** can be used to produce leakproof joints in **tubing** for laboratory equipment.

- Made from polypropylene
- Outside diameter 10mm
- Manufacturer's part **CH0765G**

| Outer diameter | Order code | 1+ |
|----------------|----------------|------|
| 10mm | 52-4214 | 0.58 |

568101



Bottles



Clear Dropping Bottles 50ml

These 50ml clear soda-lime glass dropping bottles have a stopper size of 14.5/23.

- Supplied **singly**

| Type | Order code | 1+ |
|-------------|----------------|------|
| 50ml single | 52-0837 | 2.64 |

066601



Powder Glass Bottles

These clear glass **powder bottles** from **Academy** have an attached **black polypropylene cap** and EPE liner.

- Wide neck
- Made from soda-lime glass
- Available in a choice of sizes

| Order code | Capacity | Diameter | Height | Mfrs part no. |
|----------------|----------|----------|--------|---------------|
| 52-1989 | 30ml | 38.9mm | 58.7mm | BCP030C-10 |
| 52-1988 | 120ml | 55.2mm | 96mm | BCP0120C-10 |

| Capacity | Order code | 1+ |
|----------|-----------------|------|
| 30ml | 52-1989 | 3.10 |
| 120ml | 52-1988 | 3.80 |
| 125ml | N56-5518 | 5.95 |

568011



Reagent Bottles

Plain clear glass reagent bottles, with narrow neck and dustproof plastic stopper.

- Supplied in **packs of 10**

| Contents | Order code | 1+ |
|----------|----------------|-------|
| 50ml | 52-0226 | 12.55 |
| 250ml | 52-0230 | 17.05 |
| 500ml | 52-1061 | 26.81 |

066602



SIMAX

Clear Graduated Laboratory Bottles



Clear, graduated laboratory bottles with screw caps.

- Borosilicate glass
- Complete with blue screw cap and pouring ring
- Conform to **ISO 4796** and **ISO -GL 45**
- Supplied in **packs of 10**

| Capacity | Order code | 1+ |
|----------|----------------|-------|
| 50ml | 52-1203 | 28.75 |
| 100ml | 52-0986 | 19.72 |
| 250ml | 52-0988 | 19.43 |
| 500ml | 52-0990 | 26.73 |
| 1000ml | 52-0992 | 37.93 |

073137

Gas Washing Bottles

SIMAX

Gas Washing Bottles

Simax gas washing bottles manufactured from borosilicate glass.

- Capacity 100ml
- Overall height 250mm
- Height of bottle 200mm
- Inlet/outlet pipe diameter 8mm
- Supplied **singly**



| Type | Order code | 1+ |
|-------|----------------|-------|
| 100ml | 52-0982 | 17.92 |

073136



Distilling Apparatus

A set of high quality borosilicate glassware ideal for distillation experiments.

- All joint sizes are 19/26
- **Set includes the following glass components:**
- Round-bottom boiling flask 500ml
- Still head
- Liebig condenser
- Receiver adapter
- Separating funnel with stopper
- Supplied as a set



Please note that no tubing, heat source or stands are included.

| Type | Order code | 1+ |
|----------------------|----------------|-------|
| Distilling glassware | 52-3438 | 54.89 |

565587

Crystallising Dishes

SIMAX

Glass Crystallising Dishes with Flat Bottom and No Spout

Crystallising dishes from Simax with a flat bottom but without a spout, ideal for use in laboratory applications.

- Available in a range of sizes
- Made from borosilicate glass
- Conforms to PN 70 0121



| Order code | Capacity | Size (D x H) | Quantity | Mfrs part no. |
|----------------|----------|--------------|----------|---------------|
| 52-1207 | 20ml | 40 x 25mm | 10 | 174/40 |
| 52-1209 | 40ml | 50 x 30mm | 10 | 174/50 |
| 52-1211 | 60ml | 60 x 35mm | 10 | 174/60 |
| 52-1213 | 100ml | 70 x 40mm | 10 | 174/70 |
| 52-1215 | 150ml | 80 x 45mm | 10 | 174/80 |
| 52-1217 | 300ml | 95 x 55mm | 10 | 174/95 |
| 52-1219 | 500ml | 115 x 65mm | 10 | 174/115 |
| 52-1221 | 900ml | 140 x 75mm | 10 | 174/140 |
| 52-1223 | 2000ml | 190 x 90mm | 4 | 174/190 |
| 52-1225 | 3500ml | 230 x 100mm | 4 | 174/230 |

| Capacity | Diameter | Order code | 1+ |
|--------------------|----------|----------------|--------|
| Packs of 10 | | | |
| 20ml | 40mm | 52-1207 | 54.27 |
| 40ml | 50mm | 52-1209 | 48.47 |
| 60ml | 60mm | 52-1211 | 44.42 |
| 100ml | 70mm | 52-1213 | 73.31 |
| 150ml | 80mm | 52-1215 | 54.27 |
| 300ml | 95mm | 52-1217 | 68.45 |
| 500ml | 115mm | 52-1219 | 93.69 |
| 900ml | 140mm | 52-1221 | 119.61 |
| Packs of 4 | | | |
| 2000ml | 190mm | 52-1223 | 100.17 |
| 3500ml | 230mm | 52-1225 | 108.30 |

567970

Coplin Jars

ACADEMY

Glass Coplin Jar

This coplin jar from Academy can be used to stain cells and tissues on microscope slides.

- Made from soda-lime glass
- Height 115mm
- Diameter 90mm
- Supplied in **packs of 10**
- Manufacturer's part **2959**



| Size (H x D) | Order code | 1+ |
|--------------|----------------|------|
| 115 x 90mm | 52-1093 | 5.62 |

567968

Watch Glass

eisco

Watch Glasses

Watch glasses are highly functional items of glassware that have a variety of uses in the classroom or laboratory. They work well as lids for flasks and beakers, or for holding small samples for observation under a low-power microscope. They are also ideal for evaporating liquids from samples, such as when growing seed crystals, and can be used for making lenses from ice or other liquids.

Eisco watch glasses are manufactured with sturdiness in mind. Their 2mm thick construction resists shattering and as they have ground edges, as well as a polished surface, so you can be sure that they are a safe product to handle in the classroom or the laboratory.

- Available in a range of diameters
- **Eisco CH0554 series**

| Diameter | Order code | 1+ |
|----------|----------------|-------|
| 50mm | 52-3467 | 1.73 |
| 60mm | 52-3559 | 2.03 |
| 75mm | 52-3468 | 3.36 |
| 90mm | 52-3469 | 3.93 |
| 100mm | 52-3470 | 4.28 |
| 125mm | 52-3560 | 10.00 |
| 150mm | 52-3561 | 5.59 |

565603

Glass Filter Funnels

RVFM

Long Stem Borosilicate Glass Filter Funnels

Borosilicate glass laboratory funnels with long stems. The longer, non-tapering stems of these funnels are useful when using funnels with tubing and when mounting them in bungs for use with flasks, bottles and retorts, etc.

- Can be used with folded circular filter paper
- Available in a range of diameters



| Technical specification | Stem Diameter (mm) | Order code |
|-------------------------|--------------------|----------------|
| Diameter (mm) | | |
| 50 | 7 | 52-0909 |
| 75 | 8 | 52-0911 |
| 100 | 9 | 52-0913 |
| 125 | 16 | 52-0915 |
| 150 | 16 | 52-0917 |

| Type | Order code | 1+ |
|--------------|----------------|------|
| 50mm single | 52-0909 | 1.26 |
| 75mm single | 52-0911 | 2.02 |
| 125mm single | 52-0915 | 3.70 |
| 150mm single | 52-0917 | 5.57 |

500177



Borosilicate Glass Filter Funnels

Borosilicate glass, plain filter funnels with 60° angled sides.

The shape of the funnels makes them ideal for use with a folded circular filter paper.

- Borosilicate 3.3 glass



| Diameter | Order code | 1+ |
|----------|----------------|------|
| 55mm | 52-3465 | 1.19 |
| 75mm | 52-3466 | 1.25 |

565602

Evaporating Dishes



Porcelain Evaporating Dishes

Superior quality porcelain round-form evaporating dishes with pouring spout. The dishes are fully glazed except for the outside base.

- Eisco CH0071 series

| Capacity | Order code | 1+ |
|----------|----------------|------|
| 80ml | 52-3378 | 0.72 |
| 100ml | 52-3379 | 0.81 |

565554



Evaporating Basins - Porcelain Flat Form with Spout

A range of porcelain flat-form evaporating basins.

- Glazed inside and outside except for rim
- Spout for easy pouring
- Eisco CH0070 series

| Capacity | Order code | 1+ |
|----------|----------------|------|
| 35ml | 52-3519 | 0.81 |
| 50ml | 52-3520 | 0.92 |
| 200ml | 52-3522 | 1.19 |
| 300ml | 52-3523 | 2.44 |

565627



Porcelain Hirsch Separating Funnels



Hirsch funnels are used for straining and filtering liquids or for separating solids and liquids.

This range is made from porcelain for minimum contamination and ease of cleaning. They can be used in conjunction with filter paper for superior separation.

- Angled sides
- Glazed
- Perforated plate

Technical specification

| Eisco type | Top outside dia. | Filter paper dia. | Approx. capacity | Overall length | Order code |
|------------|------------------|-------------------|------------------|----------------|----------------|
| CH0465B | 42mm | 8 to 10mm | 10ml | 70mm | 52-3563 |
| CH0465C | 55mm | 13 to 15mm | 20ml | 75mm | 52-3564 |
| CH0465D | 78mm | 40 to 45mm | 50ml | 130mm | 52-3565 |
| CH0465E | 96mm | 52-56mm | 130ml | 175mm | 52-3566 |

| Diameter | Order code | 1+ |
|----------|----------------|------|
| 30mm | 52-3562 | 0.92 |
| 40mm | 52-3563 | 1.07 |
| 50mm | 52-3564 | 1.48 |
| 75mm | 52-3565 | 2.22 |
| 100mm | 52-3566 | 2.36 |

565631



Porcelain Buchner Funnels

Buchner Funnels are used for straining and filtering liquids or for separating solids and liquids. This range is made from porcelain for minimum contamination and ease of cleaning. They can be used in conjunction with filter paper for superior separation.



- Straight sides
- Perforated plate
- Used for straining and filtering liquids or separating solids and liquids
- Made from porcelain for minimum contamination and easy cleaning
- Can be used in conjunction with filter paper for superior separation
- Available in a range of diameters

| Type | Order code | 1+ |
|-------|----------------|------|
| 50mm | 52-1937 | 2.42 |
| 125mm | 52-1945 | 7.59 |

501854

Pestle & Mortars



Porcelain Mortars & Pestles

A range of porcelain mortars and pestles with unglazed grinding surfaces.

- Supplied as a set containing one mortar and one pestle



| Mortar capacity | Order code | 1+ |
|-----------------|----------------|-------|
| 60ml | 52-3571 | 1.22 |
| 275ml | 52-3572 | 2.52 |
| 550ml | 52-3573 | 4.04 |
| 900ml | 52-3574 | 4.38 |
| 1500ml | 52-3575 | 5.27 |
| 2000ml | 52-3576 | 10.21 |

565633

Crucibles



Crucibles - Tall

A range of tall-form porcelain crucibles and lids with ring handle.

- Glazed inside and outside except base
- Eisco CH0074 series

| Capacity | Order code | 1+ |
|----------|----------------|------|
| 10ml | 52-3542 | 0.61 |
| 25ml | 52-3543 | 0.73 |
| 40ml | 52-3544 | 0.86 |
| 50ml | 52-3545 | 0.99 |
| 100ml | 52-3546 | 1.22 |

565629



Funnels & Holders



100mm Polythene Funnel

This unbreakable polythene laboratory funnel is unaffected by acids and alkalis, etc.

- Diameter 100mm
- Stem length 80mm
- Eisco type CH0454D



| Type | Order code | 1+ |
|----------------------|----------------|------|
| 100mm plastic funnel | 52-3419 | 0.36 |

565517



Economy Plastic Funnels

A range of economical funnels suitable for a wide range of applications in the laboratory. The funnels are made from unbreakable plastic, making them ideal for younger scientists.

- Economical
- Unbreakable plastic
- Wide range of uses



| Type | Order code | MOQ 4 |
|------|----------------|-------|
| 50mm | 52-0925 | 0.281 |

| Type | Order code | MOQ 3 |
|-------|----------------|-------|
| 62mm | 52-0927 | 0.327 |
| 75mm | 52-0929 | 0.327 |
| 100mm | 52-0933 | 0.484 |

502499



Polypropylene Buchner Funnels

These 2-piece plastic funnels are lightweight, easy to clean and autoclavable. They are much less prone to breakage than the traditional porcelain types.

- Rugged construction
- Top part has perforated filter plate
- Parts snap together to give vacuum seal
- Corrosion free polypropylene construction
- Available in 70 and 130mm diameters



| Type | Order code | 1+ |
|-------|----------------|------|
| 70mm | 52-1498 | 2.47 |
| 130mm | 52-1500 | 5.24 |

122488



Powder Funnels

These polythene funnels have wide, parallel stems and are ideal for transferring powders.

- Corrosion free polypropylene construction
- Available in 80, 100 and 150mm diameters



| Type | Order code | MOQ 2 |
|------|----------------|-------|
| 80mm | 52-1502 | 0.719 |

| Type | Order code | Price each |
|-------|----------------|------------|
| 100mm | 52-1504 | 1.03 |
| 150mm | 52-1506 | 2.02 |

122489

Free Delivery*

on all orders over £30 (excl. VAT) – (UK mainland only)

* See Terms & Conditions for full details

RVFM

Funnel Holder

Holders for suspending funnels on retort stands.

- Holds funnels 76 to 152mm
- Supplied with adaptor for 25 to 76mm funnels
- Corrosion free polypropylene construction
- Includes tapered wedges to ensure firm grip on both 9.5mm (3/8in.) and 12.7mm (1/2in.) retort stand rods



| Type | Order code | 1+ |
|---------------|------------|------|
| Funnel holder | 52-1464 | 2.07 |

122491

RVFM

Separator Funnel Holder

Holders for suspending separatory funnels on retort stands.

- Front opening gives clear view of solution
- Allows unobstructed placement of funnel
- Corrosion free polypropylene construction
- Includes tapered wedges to ensure firm grip on both 9.5mm (3/8in.) and 12.7mm (1/2in.) retort stand rods



| Type | Order code | 1+ |
|-------------------------|------------|------|
| Separator funnel holder | 52-1466 | 2.68 |

122492

Stoppers & Bungs



Laboratory Rubber Stoppers

A wide range of **rubber stoppers** with or without holes.

- Wide range of sizes
- Available with or without holes
- Supplied as an **assorted pack of 50** or in **packs of 10**



Technical specification

| Top diameter | Bottom diameter | Hole? | Pack quantity | Order code |
|--------------|-----------------|-------|---------------|------------|
| Various | Various | No | 50 | 52-3356 |
| 16mm | 13mm | No | 10 | 52-3420 |
| 22mm | 19mm | No | 10 | 52-3422 |
| 28mm | 25mm | No | 10 | 52-3423 |
| 16mm | 13mm | Yes | 10 | 52-3421 |
| 28mm | 25mm | Yes | 10 | 52-3424 |
| 33mm | 29mm | Yes | 10 | 52-3440 |

| Top/bottom diameter | Pack quantity | Order code | 1+ |
|---------------------|---------------|------------|-------|
| Solid | | | |
| Various | 50 | 52-3356 | 4.97 |
| 16mm/13mm | 10 | 52-3420 | 0.909 |
| 22mm/19mm | 10 | 52-3422 | 1.33 |
| 28mm/25mm | 10 | 52-3423 | 2.06 |
| With hole | | | |
| 16mm/13mm | 10 | 52-3421 | 0.758 |
| 28mm/25mm | 10 | 52-3424 | 2.24 |
| 33mm/29mm | 10 | 52-3440 | 2.69 |

565541



Assorted Cork Tops

Cork stoppers and bungs in a variety of sizes.

- General purpose natural modelling material
- Ideal for adding buoyancy to models
- Supplied in **packs of 100g**



| Type | Order code | 1+ |
|----------------|------------|------|
| Cork tops 100g | 06-1310 | 2.12 |

073058

Cork Borers

RVFM

Cork Borers - Sets of 6 and 12

These sets of cutters are for boring holes into cork stoppers and bungs to allow the insertion of glass or plastic tubes, etc.

A single cutter of the desired diameter is simply twisted round using the handles while applying pressure on to the stopper. A push rod is also included for removing the waste material from within the cutter.

- Sets of cutters for boring holes into cork stoppers
- Allows the insertion of glass or plastic tubes, etc.
- Simply twist round using the handles while applying pressure
- A push rod is included for removing the waste material
- Available in **sets of 6 or 12**



Technical specification

| Set | Sizes |
|----------|---|
| 6-piece | 4, 4.7, 5.4, 6.5, 8.3 and 9.3mm |
| 12-piece | 3, 4, 5, 6, 8, 9, 11, 13, 14, 15, 17 and 19mm |

| Type | Order code | 1+ |
|-----------|------------|-------|
| Set of 6 | 06-6601 | 23.66 |
| Set of 12 | 06-6605 | 56.18 |

501651



Cork Borer Sharpener



Superior quality cork **borer sharpener** from **Eisco** with a hinged **brass cutter** blade set into a slot and wooden handle.

- Plated metal cone
- Suitable for borers 4mm to 27mm diameter
- Manufacturer's part **CH0324B**

| Type | Order code | 1+ |
|----------------------|------------|-------|
| Cork borer sharpener | 52-4093 | 10.07 |

568070

Reusable Syringes

ELECTROLUBE

THE SOLUTIONS PEOPLE

Electrolube Reusable Syringes

Re-usable syringes.

- Ideal for precise application of glues, greases, pastes and two-part compounds, where a precise amount of each is to be mixed
- Supplied in **packs of 10**



| Type | Order code | 1+ | 5+ | 10+ |
|------|------------|-------|-------|-------|
| 20ml | 87-0346 | 12.30 | 12.06 | 11.52 |

035703

RVFM

Re-Usable Syringes

A range of re-usable syringes, ideal for precise application of glues, greases, pastes and two-part compounds, where a precise amount of each is to be mixed.

- The 12ml syringe has a fine, curved tip, ideal for reaching awkward places



| MOQ 2 | | | | |
|-------|------------|-------|-------|-------|
| Type | Order code | 2+ | 10+ | 50+ |
| 1ml | 87-0338 | 0.571 | 0.483 | 0.443 |
| 5ml | 87-0343 | 0.637 | 0.555 | 0.501 |

| Price each | | | |
|-------------|------------|------|------|
| Type | Order code | 1+ | 10+ |
| 12ml curved | 87-0345 | 3.33 | 3.13 |

061886

RVFM

Syringe 100ml Glass

This **glass syringe** has a Luer fitting, interchangeable pistons and barrels.

- Capacity 100ml
- Supplied with metal tip



| Capacity | Order code | 1+ |
|----------|------------|-------|
| 100ml | 52-2669 | 24.04 |

550596

Science Magnetism Tube - Iron Fillings 130 x 90mm



Only

£9.96

Order code 06-0598

Page 258

Need a product urgently?

We can offer a next day, before noon, delivery service

01206 751166

Measuring Beakers



Polypropylene Measuring Jugs

A range of clear polypropylene measuring jugs with good chemical resistance.

- Graduations every 10ml
- Can be autoclaved
- Eisco CH0356 series



| Capacity | Order code | 1+ |
|----------|----------------|------|
| 250ml | 52-3373 | 0.81 |
| 500ml | 52-3374 | 1.21 |
| 1000ml | 52-3375 | 1.37 |

565552



Plastic Laboratory Measuring Beakers

Polypropylene measuring beakers with moulded graduations for ease of use.

- 50ml, 100ml, 250ml and 500ml supplied in **packs of 12**
- 1 litre beakers supplied in **packs of 6**



| Type | Order code | 1+ |
|--------------|----------------|------|
| 50ml pk 12 | 52-0176 | 3.59 |
| 100ml pk 12 | 52-0178 | 3.70 |
| 250ml pk 12 | 52-0180 | 5.94 |
| 500ml pk 12 | 52-0182 | 8.99 |
| 1 Litre pk 6 | 52-0184 | 7.74 |

066655


Plastic Measuring Cylinders



Plastic Measuring Cylinders

High quality, laboratory grade measuring cylinders made from polypropylene.

- Clear graduation markings on the side
- 25ml and 50ml sizes supplied in **packs of 12**
- 10ml, 100ml and 250ml sizes supplied **singly**



| MOQ 3 | | | |
|-------|----------|----------------|-------|
| Type | Quantity | Order code | 3+ |
| 10ml | Single | 52-0177 | 0.439 |

| Price each | | | |
|------------|------------|----------------|------|
| Type | Order code | 1+ | |
| 25ml | 12 | 52-0172 | 6.74 |
| 50ml | 12 | 52-0174 | 7.86 |

| MOQ 2 | | | |
|-------|------------|----------------|-------|
| Type | Order code | 2+ | |
| 100ml | Single | 14-2030 | 0.777 |

| Price each | | | |
|------------|------------|----------------|------|
| Type | Order code | 1+ | |
| 250ml | Single | 14-2032 | 1.52 |

034402

Polypropylene Tubes



Ultra-clear Polypropylene Tubes



These ultra-clear polypropylene tubes from Medline are ideal for use in rough environments where the use of glass tubes is not crucial. The tubes have greater crush resistance and are shatterproof.

- Autoclavable up to 121°C
- Matching natural-coloured polyethylene caps available separately for some sizes
- Supplied in **packs of 100**

| Technical specification | | | | | |
|-------------------------|------------------------|------------------------|-------------------|---------------------|----------------|
| Medline type | Internal diameter (mm) | External diameter (mm) | Total length (mm) | Maximum volume (ml) | Order code |
| 400800 | 10.3 | 11.7 | 73.9 | 5.3 | 52-1901 |
| 400700 | 10.9 | 12.7 | 73.7 | 6.4 | 52-1903 |
| 400705 | 13.7 | 15.8 | 98.6 | 12.7 | 52-1905 |

| Type | Quantity | Order code | 1+ |
|------------------------|----------|----------------|------|
| 12 x 75mm | 100 | 52-1901 | 3.22 |
| 13 x 75mm | 100 | 52-1903 | 3.59 |
| 16 x 100mm | 100 | 52-1905 | 4.01 |
| Cap for 52-1901 | 100 | 52-1909 | 3.50 |
| Cap for 52-1905 | 100 | 52-1913 | 2.23 |

500336

Polypropylene Coplin Jar



Coplin Jar

A Coplin jar that can hold ten 1 x 3 inch slides back-to-back.

- Interior is grooved to hold slides upright
- Microwaveable
- Domed, shallow threaded screw cap protects slides
- Corrosion free polypropylene construction



| Type | Order code | 1+ |
|------------|----------------|------|
| Coplin jar | 52-1512 | 1.34 |

122501

Containers



Polystyrene Containers

Medline polystyrene containers with polyethylene lids, ideal for the collection of biological samples or the storage of small amounts of chemicals.



- Ideal for samples
- Polystyrene containers
- Polyethylene screw-on lids
- Non-sterile
- Supplied **singly**

| Technical specification | | | | | |
|-------------------------|-----------------|--------------|--------|--------------|----------------|
| Capacity | Bottom diameter | Top diameter | Height | Medline type | Order code |
| 30ml | 25.1mm | 30.8mm | 92.5mm | 309202 | 56-1517 |
| 60ml | 39.3mm | 44.2mm | 66mm | 309502 | 56-1519 |
| 200ml | 58mm | 62mm | 95mm | 309903 | 56-1521 |

| MOQ 6 | | | |
|-------|----------------|-------|--|
| Type | Order code | 6+ | |
| 30ml | 56-1517 | 0.14 | |
| 60ml | 56-1519 | 0.162 | |
| MOQ 2 | | | |
| Type | Order code | 2+ | |
| 200ml | 56-1521 | 0.545 | |

500329



Polypropylene Containers

Medline polypropylene containers with polyethylene lids, ideal for the collection of biological samples or the storage of small amounts of chemicals.

- Ideal for samples
- Polyethylene screw-on lids
- Non-sterile
- Supplied **singly**



| Technical specification | | | | | |
|-------------------------|-----------------|--------------|---------|--------------|----------------|
| Capacity | Bottom diameter | Top diameter | Height | Medline type | Order code |
| 60ml | 38.8mm | 44.2mm | 66.1mm | 409502 | 56-1523 |
| 125ml | 56.3mm | 62.1mm | 74.3mm | 409702 | 56-1525 |
| 200ml | 56.5mm | 62.2mm | 115.5mm | 409902 | 56-1527 |

| MOQ 6 | | | |
|-------|----------------|-------|--|
| Type | Order code | 6+ | |
| 60ml | 56-1523 | 0.162 | |
| 150ml | 56-1525 | 0.252 | |
| MOQ 4 | | | |
| Type | Order code | 4+ | |
| 200ml | 56-1527 | 0.311 | |

500330

Bottles



Measuring Bottle Set



Set of five **graduated bottles** with lids, suitable for measuring and holding a wide range of liquids.

- Bottles in 5 sizes ranging from 200ml to 3000ml
- Capacities marked in metric and imperial scales on opposite sides of bottle
- Bottles nest for easy storage

| Type | Order code | 1+ |
|----------|----------------|-------|
| Set of 5 | 06-9937 | 13.84 |

563474



Round Narrow Mouth Bottles

A range of lightweight general-purpose polythene storage bottles.

- 5 litre bottle has carrying handle
- Supplied **singly**



Technical specification

| Nom Capacity ml | Actual Capacity ml | Height mm | Body mm | Neck mm | Material | Order Code |
|-----------------|--------------------|-----------|---------|---------|--------------|----------------|
| 125 | 138 | 112 | 48 | 15 | LD Polythene | 14-2000 |
| 250 | 280 | 139 | 60 | 15 | LD Polythene | 14-2002 |
| 1000 | 1080 | 197 | 94 | 21 | HD Polythene | 14-2006 |
| 5000 | 5300 | 295 | 176 | 36 | HD Polythene | 14-2010 |

MOQ 4

| Capacity | Order code | 4+ |
|----------|----------------|-------|
| 125ml | 14-2000 | 0.336 |

MOQ 3

| Capacity | Order code | 3+ |
|----------|----------------|-------|
| 250ml | 14-2002 | 0.452 |

MOQ 2

| Capacity | Order code | 2+ |
|----------|----------------|-------|
| 1000ml | 14-2006 | 0.639 |

MOQ 100

| Capacity | Order code | 100+ |
|----------|----------------|-------|
| 5000ml | 14-2010 | 13.85 |

MOQ 9

| Capacity | Order code | 9+ |
|---------------|----------------|-------|
| Dispenser cap | 14-2036 | 0.136 |

034396



Round Wide Mouth Bottles

Wide mouthed bottles for general-purpose storage.

- Made from high density polythene



Technical specification

| Nom Capacity ml | Actual Capacity ml | Height mm | Body mm | Neck mm | Material | Order Code |
|-----------------|--------------------|-----------|---------|---------|--------------|----------------|
| 100 | 123 | 91 | 47 | 35 | HD Polythene | 14-2012 |
| 250 | 254 | 114 | 59 | 40 | HD Polythene | 14-2014 |
| 500 | 518 | 147 | 74 | 40 | HD Polythene | 14-2016 |
| 1000 | 1100 | 195 | 93 | 49 | HD Polythene | 14-2018 |
| 2500 | 2800 | 218 | 140 | 70 | HD Polythene | 14-2020 |

MOQ 3

| Type | Order code | 3+ |
|---------------------|----------------|-------|
| Rd wide mouth 100ml | 14-2012 | 0.405 |
| Rd wide mouth 250ml | 14-2014 | 0.406 |

MOQ 2

| Type | Order code | 2+ |
|----------------------|----------------|-------|
| Rd wide mouth 500ml | 14-2016 | 0.567 |
| Rd wide mouth 1000ml | 14-2018 | 0.752 |

Price each

| Type | Order code | 1+ |
|----------------------|----------------|------|
| Rd wide mouth 2500ml | 14-2020 | 2.26 |

034398



Wide Mouth Bottles with Sealing Cap

Strong, light, general-purpose wide-mouth bottles with sealing caps.

- Made from HD polythene
- Supplied **singly**



Technical specification

| Nom Capacity ml | Actual Capacity ml | Height mm | Body mm | Neck mm | Material | Order Code |
|-----------------|--------------------|-----------|---------|---------|--------------|----------------|
| 300 | 344 | 113 | 70 | 48 | HD Polythene | 14-2038 |
| 700 | 775 | 169 | 86 | 48 | HD Polythene | 14-2008 |
| 1250 | 1348 | 213 | 102 | 48 | HD Polythene | 14-2040 |

MOQ 2

| Capacity | Order code | 2+ |
|----------|----------------|-------|
| 300ml | 14-2038 | 0.652 |
| 700ml | 14-2008 | 0.821 |

Price each

| Capacity | Order code | 1+ |
|----------|----------------|------|
| 1250ml | 14-2040 | 1.08 |

034399



Wash Bottles

Translucent, unbreakable wash bottles with built-in delivery tubes.

- Graduations on outer surface
- Low density polyethylene (LDPE) construction
- Available in **125, 250 and 500ml** capacities



| Type | Order code | 1+ |
|-------|----------------|------|
| 125ml | 52-1462 | 1.34 |
| 250ml | 52-1458 | 1.52 |
| 500ml | 52-1460 | 1.88 |

122490



Wash Bottles

A high quality wash bottle with washing tube.

- Simply squeeze to provide jet of liquid
- Available in **250ml** and **500ml** capacities
- Supplied **singly**



| Type | Order code | 1+ |
|-------------------------|----------------|------|
| Round wash bottle 250ml | 14-2022 | 1.48 |
| Round wash bottle 500ml | 14-2024 | 1.93 |

034400



Polypropylene Storage Vials

Storage vials for biological material, human and animal cells, etc.

- Leak-proof built-in seal
- Corrosion free polypropylene construction
- Available in **2ml** and **5ml** capacities



MOQ 6

| Type | Order code | 6+ |
|------|----------------|------|
| 2ml | 52-1520 | 0.18 |

MOQ 4

| Type | Order code | 4+ |
|------|----------------|-------|
| 5ml | 52-1522 | 0.259 |

122504

Over 500 new lines added in Laboratory Equipment



Burettes

For full product details visit
www.rapidonline.com

RVFM

Stopcock Burette with Rotaflow 50ml Capacity

A large borosilicate glass burette with a Rotaflow stopcock to accurately control the efflux of liquids.

| Type | Order code | 1+ |
|-----------------------|------------|------|
| Burette with Rotaflow | 52-1260 | 7.30 |

RVFM

Straight Bore Burettes with PTFE Stopcocks – Class B

Graduated straight bore burettes.

| Type | Order code | 1+ |
|------|------------|-------|
| 50ml | 52-1032 | 11.49 |

RVFM

Acrylic Burettes

Burettes with acrylic bodies and leakproof stopcocks fitted with self-lubricating PTFE plugs.

| Type | Order code | 1+ |
|-------|------------|-------|
| 50ml | 52-1454 | 6.51 |
| 100ml | 52-1456 | 10.74 |

ACADEMY

Straight Bore Burettes with PTFE Stopcock

These straight bore burettes from Academy have a PTFE key stopcock.

| Capacity | Order code | 1+ |
|----------|------------|-------|
| 10ml | 52-2011 | 18.02 |
| 25ml | 52-2013 | 18.02 |
| 50ml | 52-2015 | 12.87 |
| 100ml | 52-2027 | 28.50 |

GLASSCO

Straight Bore Burettes with Glass Stopcock

Straight bore burettes from Glassco with a glass stopcock.

| Capacity | Order code | 1+ |
|----------|------------|-------|
| 10ml | 52-2031 | 10.02 |
| 25ml | 52-2033 | 10.02 |

| | | |
|-------|---------|-------|
| 50ml | 52-2035 | 10.02 |
| 100ml | 52-2037 | 20.41 |



NEW

6

Burettes with Detachable Stopcock

These burettes from Glassco have a detachable glass stopcock.

| Capacity | Order code | 1+ |
|----------|------------|-------|
| 10ml | 52-2039 | 29.88 |
| 25ml | 52-2041 | 28.05 |
| 50ml | 52-2043 | 14.55 |



NEW

7

Modular Burette with PTFE Stopcock Class A

This Class A bureette from LabGlass has a PTFE stopcock.

| Capacity | Order code | 1+ |
|----------|------------|-------|
| 50ml | 52-4065 | 13.90 |



NEW

8

Burettes Glass Key Single Bore Class A White Graduation

These Class A burettes from LabGlass have a single straight bore and a glass key stopcock with white ceramic graduation.

| Capacity | Order code | 1+ |
|----------|------------|------|
| 10ml | 52-4058 | 6.75 |
| 25ml | 52-4059 | 8.25 |
| 50ml | 52-4060 | 8.92 |
| 100ml | 52-4057 | 9.75 |



NEW

9

Burettes Glass Key Single Bore Class B Blue Graduation

Single bore burettes from LabGlass with a glass key stopcock.

| Capacity | Order code | 1+ |
|----------|------------|-------|
| 10ml | 52-4062 | 4.65 |
| 25ml | 52-4063 | 5.95 |
| 50ml | 52-4064 | 7.48 |
| 100ml | 52-4061 | 11.71 |



NEW

10

Burettes with PTFE Rotaflow Stopcock Class B Blue Graduation

These burettes from LabGlass have a PTFE Rotaflow stopcock.

| Capacity | Order code | 1+ |
|----------|------------|------|
| 10ml | 52-4074 | 5.62 |
| 25ml | 52-4075 | 6.87 |
| 50ml | 52-4076 | 7.45 |
| 100ml | 52-4073 | 8.12 |



NEW

11

Burettes Single Bore with Pinch Clip Class B

Single bore Class B burettes from LabGlass with a detachable rubber tube and pinch clip.

| Capacity | Order code | 1+ |
|----------|------------|------|
| 10ml | 52-4066 | 4.68 |
| 25ml | 52-4067 | 4.99 |
| 50ml | 52-4068 | 5.06 |



NEW

12

Burettes with Straight Bore PTFE Key Stopcock Class A

Class A burettes from LabGlass with a straight bore interchangeable PTFE key stopcock.

| Capacity | Order code | 1+ |
|----------|------------|------|
| 10ml | 52-4082 | 7.25 |
| 25ml | 52-4083 | 7.56 |
| 50ml | 52-4084 | 8.33 |
| 100ml | 52-4081 | 8.70 |



NEW

13

Burettes with Straight Bore PTFE Key Stopcock Class B

Class B burettes from LabGlass with a straight bore interchangeable PTFE key stopcock.

| Capacity | Order code | 1+ |
|----------|------------|------|
| 10ml | 52-4086 | 5.80 |
| 25ml | 52-4087 | 6.53 |
| 50ml | 52-4088 | 7.25 |
| 100ml | 52-4085 | 7.98 |




NEW

14

Schellbach Burettes Single Bore with Glass Stopcock Class B

Class B Schellbach glass burettes from LabGlass with a glass stopcock.

| Capacity | Order code | 1+ |
|----------|------------|------|
| 10ml | 52-4078 | 7.18 |
| 25ml | 52-4079 | 7.98 |
| 50ml | 52-4080 | 8.19 |
| 100ml | 52-4077 | 9.08 |



Pipettes & Pipette Fillers



NEW

Pipettes Bulb Form One Mark Class A

One mark bulb form **pipettes** from **GLASSCO**, supplied in **packs of 5**.

- Made from alkaline resistant glass
- Class B

- Available in a choice of sizes

Technical specification

| Order code | Capacity | Tolerance | Length |
|------------|----------|-----------|--------|
| 52-2237 | 2ml | ±0.01ml | 305mm |
| 52-2238 | 5ml | ±0.015ml | 360mm |
| 52-2239 | 10ml | ±0.02ml | 450mm |
| 52-2240 | 20ml | ±0.03ml | 515mm |
| 52-2241 | 25ml | ±0.03ml | 520mm |

| Capacity | Colour | Order code | 1+ |
|----------|--------|------------|-------|
| 2ml | Orange | 52-2237 | 12.08 |
| 5ml | White | 52-2238 | 12.08 |
| 10ml | Red | 52-2239 | 12.08 |
| 20ml | Yellow | 52-2240 | 15.39 |
| 25ml | Blue | 52-2241 | 15.39 |

568019



NEW

Pipettes Bulb Form One Mark Class B

One mark bulb form **pipettes** from **GLASSCO**, supplied in **packs of 5**.

- Made from alkaline resistant glass
- Class B
- Available in a choice of sizes

Technical specification

| Order code | Capacity | Tolerance | Length |
|------------|----------|-----------|--------|
| 52-2045 | 5ml | ±0.015ml | 360mm |
| 52-2047 | 20ml | ±0.03ml | 515mm |
| 52-2236 | 25ml | ±0.03ml | 520mm |

| Capacity | Colour | Order code | 1+ |
|----------|--------|------------|-------|
| 5ml | White | 52-2045 | 10.40 |
| 20ml | Yellow | 52-2047 | 11.75 |
| 25ml | Blue | 52-2236 | 11.75 |

568018



NEW

Glass Bulb Form Pipettes Class A

Colour coded bulb form **pipettes** from **LabGlass**, made from **borosilicate glass**.

- Available in a range of sizes
- One graduation mark
- Class A
- Conforms to DIN ISO 648 standard

Technical specification

| Order code | Capacity | Tolerance |
|------------|----------|-----------|
| 52-4195 | 2ml | ±0.01ml |
| 52-4196 | 5ml | ±0.015ml |
| 52-4191 | 10ml | ±0.02ml |
| 52-4192 | 15ml | ±0.025ml |
| 52-4193 | 20ml | ±0.03ml |
| 52-4194 | 25ml | ±0.03ml |

| Capacity | Colour | Order code | 1+ |
|----------|--------|------------|------|
| 2ml | Orange | 52-4195 | 1.62 |
| 5ml | White | 52-4196 | 1.62 |
| 10ml | Red | 52-4191 | 1.62 |
| 15ml | Green | 52-4192 | 1.72 |
| 20ml | Yellow | 52-4193 | 1.72 |
| 25ml | Blue | 52-4194 | 1.72 |



NEW

Glass Bulb Form Pipettes Class B

Colour coded bulb form **pipettes** from **LabGlass**, made from **borosilicate glass**.

- Available in a range of sizes
- One graduation mark
- Class A
- Conforms to DIN ISO 648 standard

Technical specification

| Order code | Capacity | Tolerance |
|------------|----------|-----------|
| 52-4201 | 5ml | ±0.03ml |
| 52-4197 | 10ml | ±0.04ml |
| 52-4198 | 15ml | ±0.05ml |
| 52-4199 | 20ml | ±0.06ml |
| 52-4100 | 25ml | ±0.06ml |

| Capacity | Colour | Order code | 1+ |
|----------|--------|------------|------|
| 5ml | White | 52-4201 | 1.12 |
| 10ml | Red | 52-4197 | 1.17 |
| 15ml | Green | 52-4198 | 1.17 |
| 20ml | Yellow | 52-4199 | 1.17 |
| 25ml | Blue | 52-4200 | 1.27 |



NEW

Serological Pipettes Class B

Serological **pipettes** from **LabGlass**, designed so the last drop can be expelled by blowing.

- Available in a range of sizes
- Calibrated for delivery to jet
- Class B
- Colour coded
- Blue graduation
- Conforms to DIN ISO 835 standard
- Supplied in **packs of 5**

Technical specification

| Order code | Capacity | Tolerance |
|------------|----------|-----------|
| 52-4202 | 1ml | ±0.01ml |
| 52-4204 | 2ml | ±0.01ml |
| 52-4206 | 5ml | ±0.05ml |
| 52-4203 | 10ml | ±0.05ml |
| 52-4205 | 25ml | ±0.2ml |

| Capacity | Colour | Order code | 1+ |
|----------|--------|------------|------|
| 1ml | Yellow | 52-4202 | 8.80 |
| 2ml | Black | 52-4204 | 8.43 |
| 5ml | Red | 52-4206 | 8.80 |
| 10ml | Orange | 52-4203 | 8.43 |
| 25ml | White | 52-4205 | 9.15 |



Education

13

General Laboratory Equipment

RVFM




Dropping Pipettes

These dropping pipettes are useful for dispensing liquid from test tubes.

- Pipettes have soft rubber teats
- Glass body of 125mm length
- Supplied in **packs of 10**

Order code **52-1266**
Pack of 10 **£5.10**

RVFM




Plastic Pipettes Graduated to 3ml

A small plastic pipette, ideal for dispensing small amounts of liquid.

- Soft bulb is squeezed to suck up and dispense liquid
- Graduated up to 3ml

MOQ 16
Order code **06-6066**
£0.059

medline
scientific limited



Graduated Disposable Pasteur-type Pipettes

Disposable, graduated Pasteur-type pipettes from Medline, made from transparent, inert, low-intensity polythene.


- Volumetric tolerance ± 10%
- Not sterile
- Supplied in **packs of 500**

Technical specification

| Nominal capacity | Length | Stem diameter | Total capacity | Bulb capacity | Graduations |
|------------------|--------|---------------|----------------|---------------|-------------|
| 1ml | 154mm | 5mm | 5ml | 3.1ml | 0.25ml |
| 3ml | 154mm | 7.8mm | 7ml | 3.2ml | 0.5ml |

| Size | Quantity | Order code | 1+ |
|------|----------|------------|------|
| 1ml | 500 | 06-7019 | 7.39 |
| 3ml | 500 | 06-7021 | 7.82 |

RVFM



Suction Pipette Filler


A suction type filler for measuring and volumetric pipettes.

- Rubber squeeze bulb with valves
- 50cc capacity
- Withstands acids and other hazardous chemicals
- Features 3 flow control valves, that are opened by squeezing

Colour supplied will vary.

Order code **52-8058**
Pipette filler **£3.77**

eisco
Trust | Deliver | Learn



Pipette Pumps


A range of fast-release pipette pumps for precise and quick dispensing.

A knurled thumb wheel can be rotated to draw up or dispense liquids, or the release lever can be pushed in for quick emptying. The moulded chuck has a silicon rubber collet inside to hold various standard sized pipettes. The pump resists acids and alkalis and can be easily disassembled for thorough cleaning.

- Knurled thumb wheel
- Quick release lever
- Holds various standard sized pipettes
- Resistant to acids & alkalis
- Can be disassembled for cleaning

| Capacity | Order code | 1+ |
|----------|------------|------|
| 2ml | 52-3426 | 3.16 |
| 10ml | 52-3427 | 3.56 |
| 25ml | 52-3428 | 3.96 |

RVFM



Rubber Bulbs for Pipettes

Rubber bulbs for filling pipettes.

- Ideal for filling pipettes, etc., especially with corrosive or harmful chemicals
- Pear-shaped bulbs available in 5, 15 and 50ml capacities
- Dropper teat available in large size

| MOQ 3 | | | |
|--------------|------------|-------|--|
| Type | Order code | 3+ | |
| Bulb - 5ml | 06-7018 | 0.428 | |
| Bulb - 15ml | 06-7020 | 0.468 | |
| Price each | | | |
| Type | Order code | 1+ | |
| Bulb - 50ml | 06-7022 | 1.53 | |
| MOQ 2 | | | |
| Type | Order code | 2+ | |
| Teat - large | 06-7026 | 0.656 | |

Petri Dishes & Racks

RVFM

Autoclaveable Glass Petri Dishes

Clear glass petri dishes with lids. Can be autoclaved at a temperature of 120°C.

- Supplied in **packs of 18**

| Type | Order code | 1+ |
|------------|----------------|-------|
| 60 x 12mm | 52-0240 | 12.22 |
| 100 x 15mm | 52-0242 | 15.79 |

066667

medline

55mm 4-Vent Petri Dishes

These Aseptic 55mm Petri Dishes from Medline are made from polystyrene and have 4 vents. They are supplied in packs of 10 and are suitable for use with automatic filling machines.

- Diameter 55mm
- Height 14mm
- Supplied in **packs of 10**
- **Medline type 200201**

| Type | Order code | 1+ |
|-------------------|----------------|------|
| Petri Dishes (10) | 52-0179 | 1.06 |

500335

medline

90mm Triple Vent Petri Dishes

These Aseptic Petri Dishes from Medline are made from polystyrene and have 3 vents. They are supplied in packs of 20 and are suitable for automatic filling machines.

- Diameter 90mm
- Height 14mm
- Side mark for orientation
- Writing area on bottom
- Supplied in **packs of 20**
- **Medline type 200200.5**

| Type | Order code | 1+ |
|------------------|----------------|------|
| 90mm triple (20) | 52-0173 | 1.81 |

500404

RVFM

Petri Dishes

Clear, economical unbreakable petri dishes.

- Corrosion free polypropylene construction
- Autoclavable
- Available in 50, 125 and 150mm diameters



MOQ 4

| Type | Order code | 4+ |
|------|----------------|-------|
| 50mm | 52-1528 | 0.248 |

Price each

| Type | Order code | 1+ |
|-------|----------------|------|
| 125mm | 52-1530 | 1.11 |
| 150mm | 52-1532 | 1.52 |

122506

eISCO

Clear Acrylic Petri Dish Racks

Clear acrylic racks with white polycarbonate posts for holding and transporting petri dishes.

The racks can be very useful during inoculation, incubation and storage as the excellent visibility from all sides enables the culture to be seen and checked during incubation.

- Available in sizes to suit 60mm and 90mm dishes
- **Eisco CH0376 series**

| Dish size | Order code | 1+ |
|-----------|----------------|-------|
| 60mm | 52-3578 | 17.08 |
| 90mm | 52-3577 | 19.98 |

565634

medline

Triple Compartment Petri Dishes 90mm

Aseptic polystyrene Petri Dishes with 3 compartments and 3 vents from Medline. The dishes are supplied in packs of 20, packed in heat-sealed bags. They are suitable for use in automatic filling machines.

- 90mm diameter x 14mm high
- Aseptic polystyrene
- 3 compartments
- 3 vents
- Suitable for use in automatic filling machines
- Supplied in packs of 20 in heat-sealed bags
- **Medline type 200203**

| Type | Order code | 1+ |
|-------------------|----------------|------|
| 90mm Petri dishes | 52-0169 | 3.53 |

500334

Chromatography

RVFM

Chromatography Paper Rolls

This **chromatography paper** can be used to separate and analyse coloured chemicals and other substances.

- Ideal for use by schools and colleges
- Grade 1
- Supplied in rolls



| Width | Length | Order code | 1+ |
|-------|--------|----------------|-------|
| 40mm | 100m | 52-1959 | 31.99 |
| 50mm | 100m | 52-1981 | 36.70 |

568006

RVFM

Chromatography Paper Packs of 100 Sheets

This **chromatography paper** can be used to separate and analyse coloured chemicals and other substances.

- Ideal for use by schools and colleges
- Grade 1
- Supplied in **packs of 100 sheets**

| Size | Order code | 1+ |
|-------------|----------------|-------|
| 100 x 300mm | 52-1982 | 22.82 |
| 200 x 200mm | 52-1983 | 29.38 |

568007

GLASSCO

Chromatography Columns with Sintered Disc

Chromatography columns from Glassco with sintered disc.

- Made from borosilicate glass
- Porosity 0
- Available in a range of sizes

| Technical specification | | | |
|-------------------------|----------|-------------|--------|
| Order code | Diameter | Socket size | Length |
| 52-1699 | 10mm | 14/23 | 100mm |
| 52-1701 | 10mm | 14/23 | 200mm |
| 52-1703 | 10mm | 14/23 | 300mm |
| 52-1705 | 10mm | 14/23 | 400mm |
| 52-1707 | 20mm | 19/26 | 100mm |
| 52-1709 | 20mm | 19/26 | 200mm |
| 52-1711 | 20mm | 19/26 | 300mm |
| 52-1713 | 20mm | 19/26 | 400mm |
| 52-1715 | 20mm | 19/26 | 500mm |
| 52-1717 | 26mm | 24/29 | 300mm |
| 52-1719 | 26mm | 24/29 | 400mm |
| 52-1721 | 26mm | 24/29 | 500mm |
| 52-1723 | 30mm | 34/35 | 400mm |
| 52-1725 | 30mm | 34/35 | 500mm |
| 52-1727 | 30mm | 40/38 | 400mm |
| 52-1729 | 30mm | 40/38 | 500mm |

| Diameter | Length | Order code | 1+ |
|----------|--------|----------------|-------|
| 10mm | 100mm | 52-1699 | 38.14 |
| 10mm | 200mm | 52-1701 | 38.14 |
| 10mm | 300mm | 52-1703 | 38.15 |
| 10mm | 400mm | 52-1705 | 38.12 |
| 20mm | 100mm | 52-1707 | 40.04 |
| 20mm | 200mm | 52-1709 | 40.01 |
| 20mm | 300mm | 52-1711 | 40.01 |
| 20mm | 400mm | 52-1713 | 40.04 |
| 20mm | 500mm | 52-1715 | 40.04 |
| 26mm | 300mm | 52-1717 | 46.87 |
| 26mm | 400mm | 52-1719 | 46.87 |
| 26mm | 500mm | 52-1721 | 49.02 |
| 30mm | 400mm | 52-1723 | 51.54 |
| 30mm | 500mm | 52-1725 | 61.51 |
| 30mm | 400mm | 52-1727 | 62.02 |
| 30mm | 500mm | 52-1729 | 64.41 |

567994

ACADEMY

Chromatography Glass Tank and Lid

Chromatography tank and lid from Academy for use in the appropriate laboratory work.

- Made from soda-lime glass
- Length 230mm
- Width 90mm
- Tank and lid available separately



| Type | Order code | 1+ |
|------|----------------|-------|
| Tank | 52-1984 | 39.56 |
| Lid | 52-1985 | 8.45 |

568009

Filter Paper

ACADEMY

Professional Filters

These professional **filter papers** from Academy are suitable for a wide range of routine applications in the **laboratory**.

- Available in a range of sizes
- Supplied in **packs of 100**



| Diameter | Order code | 1+ |
|----------|----------------|-------|
| 55mm | 52-1095 | 3.21 |
| 70mm | 52-1097 | 3.72 |
| 90mm | 52-1098 | 4.44 |
| 110mm | 52-1099 | 5.47 |
| 125mm | 52-1109 | 5.56 |
| 150mm | 52-1185 | 7.49 |
| 185mm | 52-1187 | 11.32 |

567969



Premium Filter Paper – Packs of 100

Qualitative filter paper for use in the chemistry laboratory.

- Range of diameters
- Supplied in **packs of 100**
- **Eisco CH0390 series**



| Diameter | Order code | 1+ |
|----------|----------------|------|
| 90mm | 52-3549 | 1.12 |
| 110mm | 52-3550 | 1.32 |
| 125mm | 52-3551 | 1.78 |
| 150mm | 52-3552 | 2.91 |

565630

Indicator Test Paper



Indicator Papers



Indicator papers available in a range of types and pack sizes.

- Supplied in convenient plastic dispensers
- Universal pack includes pH indicator scale
- **Pack of 200** contains 10 books of 20 strips 10mm wide
- **Pack of 100** contains 100 loose strips 10mm wide
- **5m pack** contains a single continuous strip 7mm wide

| Price each | | |
|-----------------|----------------|------|
| Type | Order code | 1+ |
| Blue litmus 200 | 52-8000 | 2.93 |
| Blue litmus 100 | 52-8002 | 1.25 |
| Blue litmus 5m | 52-8004 | 2.16 |
| Red litmus 200 | 52-8006 | 2.93 |

MOQ 10 - In Multiples of 10

| Type | Order code | 10+ |
|----------------|----------------|------|
| Red litmus 100 | 52-8008 | 1.25 |

| Price each | | |
|-------------------|----------------|------|
| Type | Order code | 1+ |
| Red litmus 5m | 52-8010 | 2.16 |
| Ph 1-11 univ. 200 | 52-8012 | 3.18 |
| Ph 1-11 univ. 100 | 52-8014 | 1.65 |
| Ph 1-11 univ. 5m | 52-8016 | 2.27 |
| Ph 1-14 univ. 200 | 52-8018 | 3.48 |
| Ph 1-14 univ. 100 | 52-8020 | 1.87 |
| Ph 1-14 univ. 5m | 52-8022 | 2.27 |

075339

RVFM

Clinical Test Strips

These **clinical test strips** are suitable for use in testing for glucose or protein.

- Supplied in **packs of 50**



| Type | Pack size | Order code | 1+ |
|----------|-----------|----------------|-------|
| Diastix | 50 | 52-2611 | 8.64 |
| Albustix | 50 | 52-2612 | 10.22 |

550549

Cotton Wool

RVFM

Absorbent Cotton Wool

This absorbent white **cotton wool** is suitable for use in the laboratory, classroom, first aid kit, workplace and the home.

- Hospital quality
- Supplied in **packs of 500g**



| Pack size | Order code | 1+ |
|-----------|----------------|------|
| 500g | 52-2756 | 5.79 |

550641

Tongs & Holders

RVFM

200mm Crucible Tongs

200mm crucible tongs available in economy and stainless steel models. These tongs are essential for the safe handling of hot crucibles.

- Length 200mm
- Economy or Stainless Steel models

| Type | Order code | 1+ |
|-----------------|----------------|------|
| Economy | 52-0515 | 1.02 |
| Stainless Steel | 52-0517 | 2.01 |

300783

RVFM

Bowed Laboratory Tongs

High quality polished mild steel crucible tongs.

- Length 200mm
- Bowed jaws
- Supplied in **packs of 5**



| Type | Order code | 1+ |
|-------------|----------------|------|
| Bowed tongs | 52-0158 | 5.91 |

070950

RVFM

Economy Beaker Tongs with Plastic Jaws

Nickel-plated steel tongs with non-slip plastic-coated jaws, ideal for handling laboratory utensils like beakers, large crucibles, evaporating dishes and other round labware.

- Plastic covered jaws for good grip
- Jaws open to 115mm (4.5in.)
- Holds 50 to 2000ml beakers
- Length 240mm (9.5in.)



| Type | Order code | 1+ |
|---------------------|----------------|------|
| Tong (plastic jaws) | 52-0461 | 2.02 |

501655

RVFM

Radioactive Source Handling Tongs



These custom designed stainless steel **tongs** are ideal for handling **radioactive** sources.

- Dimensions (W x L): 12 x 165mm

| Size | Order code | 1+ |
|------------|----------------|-------|
| 12 x 165mm | 52-2698 | 11.45 |

550622

Spatulas, Spoons & Scoops



Laboratory Spatulas, Spoons and Pick Scoops

A range of general purpose laboratory spatulas, spoons and scoops, ideal for use in the chemistry laboratory.



| Type | Length | Order code | 1+ |
|-----------------|--------|----------------|-------|
| Spatula / spoon | 150mm | 52-3429 | 0.478 |
| Spatula / spoon | 200mm | 52-3372 | 3.39 |
| Chattaway | 150mm | 52-3528 | 0.55 |
| Chattaway | 200mm | 52-3529 | 0.61 |
| Pick scoop | 160mm | 52-3570 | 3.33 |
| Polypropylene | 150mm | 52-3583 | 0.24 |
| Polypropylene | 200mm | 52-3584 | 0.337 |

565551

Order online

Save time, and place your order at:
www.rapidonline.com



Inventors Kit
Page 19



Only
£39.94
Order code 73-5500

RVFM

Spatulas with Spoons

Stainless steel laboratory spatulas with a spoon bowl at one end and a rectangular flat at the other.



- Available in 120 and 150mm lengths

| MOQ 2 | | | |
|------------|------------|-------|--|
| Type | Order code | 2+ | |
| 120mm | 52-1275 | 0.777 | |
| Price each | | | |
| Type | Order code | 1+ | |
| 150mm | 52-1277 | 0.47 | |

562653



Deflagrating Spoon and Cap

A deflagrating spoon consisting of a steel cup and rod held by a cork in the aluminium cap.

- Steel cup and rod
- Aluminium cap
- Length 350mm
- Diameter of cap 90mm
- Diameter of cup 18mm
- Eisco type CH0520



| Type | Order code | 1+ |
|--------------------|------------|------|
| Deflagrating spoon | 52-3418 | 1.06 |

565576

RVFM

Nuffield Spatulas

These Laboratory spatulas, made of high quality mild polished steel offer good value for money.

- Length 140mm
- Supplied in **packs of 5**



| Type | Order code | 1+ |
|------------------|------------|------|
| Nuffield spatula | 52-0164 | 2.13 |

062559

RVFM

Chattaway Stainless Steel Spatulas

Double-ended stainless steel spatulas, ideal for loading small amounts of powdered or granular chemicals into test tubes, flasks, etc. One end is flat with a square end, the other end is rounded with an angled tip.



- Stainless steel
- Available in 100, 130 and 150mm lengths

| MOQ 2 | | | |
|------------|------------|-------|--|
| Type | Order code | 2+ | |
| 100mm | 52-9033 | 0.844 | |
| Price each | | | |
| Type | Order code | 1+ | |
| 130mm | 52-9031 | 1.00 | |
| 150mm | 52-9035 | 0.50 | |

562651

Free Delivery*

on all orders over £30 (excl. VAT)
(UK mainland only)

* See Terms & Conditions for full details - www.rapidonline.com/terms

Stirring Rods



Laboratory Stirring Rods

A range of general-purpose stirring rods, ideal for many jobs in the chemistry laboratory.



Technical specification

| Order code | Type | Length | Diameter | Material |
|------------|----------------------|--------|----------|---------------|
| 52-3580 | Policeman rod | 245mm | 6mm | Polypropylene |
| 52-3581 | Glass stirring rod | 200mm | 7mm | Glass |
| 52-3582 | Button end glass rod | 300mm | 7mm | Glass |

| Type | Order code | 1+ |
|----------------------|------------|------|
| Policeman rod | 52-3580 | 0.39 |
| Glass stirring rod | 52-3581 | 1.58 |
| Button end glass rod | 52-3582 | 2.15 |

565636



Glass Stirring Rods



6mm diameter glass stirring rods.

- Simax Borosilicate glass
- Supplied in **packs of 10**

| Type | Order code | 1+ |
|-------|------------|------|
| 125mm | 52-1006 | 5.14 |
| 150mm | 52-1008 | 5.92 |
| 200mm | 52-1010 | 5.92 |
| 300mm | 52-1012 | 6.05 |

073141

Tweezers



Disposable Plastic Tweezers

Disposable plastic forceps / tweezers for general purpose use in the laboratory.

- Length 110mm
- Serrated jaw tips
- Supplied in **packs of 12**
- Eisco type BI0177

| Type | Order code | 1+ |
|---------------------|------------|------|
| Disposable tweezers | 52-3703 | 8.88 |

565676

RVFM

Plastic Tweezers

Economical, plastic tweezers, ideal for science and as an assembly aid for small components.

- Serrated tips
- Locating lugs hold tips straight when closed
- Made from recyclable ABS plastic
- Length approx. 110mm

| Type | Order code | 1+ |
|------------------|------------|------|
| Plastic tweezers | 06-6064 | 0.18 |

080612

Burners & Stands



Melting Point Apparatus

This **melting point apparatus** from Eisco has been designed with safety in mind. A single control knob on the front panel incorporates the mains On/Off switch and a rapid heat switch allows higher temperatures to be obtained quickly. Sample tubes are illuminated from behind and magnified through a lens.

- Selector at rear of the instrument allows a light or dark background
- Ceramic insulation around aluminium heating block minimises heat transfer to the casing
- Rating 230V, 50 to 60Hz
- Manufacturer's part **CH0801**



| Type | Order code | 1+ |
|-------------------------|------------|--------|
| Melting point apparatus | 52-4189 | 215.93 |

568095



Tall Triangular Tripod

A laboratory tripod with a triangular zinc-plated, cast-iron top and mild steel legs.

- Zinc-plated cast-iron top
- Mild steel legs
- Length of side 120mm
- Height 210mm
- Eisco type CH0645A



| Type | Order code | 1+ |
|-------------------|------------|------|
| Triangular tripod | 52-3387 | 3.13 |

565561



Pipe Clay Triangles

A range of pipe clay triangles for supporting laboratory items being heated by a Bunsen burner or other heat source.



The triangles are made of wires strung in an equilateral triangle with three hollow ceramic tubes threaded onto it. The triangle is usually supported on a tripod or iron ring and, in turn, supports a crucible, etc., allowing it to be directly heated by the flame.

- Pipe clay triangles
- Available in a range of sizes

| Type | Order code | 1+ |
|------|------------|-------|
| 50mm | 52-3380 | 0.272 |
| 60mm | 52-3537 | 0.306 |
| 75mm | 52-3538 | 0.434 |

565555



We bring
STEM to life



Wire Gauze Squares

A range of iron wire gauze squares available with or without a ceramic centre, ideal for supporting flasks, etc, while being heated on a tripod stand.

- Wire gauze with or without ceramic centre
- High quality, extra strong



| Size | Ceramic centre | Order code | 1+ |
|--------------------|----------------|------------|------|
| Packs of 10 | | | |
| 125 x 125mm | Yes | 52-3327 | 3.98 |
| 150 x 150mm | Yes | 52-3328 | 4.14 |
| 125 x 125mm | No | 52-3567 | 2.89 |
| 150 x 150mm | No | 52-3568 | 4.37 |

565518



Laboratory Alcohol/Spirit Lamps

Spirit / alcohol burning lamps ideal for smaller heating tasks in the laboratory.

- Glass or stainless steel construction
- Supplied complete with cap



| Construction | Capacity | Order code | 1+ |
|--------------|----------|------------|------|
| Glass | 120ml | 52-3518 | 2.22 |

565626



Tripod Stand and Stainless Steel Alcohol Burner

A laboratory alcohol burner and a suitable tripod stand.

- Lamp is made from stainless steel and has a fuel capacity of 80ml
- Stand is 110mm high with an inner top diameter of 95mm
- Sold separately



| Type | Order code | 1+ |
|----------------|------------|------|
| Alcohol burner | 52-3325 | 4.42 |
| Tripod | 52-3326 | 1.83 |

565520

Metal Test Tube Holder



MOQ 2+

£0.35

Order code 52-8040

www.rapidonline.com



Laboratory Bunsen Burners 13mm

A range of Bunsen burners consisting of a nickel-plated burner tube mounted on a die-cast base.

- Rotating air regulator
- Base diameter 80mm
- Tube diameter 13mm
- Height 142mm
- Weight 280g
- Eisco CH0088 series

See order code 52-3590 for suitable rubber tubing.



| Fuel | Order code | 1+ |
|-------------|------------|------|
| Natural gas | 52-3365 | 4.95 |
| LPG | 52-3366 | 5.45 |

565547



11mm Natural Gas Bunsen Burner

A Laboratory Bunsen Burner for use with natural gas. The burner has a nickel-plated burner tube with a rotatable air regulator and an enamelled cast base for good stability.

- Barrel diameter 11mm
- Height: 125mm
- Base diameter 80mm
- 11mm nickel-plated burner tube
- Rotatable air regulator
- Enamelled cast base
- Cylindrical rifled connector
- 8mm gas inlet



Technical specification

| Type | Order code | Jet size |
|------------------|------------|----------|
| Natural gas 11mm | 52-0153 | 0.65mm |

| Type | Order code | 1+ |
|------------------|------------|------|
| 11mm Natural Gas | 52-0153 | 3.95 |

561648



Heat-Resistant Asbestos-Free Bunsen Burner Mats

Asbestos-free, heat-resistant bench mats, ideal for use under bunsen burners. The mats are manufactured from calcium silicate and are in the form of rigid sheets.

- Size 300 x 300mm
- Thickness approx. 3.5mm
- Available singly and in packs of 10



| Type | Order code | 1+ |
|------------|------------|-------|
| Single | 52-0127 | 1.60 |
| Pack of 10 | 52-0125 | 13.99 |

081315

How do I ...

Email baskets?
Register Online?
Find invoices?

www.rapidonline.com/schools-faq



Calcium Silicate Bench Mats

Laboratory bench mats from Eisco, ideal for use underneath a bunsen burner.

- Made from calcium silicate
- Finished edges
- Size 230 x 230mm
- Manufacturer's part CH0101E



| Size | Order code | 1+ |
|-------------|------------|------|
| 230 x 230mm | 52-4056 | 1.81 |

568084

Laboratory Jacks



Laboratory Jacks




This scissor jack from Eisco provides strong and stable support for a range of laboratory equipment.

- Screw-operated scissor action mechanism
- Platform size 150 x 135mm
- Minimum height 60mm
- Maximum elevation 250mm
- Finished in blue
- Maximum load 25kg
- Manufacturer's part CH0642A

| Type | Order code | 1+ |
|------------------|------------|-------|
| Laboratory jacks | 52-4188 | 24.64 |

568094

Dash Robot



wonder
workshop

Only

£134.99

Order code 70-1100

www.rapidonline.com

Retort Stands & Clamps

eisco
Trust • Deliver • Learn

Laboratory Retort Stand Set

This laboratory **retort stand set** from **Eisco** is made from high quality materials for a long service life and is an essential piece equipment for all science labs in schools, factories and research units.

The set consists of a heavy 200 x 125mm retort stand base, 600mm stainless steel rod, 75mm retort ring and 3-prong clamp. It is suitable for holding and supporting a wide variety of laboratory equipment used in physics and chemistry, including filtration, measurement, chemical experiments, etc.

Stand set includes:

- Base 200 x 125mm, 1200g (CH0649B)
- Rod 600mm (CH0657B)
- Retort ring 75mm O.D. with boss-head (CH0627B)
- Clamp - three prong with boss-head (CH0688)

Retort ring:

- Plated mild steel with 8mm diameter stem
- Fitted boss-head with thumb-screw to accept rods from 8mm to 12.5mm dia.
- Distance from centre of support to centre of ring: 140mm
- ID of ring 75mm

Clamp:

- 3-prong universal retort clamp with built-in boss-head
- 210mm overall length
- Jaws open up to 90mm wide
- Distance from centre of support to centre of jaws (reach): 155mm
- Reach adjustable with thumbscrew
- Commonly used to hold irregularly shaped items
- Provides a firm grip to most commonly used glassware items in the lab

Order code **52-3705**

£9.87

RVFM

Economy Retort Stands

These economical retort stands have bases made from enamel-finished steel. The 12mm plated-steel rod screws into the base and can therefore be removed for easier storage.

- Rubber feet for stability
- Small: base 200 x 125mm, height 600mm
- Large: base 225 x 150mm, height 750mm

| Type | Order code | 1+ |
|-------------------|----------------|------|
| 200 x 125 x 600mm | 52-1305 | 6.29 |
| 225 x 150 x 750mm | 52-1307 | 7.63 |

RVFM

Bosshead Clamps

These **bosshead clamps** have perpendicular jaws and thumbscrews set 90° apart and are ideal for connecting clamps, etc. to **retort stands**.

- Available in a range of sizes

| Material | Size (mm) | Order code | 1+ |
|----------|-----------|----------------|------|
| Diecast | 16 | 06-2131 | 2.15 |

eisco
Trust • Deliver • Learn

Retort Stand Clamps and Bossheads

A range of retort stand clamps including boss-head clamps and tube clamps with rubber or cork lined jaws.

- Clamps for use with retort stands

| Type | Jaw covering | Order code | 1+ |
|---------------------|--------------|----------------|------|
| Clamp+bosshead | Cork | 52-3313 | 3.78 |
| Clamp+bosshead | PVC | 52-3314 | 5.51 |
| Clamp+bosshead | PVC | 52-3305 | 3.78 |
| Clamp only | PVC | 52-3367 | 2.18 |
| Bossheads pack of 5 | | 52-3368 | 9.34 |
| Bosshead - single | | 52-3391 | 5.47 |

Order online

Save time, and place your order at:
www.rapidonline.com

RVFM

Steel Retort Stand Bases

A range of retort stand bases for use with retort stand rods, etc.

- Heavy steel construction
- Threaded M10 x 1.5 metric thread in centre of short side
- Stove enamelled
- Rubberised anti-slip strips
- Range of sizes



Retort stand rods not included.

| Type | Order code | 1+ |
|-------------|----------------|-------|
| 160 x 100mm | 06-2122 | 7.68 |
| 200 x 125mm | 06-2123 | 6.00 |
| 250 x 160mm | 06-2124 | 11.46 |
| 315 x 200mm | 06-2125 | 11.52 |

533992



Retort Stand Clamps and Bossheads

A range of retort stand clamps including boss-head clamps and tube clamps with rubber or cork lined jaws.

- Clamps for use with retort stands



| Type | Jaw covering | Order code | 1+ |
|---------------------|--------------|----------------|------|
| Clamp+bosshead | Cork | 52-3313 | 3.78 |
| Clamp+bosshead | PVC | 52-3314 | 5.51 |
| Clamp+bosshead | PVC | 52-3305 | 3.78 |
| Clamp only | PVC | 52-3367 | 2.18 |
| Bossheads pack of 5 | | 52-3368 | 9.34 |
| Bosshead - single | | 52-3391 | 5.47 |

565513

RVFM

Retort Stand Clamp 4 Prong

This universal retort stand clamp is made from aluminium and has 4 jaws.

- The jaws allow objects from 2 - 90mm in diameter to be clamped securely
- The design of the jaws ensures a firm grip at all angles of opening
- The four interlocking jaws are cork lined
- Overall length is 24cm



| Type | Order code | 1+ |
|--------------------|----------------|------|
| Retort stand clamp | 52-0518 | 4.48 |

072276

RVFM

3-Prong Clamps

A range of 3-prong clamps with rods that can be attached to a retort stand by means of a boss-head clamp.

- Retort stands and boss-head clamps available separately



| Type | Order code | 1+ |
|--------------------|----------------|------|
| Zinc alloy | 06-2126 | 7.44 |
| Aluminium casting | 06-2127 | 5.95 |
| Die-cast aluminium | 06-2128 | 5.95 |

534071

RVFM

Burette Clamps

These burette clamps attach to retort stands and have rounded steel jaws that open from 10 to 35mm diameter.

- Jaws can be rotated through 360° and locked in any position
- Fits support rods up to 15mm diameter
- Available with or without plastic coated jaws



| Type | Order code | 1+ |
|---------------------|----------------|------|
| Metal jaws | 06-2129 | 5.04 |
| Plastic coated jaws | 06-2130 | 5.72 |

534072



Retort Stand Rings

A range of supporting rings for use with retort stands.

The 50 and 75mm rings have built-in boss-head clamps, whereas the 150mm ring uses a separate boss-head clamp (not included) that allows the distance of the ring from the stand rod to be varied.

- 50 and 75mm rings have built-in boss-head clamps
- 150mm ring uses a separate boss-head clamp
- **Eisco CH0672 & CH0668 series**



| Diameter | Boss-head | Order code | 1+ |
|----------|-----------|----------------|------|
| 50mm | Yes | 52-3462 | 2.11 |
| 75mm | Yes | 52-3463 | 2.25 |
| 150mm | No | 52-3371 | 2.05 |

565550

RVFM

Vertical Burette Rack

A polished hardwood rack for storing burettes vertically.

- Upper tier has recesses to locate burettes
- Can take up to 12 burettes
- Size (H x W x D): 455 x 400 x 77mm
- Wall mountable



| Type | Order code | 1+ |
|--------------|----------------|-------|
| Burette rack | 06-6914 | 14.61 |

079609



Funnel Stands

Polished wooden funnel stands with clamping screws.

- Rod is approx. 460mm tall x 16mm diameter
- **Eisco CH0689 series**



Funnels not included.

| Type | Order code | 1+ |
|--------|----------------|------|
| Single | 52-3600 | 7.55 |
| Double | 52-3601 | 8.15 |

565642



Funnel and Burette Stand

A polished wooden funnel and burette stand with clamping screws for adjusting the height and securing the burette.

- Rod approx. 460mm tall x 16mm diameter
- Base size 290 x 110mm
- **Eisco type CH0690**



Funnel and burette not included.

| Type | Order code | 1+ |
|----------------------|----------------|-------|
| Funnel+burette stand | 52-3599 | 10.92 |

565641



Wooden Burette Stands

Stands, designed to support up to two burettes.

The stands are made from polished seasoned hardwood, and have a separate clamping screw for each burette.

- For one or two burettes
- Polished, seasoned hardwood
- Individual clamping screws
- Rod is approx. 460 x 16mm
- **Eisco CH0264 series**

Burettes not included.




| Type | Order code | 1+ |
|--------|----------------|-------|
| Single | 52-3430 | 7.69 |
| Double | 52-3598 | 11.56 |

565580



Wooden Test Tube Racks



Wooden test tube stands with 22mm diameter holes.

- Width 65mm
- Height 115mm
- **Eisco CH0704 series**

Test tubes not included.

| Number of holes | Order code | 1+ |
|-----------------|----------------|------|
| 6 | 52-3449 | 4.14 |
| 12 | 52-3448 | 6.36 |

565595

Calorimeters

Rapid

Metal Block Calorimeter Bundle

This money-saving calorimeter bundle provides a convenient way to buy four metal block calorimeters, made from different metals, for specific heat capacity comparison experiments.

Each cylindrical block has a mass of 1kg adjusted to an accuracy of 2%. The blocks are drilled with two holes: a larger 12.5mm central hole for a heater and a smaller hole, 7.5mm in diameter, for a thermometer or temperature sensor.

Bundle contains one each of:

- Aluminium block calorimeter
- Brass block calorimeter
- Copper block calorimeter
- Steel block calorimeter

Order code
78-7207

£54.62

508198



RVFM

Joule's Calorimeter

A Joule's Calorimeter for experimenting with the conversion of electrical energy into heat energy. The calorimeter consists of a nickel-plated copper outer vessel with a lagged copper inner vessel. The cover has terminals for the 3 to 6V heating coil, a built-in stirrer and a hole for a thermometer to record the temperature changes.



- Apparatus for experimenting with the conversion of electrical energy into heat energy
- Nickel-plated copper outer vessel
- Copper inner vessel
- Felted wool cloth lagging
- Outer vessel is 100mm tall and 75mm in diameter
- Inner vessel is 75mm tall and 50mm in diameter
- 3 to 6V heating coil, Max. current 1A
- Built-in stirrer
- Hole for a thermometer (not included)

| Type | Order code | 1+ |
|---------------------|------------|-------|
| Joule's Calorimeter | 52-9535 | 10.50 |

501638

EISCO

Aluminium and Copper Calorimeters

A range of calorimeters with parallel sides and a rolled rim.

- Available in aluminium or copper
- Eisco PH0438 & PH0440 series



Stirrer not included.

| Metal | Size | Order code | 1+ |
|-----------|------------|------------|------|
| Aluminium | 75 x 50mm | 52-3645 | 1.37 |
| Aluminium | 100 x 75mm | 52-3644 | 1.53 |
| Copper | 75 x 50mm | 52-3647 | 2.84 |
| Copper | 100 x 75mm | 52-3646 | 4.60 |

565655

EISCO

Metal Block Calorimeters

A range of metal block calorimeters that can be used for the experimental determination of the specific heat capacity of various metals.

Each cylindrical block has a mass of 1kg adjusted to an accuracy of 2%. The blocks are drilled with two holes: a larger 12.5mm central hole for a special immersion heater and a smaller hole 7.5mm diameter for a thermometer or temperature sensor.



565659

- Eisco PH0435 series

| Material | Order code | 1+ |
|-----------|------------|-------|
| Aluminium | 52-3651 | 12.26 |
| Brass | 52-3652 | 16.34 |
| Copper | 52-3653 | 20.99 |
| Steel | 52-3654 | 5.82 |

Measuring

EISCO

Ticker Tape Timer



This **ticker tape timer** from Eisco is housed in a tough moulded plastic case. The timer operates on 12V AC supply and produces 50/60 dots per second, depending on the

mains supply frequency. The case has a tape guide and a carbon disc plug which can be moved to maximise the use of the discs.

- Supplied with one 50m paper tape roll and a box of 100 carbon discs
- Manufacturer's part PH0353A

| Type | Order code | 1+ |
|-------------------|------------|-------|
| Ticker tape timer | 52-4213 | 25.60 |

568100

INVICTA

Leicester Height Measure

An accurate portable free standing height measure, complete with case.

- Quickly assembled
- Measuring range 210cm dual reading both metric and imperial
- Graduation 1mm and 1/8in
- Fun and easy to use



| Type | Order code | 1+ |
|--------------------------|------------|-------|
| Leicester height measure | 52-0579 | 60.75 |

073930



Clinometer Mk1

A traditional lightweight angle-measuring instrument to calculate heights.

- Complete with product guide
- Wheel size: 130mm diameter



| Type | Order code | 1+ |
|----------------|------------|------|
| Clinometer Mk1 | 52-9856 | 9.24 |

081638



Clinometer Mk2

A compact Clinometer with no external moving parts and a combined sighting angle-reading eyepiece

- A window on the side allows a second person to check a reading
- All angles in degrees followed by a plus or minus to indicate an upward or downward slope
- Complete with product guide
- Size: 140mm diameter



| Type | Order code | 1+ |
|----------------|------------|-------|
| Clinometer Mk2 | 52-9858 | 12.24 |

081639



Trundle Wheel

Measure intermediate distances with this robust and durable Trundle wheel.

- Clicker can be adjusted to one of three positions: off, click every 10cm or click every metre
- Splits into two parts for easy storage
- Length 83cm
- Supplied with carry bag and product guide
- Ideal primary school resource
- Suitable for **Key Stages 1 & 2** (ages 5 to 11)



| Type | Order code | 1+ |
|---------------|------------|------|
| Trundle wheel | 52-0656 | 9.98 |

070780



Trundle Wheel Counter

This robust counter extends the number of activities that can be performed by the Trundle Wheel, **52-0656**.

- Accurately counts metres up to 9999
- Can also be set to register every 10cm giving a maximum of 999.9 metres
- Fits in place of the standard clicker



Trundle wheel not included.

| Type | Order code | 1+ |
|-----------------------|------------|-------|
| Trundle wheel counter | 52-9848 | 10.16 |

081634



Metric Calliper

Measures most shapes from 1mm to 30cm by simply reading measurements through a single viewing window.

- Designed for calculating areas and volumes
- Able to measure depth, width and diameter
- Size: 420 x 195mm



| Type | Order code | 1+ |
|-----------------|------------|------|
| Metric calliper | 52-9854 | 5.00 |

081637

Health & Safety



Clear Vented Safety Glasses

These safety glasses can be worn alone, or are perfect for fitting over most prescription spectacles.

- Vented to prevent fogging
- UV protected
- Lightweight polycarbonate
- Impact resistant lens
- CE marked
- Conform to ANSI Z87.1 2010 side-shield protection
- **Eisco type CH0619A**



| Type | Order code | 1+ |
|----------------|------------|------|
| Safety glasses | 52-3596 | 1.52 |

505639



Stealth 7000 Safety Spectacles



Sports style safety spectacles offering excellent protection combined with a modern design.

- Ultra lightweight
- Contour design fits well onto smaller faces, suitable for children
- Clear polycarbonate frame and scratch-resistant lens
- **Conforms to EN166.1.F**
- Available in clear and smoke versions

| Type | Order code | 1+ | 5+ | 10+ |
|--------------------|------------|------|------|------|
| Stealth 7000 clear | 87-3114 | 3.85 | 3.69 | 3.25 |
| Stealth 7000 smoke | 87-3122 | 3.85 | 3.69 | 3.32 |

060179

Xytronic 456DLX Fume Extractor with Iron

Only

£95.23

Order code 85-1044



Page 194



Martcare Indirectly Ventilated Safety Goggles

These Martcare indirectly-ventilated goggles from JSP are ideally suited for general-purpose eye protection due to their economical pricing and simplicity of use. The indirect ventilation system of the JSP Martcare goggles means that dust or liquid cannot directly fall into the goggles and gives additional protection over goggles which simply have perforated frames to allow air flow.



- Clear PVC lens
- Comfortable soft body
- Adjustable elasticated head-strap
- **Conforms to EN 166-1.B.3.4**

| Type | Order code | 1+ | 5+ |
|------------------|------------|------|------|
| Martcare goggles | 87-3104 | 1.68 | 1.48 |

081349



JSP Martcare Indirect Vent Safety Goggles Class Pack of 20

A classpack of 20 JSP Indirect Vent Martcare Goggles in a deep Gratnell's Tray with lid.

See order code **87-3104** for full details of the JSP Martcare goggles.

- Perfect storage solution for laboratory goggles



| Type | Order code | 1+ |
|----------------------|------------|-------|
| Goggles Classpack 20 | 87-3103 | 31.11 |

525067



JSP Stealth 7000 Safety Specs Class Pack 20 + Gratnell Tray

A classpack of 20 Junior Stealth Safety Spectacles in a deep Gratnell's Tray with lid.

See order code **87-3114** for full details of the JSP Stealth 7000 Safety Spectacles.

- Perfect storage solution for safety spectacles



| Type | Order code | 1+ |
|----------------------|------------|-------|
| Safety Specs Pack 20 | 87-3113 | 64.10 |

525065



JSP Stealth 7000 Safety Specs Junior Class Pack 20 + Gratnell Tray

A classpack of 20 Junior Stealth Safety Spectacles in a deep Gratnell's Tray with lid.

See order code **87-0914** for full details of the JSP Junior Stealth Safety Spectacles.

- Perfect storage solution for safety spectacles



| Type | Order code | 1+ |
|----------------------|------------|-------|
| Junior Specs Pack 20 | 87-0913 | 63.76 |

525066



Junior Laboratory Spectacles

High quality lightweight junior spectacles with smaller frame, ideal for children and people with small facial features.

- Scratch resistant lens
- Can be worn over most glasses
- Conforms to **EN166**



| Type | Order code | 1+ | 10+ |
|-------------------|----------------|------|------|
| Junior spectacles | 87-0914 | 3.14 | 2.96 |

072695

Economy Junior Goggles

Economy junior goggles especially designed for younger people and people with small facial features.

- General purpose protection against splashes, dust, fumes etc
- Frame made from soft PVC for a comfortable fit and adjustment to individual's faces
- Conforms to **EN166**



| Type | Order code | 1+ | 10+ |
|------------------------|----------------|------|------|
| Economy junior goggles | 87-1016 | 1.67 | 1.56 |

061742

BLUE DOT™

Emergency Eye Wash

Sterile sodium chloride 0.9% w/v sterile water for ocular and topical irrigation and wound cleansing.

- Available in **packs of 25 single-use 20ml pods** and in **500ml bottles**



| Type | Order code | 1+ |
|------------------|----------------|------|
| Pack of 25x 20ml | 87-4221 | 6.58 |
| 500ml bottle | 87-4225 | 1.51 |

300550

Polycotton Lab Coats

Poly/cotton-mix lab coats for safety and protection of clothing.

- 1x breast pocket
- 2x side pocket
- Material: 65% polyester, 35% cotton
- Available in white or navy blue



| Chest size | Colour | Order code | 1+ |
|--------------|-----------|----------------|-------|
| 86cm (34in) | White | 52-1194 | 13.89 |
| 86cm (34in) | Navy blue | 52-1195 | 17.36 |
| 106cm (42in) | White | 52-1196 | 13.89 |
| 106cm (42in) | Navy blue | 52-1197 | 16.51 |
| 122cm (48in) | White | 52-1198 | 14.88 |
| 122cm (48in) | Navy blue | 52-1199 | 16.51 |

081774

RVFM

Ladies Warehouse/ Laboratory White Coats

Ladies Poly Cotton Coats made from hard wearing but comfortable 245g poly/cotton fabric.

- Concealed stud front fastening
- 3 patch pockets
- Colour: white



| Type | Order code | 1+ |
|--------------|----------------|-------|
| 92 to 124cm | 52-1117 | 14.36 |
| 128 to 148cm | 52-1119 | 15.09 |

530477



Black Rubber Bib Aprons

Basic black rubber aprons, perfect for the chemistry laboratory.

The aprons are comfortable and flexible, waterproof and resistant to most chemicals likely to be used by students.

- Available in medium or large sizes
- Medium: width 685mm (27in.), length 915mm (36in.)
- Large: width 685mm (27in.), length 1065mm (42in.)
- **Eisco RBAP series**



| Size | Order code | 1+ |
|--------|----------------|------|
| Medium | 52-3595 | 6.12 |
| Large | 52-3594 | 6.12 |

565638



Powder-free Latex Gloves

Powder-free latex gloves providing higher protection than vinyl, and maintaining integrity under prolonged use. Ideal for protecting the hands against degreasing and cleansing solvents, ferric chloride etchant, caustic soda based products and most other chemicals associated with the electronics industry.



- Powder-free
- Non-sterile
- Beaded cuff
- High tensile strength
- May be used for either left or right hand
- Recommended for use with blood, blood stained fluids and harsh chemicals
- Supplied in **dispenser boxes of 100**

These gloves will not provide 100% protection under all working conditions and the user should establish suitability prior to use.

| Type | Order code | 1+ | 5+ | 10+ |
|-------|----------------|------|------|------|
| Large | 87-0951 | 5.77 | 5.66 | 5.43 |

300536

microplast®

Blue Detectable Plasters

Bright blue sterile catering plasters.

- Blue colour stands out if accidentally lost in foodstuffs
- Occlusive material provides integral barrier to bacteria
- Metal detectable for food production facilities
- Supplied in an **assorted pack of 100**



| Type | Order code | 1+ |
|---------------|----------------|------|
| Blue plasters | 87-4195 | 3.79 |

300544

Fume Extraction



Spare/Replacement Filters



A range of spare/replacement filters for use with BenchVent extraction and filtration systems.

- Please see Technical Specification for Model/Filter cross-reference chart

| Technical specification | | | | | | | | | |
|-------------------------|--------------|-------------------|-----------|--------------------|---------------------------|----------------|-------------------|-------|--------|
| Extractor Model | 10µ PST Pads | Standard 5 micron | HEPA 0.3µ | 99.95% to Charcoal | Standard Activated Carbon | Low Level Fume | Low Level Tanning | Spray | |
| BV300S | PRE495 | IFA3 | HE495 | CHA3 | - | FAK3 | - | - | |
| BV200S | PRE705 | IFA2 | HE705 | CHA2 | - | FAK2 | - | - | |
| BV200H | PRE495 | IFA3 | HE495 | CHA3 | - | FAK3 | - | - | |
| BV100H | PRE705 | IFA2 | HE705 | CHA2 | - | FAK2 | - | - | |
| BV200H-D | - | IFA3 | - | - | - | - | - | - | |
| BV100H-D | - | IFA2 | - | - | - | - | - | - | |
| BV300S-D | - | IFA3 | - | - | - | - | - | - | |
| BV500S-D | - | IFA3 | - | - | - | - | - | - | |
| BV500S-C | PRE495 | IFA3 | HE495 | - | AC200 | - | - | - | |
| BV570H-H | PRE405 | - | HE495 | - | - | - | - | - | |
| BV570H-C | PRE405 | - | - | - | AC200 | - | - | - | |
| BV700S-C | PRE705 | IFA2 | HE705 | - | AC100 | - | - | - | |
| BV660H-C | PRE495 | IFA3 | HE495 | - | AC200 | - | - | - | |
| BV930H-C | PRE705 | IFA2 | HE705 | - | AC100 | - | - | - | |
| BV660H-D | - | IFA3 | - | - | - | - | - | - | |
| BV930H-D | - | IFA2 | - | - | - | - | - | - | |
| BV500 | - | IFA3 | - | - | - | - | - | - | IFA3PT |

| Price each | | | |
|----------------|------|----------------|--------|
| Size (mm) | Type | Order code | 1+ |
| 495 x 372 x 23 | IFA3 | 87-5535 | 75.69 |
| 495 x 495 x 23 | IFA3 | 87-5536 | 78.30 |
| 705 x 502 x 47 | IFA2 | 87-5537 | 101.79 |
| 495 x 372 x 12 | CHA3 | 87-5538 | 17.40 |
| 495 x 495 x 12 | CHA3 | 87-5539 | 23.92 |
| 705 x 502 x 12 | CHA2 | 87-5540 | 33.93 |
| 495 x 372 x 23 | FAK3 | 87-5541 | 51.76 |
| 705 x 502 x 47 | FAK2 | 87-5542 | 73.95 |
| 495 x 495 x 23 | FAK3 | 87-5543 | 54.81 |
| 495 x 372 x 23 | IFA3 | 87-5544 | 40.02 |
| 705 x 502 x 47 | IFA2 | 87-5545 | 54.81 |

| MOQ 6 - In Multiples of 6 | | | |
|---------------------------|--------|----------------|------|
| Size (mm) | Type | Order code | 6+ |
| 495 x 372 x 23 | PRE495 | 87-5546 | 3.48 |

| Price each | | | |
|----------------|-----------|----------------|--------|
| Size (mm) | Type | Order code | 1+ |
| 705 x 502 | PRE705 | 87-5547 | 6.96 |
| 705 x 502 x 47 | HEA2 | 87-5549 | 54.81 |
| 405 x 320 x 47 | HEA05 | 87-5550 | 79.17 |
| 495 x 372 x 23 | HEA95 | 87-5551 | 100.92 |
| 705 x 502 x 47 | HE705 | 87-5552 | 138.33 |
| 405 x 320 x 73 | HE/CA/405 | 87-5553 | 173.13 |
| 405 x 320 x 50 | AC200 | 87-5554 | 94.83 |
| 585 x 450 x 50 | AC100 | 87-5555 | 138.33 |

519008

BenchVent

The Bench Ventilation Company

BenchVent bench top units help protect pupils and staff from the fumes associated with GCSE, A Level, and higher education classroom experiments.

BenchVent is one of the first British companies to design and manufacture products specifically addressing the fume extraction requirements of school science laboratories.

Built in the UK, BenchVent offers an industry-leading lifetime guarantee for complete peace of mind. All units conform to the guidance of the Health and Safety Executive CoSHH regulations.



| Order Code | Model | Description | Air Volume cap | Size | 1+ |
|----------------|----------|------------------------------------|----------------|-----------|-----------------|
| 87-5500 | BV300S | Glue Spray Air Filtration Unit | 325m³/hr | A3 | £272.83 |
| 87-5501 | BV200S | Glue Spray Air Filtration Unit | 325m³/hr | A2 | £332.10 |
| 87-5504 | BV300S-D | Air Extraction Unit | 355m³/hr | A3 | £253.11 |
| 87-5502 | BV200H | Air Filtration Hoods & Spray Booth | 325m³/hr | A2 | £595.35 |
| 87-5503 | BV100H | Air Filtration Hoods & Spray Booth | 650m³/hr | A1 | £809.19 |
| 87-5505 | BV200H-D | Air Extraction Spray Booth | 355m³/hr | A2 | £676.14 |
| 87-5506 | BV100H-D | Air Extraction Spray Booth | 710m³/hr | A2 | £1033.35 |
| 87-5521 | BV550S-D | Fume and Vapour Extraction Unit | 355m³/hr | 510x360mm | £628.22 |
| 87-5517 | BV570H-C | Small Desktop Fume Cabinet | 202m³/hr | 570x465mm | £805.95 |
| 87-5513 | BV500S-C | Desk/Bench Top Fume Cabinet | 325m³/hr | 575x385mm | £1056.32 |
| 87-5514 | BV700S-C | Desk/Bench Top Fume Cabinet | 650m³/hr | 515x785mm | £1563.30 |
| 87-5519 | BV660H-D | Fume Extraction Hood & Cabinet | 355m³/hr | 680x600mm | £854.55 |
| 87-5520 | BV930H-D | Fume Extraction Hood & Cabinet | 710m³/hr | 960x740mm | £1308.15 |
| 87-5515 | BV660H-C | Fume Filtration Hood & Cabinet | 355m³/hr | A2 | £1141.29 |
| 87-5516 | BV930H-C | Fume Filtration Hood & Cabinet | 710m³/hr | A2 | £1701.00 |



Spare & replacement
filters available

For full details and technical specifications visit
www.rapidonline.com

Hot Stirrer

medline
SCIENTIFIC LIMITED

MS-300 Hot Plate Stirrers

The Medline MS-300 Hot Plate Stirrer offers a large heating area of 180 x 180mm and is ideal for use with flat-bottomed vessels. With safe, controlled heating up to 400°C, the Medline MS300 provides a safer, more accurate heat source than the



conventional Bunsen burner arrangement. The speed of the built-in magnetic stirrer of the Medline MS-300 Hot Plate Stirrer can be controlled between 100 and 1500rpm.

Also available are two sizes of octahedral stirring bars 15 x 8mm or 25 x 8mm. Both types feature pivot rings.

- Heating area 180 x 180mm
- Temperature up to 400°C
- Stirrer speed 100 to 1500rpm
- Operating voltage 220V AC
- **Medline type MS-300**

| Type | Order code | 1+ |
|-------------------|----------------|--------|
| Hot plate stirrer | 52-0449 | 174.71 |
| 16mm Stirring bar | 52-1029 | 2.90 |
| 25mm Stirring bar | 52-1031 | 3.40 |

500331

RVFM

Wadding

Wadding for stuffing puppets, quilting and many other textiles projects.

- Size 1m x 1m
- Weight 135g (4oz.) per metre

| Type | Order code | 1+ |
|---------|----------------|------|
| Wadding | 06-0439 | 3.31 |

500631



RVFM

Mini Hot Plate

This thermostatically-controlled hotplate can be programmed to maintain a steady temperature anywhere between room temperature and 80 °C. It has a variety of applications, including the investigation of the effect of different materials on the rate of energy transfer.



- Thermochromic film (included) on the top plate changes colour as the top plate heats up
- Area of the plate is 5cm square

Requires a regulated 12V power supply with a current rating of at least 2A.

| Type | Order code | 1+ |
|----------------|----------------|-------|
| Mini hot plate | 06-1589 | 33.56 |

503712

Heating Mantles

medline
SCIENTIFIC LIMITED

E Series Temperature Controlled Heating Mantles



Medline E Series Temperature Controlled Heating Mantles have Nichrome wire heating elements and woven glass fibre mat mantles. An important addition to any science

laboratory, the Medline E Series mantles benefit from rugged steel construction and can heat up to 450°C.

- Nichrome wire heating element
- Mantle made from woven glass fibre mat
- Steel case construction with chemical-resistant coating
- Moulded silica powder thermal insulation
- Temperature range up to 450°C (Max.)
- Power Supply: 220V AC

Technical specification

| Model No. | Capacity | Watts |
|-----------|----------|-------|
| E1005 | 50ml | 60 W |
| E101 | 100ml | |
| E102 | 250ml | 150 W |
| E103 | 500ml | 260 W |
| E104 | 1000ml | 350 W |

| Type | Order code | 1+ |
|---------|----------------|--------|
| 50ml | 52-0451 | 96.60 |
| 100ml | 52-0835 | 99.37 |
| 250ml | 52-0453 | 119.90 |
| 500ml | 52-0455 | 154.95 |
| 1 litre | 52-0457 | 149.95 |

500332

How do I ...

Email baskets?

Register Online?

Find invoices?


www.rapidonline.com/schools-faq

| Order code | Description | 1+ |
|----------------|-----------------------|---------------|
| 75-0171 | Romeo V1+motor driver | £22.95 |
| 75-0167 | Romeo V2+motor driver | £24.95 |
| 75-0169 | Romeo BLE | £29.95 |
| 75-0168 | Romeo BLE mini | £17.95 |

DFRobot Romeo Arduino Robot Control Boards

The Romeo family is an All-in-One Arduino-based control board especially designed for robotics applications from DFRobot. It benefits from the Arduino open source platform, it is supported by thousands of open source codes, and can easily be expanded with your Arduino shields. The integrated 2-way DC motor driver and wireless socket allows you to start your own robot project immediately without the need for an additional motor driver. Romeo is also designed to have extra power for servos which need more current.

Romeo is also featured with DFRobot's standard 3 pin-out design and is compatible with Gravity series sensors and actuators. Hundreds of sensors are now plug-play with Romeo. You may also check the Bluetooth microcontroller selection guide to get more information.



DFROBOT®
DRIVE THE FUTURE