



General Laboratory Equipment

Beakers	218	Filter Paper	234	Petri Dishes & Racks	233
Bottles	226	Flasks	219	Plastic Measuring Cylinders	229
Burettes	231	Fume Extraction	240	Polypropylene Coplin Jar	230
Burners & Stands	236	Funnels & Holders	228	Re-Useable Syringes	229
Chromatography	234	Glass Filter Funnels	227	Retort Stands & Clamps	237
Calorimeters	238	Glass Tubing	226	Spatulas, Spoons & Scoops	235
Containers	230	Gas Washing Bottles	227	Stirring Rods	236
Coplin Jars	227	Heating Mantles	242	Stoppers & Bungs	229
Cork Borers	229	Health & Safety	239	Storage Vials	231
Cotton Wool	235	Hot Stirrer	242	Test Tube Brushes	223
Crucibles	228	Indicator Test Paper	235	Test Tube Holders	223
Crystallising Dishes	227	Jointed Glassware	226	Test Tubes	223
Culture Tubes	223	Measuring	238	Tongs & Holders	235
Cylinders	222	Measuring Beakers	229	Tweezers	236
Drying Tubes	223	Pestle & Mortars	228	Watch Glass	227
Evaporating Dishes	227	Pipette Fillers	233		
Expansion and Reduction Adapters	224	Pipettes	232		

Full range of General Laboratory Equipment available at:

www.rapidonline.com

ACADEMY
Science ProductsSIMAX®
LAB GLASS®
KIMBLE CHASE

Tall Form Beakers

Capacity	Academy				LabGlass			
	Order code	Unit price	Pack size	Price	Order code	Unit price	Pack size	Price
25ml					52-4051	£0.69	12	£8.28
50ml	52-2242	£0.59	12	£7.13	52-4054	£0.88	12	£10.50
100ml	52-2243	£0.68	12	£8.10	52-4048	£1.21	12	£11.43
150ml	52-2244	£0.73	12	£8.75	52-4049	£1.08	12	£12.94
250ml	52-2245	£0.97	12	£11.66	52-4050	£1.13	12	£13.58
400ml	52-2246	£1.23	12	£14.74	52-4052	£1.31	6	£7.83
500ml					52-4053	£1.59	6	£9.54
600ml	52-2247	£1.65	6	£9.88	52-4055	£1.73	6	£10.40
800ml	52-2248	£2.11	6	£12.64				
1000ml	52-2249	£2.39	6	£14.34	52-4047	£2.58	6	£15.49
2000ml	52-2250	£7.25	4	£29.00				
3000ml	52-2251	£10.72	1	£10.72				



Tall Form Beaker

Low Form Heavy Wall Beakers

Capacity	Academy				Kimble Chase			
	Order code	Unit price	Pack size	Price	Order code	Unit price	Pack size	Price
150ml	52-1063	£1.50	12	£17.99				
250ml	52-1065	£1.80	12	£21.59				
400ml	52-1067	£2.28	12	£27.36				
600ml	52-1069	£3.42	6	£20.56	52-1898	6.92	1	£6.92
1000ml	52-1071	£4.33	6	£25.96				
2000ml	52-1073	£6.93	4	£27.70				



Low Form Beaker



Low Form Heavy Wall Beaker

Low Form Beakers

Capacity	Academy				LabGlass				Simax				Kimble Chase			
	Order code	Unit price	Pack size	Price	Order code	Unit price	Pack size	Price	Order code	Unit price	Pack size	Price	Order code	Unit price	Pack size	Price
5ml					52-4044	£0.72	10	£7.18								
10ml					52-4034	£0.66	12	£7.95								
25ml	52-1088	£0.34	12	£4.11	52-4038	£0.70	12	£8.38								
50ml	52-0949	£0.54	12	£6.42	52-4043	£0.85	12	£10.19	52-0202	£0.84	10	£8.43	52-2264	£3.01	12	£36.15
100ml	52-0951	£0.54	12	£6.52	52-4033	£0.87	12	£10.41	52-0204	£0.88	10	£8.78	52-2265	£3.29	12	£39.45
150ml					52-4035	£0.88	12	£10.50								
250ml	52-0953	£0.63	12	£7.50	52-4037	£0.93	12	£11.13	52-0206	£0.91	10	£9.12	52-2266	£3.59	12	£43.12
400ml					52-4040	£1.15	6	£6.88	52-0208	£1.26	10	£12.58	52-2267	£4.29	12	£51.42
500ml					52-4042	£1.39	6	£8.36								
600ml	52-0955	£1.01	6	£6.04	52-4045	£1.68	6	£10.07	52-0210	£1.51	10	£15.07	52-2268	£5.46	6	£32.78
800ml					52-4046	£2.01	6	£12.03					52-2269	£9.48	6	£56.88
1000ml	52-0959	£1.32	6	£7.93	52-4032	£2.20	6	£13.18	52-0212	£2.21	10	£22.06				
2000ml	52-1089	£4.12	4	£16.46	52-4036	£4.85	1	£4.85								
3000ml					52-4039	£11.86	1	£11.86								
5000ml	52-1091	£14.31	1	£14.31	52-4041	£18.23	1	£18.23								
10,000ml					52-4031	£50.99	1	£50.99								

Conical Flasks – Narrow Neck



Capacity	Academy			
	Order code	Unit price	Pack size	Price
10ml				
25ml				
50ml				
100ml	52-0969	£0.67	12	£8.08
250ml	52-0971	£0.87	6	£5.23
500ml	52-0973	£1.56	6	£9.38
1000ml	52-1075	£2.67	6	£16.01
2000ml	52-1077	£8.24	1	£8.24
3000ml				
5000ml				

Capacity	LabGlass			
	Order code	Unit price	Pack size	Price
10ml	52-4155	£0.79	12	£9.48
25ml	52-4158	£0.92	12	£11.06
50ml	52-4162	£0.72	12	£8.60
100ml	52-4154	£1.21	12	£14.47
250ml	52-4157	£0.92	12	£11.06
500ml	52-4161	£1.63	6	£9.75
1000ml	52-4153	£2.41	6	£14.47
2000ml	52-4156	£9.32	1	£9.32
3000ml	52-4159	£9.58	1	£9.58
5000ml	52-4160	£18.50	1	£18.50

Capacity	Simax			
	Order code	Unit price	Pack size	Price
10ml				
25ml				
50ml	52-1189	£2.58	10	£25.80
100ml	52-0214	£1.07	10	£10.73
250ml	52-0216	£1.13	10	£11.28
500ml	52-1191	£1.76	10	£17.62
1000ml	52-1193	£3.25	10	£32.48
2000ml	52-1201	£9.67	6	£57.99



Conical Flasks – Wide Neck



Capacity	Simax			
	Order code	Unit price	Pack size	Price
25ml	52-1246	£3.89	10	£38.85
50ml	52-1247	£6.55	10	£65.45
100ml	52-1248	£1.29	10	£12.86
250ml	52-1249	£1.59	10	£15.85
300ml	52-1250	£2.99	10	£29.85
500ml	52-1251	£2.29	10	£22.85
1000ml	52-1252	£6.42	10	£64.19
2000ml	52-1253	£10.98	6	£65.90

Volumetric Flasks with Stopper Class A



Volumetric flasks from LabGlass fitted with a chemical resistant polypropylene stopper.

- Available in a range of sizes
- Made from borosilicate glass with one graduation mark
- Blue graduation
- Conforms to DIN ISO 1042 standard

Capacity	LabGlass				
	Order code	Unit price	Pack size	Socket size	Price
5ml	52-4177	£1.43	2	10/19	£2.86
10ml	52-4171	£1.43	2	10/19	£2.86
25ml	52-4174	£1.57	2	10/19	£3.13
50ml	52-4176	£1.77	2	12/21	£3.53
100ml	52-4170	£2.03	2	14/23	£4.05
250ml	52-4173	£3.13	2	14/23	£6.26
500ml	52-4175	£4.00	2	19/26	£8.00
1000ml	52-4169	£5.56	2	24/29	£11.12
2000ml	52-4172	£10.00	1	29/32	£10.00



Volumetric Flask Class B



Capacity/ socket size	LabGlass			
	Order code	Unit price	Pack size	Price
10ml 10/19	52-4180	£1.31	2	£2.61
20ml 10/19	52-4182	£1.15	10	£11.50
25ml 10/19	52-4184	£1.67	2	£3.33
50ml 12/21	52-4186	£1.93	2	£3.86
100ml 14/23	52-4179	£1.90	2	£3.79
200ml 14/23	52-4181	£2.55	2	£5.09
250ml 14/23	52-4183	£2.87	2	£5.74
500ml 19/26	52-4185	£3.53	2	£7.05
1000ml 24/29	52-4178	£4.83	2	£9.66

Capacity	Glassco			
	Order code	Unit price	Pack size	Price
10ml				
25ml				
50ml				
100ml				
250ml				
500ml				
1000ml				
2000ml				
52-0998	£3.46	2	£6.92	
52-0999	£4.64	2	£9.27	
52-1455	£6.34	2	£12.68	
52-1457	£10.73	2	£21.45	



Round Bottom Boiling Flasks, Narrow Neck

ACADEMY



SIMAX

Capacity	Academy				LabGlass				Simax			
	Order code	Unit price	Pack size	Price	Order code	Unit price	Pack size	Price	Order code	Unit price	Pack size	Price
25ml					52-4146	£0.95	12	£11.41				
50ml	52-2252	£1.05	12	£12.56	52-4148	£1.19	12	£14.30	52-1990	£3.91	10	£39.15
100ml	52-2253	£1.20	12	£14.45	52-4143	£1.92	12	£23.01	52-1991	£7.91	10	£79.11
150ml					52-4144	£2.00	12	£23.99				
250ml	52-2254	£2.66	12	£31.97	52-4145	£2.67	12	£32.05	52-1992	£5.75	10	£57.51
500ml	52-2255	£3.86	8	£30.89	52-4147	£3.48	6	£20.88	52-1993	£6.97	10	£69.66
1000ml	52-2256	£5.06	6	£30.35	52-4142	£4.84	6	£29.02	52-1994	£9.44	10	£94.37



Round Bottom Boiling Flasks, Wide Neck



Capacity	LabGlass			
	Order code	Unit price	Pack size	Price
25ml	52-4149	£1.32	12	£15.81
50ml	52-4150	£1.73	12	£20.77
100ml	52-4151	£2.16	12	£25.89
150ml	52-4152	£1.99	12	£23.82



Boiling Flasks, Flat Bottom, Wide Neck



Capacity	LabGlass			
	Order code	Unit price	Pack size	Price
50ml	52-4141	£1.13	12	£13.59
100ml	52-4138	£1.49	12	£17.90
250ml	52-4139	£2.60	12	£31.18
500ml	52-4140	£4.13	6	£24.78
1000ml	52-4137	£6.33	6	£37.97



Boiling Flasks, Flat Bottom, Narrow Neck

ACADEMY



SIMAX

Capacity	Academy				LabGlass				Simax			
	Order code	Unit price	Pack size	Price	Order code	Unit price	Pack size	Price	Order code	Unit price	Pack size	Price
25ml					52-4134	£0.95	12	£11.35				
50ml	52-2257	£1.07	12	£12.89	52-4136	£1.14	12	£13.72	52-1995	3.51	10	£35.10
100ml	52-2258	£1.12	12	£13.46	52-4131	£1.26	12	£15.16	52-1996	1.54	10	£15.39
150ml					52-4132	£1.42	12	£17.03				
250ml	52-2259	£1.47	12	£17.60	52-4133	£1.60	12	£19.19	52-1997	6.26	10	£62.64
500ml	52-2260	£2.10	12	£25.15	52-4135	£2.30	6	£13.82	52-1998	2.77	10	£27.70
1000ml	52-2261	£3.35	6	£20.09	52-4130	£5.78	6	£34.67	52-1999	12.46	10	£124.61





Round Bottom Flasks with Two Necks

Round bottomed borosilicate glass flasks from Glassco with two necks - one jointed in the centre and one angled at the side. Ideal for use in a range of laboratory applications.

- Available in a range of sizes



Capacity	Centre socket	Side socket	Order code	Price
100ml	14/23	14/23	52-1545	£8.78
100ml	24/29	14/23	52-1547	£10.76
100ml	24/29	19/26	52-1549	£12.20
250ml	24/29	14/23	52-1551	£9.53
250ml	24/29	19/26	52-1553	£10.23
500ml	24/29	14/23	52-1555	£10.54
500ml	24/29	19/26	52-1557	£11.92
1000ml	24/29	14/23	52-1559	£12.57
1000ml	24/29	19/26	52-1561	£22.57

567986



Round Bottom Flasks with Three Necks

Round bottomed borosilicate glass flasks from Glassco with three jointed necks - one in the centre and two angled at the side. Ideal for use in a range of laboratory applications.

- Available in a range of sizes



Capacity	Centre socket	Side socket	Order code	Price
100ml	19/26	14/23	52-1563	£13.41
100ml	24/29	14/23	52-1565	£13.41
100ml	24/29	19/26	52-1567	£15.30
250ml	19/26	14/23	52-1569	£13.41
250ml	19/26	19/26	52-1571	£16.62
250ml	24/29	14/23	52-1573	£16.62
250ml	24/29	19/26	52-1575	£16.62
500ml	24/29	14/23	52-1577	£14.05
500ml	24/29	19/26	52-1579	£17.25
500ml	29/32	14/23	52-1581	£15.53
1000ml	24/29	19/26	52-1583	£23.15
1000ml	24/29	19/26	52-1585	£23.44
1000ml	34/35	19/26	52-1587	£25.73
2000ml	24/29	19/26	52-1589	£35.87
2000ml	343/35	19/26	52-1591	£37.42

567987



Wide Neck Flat Bottom Flasks

These flat-bottomed flasks from Simax have a wide neck with a rim and are suitable for use in a range of laboratory applications.

- Made from borosilicate glass
- Meets ISO 24450 standard
- Available in range of sizes
- Supplied in packs of 10



Capacity	Overall dia.	Neck dia.	Height	Order code	Price
50ml	51mm	34mm	100mm	52-2001	£55.76
100ml	64mm	34mm	110mm	52-2003	£83.97
250ml	85mm	50mm	140mm	52-2005	£67.91
500ml	105mm	50mm	170mm	52-2007	£80.33
1000ml	131mm	50mm	200mm	52-2009	£104.09

568014



Pear Shape Single Neck Flasks

Pear-shaped flasks from Glassco with a single neck suitable for use in a number of laboratory applications.

- Made from borosilicate glass
- Available in a choice of sizes
- Supplied in packs of 10



Capacity	Socket size	Height	Diameter	Order code	Price
50ml	14/23	115mm	50mm	52-1803	£36.18
50ml	19/26	130mm	50mm	52-1805	£83.30
100ml	14/23	135mm	60mm	52-1809	£36.99
100ml	19/26	140mm	60mm	52-1827	£36.64

567998



Round Bottom Distilling Flasks with Side Arm

These distilling flasks from LabGlass have a round bottom and a side arm.

- Available in a choice of sizes
- Made from borosilicate glass



Capacity	Diameter	Height	Arm length	Order code	Price
100ml	64mm	215mm	100mm	52-4163	£3.04
250ml	250mm	225mm	125mm	52-4164	£3.78
500ml	105mm	240mm	140mm	52-4165	£4.99

567998



Conical Filtering Flasks with Plastic Screw and Integral Side Arm

These conical filtering flasks from LabGlass have an integral plastic screw thread side arm.

- Available in a choice of sizes
- Made from borosilicate glass



Capacity	Order code	Price
250ml	52-4167	£4.79
500ml	52-4168	£6.37
1000ml	52-4166	£7.10

568086



Rapid We bring STEM to life
education

Round Base Cylinder Class B

ACADEMY

Capacity	Academy				LabGlass			
	Order code	Unit Price	Pack Size	Price	Order code	Unit Price	Pack Size	Price
10ml	52-1431	£0.96	1	£0.96	52-4122	£0.85	10	£8.52
25ml	52-1433	£1.06	1	£1.06	52-4125	£1.10	2	£2.19
50ml	52-1435	£1.16	1	£1.16	52-4127	£1.26	2	£2.52
100ml	52-1437	£1.51	1	£1.51	52-4121	£1.56	2	£3.12
250ml	52-1439	£2.51	1	£2.51	52-4124	£2.44	2	£4.87
500ml					52-4126	£3.60	2	£7.19
1000ml					52-4123	£6.45	2	£12.89



Round Base

Hexagonal Base

Hexagonal Base Cylinder Class B

SIMAX®

Capacity	LabGlass				Simax			
	Order code	Unit Price	Pack Size	Price	Order code	Unit Price	Pack Size	Price
5ml	52-4116	£1.22	2	£2.44	52-0192	£3.88	1	£3.88
10ml	52-4117	£1.33	2	£2.65	52-0196	£3.95	1	£3.95
25ml	52-4120	£2.34	2	£4.68	52-0198	£4.75	1	£4.75
50ml	52-4115	£2.86	2	£5.71	52-0200	£6.01	1	£6.01
100ml	52-4114	£2.65	2	£5.30	52-1205	£10.19	1	£10.19
250ml	52-4119	£4.02	2	£8.04				
500ml	52-4113	£6.05	2	£12.10				
2000ml	52-4118	£15.44	1	£15.44				



Hexagonal Base Cylinder with Spout Class A

These measuring cylinders from LabGlass have a hexagonal base and spout.

- Available in a choice of sizes
- White graduation
- Made from borosilicate glass
- Class A
- Complies with DIN EN ISO 4788 standard
- Supplied in packs of 2 (except 2 litre version)



Squat Form Hexagonal Base Cylinder with Spout Class B

Squat form measuring cylinders from LabGlass with a hexagonal base and spout.

- Available in a choice of sizes
- White graduation
- Made from borosilicate glass
- Class B
- Supplied in packs of 2



Capacity	Order code	Sub-division	Unit price	Pack size	Price
5ml	52-4108	0.1ml	£2.33	2	£4.66
10ml	52-4109	0.2ml	£2.24	2	£4.47
25ml	52-4110	0.25ml	£3.66	2	£7.31
50ml	52-4107	1ml	£4.30	2	£8.59
100ml	52-4099	1ml	£4.96	2	£9.92
250ml	52-4111	2ml	£6.86	2	£13.71
500ml	52-4098	5ml	£10.49	2	£20.97
1000ml	52-4097	10ml	£12.79	2	£25.58
2000ml	52-4112	20ml	£20.10	1	£20.10

568061

Capacity	Order code	Sub-division	Unit price	Pack size	Price
50ml	52-4096	1ml	£3.80	2	£7.59
100ml	52-4094	2ml	£4.77	2	£9.53
250ml	52-4095	5ml	£5.48	2	£10.96

568060

SIMAX®

Desiccator

Desiccator from Simax with a knobbed lid and a perforated ceramic disc ideal for laboratory use.

- Made from borosilicate glass
- Size 200mm
- Overall diameter 269mm
- Base diameter 190mm
- Manufacturer's part 262D/200

Order code
52-1987
200mm

£82.28

Test Tubes



Test Tubes and Boiling Tubes with Rims

These **test tubes** from **Kimble Chase** are manufactured from borosilicate glass tubing and can be used for a wide range of applications. They are designed for **maximum heat transfer** and chemical resistance.

- Wall thickness between 0.8 to 1.0mm
- Smaller tubes are supplied in **packs of 100**
- 24 x 150mm tubes are supplied in **packs of 50**

Size	Quantity	Order code	1+
10 x 75mm	100	52-1895	15.64
12 x 75mm	100	52-1254	15.36
16 x 100mm	100	52-1255	25.38
16 x 125mm	100	52-1900	33.13
16 x 150mm	100	52-1897	35.00
24 x 150mm	50	52-1902	24.83



Test Tubes with Side Arms

These test tubes are made from Borosilicate glass and feature a side arm.

- Available in various sizes

Length/dia.	Order code	1+
125 x 17mm	52-1282	0.889
150 x 19mm	52-1284	0.91
150 x 24mm	52-1286	1.28



Absorption Tubes 150 x 20mm (Pack of 2)

A borosilicate glass U-form absorption tube, with strong walls and side tubes. Absorption tubes are commonly used with calcium chloride or other desiccants to remove moisture from gases passed through them.

- Length 150mm
- Diameter 20mm
- Supplied in **packs of 2**
- **Eisco type CH0042C**

Type	Order code	1+
Absorption tube	52-3432	4.78

Test Tube Brushes



Test Tube Brushes



Brushes for cleaning test tubes and other tubular equipment.

- High quality bristles mounted in heavy gauge twisted galvanised wire

- Wire handles can be bent to clean awkward shapes
- Available in a range of sizes
- Supplied **singly**

Technical specification		
Size	Brush area size	Overall length
Small	50 x 17mm dia.	150mm
Medium	75 x 25mm dia.	200mm
Large	75 x 35mm dia.	240mm

MOQ 4		
Type	Order code	4+
Small	52-8048	0.257

MOQ 3		
Type	Order code	3+
Medium	52-8050	0.413

MOQ 2		
Type	Order code	2+
Large	52-8052	0.498



Cleaning Brushes for Laboratory Glassware and Plasticware

Cleaning brushes for beakers, burettes, test tubes, measuring cylinders and many other items of other laboratory glassware and plasticware. The hard nylon bristles are mounted in twisted galvanised iron wire.

- Suitable for beakers, burettes, test tubes, measuring cylinders and many other items of other laboratory glassware and plasticware
- Hard nylon bristles, mounted in twisted galvanised iron wire

MOQ 2		
Type	Order code	2+
Beaker Brush	52-8053	0.592

Price each		
Type	Order code	1+
Burette Brush	52-8055	0.549

MOQ 2		
Type	Order code	2+
Test Tube Brush	52-8057	0.75



Flask, Bottle, Burette and Beaker Brushes

A range of brushes for cleaning laboratory equipment.

Type	Order code	1+
Flask / bottle brush	52-3451	0.802
Burette brush	52-3452	0.712
Economy beaker brush	52-3524	5.40
Nylon beaker brush	52-3525	1.43

Drying Tubes



Angled Glass Drying Tubes

These **angled drying tubes** from **Glassco** are suitable for use with other laboratory equipment.

- Made from borosilicate glass
- Available in a range of sizes

Rapid education **We bring STEAM to life**

Size	Order code	1+
10/19	52-1873	5.40
14/23	52-1877	5.40
19/26	52-1879	6.13
24/29	52-1881	6.75
29/32	52-1883	6.75

Culture Tubes



Plain Disposable Culture Tubes

These plain disposable **culture tubes** from **Kimble Chase** have a rim top and are made from borosilicate glass.

- Available in a range of sizes
- Supplied in **packs of 1000** (500 for 18 x 150mm)

Size	Quantity	Order code	1+
10 x 75mm	1000	52-1257	24.59
12 x 75mm	1000	52-1259	35.45
13 x 100mm	1000	52-1261	52.77
16 x 125mm	1000	52-1263	55.51
16 x 150mm	1000	52-1276	57.00
18 x 150mm	500	52-1279	65.31

Test Tube Holders



Wooden Test Tubes Holders with Spring (Pack of 10)

A 180mm long clothes peg-style, wooden test tube holder.

- Accepts 11 to 19mm diameter test tubes
- Jaws open to 32mm
- Made from wood with a metal spring
- Supplied in **packs of 10**
- **Eisco type CH0726A**

Test tube not included.

Type	Order code	1+
Test tube holders	52-3386	3.99



Metal Test Tube Holder

A Stoddard's pattern test tube holder ideal for students.

- Spring action clamps tubes in place
- Finger grips for safe holding
- Holds tubes up to 25mm diameter
- Nickel plated steel construction
- Overall length 130mm

MOQ 2		
Type	Order code	2+
Test tube holder	52-8040	0.35

Expansion Adapters



Joints Size	Glassco			
	Order code	Unit Price	Pack Size	Price
14/23, 10/19	52-1611	£8.114	10	£81.14
19/26, 14/23	52-1613	£4.361	10	£43.61
24/29, 14/23	52-1615	£4.361	10	£43.61
24/29, 19/26	52-1617	£4.361	10	£43.61
29/32, 14/23	52-1619	£5.279	10	£52.79
29/32, 19/26	52-1629	£5.279	10	£52.79
29/32, 24/29	52-1631	£5.279	10	£52.79
34/35, 19/26	52-1633	£5.93	1	£5.93
34/35, 24/29	52-1635	£5.93	1	£5.93
34/35, 29/32	52-1637	£8.19	1	£8.19
40/38, 29/32	52-1639	£11.21	1	£11.21

Order code	Unit Price	Pack Size	A PLUS	
			Price	
52-1349	£9.50	1	£9.50	
52-1387	£8.68	1	£8.68	
52-1388	£8.68	1	£8.68	
52-1389	£11.69	1	£11.69	
52-1390	£11.87	1	£11.87	



Reduction Adapters



Joints Size	Glassco			
	Order code	Unit Price	Pack Size	Price
10/19, 14/23	52-1641	£5.02	10	£50.22
14/23, 19/26	52-1643	£4.47	10	£44.69
14/23, 24/29	52-1645	£4.47	10	£44.69
14/23, 29/32	52-1647	£4.47	10	£44.69
19/26, 24/29	52-1649	£4.47	10	£44.69
19/26, 29/32	52-1651	£4.67	10	£46.71
19/26, 34/35	52-1653	£5.83	10	£58.32
19/26, 40/38	52-1655	£7.02	10	£70.20
19/26, 45/40	52-1657	£7.79	10	£77.90
24/29, 29/32	52-1659	£4.67	10	£46.71
24/29, 34/35	52-1661	£5.95	10	£59.54
24/29, 40/38	52-1663	£7.02	10	£70.20
24/29, 45/40	52-1665	£8.07	10	£80.73
24/29, 50/42	52-1667	£7.66	10	£76.55
29/32, 34/35	52-1669	£5.66	10	£56.57
29/32, 45/40	52-1671	£10.14	10	£101.39
34/35, 40/38	52-1673	£8.84	10	£88.43
34/35, 45/40	52-1675	£12.38	10	£123.80
34/35, 50/42	52-1677	£12.38	10	£123.80

Order code	Unit Price	Pack Size	A PLUS	
			Price	
52-1391	£6.73	1	£6.73	
52-1392	£6.73	1	£6.73	
52-1393	£6.73	1	£6.73	
52-1394	£6.73	1	£6.73	



Jointed Adaptors with Drying Tube

Jointed glass adaptors from A PLUS with a drying tube set at a 75° angle.

- Available in choice of sizes



Joint	Order code	1+
14/23	52-1427	£10.66
19/26	52-1429	£11.38

For full details visit
www.rapidonline.com



Jointed Liebig Condensers and Connectors

These glass Liebig condensers from A PLUS have removable hose connections and can be used to cool and condense hot vapour as part of a laboratory distilling apparatus.

- Available in a choice of sizes




Overall height	Order code	1+
200mm	52-1398	£22.00
280mm	52-1397	£20.66
300mm	52-1399	£23.36



Liebig Condensers

These glass Liebig condensers from A PLUS are used to cool and condense hot vapour as part of a laboratory distilling apparatus.

- Available in a choice of sizes



Overall height	Order code	1+
280mm	52-1395	£19.30
330mm	52-1396	£19.76



Glass Still Head Adaptors

These glass still head adaptors from A PLUS are suitable for use in connecting a flask with a condenser in a laboratory distillation assembly.

- Available in a choice of sizes



Technical specification

Order code	Top joint	Bottom joint	Side joint
52-1401	14/23	14/23	14/23
52-1403	19/26	19/26	19/26
52-1405	24/29	24/29	24/29
52-1407	14/23	24/29	19/26

Top joint	Bottom joint	Order code	1+
14/23	14/23	52-1401	£13.00
19/26	19/26	52-1403	£14.27
24/29	24/29	52-1405	£15.47
14/23	24/29	52-1407	£18.47



Vacuum/Inert Gas Adaptors

These glass vacuum/inert gas adaptors from A PLUS are ideal for use in a laboratory applications.

- Available in a choice of sizes



Technical specification

Order code	Hose diameter (OD)	Joint size
52-1346	8mm	14/23
52-1347	8mm	19/26
52-1348	10mm	24/29

Joint	Hose diameter	Order code	1+
14/23	8mm	52-1346	£9.11
19/26	8mm	52-1347	£8.63
24/29	10mm	52-1348	£8.70

Jointed Round Bottom Flask Single Neck

Capacity	Joint Size	Glassco				A PLUS			
		Order code	Unit Price	Pack Size	Price	Order code	Unit Price	Pack Size	Price
5ml	14/23	52-1467	£3.58	10	£35.75	52-1281	£6.40	1	£6.40
10ml	10/19	52-1469	£4.05	10	£40.50				
10ml	14/23	52-1471	£4.05	10	£40.50	52-1283	£6.40	1	£6.40
25ml	14/23	52-1473	£4.17	10	£41.72	52-1285	£6.26	1	£6.26
25ml	19/26	52-1475	£4.17	10	£41.72	52-1287	£6.26	1	£6.26
25ml	24/29	52-1477	£4.17	10	£41.72	52-1289	£6.26	1	£6.26
50ml	14/23	52-1479	£4.64	10	£46.44	52-1291	£6.70	1	£6.70
50ml	19/26	52-1481	£4.64	10	£46.44	52-1293	£7.78	1	£7.78
50ml	24/29	52-1483	£4.64	10	£46.44	52-1295	£7.78	1	£7.78
50ml	34/35	52-1485	£5.95	10	£59.54				
100ml	14/23	52-1487	£4.19	10	£41.85	52-1297	£8.32	1	£8.32
100ml	19/26	52-1489	£4.19	10	£41.85	52-1299	£8.32	1	£8.32
100ml	24/29	52-1491	£4.19	10	£41.85	52-1301	£8.32	1	£8.32
100ml	29/32	52-1493	£5.10	10	£51.03	52-1303	£8.32	1	£8.32
100ml	34/35	52-1495	£5.54	10	£55.35				
150ml	19/26	52-1497	£5.16	10	£51.57				
150ml	24/29	52-1499	£5.16	10	£51.57				
250ml	14/23	52-1501	£5.13	10	£51.30				
250ml	19/26	52-1503	£5.13	10	£51.30	52-1309	£9.80	1	£9.80
250ml	24/29	52-1505	£5.13	10	£51.30	52-1311	£9.80	1	£9.80
250ml	29/32	52-1507	£5.13	10	£51.30	52-1313	£10.89	1	£10.89
250ml	34/35	52-1509	£7.02	10	£70.20				
500ml	19/26	52-1511	£7.07	10	£70.74	52-1315	£12.38	1	£12.38
500ml	24/29	52-1513	£7.07	10	£70.74	52-1317	£12.38	1	£12.38
500ml	29/32	52-1515	£7.07	10	£70.74	52-1319	£12.38	1	£12.38
500ml	34/35	52-1517	£7.63	10	£76.28				
500ml	45/40	52-1519	£10.23	10	£102.33				
1000ml	19/26	52-1521	£9.77	10	£97.74				
1000ml	24/29	52-1523	£9.77	10	£97.74				
1000ml	29/32	52-1525	£9.91	10	£99.09				
1000ml	34/35	52-1527	£10.76	10	£107.60				
2000ml	24/29	52-1529	£17.24	10	£172.40				
2000ml	29/32	52-1531	£17.47	10	£174.69				
2000ml	34/35	52-1533	£18.12	10	£181.17				
3000ml	24/29	52-1535	£29.32	1	£29.32				
3000ml	34/35	52-1537	£29.92	1	£29.92				
5000ml	29/32	52-1539	£38.62	1	£38.62				
5000ml	34/35	52-1541	£39.38	1	£39.38				
5000ml	45/40	52-1543	£39.81	1	£39.81				



Jointed Round Bottom Flask Two Necks

Capacity	Centre Joint	Side Joint	Glassco				A PLUS			
			Order code	Unit Price	Pack Size	Price	Order code	Unit Price	Pack Size	Price
100ml	14/23	14/23					52-1321	£17.00	1	£17.00
100ml	14/23	14/23	52-1545	£8.78	1	£8.78	52-1323	£17.06	1	£17.06
100ml	24/29	14/23	52-1547	£10.76	1	£10.76	52-1325	£17.06	1	£17.06
100ml	24/29	19/26	52-1549	£12.20	1	£12.20	52-1327	£17.06	1	£17.06
250ml	24/29	14/23	52-1551	£9.53	1	£9.53				
250ml	24/29	19/26	52-1553	£10.23	1	£10.23	52-1329	£17.14	1	£17.14
500ml	24/29	14/23	52-1555	£10.54	1	£10.54				
500ml	24/29	19/26	52-1557	£11.92	1	£11.92				
1000ml	24/29	14/23	52-1559	£12.57	1	£12.57				
1000ml	24/29	19/26	52-1561	£22.57	1	£22.57				



Jointed Glassware



Glassware Joint Clips

These plastic **joint clips** from **Eisco** are resistant to both temperature and chemicals and are ideal for holding together jointed laboratory glassware, reducing the need for **clamping**.



- Colour: yellow
- Joint size 14/23
- Recommended maximum temperature through joint 80°C
- Supplied in **packs of 10**
- Manufacturer's part **CH0869B**

Type	Order code	1+
Glassware joint clips	52-4187	10.22

56803



Plastic Joint Clips

Conical **joint clips** from **Glasco** designed to hold laboratory equipment in place.



- Available in a range of colours
- Supplied in **packs of 10**

Colour	Size	Order code	1+
Black	10/19	52-1917	14.58
Violet	12/21	52-1919	14.58
Yellow	14/23	52-1921	14.58
Blue	19/26	52-1923	14.04
Green	24/29	52-1925	14.58
Red	29/32	52-1927	14.58
Orange	34/35	52-1929	16.07

56803



Organic Chemistry Sets



These **organic chemistry** sets from **Glasco** include the glassware and other equipment required to conduct increasingly complex experiments, ranging from basic preparations to **advanced** level.

- Equipment made from borosilicate glass

Type	Order code	1+
Set 1	52-1931	30.86
Set 2	52-1933	55.40
Set 7	52-1935	98.09
Set 27	52-1947	56.09

56803



Interchangeable Glassware Organic Chemistry Kit

A 9-piece set of borosilicate 3.3 glassware for organic chemistry experiments. All items use an ISO 383 standard taper 14/23 joint size for maximum versatility. The set is housed in a die-cut foam-lined storage box.



Kit contains:

- 1x flask, pear shaped, 50ml
- 1x still head
- 1x Liebig condenser
- 1x screw-cap adapter
- 1x receiver adaptor
- 1x air leak / steam inlet tube
- 1x dropping funnel 50ml with GP rota-flow tap
- 1x stopper
- 1x -10 to +110°C thermometer
- **Supplied as a set**
- Borosilicate 3.3 glass
- ISO 383 standard taper 14/23 joint size
- **Eisco type CH0876**

Type	Order code	1+
Glassware kit	52-3439	38.99

56588

Glass Tubing



Glass Tubing Cutter

This rugged laboratory glass tube cutter is made from nickel-plated, die-cast metal.



It is fitted with a spring-loaded steel wheel and can cut glass tubes up to 40mm in diameter.

- Nickel-plated, die-cast metal
- Spring-loaded steel wheel
- Cuts glass tubes up to 40mm dia.
- **Eisco type CH0759SUP**

Type	Order code	1+
Glass tubing cutter	52-3569	7.19

565632



Soda Glass Tubing

This soda **glass tubing** is ideal for use in the science laboratory.

- Available in 5mm and 6mm diameter
- Length 0.5m
- Supplied in **packs of 30**




Diameter	Order code	1+
5mm	52-2751	25.94
6mm	52-2752	25.94

550637



Polypropylene Cross Tubing Connectors

This 4-way cross-shaped **connector** from **Eisco** can be used to produce leakproof joints in **tubing** for laboratory equipment.



- Made from polypropylene
- Outside diameter 10mm
- Manufacturer's part **CH0765G**

Outer diameter	Order code	1+
10mm	52-4214	0.476

568101

Bottles



Clear Dropping Bottles 50ml

These 50ml clear soda-lime glass dropping bottles have a stopper size of 14.5/23.

- Supplied **singly**



Type	Order code	1+
50ml single	52-0837	2.73

066611



Powder Glass Bottles with Black Caps

These clear glass **powder bottles** from **Academy** have an attached **black polypropylene cap** and EPE liner.

- Wide neck
- Made from soda-lime glass
- Available in a choice of sizes



Order code	Capacity	Diameter	Height	Mfrs part no.
52-1989	30ml	38.9mm	58.7mm	BCP030C
52-1988	120ml	55.2mm	96mm	BCP0120C

Capacity	Order code	1+
30ml	52-1989	0.408
120ml	52-1988	0.394

568011



Reagent Bottles

Plain clear glass reagent bottles, with narrow neck and dustproof plastic stopper.

- Supplied in **packs of 10**



Contents	Order code	1+
50ml	52-0226	20.00
250ml	52-0230	20.63
500ml	52-1061	32.25

066662

SIMAX®

Clear Graduated Laboratory Bottles

Clear, graduated laboratory bottles with screw caps.

- Borosilicate glass
- Complete with blue screw cap and pouring ring
- Can be Autoclaved up to 140°C
- Conform to **ISO 4796** and **ISO -GL 45**
- Supplied in **packs of 10**



Capacity	Order code	1+
50ml	52-1203	28.75
100ml	52-0986	19.72
250ml	52-0988	19.43
500ml	52-0990	26.73
1000ml	52-0992	37.93

073137

Gas Washing Bottles

SIMAX®

Gas Washing Bottles

Simax gas washing bottles manufactured from borosilicate glass.

- Capacity 100ml
- Overall height 250mm
- Height of bottle 200mm
- Inlet/outlet pipe diameter 8mm
- Supplied **singly**



Type	Order code	1+
100ml	52-0982	17.92

073136



Distilling Apparatus



A set of high quality borosilicate glassware ideal for distillation experiments.

- All joint sizes are 19/26
- Set includes the following glass components:**
- Round-bottom boiling flask 500ml
- Still head
- Liebig condenser
- Receiver adapter
- Separating funnel with stopper
- Supplied as a set

Please note that no tubing, heat source or stands are included.

Type	Order code	1+
Distilling glassware	52-3438	58.43

565387

Crystallising Dish

SIMAX®

Glass Crystallising Dishes with Flat Bottom and No Spout



Crystallising dishes from Simax with a flat bottom but without a spout, ideal for use in laboratory applications.

- Available in a range of sizes
- Made from borosilicate glass
- Conforms to PN 70 0121

Technical specification

Order code	Capacity	Size (D x H)	Quantity	Mfrs part no.
52-1209	40ml	50 x 30mm	10	174/50
52-1211	60ml	60 x 35mm	10	174/60
52-1213	100ml	70 x 40mm	10	174/70
52-1215	150ml	80 x 45mm	10	174/80
52-1217	300ml	95 x 55mm	10	174/95
52-1219	500ml	115 x 65mm	10	174/115
52-1221	900ml	140 x 75mm	10	174/140
52-1223	2000ml	190 x 90mm	4	174/190
52-1225	3500ml	230 x 100mm	4	174/230

Capacity	Diameter	Order code	1+
Packs of 10			
40ml	50mm	52-1209	48.47
60ml	60mm	52-1211	44.42
100ml	70mm	52-1213	73.31
150ml	80mm	52-1215	54.27
300ml	95mm	52-1217	50.70
500ml	115mm	52-1219	90.25
900ml	140mm	52-1221	115.13

Capacity	Diameter	Order code	1+
Packs of 4			
2000ml	190mm	52-1223	100.17
3500ml	230mm	52-1225	104.30

567970

Coplin Jars

ACADEMY®

Glass Coplin Jar

This coplin jar from Academy can be used to stain cells and tissues on microscope slides.

- Made from soda-lime glass
- Height 115mm
- Diameter 90mm
- Supplied in **single jars**
- Manufacturer's part **2959**



Size (H x D)	Order code	1+
115 x 90mm	52-1093	6.60

567968

Full range available online

www.rapidonline.com/education

Watch Glass

eisco

Watch Glasses

Watch glasses are highly functional items of glassware that have a variety of uses in the classroom or laboratory. They are essentially very shallow glass saucers and work well as lids for flasks and beakers, or for holding small samples for observation under a low-power microscope. They are also ideal for evaporating liquids from samples, such as when growing seed crystals, and can be used for making lenses from ice or other liquids.



Eisco watch glasses are manufactured with sturdiness in mind. Their 2mm thick construction resists shattering and as they have ground edges, as well as a polished surface, so you can be sure that they are a safe product to handle in the classroom or the laboratory.

- Available in a range of diameters
- **Eisco CH0554 series**

Diameter	Order code	1+
50mm	52-3467	1.73
60mm	52-3559	2.03
75mm	52-3468	3.36
90mm	52-3469	3.32
100mm	52-3470	4.28
125mm	52-3560	10.00
150mm	52-3561	9.18

565603

Glass Filter Funnels



Borosilicate Glass Filter Funnels

Borosilicate glass, plain filter funnels with 60° angled sides.

The shape of the funnels makes them ideal for use with a folded circular filter paper.

- Borosilicate 3.3 glass



Diameter	Order code	1+
55mm	52-3465	1.27
75mm	52-3466	1.33

565602

Evaporating Dishes

eisco

Porcelain Evaporating Dishes

Superior quality porcelain round-form evaporating dishes with pouring spout. The dishes are fully glazed except for the outside base.

- **Eisco CH0071 series**



Capacity	Order code	1+
80ml	52-3378	0.72
100ml	52-3379	0.81

565554



Evaporating Basins - Porcelain Flat Form with Spout

A range of porcelain flat-form evaporating basins.

- Glazed inside and outside except for rim
- Spout for easy pouring
- Eisco CH0070 series



Capacity	Order code	1+
35ml	52-3519	0.81
50ml	52-3520	0.92
200ml	52-3522	1.19
300ml	52-3523	2.44

565627



Porcelain Hirsch Separating Funnels

Hirsch funnels are used for straining and filtering liquids or for separating solids and liquids.

This range is made from porcelain for minimum

contamination and ease of cleaning. They can be used in conjunction with filter paper for superior separation.

- Angled sides
- Glazed
- Perforated plate



Technical specification

Top outside dia.	Filter paper dia.	Approx. capacity	Overall length	Order code
42mm	8 to 10mm	10ml	70mm	52-3563
55mm	13 to 15mm	20ml	75mm	52-3564
78mm	40 to 45mm	50ml	130mm	52-3565
96mm	52-56mm	130ml	175mm	52-3566

Diameter	Order code	1+
30mm	52-3562	0.92
40mm	52-3563	1.07
50mm	52-3564	1.48
75mm	52-3565	2.22
100mm	52-3566	2.36

565631



Porcelain Buchner Funnels

Buchner Funnels are used for straining and filtering liquids or for separating solids and liquids. This range is made from porcelain for minimum contamination and ease of cleaning. They can be used in conjunction with filter paper for superior separation.

- Straight sides
- Perforated plate
- Used for straining and filtering liquids or separating solids and liquids
- Made from porcelain for minimum contamination and easy cleaning
- Can be used in conjunction with filter paper for superior separation
- Available in a range of diameters



Type	Order code	1+
50mm	52-1937	2.42
125mm	52-1945	7.59

501654

Order online

Save time, and place your order at:
www.rapidonline.com
 24 hours a day



We bring
STEAM to life

Pestle & Mortars



Porcelain Mortars & Pestles

A range of porcelain mortars and pestles with unglazed grinding surfaces.

- Supplied as a set containing one mortar and one pestle



Mortar capacity	Order code	1+
60ml	52-3571	1.22
275ml	52-3572	2.52
550ml	52-3573	4.04
900ml	52-3574	4.38
1500ml	52-3575	5.27
2000ml	52-3576	10.21

565633

Crucibles



Crucibles - Tall

A range of tall-form porcelain crucibles and lids with ring handle.

- Glazed inside and outside except base
- Eisco CH0074 series



Capacity	Order code	1+
10ml	52-3542	0.61
25ml	52-3543	0.73
40ml	52-3544	0.86
50ml	52-3545	0.99
100ml	52-3546	1.22

565629

Funnels & Holders



Economy Plastic Funnels

A range of economical funnels suitable for a wide range of applications in the laboratory. The funnels are made from unbreakable plastic, making them ideal for younger scientists.

- Economical
- Unbreakable plastic
- Wide range of uses



MOQ 4

Type	Order code	4+
50mm	52-0925	0.281

MOQ 3

Type	Order code	3+
62mm	52-0927	0.327
75mm	52-0929	0.327
100mm	52-0933	0.484

502649



Polypropylene Buchner Funnels

These 2-piece plastic funnels are lightweight, easy to clean and autoclavable. They are much less prone to breakage than the traditional porcelain types.

- Rugged construction
- Top part has perforated filter plate
- Parts snap together to give vacuum seal
- Corrosion free polypropylene construction
- Available in 70 and 130mm diameters



Type	Order code	1+
70mm	52-1498	2.47
130mm	52-1500	5.24

122488



Powder Funnels

These polythene funnels have wide, parallel stems and are ideal for transferring powders.

- Corrosion free polypropylene construction
- Available in 80, 100 and 150mm diameters



MOQ 2

Diameter	Order code	2+
80mm	52-1502	0.719

Price each

Diameter	Order code	1+
100mm	52-1504	1.03
150mm	52-1506	2.02

122489



Funnel Holder

Holders for suspending funnels on retort stands.

- Holds funnels 76 to 152mm
- Supplied with adaptor for 25 to 76mm funnels
- Corrosion free polypropylene construction
- Includes tapered wedges to ensure firm grip on both 9.5mm (3/8in.) and 12.7mm (1/2in.) retort stand rods



Type	Order code	1+
Funnel holder	52-1464	2.07

122491



Separator Funnel Holder

Holders for suspending separator funnels on retort stands.

- Front opening gives clear view of solution
- Allows unobstructed placement of funnel
- Corrosion free polypropylene construction
- Includes tapered wedges to ensure firm grip on both 9.5mm (3/8in.) and 12.7mm (1/2in.) retort stand rods



Type	Order code	1+
Separator funnel holder	52-1466	2.68

122492

Stoppers & Bungs



Laboratory Rubber Stoppers

A wide range of **rubber stoppers** with or without holes.

- Wide range of sizes
- Available with or without holes
- Supplied as an **assorted pack of 50** or in **packs of 10**



Top/bottom diameter	Pack quantity	Order code	1+
Solid			
Various	50	52-3356	4.97
16mm/13mm	10	52-3420	0.909
22mm/19mm	10	52-3422	1.33
28mm/25mm	10	52-3423	2.06
With hole			
16mm/13mm	10	52-3421	0.758
28mm/25mm	10	52-3424	2.24
33mm/29mm	10	52-3440	2.69



Assorted Cork Tops

Cork stoppers and bungs in a variety of sizes.

- General purpose natural modelling material
- Ideal for adding buoyancy to models
- Supplied in **packs of 100g**



Type	Order code	1+
Cork tops 100g	06-1310	2.01

Cork Borers



Cork Borers - Sets of 6 and 12

These sets of cutters are for boring holes into cork stoppers and bungs to allow the insertion of glass or plastic tubes, etc.

A single cutter of the desired diameter is simply twisted round using the handles while applying pressure on to the stopper. A push rod is also included for removing the waste material from within the cutter.

- Sets of cutters for boring holes into cork stoppers
- Allows the insertion of glass or plastic tubes, etc.
- Simply twist round using the handles while applying pressure
- A push rod is included for removing the waste material
- Available in **sets of 6 or 12**



Technical specification

Set	Sizes
6-piece	4, 4.7, 5.4, 6.5, 8.3 and 9.3mm
12-piece	3, 4, 5, 6, 8, 9, 11, 13, 14, 15, 17 and 19mm

Type	Order code	1+
Set of 6	06-6601	23.66
Set of 12	06-6605	56.18



Cork Borer Sharpener



Superior quality cork **borer sharpener** from **Eisco** with a hinged **brass cutter** blade set into a slot and wooden handle.

- Plated metal cone
- Suitable for borers 4mm to 27mm diameter
- Manufacturer's part **CH0324B**

Type	Order code	1+
Cork borer sharpener	52-4093	10.07

Re-Useable Syringes



Reusable Syringes

Re-usable syringes.

- Ideal for precise application of glues, greases, pastes and two-part compounds, where a precise amount of each is to be mixed
- Supplied in **packs of 10**



Type	Order code	1+	5+	10+
20ml	87-0346	12.30	12.06	11.52



Re-Useable Syringes

A range of re-usable syringes, ideal for precise application of glues, greases, pastes and two-part compounds, where a precise amount of each is to be mixed.

- The 12ml syringe has a fine, curved tip, ideal for reaching awkward places



MOQ 2				
Type	Order code	2+	10+	50+
1ml	87-0338	0.571	0.483	0.443
5ml	87-0343	0.637	0.555	0.501
Price each				
Type	Order code	1+	10+	
12ml curved	87-0345	3.33	3.13	



Syringe 100ml Glass

This **glass syringe** has a Luer fitting, interchangeable pistons and barrels.

- Capacity 100ml
- Supplied with metal tip



Capacity	Order code	1+
100ml	52-2669	27.24

Measuring Beakers



Polypropylene Measuring Jugs

A range of clear polypropylene measuring jugs with good chemical resistance.

- Graduations every 10ml
- Can be autoclaved
- **Eisco CH0356 series**



Capacity	Order code	1+
250ml	52-3373	0.81
500ml	52-3374	1.21
1000ml	52-3375	1.37



Plastic Laboratory Measuring Beakers

Polypropylene measuring beakers with moulded graduations for ease of use.

- 50ml, 100ml, 250ml and 500ml supplied in **packs of 12**
- 1 litre beakers supplied in **packs of 6**



Type	Order code	1+
50ml pack 12	52-0176	3.59
100ml pack 12	52-0178	3.70
250ml pack 12	52-0180	5.94
500ml pack 12	52-0182	8.99
1 Litre pack 6	52-0184	7.74

Plastic Measuring Cylinders



Plastic Measuring Cylinders

High quality, laboratory grade measuring cylinders made from polypropylene.

- Clear graduation markings on the side
- 25ml and 50ml sizes supplied in **packs of 12**
- 10ml, 100ml and 250ml sizes supplied **singly**



MOQ 3	
Type	Order code
10ml (single)	52-0177

Price each	
Type	Order code
25ml (12)	52-0172
50ml (12)	52-0174

MOQ 2	
Type	Order code
100ml (single)	14-2030

Price each	
Type	Order code
250ml (single)	14-2032

Ultra-clear Polypropylene Tubes



These ultra-clear polypropylene tubes from Medline are ideal for use in rough environments where the use of glass tubes is not crucial. The tubes have greater crush resistance and are shatterproof.

- Autoclavable up to 121°C
- Matching natural-coloured polyethylene caps available separately for some sizes
- Supplied in **packs of 100**

Technical specification				
Internal diameter (mm)	External diameter (mm)	Total length (mm)	Maximum volume (ml)	Order code
10.3	11.7	73.9	5.3	52-1901
10.9	12.7	73.7	6.4	52-1903
13.7	15.8	98.6	12.7	52-1905

Type	Order code	1+
12 x 75mm (100)	52-1901	3.22
13 x 75mm (100)	52-1903	3.59
16 x 100mm (100)	52-1905	4.01
Cap for 52-1901 (100)	52-1909	3.50
Cap for 52-1905 (100)	52-1913	2.23

Technical specification					
Capacity	Bottom diameter	Top diameter	Height	Medline type	Order code
30ml	25.1mm	30.8mm	92.5mm	309202	56-1517
60ml	39.3mm	44.2mm	66mm	309502	56-1519
200ml	58mm	62mm	95mm	309903	56-1521

MQQ 6

Type	Order code	6+
30ml	56-1517	0.14
60ml	56-1519	0.162

MQQ 2

Type	Order code	2+
200ml	56-1521	0.545

Polypropylene Containers

Medline polypropylene containers with polyethylene lids, ideal for the collection of biological samples or the storage of small amounts of chemicals.



- Ideal for samples
- Polyethylene screw-on lids
- Non-sterile
- Supplied **singly**

Technical specification					
Capacity	Bottom diameter	Top diameter	Height	Medline type	Order code
60ml	38.8mm	44.2mm	66.1mm	409502	56-1523
125ml	56.3mm	62.1mm	74.3mm	409702	56-1525
200ml	56.5mm	62.2mm	115.5mm	409902	56-1527

MQQ 6

Type	Order code	6+
60ml	56-1523	0.162
150ml	56-1525	0.252

MQQ 4

Type	Order code	4+
200ml	56-1527	0.311



Round Narrow Mouth Bottles

A range of lightweight general-purpose polythene storage bottles.

- 5 litre bottle has carrying handle
- Supplied **singly**



Technical specification						
Nom Capacity	Actual Capacity	Height	Body	Neck	Material	Order Code
125	138	112	48	15	LD Polythene	14-2000
250	280	139	60	15	LD Polythene	14-2002
1000	1080	197	94	21	HD Polythene	14-2006
5000	5300	295	176	36	HD Polythene	14-2010

MQQ 4

Capacity	Order code	4+
125ml	14-2000	0.336

MQQ 3

Capacity	Order code	3+
250ml	14-2002	0.452

MQQ 2

Capacity	Order code	2+
1000ml	14-2006	0.639

MQQ 100

Capacity	Order code	100+
5000ml	14-2010	12.36

MQQ 9

Capacity	Order code	9+
Dispenser cap	14-2036	0.136



Round Wide Mouth Bottles

Wide mouthed bottles for general-purpose storage.

- Made from high density polythene



Technical specification						
Nom Capacity	Actual Capacity	Height	Body	Neck	Material	Order Code
100	123	91	47	35	HD Polythene	14-2012
250	254	114	59	40	HD Polythene	14-2014
500	518	147	74	40	HD Polythene	14-2018
1000	1100	195	93	49	HD Polythene	14-2018
2500	2800	218	140	70	HD Polythene	14-2020

MQQ 3

Type	Order code	3+
Rd wide mouth 100ml	14-2012	0.405
Rd wide mouth 250ml	14-2014	0.406

MQQ 2

Type	Order code	2+
Rd wide mouth 500ml	14-2016	0.567
Rd wide mouth 1000ml	14-2018	0.752

Price each

Type	Order code	1+
Rd wide mouth 2500ml	14-2020	2.26



Wide Mouth Bottles with Sealing Cap

Strong, light, general-purpose wide-mouth bottles with sealing caps.

- Made from HD polythene
- Supplied **singly**



Technical specification						
Nom capacity	Actual capacity	Height	Body	Neck	Material	Order code
300	344	113	70	48	HD Polythene	14-2038
700	775	169	86	48	HD Polythene	14-2008
1250	1348	213	102	48	HD Polythene	14-2040

MQQ 2

Capacity	Order code	2+
300ml	14-2038	0.652
700ml	14-2008	0.821

Price each

Capacity	Order code	1+
1250ml	14-2040	1.08



Wash Bottles

A high quality wash bottle with washing tube.

- Simply squeeze to provide jet of liquid
- Available in **250ml** and **500ml** capacities
- Supplied **singly**



Type	Order code	1+
Rd wash bottle 250ml	14-2022	1.48
Rd wash bottle 500ml	14-2024	1.93

Polypropylene Coplin Jar

Coplin Jar

A microwaveable Coplin jar that can hold ten 1 x 3 inch slides back-to-back.

- Interior is grooved to hold slides upright
- Domed, shallow threaded screw cap protects slides
- Corrosion free polypropylene construction
- Height: 115mm
- Max. width: 60mm



Type	Order code	1+
Coplin jar	52-1512	1.34

Containers

Polystyrene Containers

Medline polystyrene containers with polyethylene lids, ideal for the collection of biological samples or the storage of small amounts of chemicals.



- Ideal for samples
- Polystyrene containers
- Polyethylene screw-on lids
- Non-sterile
- Supplied **singly**

How do I ...

- Email baskets?
- Register Online?
- Find invoices?

www.rapidonline.com/schools-faq

Rapid

Wash Bottles

Translucent, unbreakable wash bottles with built-in delivery tubes.

- Graduations on outer surface
- Low density polyethylene (LDPE) construction
- Available in **125, 250 and 500ml** capacities



Type	Order code	1+
125ml	52-1462	1.34
250ml	52-1458	1.52
500ml	52-1460	1.88

122496

Storage Vials

Rapid

Polypropylene Storage Vials

Storage vials for biological material, human and animal cells, etc.

- Leak-proof built-in seal
- Corrosion free polypropylene construction
- Available in 2ml and 5ml capacities



MOQ 6		
Type	Order code	6+
2ml	52-1520	0.18

MOQ 4		
Type	Order code	4+
5ml	52-1522	0.259

122504

ACADEMY

Straight Bore Burettes with PTFE Stopcock

These straight bore burettes from Academy have a **PTFE key stopcock**.

- Made from borosilicate glass
- Class A
- Amber graduations
- Conforms to ISO 385
- Available in a choice of sizes

Technical specification

Capacity	Subdivision	Tolerance
10ml	0.05ml	±0.03ml
25ml	0.1ml	±0.05ml
50ml	0.1ml	±0.05ml
100ml	0.2ml	±0.1ml

Capacity	Order code	1+
10ml	52-2011	18.02
25ml	52-2013	11.71
50ml	52-2015	12.87
100ml	52-2027	28.50

568015

Rapid

Acrylic Burettes

Burettes with acrylic bodies and leakproof stopcocks fitted with self-lubricating PTFE plugs.

- Individually calibrated for maximum accuracy
- Acrylic body is unaffected by dilute acids and bases except hydrofluoric acid and ammonium hydroxide
- pH range 1 to 14
- Can be used up to 5% wt/wt of acids or 30% base
- Material: polymethyl methacrylate/TPX
- Available in **50 and 100ml** capacities

Technical specification

Capacity	50ml	100ml
External diameter	15mm	18mm
Internal diameter	13mm	14mm
Overall length	745mm	825mm

Type	Order code	1+
50ml	52-1454	6.51
100ml	52-1456	10.74

122489

Burettes



Burettes Glass Key Single Bore Class A White Graduation

These Class A burettes from LabGlass have a single straight bore and a glass key stopcock with white ceramic graduation.

- Accuracy as per DIN ISO 385, ASTM-E287 standard
- Available in a choice of sizes



Technical specification

Capacity	Sub-division
10ml	0.05ml
25ml	0.1ml
50ml	0.1ml
100ml	0.2ml

Capacity	Order code	1+
10ml	52-4058	7.19
25ml	52-4059	8.78
50ml	52-4060	9.49
100ml	52-4057	10.38

568053



Burettes with PTFE Rotaflow Stopcock Class B Blue Graduation

These burettes from LabGlass have a PTFE Rotaflow stopcock.

- Available in a range of sizes
- Class B
- Blue graduation
- Conforms to DIN ISO 385, ASTM-E287



Capacity	Order code	1+
10ml	52-4074	5.80
25ml	52-4075	5.81
50ml	52-4076	7.69
100ml	52-4073	8.64

568076



Burettes Glass Key Single Bore Class B Blue Graduation

Single bore burettes from LabGlass with a glass key stopcock.

- Available in a range of sizes
- Class B
- Blue graduation
- Conforms to DIN ISO 385, ASTM-E287



Capacity	Order code	1+
10ml	52-4062	3.49
25ml	52-4063	6.33
50ml	52-4064	7.96
100ml	52-4061	12.47

568075



Burettes Single Bore with Pinch Clip Class B

Single bore Class B burettes from LabGlass with a detachable rubber tube and pinch clip.

- Available in a choice of sizes



Technical specification

Capacity	Sub-division
10ml	0.05ml
25ml	0.1ml
50ml	0.1ml

Capacity	Order code	1+
10ml	52-4066	2.70
25ml	52-4067	4.00
50ml	52-4068	3.11

568075

Approved Framework Supplier





Burettes with Straight Bore PTFE Key Stopcock Class A

Class A burettes from LabGlass with a straight bore interchangeable PTFE key stopcock.

- Available in a choice of sizes
- White* graduations
- Accuracy as per DIN ISO 385, ASTM-E287 standard
- *Graduations may appear dark in the photograph to give contrast with the white background.



Technical specification	
Capacity	Sub-division
10ml	0.05ml
25ml	0.1ml
50ml	0.1ml
100ml	0.2ml

Capacity	Order code	1+
10ml	52-4082	4.39
25ml	52-4083	8.05
50ml	52-4084	8.87
100ml	52-4081	9.26



Burettes with Straight Bore PTFE Key Stopcock Class B

Class B burettes from LabGlass with a straight bore interchangeable PTFE key stopcock.

- Available in a choice of sizes
- Blue graduation
- Accuracy as per DIN ISO 385, ASTM-E287 standard



Technical specification	
Capacity	Sub-division
10ml	0.05ml
25ml	0.1ml
50ml	0.1ml
100ml	0.2ml

Capacity	Order code	1+
10ml	52-4086	4.92
25ml	52-4087	6.95
50ml	52-4088	7.71
100ml	52-4085	8.50



Schellbach Burettes Single Bore with Glass Stopcock Class B

Class B Schellbach glass burettes from LabGlass with a glass stopcock.

- Available in a choice of sizes
- Blue graduation
- Accuracy as per DIN ISO 385, ASTM-E287 standard



Technical specification	
Capacity	Sub-division
10ml	0.05ml
25ml	0.1ml
50ml	0.1ml
100ml	0.2ml

Capacity	Order code	1+
10ml	52-4078	4.61
25ml	52-4079	8.50
50ml	52-4080	8.72
100ml	52-4077	9.67



Modular Burette with PTFE Stopcock Class A

This Class A burette from LabGlass has a PTFE stopcock.

- Accuracy as per DIN ISO 385, ASTM-E287 standard
- Capacity 50ml
- Sub division 0.1ml
- Tolerance ± 0.05 ml
- Manufacturer's part CH0243C



Capacity	Order code	1+
50ml	52-4065	14.80



Straight Bore Burettes with Glass Stopcock

Straight bore burettes from Glasco with a glass stopcock.

- Made from borosilicate glass
- Conforms to DIN 12700, ISO 385
- Available in a choice of sizes



Technical specification			
Capacity	Subdivision	Tolerance	Length
10ml	0.05ml	± 0.02 ml	495mm
25ml	0.1ml	± 0.05 ml	530mm
50ml	0.1ml	± 0.05 ml	767mm
100ml	0.2ml	± 0.1 ml	785mm

Capacity	Order code	1+
10ml	52-2031	10.02
25ml	52-2033	10.02
50ml	52-2035	10.02
100ml	52-2037	20.41



Burettes with Detachable Stopcock

These burettes from Glasco have a detachable glass stopcock.

- Made from borosilicate glass
- Class B
- Amber graduations
- Conforms to DIN/ISO 385
- Available in a choice of sizes



Technical specification		
Capacity	Subdivision	Tolerance
10ml	0.05ml	± 0.05 ml
25ml	0.1ml	± 0.1 ml
50ml	0.1ml	± 0.1 ml

Capacity	Order code	1+
10ml	52-2039	28.49
25ml	52-2041	26.75
50ml	52-2043	13.87

For a quotation and special pricing for your school

Get in touch now

education@rapidonline.com

Pipettes



Pipettes AR Bulb Form One Mark Class A

One mark bulb form pipettes from Glasco, supplied in packs of 5.

- Made from alkaline resistant glass
- Class B
- Available in a choice of sizes

Technical specification				
Order code	Capacity	Colour coding	Tolerance	Length
52-2238	5ml	White	± 0.015 ml	360mm
52-2239	10ml	Red	± 0.02 ml	450mm
52-2240	20ml	Yellow	± 0.03 ml	515mm
52-2241	25ml	Blue	± 0.03 ml	520mm

Capacity	Order code	1+
5ml	52-2238	12.08
10ml	52-2239	12.08
20ml	52-2240	15.39
25ml	52-2241	15.39



Pipettes Bulb Form One Mark Class B

One mark bulb form pipettes from Glasco, supplied in packs of 5.

- Made from alkaline resistant glass
- Class B
- Available in a choice of sizes

Technical specification				
Order code	Capacity	Colour coding	Tolerance	Length
52-2045	5ml	White	± 0.015 ml	360mm
52-2047	20ml	Yellow	± 0.03 ml	515mm

Capacity	Order code	1+
5ml	52-2045	9.94
20ml	52-2047	8.70



Glass Bulb Form Pipettes Class A

Colour coded bulb form pipettes from LabGlass, made from borosilicate glass.

- Available in a range of sizes
- One graduation mark
- Class A
- Conforms to DIN ISO 648 standard

Technical specification			
Order code	Capacity	Tolerance	Colour code
52-4195	2ml	± 0.01 ml	Orange
52-4196	5ml	± 0.015 ml	White
52-4191	10ml	± 0.02 ml	Red
52-4192	15ml	± 0.025 ml	Green
52-4193	20ml	± 0.03 ml	Yellow
52-4194	25ml	± 0.03 ml	Blue

Capacity	Colour	Order code	1+
2ml	Orange	52-4195	1.72
5ml	White	52-4196	1.72
10ml	Red	52-4191	1.72
15ml	Green	52-4192	1.46
20ml	Yellow	52-4193	1.83
25ml	Blue	52-4194	1.83



Bulb Form Pipettes Class B

Colour coded bulb form pipettes from LabGlass, made from borosilicate glass.

- Available in a range of sizes
- One graduation mark
- Class A
- Conforms to DIN ISO 648 standard



Technical specification

Order code	Capacity	Tolerance	Colour code
52-4201	5ml	±0.03ml	White
52-4197	10ml	±0.04ml	Red
52-4198	15ml	±0.05ml	Green
52-4199	20ml	±0.06ml	Yellow
52-4100	25ml	±0.06ml	Blue

Capacity	Colour	Order code	1+
5ml	White	52-4201	0.60
10ml	Red	52-4197	1.21
15ml	Green	52-4198	0.69
20ml	Yellow	52-4199	1.21
25ml	Blue	52-4200	1.35



**Serological Pipettes Class B
Packs of 5**

Serological pipettes from LabGlass, designed so the last drop can be expelled by blowing.

- Available in a range of sizes
- Calibrated for delivery to jet
- Class B
- Colour coded
- Blue graduation
- Conforms to DIN ISO 835 standard
- Supplied in packs of 5

Technical specification

Order code	Capacity	Tolerance	Colour code
52-4202	1ml	±0.01ml	Yellow
52-4204	2ml	±0.01ml	Black
52-4206	5ml	±0.05ml	Red
52-4203	10ml	±0.05ml	Orange
52-4205	25ml	±0.2ml	White

Capacity	Colour	Order code	1+
1ml	Yellow	52-4202	9.37
2ml	Black	52-4204	8.71
5ml	Red	52-4206	9.37
10ml	Orange	52-4203	8.97
25ml	White	52-4205	9.74

Rapid

Dropping Pipettes

These dropping pipettes are useful for dispensing liquid from test tubes.

- Both pipettes have soft rubber teats
- Large pipette has a glass body of 125mm length
- Supplied in packs of 10



Type	Quantity	Order code	1+
Large pipette	10	52-1266	5.10

Pricing

Pricing correct at time of going to press.
For up-to-date pricing visit
www.rapidonline.com

Rapid

Plastic Pipettes Graduated to 3ml

A small plastic pipette, ideal for dispensing small amounts of liquid.

- Soft bulb is squeezed to suck up and dispense liquid
- Graduated up to 3ml



Type	Order code	16+
Pipette	06-6066	0.059



Graduated Disposable Pasteur-type Pipettes

Disposable, graduated Pasteur-type pipettes from Medline, made from transparent, inert, low-intensity polythene.

- Volumetric tolerance ± 10%
- Not sterile
- Supplied in packs of 500
- Medline types 200003 (1ml) and 200006 (3ml)

Technical specification

Nominal capacity	Length	Stem diameter	Total capacity	Bulb draw	Graduations
1ml	154mm	5mm	5ml	3.1ml	0.25ml
3ml	154mm	7.8mm	7ml	3.2ml	0.5ml

Type	Order code	1+
1ml (500)	06-7019	7.39
3ml (500)	06-7021	7.82



Pipette Pumps

A range of fast-release pipette pumps for precise and quick dispensing.



A knurled thumb wheel can be rotated to draw up or dispense liquids, or the release lever can be pushed in for quick emptying. The moulded chuck has a silicon rubber collet inside to hold various standard sized pipettes. The pump resists acids and alkalis and can be easily disassembled for thorough cleaning.

- Knurled thumb wheel
- Quick release lever
- Holds various standard sized pipettes
- Resistant to acids & alkalis
- Can be disassembled for cleaning
- Eisco CH0581 series

Capacity	Order code	1+
2ml	52-3426	4.05
10ml	52-3427	3.56
25ml	52-3428	3.96

Pipette Fillers

Rapid

Suction Pipette Filler

A suction type filler for measuring and volumetric pipettes.

- Rubber squeeze bulb with valves
- 50cc capacity
- Withstands acids and other hazardous chemicals
- Features 3 flow control valves, that are opened by squeezing



Colour supplied will vary.

Type	Order code	1+
Pipette filler	52-8058	3.77

Rapid

Rubber Bulbs for Pipettes



Rubber bulbs for filling pipettes.

- Ideal for filling pipettes, etc., especially with corrosive or harmful chemicals
- Pear-shaped bulbs available in 5, 15 and 50ml capacities
- Dropper teat available in large size

Type	Order code	3+
Bulb - 5ml	06-7018	0.428
Bulb - 15ml	06-7020	0.468

Type	Order code	1+
Bulb - 50ml	06-7022	1.53

Type	Order code	2+
Teat - large	06-7026	0.656

Petri Dishes & Racks

Rapid

Autoclavable Glass Petri Dishes

Clear glass petri dishes with lids. Can be autoclaved at a temperature of 120°C.



- Supplied in packs of 18

Type	Order code	1+
60 x 12mm	52-0240	12.22
100 x 15mm	52-0242	17.44



55mm 4-Vent Petri Dishes

These Aseptic 55mm Petri Dishes from Medline are made from polystyrene and have 4 vents. They are supplied in packs of 10 and are suitable for use with automatic filling machines.



- Diameter 55mm
- Height 14mm
- Supplied in packs of 10
- Medline type 200201

Type	Order code	1+
Petri Dishes (10)	52-0179	1.06

Order online

Save time, and place your order at:
www.rapidonline.com
24 hours a day

medline
SCIENTIFIC INSTRUMENTS

90mm Triple Vent Petri Dishes

These Aseptic Petri Dishes from Medline are made from polystyrene and have 3 vents. They are supplied in packs of 20 and are suitable for automatic filling machines.



- Diameter 90mm
- Height 14mm
- Side mark for orientation
- Writing area on bottom
- Supplied in packs of 20
- **Medline type 200200.5**

Type	Order code	1+
90mm triple (20)	52-0173	1.81

500404

Rapid

Petri Dishes

Clear, economical unbreakable petri dishes.



- Corrosion free polypropylene construction
- Autoclavable
- Available in 50, 125 and 150mm diameters

Type	Order code	4+
50mm	52-1528	0.248

MOQ 4

Type	Order code	1+
125mm	52-1530	1.11
150mm	52-1532	1.52

122506

medline
SCIENTIFIC INSTRUMENTS

90mm Triple Compartment Petri Dishes

Aseptic polystyrene Petri Dishes with 3 compartments and 3 vents from Medline. The dishes are supplied in packs of 20, packed in heat-sealed bags. They are suitable for use in automatic filling machines.



- 90mm diameter x 14mm high
- Aseptic polystyrene
- 3 compartments
- 3 vents
- Suitable for use in automatic filling machines
- Supplied in packs of 20 in heat-sealed bags
- **Medline type 200203**

Type	Order code	1+
90mm Petri dishes	52-0169	3.53

500334

eisco
TRUST & DELIVER TOGETHER

Clear Acrylic Petri Dish Racks

Clear acrylic racks with white polycarbonate posts for holding and transporting petri dishes.



The racks can be very useful during inoculation, incubation and storage as the excellent visibility from all sides enables the culture to be seen and checked during incubation.

- Available in sizes to suit 60mm and 90mm dishes
- **Eisco CH0376 series**

Dish size	Order code	1+
60mm	52-3578	17.08
90mm	52-3577	19.98

565634

Chromatography

GLASSCO

Chromatography Columns with Sintered Disc

Chromatography columns from Glassco with sintered disc.

- Made from borosilicate glass
- Porosity 0
- Available in a range of sizes

Technical specification

Order code	Diameter	Socket size	Length
52-1699	10mm	14/23	100mm
52-1701	10mm	14/23	200mm
52-1703	10mm	14/23	300mm
52-1705	10mm	14/23	400mm
52-1707	20mm	19/26	100mm
52-1709	20mm	19/26	200mm
52-1711	20mm	19/26	300mm
52-1713	20mm	19/26	400mm
52-1715	20mm	19/26	500mm
52-1717	26mm	24/29	300mm
52-1719	26mm	24/29	400mm
52-1721	26mm	24/29	500mm
52-1723	30mm	34/35	400mm
52-1725	30mm	34/35	500mm
52-1727	30mm	40/38	400mm
52-1729	30mm	40/38	500mm



Diameter	Length	Order code	1+
10mm	100mm	52-1699	36.02
10mm	200mm	52-1701	36.02
10mm	300mm	52-1703	36.04
10mm	400mm	52-1705	36.00
20mm	100mm	52-1707	37.81
20mm	200mm	52-1709	37.79
20mm	300mm	52-1711	37.79
20mm	400mm	52-1713	37.81
20mm	500mm	52-1715	37.81
26mm	300mm	52-1717	44.26
26mm	400mm	52-1719	46.87
26mm	500mm	52-1721	46.30
30mm	400mm	52-1723	48.67
30mm	500mm	52-1725	58.09
30mm	400mm	52-1727	58.57
30mm	500mm	52-1729	60.82

567994

Rapid

Chromatography Paper Rolls

This chromatography paper can be used to separate and analyse coloured chemicals and other substances.

- Ideal for use by schools and colleges
- Grade 1
- Supplied in rolls



Width	Length	Order code	1+
40mm	100m	52-1959	31.99
50mm	100m	52-1981	44.93

568006

Rapid

Chromatography Paper Packs of 100 Sheets

This chromatography paper can be used to separate and analyse coloured chemicals and other substances.

- Ideal for use by schools and colleges
- Grade 1
- Supplied in packs of 100 sheets



Size (W x L)	Order code	1+
100 x 300mm	52-1982	22.82
200 x 200mm	52-1983	24.37

568007

ACADEMY
General Products

Chromatography Glass Tank and Lid

Chromatography tank and lid from Academy for use in the appropriate laboratory work.



- Made from soda-lime glass
- Length 230mm
- Width 90mm
- Tank and lid available separately

Type	Order code	1+
Tank	52-1984	39.56
Lid	52-1985	8.45

568009

Filter Paper

ACADEMY
General Products

Professional Filters

These professional filter papers from Academy are suitable for a wide range of routine applications in the laboratory.

- Available in a range of sizes
- Supplied in packs of 100



Diameter	Order code	1+
55mm	52-1095	3.32
70mm	52-1097	3.72
90mm	52-1098	4.33
110mm	52-1099	5.47
125mm	52-1109	5.56
150mm	52-1185	5.66
185mm	52-1187	11.32

567969

eisco
TRUST & DELIVER TOGETHER

Premium Filter Paper Packs of 100

Qualitative filter paper for use in the chemistry laboratory.

- Range of diameters
- Supplied in packs of 100
- **Eisco CH0390 series**



Diameter	Order code	1+
90mm	52-3549	1.12
110mm	52-3550	1.32
125mm	52-3551	1.78
150mm	52-3552	2.91

565630

Quick Quote

Quick quote service available online
 Either click on a product and ask for a quick quote or visit
www.rapidonline.com/quotation
 for more details

Indicator Test Paper



Indicator Papers



Indicator papers available in a range of types and pack sizes.

- Supplied in convenient plastic dispensers
- Universal pack includes pH indicator scale
- **Pack of 200** contains 10 books of 20 strips 10mm wide
- **Pack of 100** contains 100 loose strips 10mm wide
- **5m pack** contains a single continuous strip 7mm wide

Price each			
Type	Order code	1+	
Blue litmus 200	52-8000	3.00	
Blue litmus 100	52-8002	1.25	
Blue litmus 5m	52-8004	2.16	
Red litmus 200	52-8006	2.93	

MOQ 10 - In Multiples of 10			
Type	Order code	10+	
Red litmus 100	52-8008	1.19	

Price each			
Type	Order code	1+	
Red litmus 5m	52-8010	2.16	
Ph 1-11 univ. 200	52-8012	3.25	
Ph 1-11 univ. 100	52-8014	1.65	
Ph 1-11 univ. 5m	52-8016	2.32	
Ph 1-14 univ. 200	52-8018	3.56	
Ph 1-14 univ. 100	52-8020	1.87	
Ph 1-14 univ. 5m	52-8022	2.32	

Rapid

Clinical Test Strips

These clinical test strips are suitable for use in testing for glucose or protein.

- Supplied in packs of 50



Type	Pack size	Order code	1+
Diastix	50	52-2611	9.04
Albustix	50	52-2612	11.64

Cotton Wool

Rapid

Absorbent Cotton Wool

This absorbent white cotton wool is suitable for use in the laboratory, classroom, first aid kit, workplace and the home.

- Hospital quality
- Supplied in packs of 500g



Pack size	Order code	1+
500g	52-2756	7.09

Tongs & Holders

Rapid

200mm Crucible Tongs

200mm crucible tongs available in economy and stainless steel models. These tongs are essential for the safe handling of hot crucibles.



- Length 200mm
- Economy or Stainless Steel models

Type	Order code	1+
Economy	52-0515	1.02
Stainless Steel	52-0517	2.01

Rapid

Bowed Laboratory Tongs

High quality polished mild steel crucible tongs.



- Length 200mm
- Bowed jaws
- Supplied in packs of 5

Type	Order code	1+
Bowed tongs	52-0158	5.91

Rapid

Economy Beaker Tongs with Plastic Jaws

Nickel-plated steel tongs with non-slip plastic-coated jaws, ideal for handling laboratory utensils like beakers, large crucibles, evaporating dishes and other round labware.



- Plastic covered jaws for good grip
- Jaws open to 115mm (4.5in.)
- Holds 50 to 2000ml beakers
- Length 240mm (9.5in.)

Type	Order code	1+
Tong (plastic jaws)	52-0461	2.02

Spatulas, Spoons & Scoops

eisco

Laboratory Spatulas, Spoons and Pick Scoops

A range of general purpose laboratory spatulas, spoons and scoops, ideal for use in the chemistry laboratory.

Type	Length	Order code	1+
Spatula / spoon	150mm	52-3429	0.478
Spatula / spoon	200mm	52-3372	3.39
Chattaway	150mm	52-3528	0.55
Chattaway	200mm	52-3529	0.61
Pick scoop	160mm	52-3570	3.33
Polypropylene	150mm	52-3583	0.24
Polypropylene	200mm	52-3584	0.337



Rapid

Spatulas with Spoons

Stainless steel laboratory spatulas with a spoon bowl at one end and a rectangular flat at the other.



- Available in 120 and 150mm lengths

MOQ 2			
Type	Order code	2+	
120mm	52-1275	0.777	

eisco

Deflagrating Spoon and Cap

A deflagrating spoon consisting of a steel cup and rod held by a cork in the aluminium cap.

- Steel cup and rod
- Aluminium cap
- Length 350mm
- Diameter of cap 90mm
- Diameter of cup 18mm
- Eisco type CH0520



Type	Order code	1+
Deflagrating spoon	52-3418	1.06

Rapid

Nuffield Spatulas

These Laboratory spatulas, made of high quality mild polished steel offer good value for money.

- Length 140mm
- Supplied in packs of 5



Type	Order code	1+
Nuffield spatula	52-0164	2.13

Rapid

Chattaway Stainless Steel Spatulas

Double-ended stainless steel spatulas, ideal for loading small amounts of powdered or granular chemicals into test tubes, flasks, etc. One end is flat with a square end, the other end is rounded with an angled tip.

- Stainless steel
- Available in 100, 130 and 150 lengths



MOQ 2			
Type	Order code	2+	
100mm	52-9033	0.844	

Price each			
Type	Order code	1+	
130mm	52-9031	1.00	
150mm	52-9035	0.50	

Rapid education **We bring STEAM to life**

Stirring Rods

eisco
Trust & Deliver Excellence

Laboratory Stirring Rods

A range of general-purpose stirring rods, ideal for many jobs in the chemistry laboratory.

Technical specification

Order code	Type	Length	Diameter	Material
52-3580	Policeman rod	245mm	6mm	Polypropylene
52-3581	Glass stirring rod	200mm	7mm	Glass
52-3582	Button end glass rod	300mm	7mm	Glass

Type	Order code	1+
Policeman rod	52-3580	0.39
Glass stirring rod	52-3581	1.58
Button end glass rod	52-3582	2.15

565636

SIMAX® Glass Stirring Rods



6mm diameter glass stirring rods.

- Simax Borosilicate glass
- Supplied in packs of 10

Type	Order code	1+
125mm	52-1006	5.14
150mm	52-1008	6.08
200mm	52-1010	6.07
300mm	52-1012	6.18

013141

Tweezers

Rapid

Plastic Tweezers

Economical, plastic tweezers, ideal for science and as an assembly aid for small components.

- Serrated tips
- Locating lugs hold tips straight when closed
- Made from recyclable ABS plastic
- Length approx. 110mm

Type	Order code	1+
Plastic tweezers	06-6064	0.202

080612

STEAM hub

Visit our STEAM hub for project ideas

www.rapidonline.com

Need a product urgently?

We can offer a next day, before noon, delivery service

01206 751166

Burners & Stands

eisco
Trust & Deliver Excellence

Melting Point Apparatus

This melting point apparatus from Eisco has been designed with safety in mind. A single control knob on the front panel incorporates the mains On/Off switch and a rapid heat switch allows higher temperatures to be obtained quickly. Sample tubes are illuminated from behind and magnified through a lens.

- Selector at rear of the instrument allows a light or dark background
- Ceramic insulation around aluminium heating block minimises heat transfer to the casing
- Rating 230V, 50 to 60Hz
- Manufacturer's part CH0801

Type	Order code	1+
Melting point apparatus	52-4189	188.59

568095

eisco
Trust & Deliver Excellence

Tall Triangular Tripod 120 x 210mm

A laboratory tripod with a triangular zinc-plated, cast-iron top and mild steel legs.

- Zinc-plated cast-iron top
- Mild steel legs
- Length of side 120mm
- Height 210mm
- Eisco type CH0645A

Type	Order code	1+
Triangular tripod	52-3387	3.13

565561

eisco
Trust & Deliver Excellence

Pipe Clay Triangles

A range of pipe clay triangles for supporting laboratory items being heated by a Bunsen burner or other heat source.

The triangles are made of wires strung in an equilateral triangle with three hollow ceramic tubes threaded onto it. The triangle is usually supported on a tripod or iron ring and, in turn, supports a crucible, etc., allowing it to be directly heated by the flame.

- Pipe clay triangles
- Available in a range of sizes

Type	Order code	1+
50mm	52-3380	0.272
60mm	52-3537	0.306
75mm	52-3538	0.434

565555

eisco
Trust & Deliver Excellence

Eisco Wire Gauze Squares

A range of iron wire gauze squares available with or without a ceramic centre, ideal for supporting flasks, etc, while being heated on a tripod stand.

- Wire gauze with or without ceramic centre
- High quality, extra strong



Size	Ceramic centre	Order code	1+
Packs of 10			
125 x 125mm	Yes	52-3327	3.98
150 x 150mm	Yes	52-3328	4.14
125 x 125mm	No	52-3567	2.89
150 x 150mm	No	52-3568	4.37

565518

eisco
Trust & Deliver Excellence

Laboratory Alcohol/Spirit Lamps

Spirit/alcohol burning lamps ideal for smaller heating tasks in the laboratory.

- Glass or stainless steel construction
- Supplied complete with cap



Construction	Capacity	Order code	1+
Glass	120ml	52-3518	2.22

565626

eisco
Trust & Deliver Excellence

Tripod Stand and Stainless Steel Alcohol Burner

A laboratory alcohol burner and a suitable tripod stand.

- Lamp is made from stainless steel and has a fuel capacity of 80ml
- Stand is 110mm high with an inner top diameter of 95mm
- Sold separately



Type	Order code	1+
Alcohol burner	52-3325	4.42
Tripod	52-3326	1.83

565520

eisco
Trust & Deliver Excellence

13mm Laboratory Bunsen Burners

A range of Bunsen burners consisting of a nickel-plated burner tube mounted on a die-cast base.

- Rotating air regulator
- Base diameter 80mm
- Tube diameter 13mm
- Height 142mm
- Weight 280g
- Eisco CH0088 series

See order code 52-3590 for suitable rubber tubing.

Fuel	Order code	1+
Natural gas	52-3365	4.95
LPG	52-3366	5.45

565547

Rapid

Bunsen Burners - Natural Gas

A Laboratory Bunsen Burner for use with natural gas. The burner has a nickel-plated burner tube with a rotatable air regulator and an enamelled cast base for good stability.



- Barrel diameter 11mm
- Height: 125mm
- Base diameter 80mm
- 11mm nickel-plated burner tube
- Rotatable air regulator
- Enamelled cast base
- Cylindrical rifflid connector
- 8mm gas inlet

Technical specification

Type	Jet size
Natural gas 11mm	0.65mm

Type	Order code	1+
11mm Natural Gas	52-0153	3.95

501048

Rapid

Heat-Resistant Asbestos-Free Bunsen Burner Mats

Asbestos-free, heat-resistant bench mats, ideal for use under bunsen burners. The mats are manufactured from calcium silicate and are in the form of rigid sheets.



- Size 300 x 300mm
- Thickness approx. 3.5mm
- Available singly and in packs of 10

Type	Order code	1+
Single	52-0127	1.81
Pack of 10	52-0125	16.25

081315

eisco

Calcium Silicate Bench Mats

Laboratory bench mats from Eisco, ideal for use underneath a bunsen burner.



- Made from calcium silicate
- Finished edges
- Size 230 x 230mm
- Manufacturer's part CH0101E

Size	Order code	1+
230 x 230mm	52-4056	1.81

563084

Full range available online

www.rapidonline.com/education

Retort Stands & Clamps

eisco

Laboratory Jacks



These **scissor jacks** from Eisco provide strong and stable support for a range of **laboratory equipment**.

The jacks are available in two platform sizes: 150 x 135mm or 150 x 150mm.

- Available in two platform sizes
- Screw-operated scissor action mechanism
- Suitable for use in both the physics and chemistry laboratory
- Anodised aluminium platforms
- Large control knob
- Smooth scissor action operation
- Finished in blue

Platform size	Order code	1+
150 x 135mm	52-4188	24.64
150 x 150mm	52-3324	34.68

568094

eisco

Retort Stand Clamps and Bossheads

A range of retort stand clamps including boss-head clamps and tube clamps with rubber or cork lined jaws.



- Clamps for use with retort stands

Type	Jaw covering	Order code	1+
Clamp+bosshead	Cork	52-3313	3.78
Clamp+bosshead	PVC	52-3314	5.51
Clamp+bosshead	PVC	52-3305	3.78
Clamp only	PVC	52-3367	2.18
Bossheds pack of 5		52-3368	9.34
Bossheds - single		52-3391	5.47

565515

Rapid

Retort Stand Clamp 4 Prong

This universal retort stand clamp is made from aluminium and has 4 jaws.



- The jaws allow objects from 2 - 90mm in diameter to be clamped securely
- The design of the jaws ensures a firm grip at all angles of opening
- The four interlocking jaws are cork lined
- Overall length is 24cm

Type	Order code	1+
Retort stand clamp	52-0518	4.48

072276

Rapid

3-Prong Clamps

A range of 3-prong clamps with rods that can be attached to a retort stand by means of a boss-head clamp.



- Retort stands and boss-head clamps available separately

Type	Order code	1+
Zinc alloy	06-2126	7.44
Aluminium casting	06-2127	5.95
Die-cast aluminium	06-2128	5.95

534071

Rapid

Burette Clamps

These burette clamps attach to retort stands and have rounded steel jaws that open from 10 to 35mm diameter.



- Jaws can be rotated through 360° and locked in any position
- Fits support rods up to 15mm diameter
- Available with or without plastic coated jaws

Type	Order code	1+
Metal jaws	06-2129	5.04
Plastic coated jaws	06-2130	5.72

534072

eisco

Retort Stand Rings

A range of supporting rings for use with retort stands.



The 50 and 75mm rings have built-in boss-head clamps, whereas the 150mm ring uses a separate boss-head clamp (not included) that allows the distance of the ring from the stand rod to be varied.

- 50 and 75mm rings have built-in boss-head clamps
- 150mm ring uses a separate boss-head clamp
- Eisco CH0672 & CH0668 series

Diameter	Boss-head	Order code	1+
50mm	Yes	52-3462	2.11
75mm	Yes	52-3463	2.25
150mm	No	52-3371	2.05

565500

Rapid

Vertical Burette Rack

A polished hardwood rack for storing burettes vertically.



- Upper tier has recesses to locate burettes
- Can take up to 12 burettes
- Size (H x W x D): 455 x 400 x 77mm
- Wall mountable

Type	Order code	1+
Burette rack	06-6914	16.57

079609



Funnel Stands

Polished wooden funnel stands with clamping screws.

- Rod is approx. 460mm tall x 16mm diameter
- Eisco CH0689 series



Funnels not included.

Type	Order code	1+
Single	52-3600	7.55
Double	52-3601	8.15

565642



Funnel and Burette Stand

A polished wooden funnel and burette stand with clamping screws for adjusting the height and securing the burette.

- Rod approx. 460mm tall x 16mm diameter
- Base size 290 x 110mm
- Eisco type CH0690



Funnel and burette not included.

Type	Order code	1+
Funnel+burette stand	52-3599	10.92

565641



Wooden Burette Stands

Stands, designed to support up to two burettes.

The stands are made from polished seasoned hardwood, and have a separate clamping screw for each burette.

- For one or two burettes
- Polished, seasoned hardwood
- Individual clamping screws
- Rod is approx. 460 x 16mm
- Eisco CH0264 series



Burettes not included.

Type	Order code	1+
Single	52-3430	7.69
Double	52-3598	11.56

565681



Wooden Test Tube Racks



Wooden test tube stands with 22mm diameter holes.

- Width 65mm
- Height 115mm
- Eisco CH0704 series

Test tubes not included.

Number of holes	Order code	1+
6	52-3449	4.14
12	52-3448	6.36

565695

Calorimeters



Aluminium and Copper Calorimeters

A range of calorimeters with parallel sides and a rolled rim.

- Available in aluminium or copper
- Eisco PH0438 & PH0440 series



Stirrer not included.

Metal	Size	Order code	1+
Aluminium	75 x 50mm	52-3645	1.17
Aluminium	100 x 75mm	52-3644	1.53
Copper	75 x 50mm	52-3647	2.33
Copper	100 x 75mm	52-3646	3.79

565655



Eisco Metal Block Calorimeters

A range of metal block calorimeters that can be used for the experimental determination of the specific heat capacity of various metals.

Each cylindrical block has a mass of 1kg adjusted to an accuracy of 2%. The blocks are drilled with two holes: a larger 12.5mm central hole for a special immersion heater and a smaller hole 7.5mm diameter for a thermometer or temperature sensor.

- Eisco PH0435 series



Material	Order code	1+
Aluminium	52-3651	11.48
Brass	52-3652	16.34
Copper	52-3653	20.99
Steel	52-3654	7.35

565656



Joule's Calorimeter

A Joule's Calorimeter for experimenting with the conversion of electrical energy into heat energy. The calorimeter consists of a nickel-plated copper outer vessel with a lagged copper inner vessel. The cover has terminals for the 3 to 6V heating coil, a built-in stirrer and a hole for a thermometer to record the temperature changes.



- Apparatus for experimenting with the conversion of electrical energy into heat energy
- Nickel-plated copper outer vessel
- Copper inner vessel
- Felted wool cloth lagging
- Outer vessel is 100mm tall and 75mm in diameter
- Inner vessel is 75mm tall and 50mm in diameter
- 3 to 6V heating coil, Max. current 1A
- Built-in stirrer
- Hole for a thermometer (not included)

Type	Order code	1+
Joule's Calorimeter	52-9535	9.39

501638

Measuring



Ticker Tape Timer

This **ticker tape timer** from Eisco is housed in a tough moulded plastic case. The timer operates on 12V AC supply and produces 50/60 dots per second, depending on the mains supply frequency. The case has a tape guide and a carbon disc plug which can be moved to maximise the use of the discs.



- Supplied with one 50m paper tape roll and a box of 100 carbon discs
- Manufacturer's part PH0353A

Type	Order code	1+
Ticker tape timer	52-4213	20.99

568100



Leicester Height Measure

An accurate portable free standing height measure, complete with case.

- Quickly assembled
- Measuring range 210cm dual reading both metric and imperial
- Graduation 1mm and 1/8in
- Fun and easy to use



Type	Order code	1+
Leicester height measure	52-0579	60.75

073930



We bring STEAM to life



Clinometer Mk1

A traditional lightweight angle-measuring instrument to calculate heights.

- Complete with product guide
- Wheel size: 130mm diameter



Type	Order code	1+
Clinometer Mk1	52-9856	9.24

061638



Clinometer Mk2

A compact Clinometer with no external moving parts and a combined sighting angle-reading eyepiece

- A window on the side allows a second person to check a reading
- All angles in degrees followed by a plus or minus to indicate an upward or downward slope
- Complete with product guide
- Size: 140mm diameter



Type	Order code	1+
Clinometer Mk2	52-9858	12.24

061639



Measure intermediate distances with this robust and durable Trundle wheel.

- Clicker can be adjusted to one of three positions: off, click every 10cm or click every metre
- Splits into two parts for easy storage
- Length 83cm
- Supplied with carry bag and product guide
- Ideal primary school resource
- Suitable for **Key Stages 1 & 2** (ages 5 to 11)



Type	Order code	1+
Trundle wheel	52-0656	8.45

070780



Trundle Wheel Counter

This robust counter extends the number of activities that can be performed by the Trundle Wheel, 52-0656.

- Accurately counts metres up to 9999
- Can also be set to register every 10cm giving a maximum of 999.9 metres
- Fits in place of the standard clicker



Trundle wheel not included.

Type	Order code	1+
Trundle wheel counter	52-9848	10.16

061634



Metric Calliper



Measures most shapes from 1mm to 30cm by simply reading measurements through a single viewing window.

- Designed for calculating areas and volumes
- Able to measure depth, width and diameter
- Size: 420 x 195mm

Type	Order code	1+
Metric calliper	52-9854	5.00

061637

Health & Safety



Clear Vented Safety Glasses

These safety glasses can be worn alone, or are perfect for fitting over most prescription spectacles.



- Vented to prevent fogging
- UV protected
- Lightweight polycarbonate
- Impact resistant lens
- CE marked
- Conform to ANSI Z87.1 2010 side-shield protection
- Eisco type **CH0619A**

Type	Order code	1+
Safety glasses	52-3596	1.60

56569



Stealth 7000 Safety Spectacles



Sports style safety spectacles offering excellent protection combined with a modern design.

- Ultra lightweight
- Contour design fits well onto smaller faces, suitable for children
- Clear polycarbonate frame and scratch-resistant lens
- Conforms to **EN166.1.F**
- Available in clear and smoke versions

Type	Order code	1+	5+	10+
Stealth 7000 clear	87-3114	4.21	4.04	3.56
Stealth 7000 smoke	87-3122	4.21	4.04	3.63

066179



Martcare Indirectly Ventilated Safety Goggles

These Martcare indirectly-ventilated goggles from JSP are ideally suited for general-purpose eye protection due to their economical pricing and simplicity of use. The indirect ventilation system of the JSP Martcare goggles means that dust or liquid cannot directly fall into the goggles and gives additional protection over goggles which simply have perforated frames to allow air flow.



- Clear PVC lens
- Comfortable soft body
- Adjustable elasticated head-strap
- Conforms to **EN 166- 1.B.3.4**

Type	Order code	1+
Martcare goggles	87-3104	1.79

061349



Stealth 7000 Safety Specs Class Pack 20 + Gratnell Tray

A classpack of 20 Junior Stealth Safety Spectacles in a deep Gratnell's Tray with lid.



See order code **87-3114** for full details of the JSP Stealth 7000 Safety Spectacles.

- Perfect storage solution for safety spectacles

Type	Order code	1+
Safety Specs Pack 20	87-3113	70.30

525065



Martcare Indirect Vent Safety Goggles Class Pack of 20

A classpack of 20 JSP Indirect Vent Martcare Goggles in a deep Gratnell's Tray with lid.



See order code **87-3104** for full details of the JSP Martcare goggles.

- Perfect storage solution for laboratory goggles

Type	Order code	1+
Goggles Classpack 20	87-3103	34.23

525067



Stealth 7000 Safety Specs Junior Class Pack 20 + Gratnell Tray

A classpack of 20 Junior Stealth Safety Spectacles in a deep Gratnell's Tray with lid.



See order code **87-0914** for full details of the JSP Junior Stealth Safety Spectacles.

- Perfect storage solution for safety spectacles

Type	Order code	1+
Junior Specs Pack 20	87-0913	70.31

525066



Junior Laboratory Spectacles

High quality lightweight junior spectacles with smaller frame, ideal for children and people with small facial features.

- Scratch resistant lens
- Can be worn over most glasses
- Conforms to **EN166**



Type	Order code	1+	10+
Junior spectacles	87-0914	3.39	3.19

072695



Economy Junior Goggles

Economy junior goggles especially designed for younger people and people with small facial features.

- General purpose protection against splashes, dust, fumes etc
- Frame made from soft PVC for a comfortable fit and adjustment to individual's faces
- Conforms to **EN166**



Type	Order code	1+	10+
Economy junior goggles	87-1016	1.93	1.74

061742

BLUE DOT™

Blue Dot Emergency Eye Wash

Sterile sodium chloride 0.9% w/v sterile water for ocular and topical irrigation and wound cleansing.

- Available in **packs of 25 single-use 20ml pods** and in **500ml bottles**



Type	Order code	1+
Pack of 25x 20ml	87-4221	6.98
500ml bottle	87-4225	1.59

300550



Polycotton Lab Coats

Poly/cotton-mix lab coats for safety and protection of clothing.

- 1x breast pocket
- 2x side pocket
- Material: 65% polyester, 35% cotton
- Available in white or navy blue



Chest size	Colour	Order code	1+
86cm (34in)	White	52-1194	14.73
86cm (34in)	Navy blue	52-1195	15.36
106cm (42in)	White	52-1196	14.73
106cm (42in)	Navy blue	52-1197	17.51
122cm (48in)	White	52-1198	15.78
122cm (48in)	Navy blue	52-1199	17.51

081774



Ladies Warehouse/Laboratory White Coats

Ladies Poly Cotton Coats made from hard wearing but comfortable 245g poly/cotton fabric.

- Concealed stud front fastening
- 3 patch pockets
- Colour: white



Type	Order code	1+
92 to 124cm	52-1117	15.23
128 to 148cm	52-1119	16.00

530477



Black Rubber Bib Aprons

Basic black rubber aprons, perfect for the chemistry laboratory.

The aprons are comfortable and flexible, waterproof and resistant to most chemicals likely to be used by students.

- Available in medium or large sizes
- Medium: width 685mm (27in.), length 915mm (36in.)
- Large: width 685mm (27in.), length 1065mm (42in.)
- **EISCO RBAP series**



Size	Order code	1+
Medium	52-3595	5.27
Large	52-3594	6.43

565638



Edition Latex Powder-free Gloves

White powder-free latex gloves providing higher protection than vinyl, and maintaining integrity under prolonged use. Ideal for protecting the hands against degreasing and cleansing solvents, ferric chloride etchant, caustic soda based products and most other chemicals associated with the electronics industry.



- Powder-free
- Non-sterile
- Beaded cuff
- High tensile strength
- May be used for either left or right hand
- Recommended for use with blood, blood stained fluids and harsh chemicals
- Supplied in **dispenser boxes of 100**

These gloves will not provide 100% protection under all working conditions and the user should establish suitability prior to use.

Size	Box quantity	Order code	1+
Medium	100	87-0949	9.99
Large	100	87-0951	9.99

MQQ 10

Size	Box quantity	Order code	10+
Extra large	90	87-0954	9.99

300538



Blue Detectable Plasters

Bright blue sterile catering plasters.

- Blue colour stands out if accidentally lost in foodstuffs
- Occlusive material provides integral barrier to bacteria
- Metal detectable for food production facilities
- Supplied in an **assorted pack of 100**



Type	Order code	1+
Blue plasters	87-4195	3.98

300544

Fume Extraction



Spare/Replacement Filters



A range of spare / replacement filters for use with BenchVent extraction and filtration systems.

- Please see Technical Specification for Model/Filter cross-reference chart

Extractor Model	10µ PST Pads	Standard 5 micron	HEPA to 0.3µ	Low Level Charcoal	Standard Activated Carbon	Low Level Fume	Spray Tanning
BV300S	PRE495	IFA3	HE495	CHA3	-	FKA3	-
BV200S	PRE705	IFA2	HE705	CHA2	-	FKA2	-
BV200H	PRE495	IFA3	HE495	CHA3	-	FKA3	-
BV100H	PRE705	IFA2	HE705	CHA2	-	FKA2	-
BV200H-D	-	IFA3	-	-	-	-	-
BV100H-D	-	IFA2	-	-	-	-	-
BV300S-D	-	IFA3	-	-	-	-	-
BV500S-D	-	IFA3	-	-	-	-	-
BV500S-C	PRE495	IFA3	HE495	-	AC200	-	-
BV570H-H	PRE405	-	HE495	-	-	-	-
BV570H-C	PRE405	-	-	-	AC200	-	-
BV700S-C	PRE705	IFA2	HE705	-	AC100	-	-
BV660H-C	PRE495	IFA3	HE495	-	AC200	-	-
BV930H-C	PRE705	IFA2	HE705	-	AC100	-	-
BV660H-D	-	IFA3	-	-	-	-	-
BV930H-D	-	IFA2	-	-	-	-	-
BV500	-	IFA3	-	-	-	-	IFA3PT

Price each

Size (mm)	Type	Order code	1+
495 x 372 x 23	IFA3	87-5535	79.48
705 x 502 x 47	IFA2	87-5537	93.60
495 x 372 x 12	CHA3	87-5538	17.14
705 x 502 x 12	CHA2	87-5540	33.43
495 x 372 x 23	FKA3	87-5541	51.00
705 x 502 x 47	FAA2	87-5542	72.86
495 x 372 x 23	IFA3	87-5544	39.43
705 x 502 x 47	IFA2	87-5545	54.00

MQQ 6 - In Multiples of 6

Size (mm)	Type	Order code	6+
495 x 372 x 23	PRE495	87-5546	3.43

Price each

Size (mm)	Type	Order code	1+
705 x 502	PRE705	87-5547	6.86
405 x 320 x 47	HE405	87-5550	78.00
495 x 372 x 23	HE495	87-5551	87.00
705 x 502 x 47	HE705	87-5552	136.29
405 x 320 x 73	HE/CA/405	87-5553	170.57
405 x 320 x 50	AC200	87-5554	99.58
585 x 450 x 50	AC100	87-5555	145.25

519008

Order online

Save time, and place your order at:
www.rapidonline.com
 24 hours a day

BenchVent

The Bench Ventilation Company

BenchVent bench top units help protect pupils and staff from the fumes associated with GCSE, A Level, and higher education classroom experiments.

BenchVent is one of the first British companies to design and manufacture products specifically addressing the fume extraction requirements of school science laboratories.

Built in the UK, BenchVent offers an industry-leading lifetime guarantee for complete peace of mind. All units conform to the guidance of the Health and Safety Executive CoSHH regulations.



Order Code	Model	Description	Air Volume cap	Size	1+
87-5500	BV300S	Glue Spray Air Filtration Unit	325m ³ /hr	A3	£286.48
87-5501	BV200S	Glue Spray Air Filtration Unit	325m ³ /hr	A2	£348.71
87-5504	BV300S-D	Air Extraction Unit	355m ³ /hr	A3	£234.36
87-5502	BV200H	Air Filtration Hoods & Spray Booth	325m ³ /hr	A2	£625.12
87-5503	BV100H	Air Filtration Hoods & Spray Booth	650m ³ /hr	A1	£799.20
87-5505	BV200H-D	Air Extraction Spray Booth	355m ³ /hr	A2	£626.06
87-5506	BV100H-D	Air Extraction Spray Booth	710m ³ /hr	A2	£956.81
87-5521	BV550S-D	Fume and Vapour Extraction Unit	355m ³ /hr	510x360mm	£620.47
87-5517	BV570H-C	Small Desktop Fume Cabinet	202m ³ /hr	570x465mm	£746.25
87-5513	BV500S-C	Desk/Bench Top Fume Cabinet	325m ³ /hr	575x385mm	£978.08
87-5514	BV700S-C	Desk/Bench Top Fume Cabinet	650m ³ /hr	515x785mm	£1447.50
87-5519	BV660H-D	Fume Extraction Hood & Cabinet	355m ³ /hr	680x600mm	£791.25
87-5520	BV930H-D	Fume Extraction Hood & Cabinet	710m ³ /hr	960x740mm	£1211.25
87-5515	BV660H-C	Fume Filtration Hood & Cabinet	355m ³ /hr	A2	£1056.75
87-5516	BV930H-C	Fume Filtration Hood & Cabinet	710m ³ /hr	A2	£1680.00



Spare & replacement filters available

For full details and technical specifications visit www.rapidonline.com

Hot Stirrer

medline

MS-300 Hot Plate Stirrers

The Medline MS-300 Hot Plate Stirrer offers a large heating area of 180 x 180mm and is ideal for use with flat-bottomed vessels. With safe, controlled heating up to 400°C, the Medline MS300 provides a safer, more accurate heat source than the conventional Bunsen burner arrangement. The speed of the built-in magnetic stirrer of the Medline MS-300 Hot Plate Stirrer can be controlled between 100 and 1500rpm.

Also available are two sizes of octahedral stirring bars 15 x 8mm or 25 x 8mm. Both types feature pivot rings.

- Heating area 180 x 180mm
- Temperature up to 400°C
- Stirrer speed 100 to 1500rpm
- Operating voltage 220V AC
- **Medline type MS-300**

Type	Order code	1+
Hot plate stirrer	52-0449	174.71
16mm Stirring bar	52-1029	2.90
25mm Stirring bar	52-1031	3.40



Rapid

Wadding

Wadding for stuffing puppets, quilting and many other textiles projects.

- Size 1m x 1m
- Weight 135g (4oz.) per metre



Type	Order code	1+
Wadding	06-0439	2.88

Heating Mantles

medline

E Series Temperature Controlled Heating Mantles



Medline E Series Temperature Controlled Heating Mantles have Nichrome wire heating elements and woven glass fibre mat mantles. An important addition to any science

laboratory, the Medline E Series mantles benefit from rugged steel construction and can heat up to 450°C.

- Nichrome wire heating element
- Mantle made from woven glass fibre mat
- Steel case construction with chemical-resistant coating
- Moulded silica powder thermal insulation
- Temperature range up to 450°C (Max.)
- Power Supply: 220V AC

Technical specification


Model No.	Capacity	Watts
E1005	50ml	60 W
E101	100ml	
E102	250ml	150 W
E103	500ml	260 W
E104	1000ml	350 W

Type	Order code	1+
50ml	52-0451	96.60
100ml	52-0835	99.37
250ml	52-0453	119.90
500ml	52-0455	154.95
1 litre	52-0457	149.95

Can't find what you need?

Get in touch

education@rapidonline.com



DFRobot Romeo Arduino Robot Control Boards

The Romeo family is an All-in-One Arduino-based control board especially designed for robotics applications from DFRobot. It benefits from the Arduino open source platform, it is supported by thousands of open source codes, and can easily be expanded with your Arduino shields. The integrated 2-way DC motor driver and wireless socket allows you to start your own robot project immediately without the need for an additional motor driver. Romeo is also designed to have extra power for servos which need more current.

Romeo is also featured with DFRobot's standard 3 pin-out design and is compatible with Gravity series sensors and actuators. Hundreds of sensors are now plug-play with Romeo. You may also check the Bluetooth microcontroller selection guide to get more information.

Order code	Description	1+
75-0171	Romeo V1+motor driver	£22.95
75-0167	Romeo V2+motor driver	£22.94
75-0169	Romeo BLE	£28.03
75-0168	Romeo BLE mini	£14.36



DFROBOT[®]
DRIVE THE FUTURE