


section 1: **IRWIN**



IRWIN®

Industrial Tools

Trusted by professionals



section 1: **IRWIN**

WISE-GRIP	2
QUICK GRIP	5
GROOVELOCK	6
PROSNIP	7
GILBOW	7
DRILL BITS	8
BOLT GRIP	9
SAWS & BLADES	10
KNIVES & BLADES	10
RECORD	11
KNEE PADS	14
TOOLBOXES	14
STRAITLINE	15

WISE GRIP

WISE-GRIP STRAIGHT JAW LOCKING PLIERS



- Straight jaws provide maximum contact on flat, square, or hex work
- Ideal for tightening, clamping, twisting and turning. Turn screw to adjust pressure and fit work. Stays adjusted for repetitive use
- High-grade heat-treated alloy steel for maximum toughness and durability
- Guarded release trigger quickly unlocks and protects from accidental release
- Hardened teeth are designed to grip from any angle

ITEM NO	TYPE	CAPACITY	LENGTH
0021000	7R	29 mm	175 mm
0011022	10R	41 mm	250 mm

WISE-GRIP CURVED JAW LOCKING PLIERS WITH WIRE CUTTER



- Curved jaw puts tremendous pressure on four points of any style nut or bolt head
- Includes convenient wire cutter
- Ideal for tightening, clamping, twisting and turning. Turn screw to adjust pressure and fit work. Stays adjusted for repetitive use
- High-grade heat-treated alloy steel for maximum toughness and durability
- Guarded release trigger quickly unlocks and protects from accidental release
- Hardened teeth are designed to grip from any angle

ITEM NO	TYPE	CAPACITY	LENGTH
0021020	4WR	24 mm	100 mm
0021022	5WR	29 mm	125 mm
0021024	7WR	41 mm	175 mm
0021026	10WR	48 mm	250 mm

WISE-GRIP CURVED JAW LOCKING PLIERS



- Curved jaw puts tremendous pressure on four points of any style nut or bolt head
- Ideal for tightening, clamping, twisting and turning. Turn screw to adjust pressure and fit work. Stays adjusted for repetitive use
- High-grade heat-treated alloy steel for maximum toughness and durability
- Guarded release trigger quickly unlocks and protects from accidental release.
- Hardened teeth are designed to grip from any angle

ITEM NO	TYPE	CAPACITY	LENGTH
0021030	7CR	41 mm	175 mm
0021032	10CR	48 mm	250 mm

WISE-GRIP LONG NOSE PLIERS WITH WIRE CUTTER



- Ideal for precision work and hobbies
- Includes a convenient wire cutter
- Ideal for tightening, clamping, twisting and turning. Turn screw to adjust pressure and fit work. Stays adjusted for repetitive use
- High-grade heat-treated alloy steel for maximum toughness and durability
- Guarded release trigger quickly unlocks and protects from accidental release
- Hardened teeth are designed to grip from any angle

ITEM NO	TYPE	CAPACITY	LENGTH
0021010	4LN	41 mm	100 mm
0021012	6LN	57 mm	150 mm
0021014	9LN	73 mm	225 mm

WISE-GRIP LOCKING WRENCH



- Locks on to 3 sides of a hex fastener
- Tremendous force can be applied without marring or slipping off the fastener
- Each wrench adjusts to over 16 different standard and metric wrench sizes
- Jaw tips are knurled for better gripping
- Parallel jaws with smooth surfaces and precise scale markings.
- Grooved internal jaw and sliding lever
- ProTouch™ grips provide maximum comfort and reduced hand fatigue.
- Hang hole for easy wall storage

ITEM NO	TYPE	CAPACITY	LENGTH
0021050	4LW	14 mm	100 mm
0021052	7LW	19 mm	175 mm
0021054	10LW	28 mm	250 mm

WISE-GRIP LARGE JAW LOCKING PLIERS



- Large locking plier applies up to 2000 pounds of pressure
- High grade alloy steel with hardened teeth
- Guarded release trigger for safety
- Non-slip rubberized grips to increase comfort and leverage by reducing vibration and hand fatigue
- Non slip rubberized grip
- Heavy duty large jaw

ITEM NO	TYPE	CAPACITY	LENGTH
0021059	6LC	79 mm	150 mm
0021060	12LC	79 mm	300 mm

WISE-GRIP LOCKING C-CLAMP WITH REGULAR TIPS



- Turn screw to adjust pressure and fit work
- With regular tips (non-swivel)
- Stays adjusted for repetitive use
- Wide-opening jaws provide greater versatility in clamping a variety of shapes
- Guarded release trigger quickly unlocks and protects from accidental release
- High-grade heat-treated alloy steel for maximum toughness and durability

ITEM NO	TYPE	CAPACITY	LENGTH
0031050	6R	50 mm	150 mm
0031052	11R	100 mm	275 mm
0031054	18R	200 mm	455 mm
0031056	24R	317 mm	600 mm

WISE-GRIP FAST RELEASE LOCKING C-CLAMP WITH REGULAR TIPS



- Hex adjusting screw allows for fine adjustment and additional controlled release of tool
- With regular tips (non-swivel)
- Wide-opening jaws provide greater versatility in clamping a variety of shapes
- High-grade heat-treated alloy steel for maximum toughness and durability
- Release is controlled and can be operated with one hand
- Easier to open from any angle by simply pulling - no need to put pressure on the trigger
- More finger room to accommodate large hands and professional tradesman who wear gloves
- Elimination of trigger means no pinching during release

ITEM NO	TYPE	CAPACITY	LENGTH
0031053	FR6R	50 mm	150 mm
0031055	FR11R	100 mm	275 mm

WISE-GRIP LOCKING C-CLAMP WITH SWIVEL PADS



- Wide-opening jaws provide greater versatility in clamping a variety of shapes
- Swivel pads hold tapered work, awkward fabricating jobs, and delicate projects without damaging the work surface
- Turn screw to adjust pressure and fit work. Stays adjusted for repetitive use
- High-grade heat-treated alloy steel for maximum toughness and durability
- Guarded release trigger quickly unlocks and protects from accidental release

ITEM NO	TYPE	CAPACITY	LENGTH
0031030	4SP	41 mm	100 mm
0031032	6SP	54 mm	150 mm
0031034	9SP	102 mm	225 mm
0031036	11SP	112 mm	275 mm
0031038	18SP	200 mm	455 mm
0031040	24SP	254 mm	600 mm

WISE-GRIP LOCKING C-CLAMP WITH LARGE THROAT



- Regular tips (not swivel)
- Locks work with the squeeze of one hand
- High alloy heat treated steel for maximum toughness and durability

ITEM NO	TYPE	LENGTH	THROAT D
0031060	9DR	225 mm	112 mm
0031066	18DR	455 mm	200 mm

WISE-GRIP LOCKING CHAIN CLAMP



- Adjusts quickly for ratchet action in either direction
- Wide variety of uses
- Chain holds and locks around any shape or size
- Ideal for awkwardly shaped pieces
- Turn screw to adjust pressure and fit work. Stays adjusted for repetitive use
- High-grade heat-treated alloy steel for maximum toughness and durability
- Guarded release trigger quickly unlocks and protects from accidental release

ITEM NO	TYPE	CAPACITY	LENGTH
0031020	20R	455 mm	225 mm
0031024	Spare Chain		

WISE-GRIP LOCKING WELDING CLAMP



- U-shaped jaws for visibility and working space
- Holds work in proper alignment. The adjusting screw gives exacting pressure
- Simply turn the adjustment screw to change jaw opening and clamping pressure
- Guarded release helps keep work fast and safe
- Powerful locking mechanism

ITEM NO	TYPE	LENGTH	THROAT D
0031000	9R	225 mm	25 mm

WISE-GRIP LOCKING PANEL CLAMP



- Provides quick clamping and alignment of auto body panels
- Adjusting screw gives exacting pressure. Simply turn the adjustment screw to change jaw opening and clamping pressure. It stays adjusted for repetitive use
- Guarded release trigger helps keep work safe and fast. It will quickly release and unlock when needed
- High-grade alloy steels heat treated for maximum toughness and durability
- The bottom jaw on this clamp slides in straight line motion

ITEM NO	TYPE	LENGTH	THROAT D
0031010	9AC	225 mm	6 mm

WISE-GRIP LOCKING PLIERS SET



- Includes cloth pouch
- TVG71 3 pc set includes: 10WR, 6LN and 5WR
- T71 4 pc set includes: 1CR, 7R, 6LN and 5WR
- T77 2 pc set includes: 10WR and 6LN
- T80SG 2 pc set includes: 7CR and 5WR
- 0011025 4 pc set includes: 10R, 5WR, 7CR and knife

ITEM NO	TYPE
0022001	3 pc Set: 10WR, 6LN, 5WR
0022005	4 pc Set: 10CR, 7R, 6LN, 5WR
0031059	2 pc set: 10WR, 6LN
0022004	2 pc set: 7CR, 5WR
0011025	4 pc set: 10R, 5WR, 7CR, knife


WISE-GRIP LOCKING PLIERS DISPLAY



- 11 pc includes: 10R, 7R, 10WR, 5WR, 4WR, 10CR, 7CR, 6LN, 9LN and 4LN

ITEM NO	TYPE	SET
0011024	Locking Pliers Display	11

WISE-GRIP PINCH-OFF TOOL



- Specially designed for the refrigeration industry. Locks on copper tubing and pinches off instantly
- High grade alloy steels
- Adjusting screw gives exacting pressure
- Guarded release helps keep work fast and safe
- Powerful locking mechanism

ITEM NO	TYPE	LENGTH	THROAT D
0021064	RR	175 mm	25 mm

WISE-GRIP LOCKING SHEET METAL TOOL



- Locks to work with powerful grip
- Perfect for sheet metal work and stretching upholstery

ITEM NO	TYPE	LENGTH	THROAT D
0021062	8R	200 mm	44 mm

WISE-GRIP DIAGONAL CUTTING PLIERS



- Cuts up to 2mm cables
- Induction hardened cutting face
- Chromium nickel steel for improved durability on cutting face
- Comfortable, pull resistant handles

ITEM NO	LENGTH
0080017	175 mm

QUICK GRIP

IRWIN QUICK CHANGE CLAMP



- For smaller jobs and applications in tight areas
- Non-marking, stay-on pads protect workpiece finish

ITEM NO	TYPE	CAPACITY
0551301	506QC	150mm / 6in in
0551303	512QC	300mm / 12in in
0551305	518QC	450mm / 18in in
0551307	524QC	600mm / 24in in
0551309	536QC	910mm / 36in in
0551311	550QC	1250mm / 50in in

IRWIN XP QUICK GRIP CLAMP



- Patented POWER LOCKS™ hold more pressure, longer. Provides 550 lbs of one-handed force (900 lbs of two-handed force)
- I-Beam bar resists twisting and bowing allowing maximum force to be applied
- QUICK-RELEASE™ trigger for non-explosive pressure release
- QUICK-CHANGE™ jaw converts quickly into a spreader
- Non-marking pads grip securely and protect workpiece finish

ITEM NO	TYPE	CAPACITY
0560010	XP twin pack	150mm / 6in in
0560002	XP	300mm / 12in in
0560011	XP twin pack	300mm / 12in in
0560003	XP	450mm / 18in in

IRWIN QUICK GRIP MINI CLAMP



- 25% smaller than Quick-Change clamps for smaller projects or for working in confined spaces
- Constructed of high-tech reinforced resin for strength and durability
- Exerts up to 150 lbs of clamping pressure
- Patented pistol grip design enhances comfort and ease of use
- Non-marring pads grip firmly and protect work
- Ideal for clamping/gluing, holding work for sawing/drilling, and positioning work for fastening

ITEM NO	TYPE	CAPACITY
0551330	546	150mm / 6in in
0551333	5412	300mm / 12in in

IRWIN QUICK GRIP HANDI CLAMP



- Made of high-tech resin material
- Lightweight and durable, they are handy and useful for a variety of applications around the shop or home
- Quick release trigger
- Jaws are designed to reach and hold around odd shapes. The jaw ends have non-marking swivel pads

ITEM NO	TYPE	CAPACITY
0551400	T59100ECD	38mm / 1.5in in
0551401	T59200ECD	50mm / 2in in
0551403	T59400ECD	101mm / 4in in

GROOVE LOCK

GROOVELOCK PLIERS



- Adjust 50% faster than traditional groove joint pliers
- Fully certified by TÜV, GS and DIN / ISO 8976 and complies to ASTM / ANSI standards
- Specially engineered, all purpose jaw grips round, hex, square and flat surfaces for incredible versatility
- Designed with twice the groove positions of traditional groove joint pliers to deliver optimal hand and jaw positioning – providing a superior grip

ITEM NO	LENGTH
0200040	200mm / 8in in
0200041	250mm / 10in in
0200042	300mm / 12in in

GROOVELOCK PLIERS SET



- Adjust 50% faster than traditional groove joint pliers
- Fully certified by TÜV, GS and DIN / ISO 8976 and complies to ASTM / ANSI standards
- Specially engineered, all purpose jaw grips round, hex, square and flat surfaces for incredible versatility
- Designed with twice the groove positions of traditional groove joint pliers to deliver optimal hand and jaw positioning – providing a superior grip

ITEM NO	LENGTH	SET
0200043	8 & 10in in	2 pcs
0200044	8, 10 & 12in in	3 pcs
0200045	250mm / 10in	10 pc Display

RECORD QUICK ADJUSTING WRENCH



- Lightweight multi-purpose pipe wrench, suitable for the professional heating and plumbing installer and professional builder
- Sintered high carbon steel upper jaw for strength, hardened serrated steel jaw teeth, lightweight but strong aluminium sliding body
- Fitted with quick release trigger
- Weight: 550g

ITEM NO	CAPACITY	LENGTH
0050112	58 mm	288 mm

PROSNIP

PROSNIP UTILITY SNIPS



- Cold-formed blades are 44% stronger, and require 25% less cutting force
- Pro-Touch Grips provide superior comfort, resists twisting, and will not slip off
- Compound cutting action with textured grips and E-Z close latch
- Great for cutting sheet metal, vinyl, plastic, rubber and many other applications
- Multi-purpose snips with compound cutting leverage
- Easy push-up safety latch allows one-handed operation

ITEM NO	TYPE	HAND
0101513	No. 104	Universal

PROSNIP AVIATION SNIPS



- Cold-formed blades are 44% stronger, and require 25% less cutting force
- Easy push-up release allows one-handed operation
- Pro-Touch Grips provide superior comfort, resists twisting, and will not slip off
- 10% Reduced hand span increases control and decreases fatigue
- Long life spring for increased durability and reliability
- Lower serrated blade grips material for a smoother cut with no double-marked edges
- 12 gauge alloy steel spines provide increased rigidity and less flexing

ITEM NO	TYPE	HAND
0101510	No. 101	Left
0101511	No. 102	Right
0101512	No. 103	Universal

PROSNIP OFFSET SNIPS



- Offset blades ensure that hands will be kept safely above the work during the cutting process
- Cold-formed blades are 44% stronger than hot forged blades and require 25% less cutting force because of more accurate blade tolerances
- Long life spring for increased durability and reliability
- Compound leverage means reduced pressure and faster and easier cutting
- 2.66 mm alloy steel spines provide increased rigidity and less flexing
- Easy push-up safety latch allows one-handed operation

ITEM NO	TYPE	HAND
0101502	20SR	Right
0101501	20SL	Left

GILBOW

GILBOW TINSNIPS



- Precision-ground edges on the blades ensure a tight grip on each cut for superior cutting quality
- Hot drop-forged steel blades provide maximum strength and long life
- Durable spring washer holds blades tightly against each other when cutting

ITEM NO	TYPE	SIZE
0080000	TG245	200mm / 8in in
0080002	TG245	250mm / 10in in
0080003	TG245	300mm / 12in in
0080004	TG245	350mm / 14in in

GILBOW HEAVY DUTY CRANKED HANDLE SHEARS



- Unique non-slip joint set
- Double hollow ground blades
- Reduced friction for easier cutting
- Safety stop prevents trapped fingers
- Drop forged carbon steel handles and blades

ITEM NO	TYPE	SIZE	HAND
0080014	TG67	275mm / 11in in	Left
0080015	TG69	275mm / 11in in	Right
0080016	TG691	350mm / 14in in	Right

DRILL BITS

TURBOMAX HSS DRILL BIT SET



- Turbomax 15 piece - Pro case: 1.5, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5, 6.0, 6.5, 7.0, 8.0, 9.0, 10.0mm
- Turbomax 19 piece - Metal case: 1mm to 10mm in steps of 0.5mm

ITEM NO	TYPE
0302449	15 pc Set (in pro case)
0302450	19 pc Set (in metal case)

TURBOMAX HSS DRILL BIT



- Turbomax is designed primarily for high performance drilling in sheet metal but performs well in all types of wood and plastic
- Can also be used for drilling stainless steel although normally the HSS Cobalt twist drill bit is recommended for this
- Remember to always use a coolant when drilling stainless steel

ITEM NO	SIZE
0302201	1 mm
0302205	1.5 mm
0302211	2 mm
0302215	2.5 mm
0302221	3 mm
0302222	3.1 mm
0302223	3.2 mm
0302224	3.3 mm
0302226	3.5 mm
0302231	4 mm
0302232	4.1 mm
0302233	4.2 mm
0302234	4.3 mm
0302236	4.5 mm
0302239	4.8 mm
0302240	4.9 mm
0302251	5 mm
0302252	5.1 mm
0302256	5.5 mm
0302261	6 mm

ITEM NO	SIZE
0302266	6.5 mm
0302271	7 mm
0302276	7.5 mm
0302281	8 mm
0302286	8.5 mm
0302291	9 mm
0302296	9.5 mm
0302301	10 mm
0302311	11 mm
0302321	12 mm
0302331	13 mm

IRWIN COBALT HSS DRILL BIT SET



- Cobalt steel extends cutting edge life and maintains cutting life after reshaping
- Extra hard drill for greater wear
- 135° split point tip starts on contact, cuts with less force
- Reduced shank above 3/8in allows the use of larger drill bits in a 3/8in chuck
- Rubber overmolded case protects kit if dropped
- Tap and drill selection chart for convenient reference
- Automatic indexing for easy bit access and identification
- Removable cartridges: easy to carry bits from case to worksite
- Sizes include 1/16in to 1/2in in 1/64in increments

ITEM NO	SIZE
0311001	15 pc set

IRWIN COBALT HSS DRILL BIT



- Cobalt steel extends cutting edge life and maintains cutting life after reshaping
- Extra hard drill for greater wear
- 135° split point tip starts on contact, cuts with less force
- Reduced shank above 3/8in allows the use of larger drill bits in a 3/8in chuck
- Rubber overmolded case protects kit if dropped
- Tap and drill selection chart for convenient reference
- Automatic indexing for easy bit access and identification
- Removable cartridges: easy to carry bits from case to worksite
- Sizes include 1/16in to 1/2in in 1/64in increments

ITEM NO	SIZE
0311015	7.5 mm
0311016	8 mm

ITEM NO	SIZE
0311017	8.5 mm
0311018	9 mm
0311019	9.5 mm
0311020	10 mm
0311022	11 mm
0311024	12 mm
0311026	13 mm

UNIBIT STEP DRILL



- Single-flute cutting edge for greater control through steps
- 3 flatted shank prevents slipping in drill chuck
- Non-skid self-starting tip eliminates skidding and the need for center punching

ITEM NO	TYPE	SIZE
0151701	1M	4,5,6,7,8,9,10,11,12 mm
0151702	2M	4,6,8,10,12 mm
0151703	3M	6,8,10,12,14,16,18 mm
0151704	4M	4,6,8,10,12,14,16,18,20,22 mm
0151705	5M	5,7.5,10,13,16,19,21,23,26,29,31,33,35 mm
0151741	PG29M	5,7.5,10,12.5,15.2,18.6,20.4,22.5,25.5,28.3 mm

IRWIN SCREWDRIVER BIT SET



- Engineered for use in hand-driving applications or with power tools when used with the IRWIN Insert Bit Holder
- Specifically designed for the higher torque requirements of power tools
- Designed to provide more clearance between the power tool and the fastener
- Available in 31 and 30 piece sets
- 30 pc Set: Ph1, 5xPh2, Ph3, Pz1, 5xPz2, Pz3, T20, T30, T40, SL6-8, SL10-12; Nut Set: 6, 8, 10, 12.; Double Ends: Ph2/Ph2, Pz2/Pz1, 2xPz2/Pz2; Bit holder
- 31 pc Set: Ph1, 5xPh2, Ph3, Pz1, 5xPz2, Pz3, 4xPh2Tin, SL6-8, SL8-10, SL10-12, 2xPh2(Powerbit), 2xPh2(Powerbit); Double Ends: 2xPh2/Ph2, Pz2/Pz1, 2xPz2/Pz2; Bit holder

ITEM NO	TYPE
0200029	30 pc Set
0200030	31 pc Set

BOLT GRIP

BOLT GRIP REMOVER BASE SET



- Unique, reverse spiral flute design securely grips and removes stubborn nuts and bolts
- Maximum gripping power. Reverse spiral flutes are designed to bite down
- Tougher than tool steel. High carbon steel ensures longer life and greater durability
- Works with most tools
- 3/8in square drive for use with hand ratchets, impact wrenches and air ratchets
- Hexagonal flats for use with flat wrench, pliers, adjustable wrench, sockets or locking pliers
- Grips both metric and imperial
- Universal lobular design fits all types of fasteners
- Base Set - 5 pieces: 3/8in, 7/16in / 11mm, 1/2in, 9/16in / 14mm, 5/8in / 16mm

ITEM NO	TYPE
0200010	Base Set (5 pcs)

BOLT GRIP EXPANSION SET



- Expansion Set - 5 pieces: 5/16in / 8mm, 10mm, 13mm, 11/16in, 3/4in / 19mm

ITEM NO	TYPE
0200015	Expert Set (5 pcs)

BOLT GRIP POWER GRIP SET



- Powergrip Set - 7 pieces: 3/16in, 1/4in, 5/16in/8mm, 3/8in, 10mm, 7/16in/11mm, 1/2in

ITEM NO	TYPE
0200025	Powergrip Set (7 pcs)

BOLT GRIP REMOVER SPECIALITY SET



- Speciality Set - 5 pieces: 3/4in / 19mm, 13/16in / 21mm, 7/8in / 22mm, 15/16in / 24mm, 1in

ITEM NO	TYPE
0200020	Speciality Set (5 pcs)

SAWS & BLADES

IRWIN HACKSAW



- Frames are built to meet the professional's demanding needs
- Blade storage means no need to search for spare blades
- Soft Touch handles ensure a comfortable sawing grip and prevents slippage
- Ergonomic metal frame for higher blade tension and prevents the blade being released when dropped
- For sawing large objects with the 90°-55° Blade Mounting
- Metal tensioning mechanism for a longer lasting tool

ITEM NO	TYPE	SIZE
0200031	100	Junior
0200032	125	300mm / 12 in
0200036	1-75 Low Tension	300mm / 12 in

IRWIN 12IN HACKSAW BLADES



- Long-lasting, flexible and virtually unbreakable with superb wear-resistance
- Pack of 10
- 300mm/12in

ITEM NO	TYPE	SIZE
0200035	24T	300mm / 12 in
0200034	32T	300mm / 12 in

KNIVES & BLADES

IRWIN STANDARD FIXED BLADE KNIFE



- Lightweight, hardwearing aluminium body
- Includes 3 x IRWIN Bi-Metal blue blades
- Unbreakable
- Stay sharp up to 3x longer than carbon steel blades

ITEM NO	TYPE
0060004	Standard Fixed

IRWIN STANDARD RETRACTABLE BLADE KNIFE



- Includes 3 IRWIN Bi-Metal blue blades
- Ideal cutting angle for reduced fatigue
- Smooth, three-position slide exposes variable blade lengths
- Inside storage clip – holds 5 blades securely

ITEM NO	TYPE
0060003	Standard Retractable

IRWIN PRO-TOUCH RETRACTABLE BLADE KNIFE



- Quick-Change mechanism allows for easy blade removal or reversal without opening knife
- Durable, 3-position slide allows different blade lengths to be used
- Patented virtually unbreakable Bi-Metal blue blade stays sharp longer
- Tough construction, designed to fit the hand comfortably in use
- One-Touch easy access to spare blades

ITEM NO	TYPE
0060001	Pro Touch Retractable

IRWIN KNIFE BLADE DISPLAY



- Irwin knife blade display

ITEM NO	TYPE	SET
0060050	Bi Metal and Carbon Steel blades	400 (bi metal) and 200 (carbon steel)

IRWIN BI-METAL KNIFE BLADE



- The new IRWIN patented Bi-Metal Blue blades have a tough, durable edge, honed for maximum sharpness and longer life – in fact, IRWIN Bi-Metal Blue blades last up to three times longer than traditional carbon steel blades
- In addition, IRWIN Bi-Metal Blue blades are more flexible, and are unbreakable under normal working conditions

ITEM NO	TYPE	SET
0060008	Bi Metal	50 pcs
0060009	Bi Metal	100 pcs
0060010	Bi Metal	10 x 10 pcs

IRWIN KNIFE BLADE



- The new IRWIN patented Bi-Metal Blue blades have a tough, durable edge, honed for maximum sharpness and longer life – in fact, IRWIN Bi-Metal Blue blades last up to three times longer than traditional carbon steel blades
- In addition, IRWIN Bi-Metal Blue blades are more flexible, and are unbreakable under normal working conditions

ITEM NO	TYPE	SET
0060006	Bi Metal	5 pcs
0060007	Bi Metal	10 pcs

IRWIN CARBON STEEL KNIFE BLADE



- High quality carbon steel blades

ITEM NO	TYPE	SET
0600010	Carbon Steel	10 pcs
0060011	Carbon Steel	10 x 10 pcs

RECORD

RECORD MECHANICS VICE



- The most popular and widely used general purpose vices for light to medium duty applications
- High quality grey iron castings resist distortion under severe pressure
- Smooth action provided by dovetailed, long barrelled, unbreakable nut
- Hardened steel replaceable jaw plates
- Fibre jaws and swivel bases are available as optional extras

ITEM NO	TYPE	WIDTH
0050034	T1	75mm / 3in in
0050035	T3	100mm / 4 in
0050036	T4	115mm / 4.5 in
0050037	T5	125mm / 5 in
0050033	T6	150mm / 6 in
0050038	T8	205mm / 8 in

RECORD MECHANICS VICES WITH SWIVEL BASE



- The quick release system allows the vice to be opened and closed in seconds
- Turn the handle 360 degrees counter-clockwise and the vice jaw will unlock and easily slide open
- Hold items from 36 to 52 lbs and apply from 4,840 to 8,800 lbs of pressure
- 360 degree swivel base and integral pipe jaws as standard features
- Replaceable steel jaws

ITEM NO	TYPE	WIDTH
0050023	T4VS	115mm / 4.5 in
0050024	T5VS	125mm / 5 in
0050025	T6VS	150mm / 6 in

RECORD ENGINEERS VICE



- Bench mounting vice with cast iron body and replaceable, serrated, steel jaws
- Smooth rolled thread for accurate clamping
- Suitable for workshop, garage and machine shop use

ITEM NO	TYPE	WIDTH
0050031	T112	150mm / 6 in
0050032	T114	205mm / 8 in

RECORD DRILL PRESS VICE



- Industry quality steel jaws
- Cast iron base jaw
- Width: 83mm
- Opening: 60mm

ITEM NO	TYPE	WIDTH
0050087	T414	100mm / 4in

RECORD SWIVEL BASE



- 360 degree swivel bases are used to rotate and lock the vice at the most convenient working angle
- Available for T4 and T5 mechanics vices either as a standard fitting or an optional extra

ITEM NO	TYPE
0050016	T4SB

RECORD GENERAL PURPOSE G-CLAMP



- Drop forged steel clamp.
- Slim section permits use in situations where space is limited
- Particularly useful for the craftsman with smaller work, the boat builder and the handyman
- Blue stove enamelled finish

ITEM NO	TYPE	CAPACITY
0051074	T119/6	150mm / 6in

RECORD SPARE JAW SET



- Replaceable jaw plates for vices
- Sold in pairs
- Hardened, CHC machined, complete with screws or bolts and ready to fit

ITEM NO	TYPE	CAPACITY
0050311	T5-D	150mm / 6 in
0050310	T6-D	125mm / 5 in

RECORD ROLLER PIPE CUTTER



- High quality robust cutter for all kinds of steel and cast iron pipe
- Guaranteed against breakage with thin section specially hardened cutting wheel
- Roller ensure cutter is set and kept square to the pipe and rolls down burr
- Head includes safety stop to prevent the cutting wheel being damaged by the rollers

ITEM NO	TYPE	CAPACITY
0050141	T202	3.2 - 50mm / 1/8 - 2 in

RECORD UNIVERSAL TUBE BENDER



- Versatile tool suitable for plumbers, gas fitters, electricians etc.
- Will accept all the most widely used sizes and types of pipe, conduit and even soft steel rod
- Features include a single universal roller for all forms of pipe, dual position tube locator for copper or conduit and an adjustable quadrant for precise repeat bends
- Capacity: copper from 15mm to 42mm diameter
- Capacity: conduit up to 32mm diameter
- Capacity: light stainless steel 15mm to 35mm diameter
- Capacity: steel, steam, gas, water pipe up to 3/4in diameter

ITEM NO	TYPE
0050157	TUL223

RECORD HANDI BENDER



- An ideal tool for the plumber, gas fitter and domestic heating engineer, handling 15mm o.d. copper and stainless steel tube and 22mm o.d. copper tube
- Hand held, it can be used in restricted spaces
- Compact and light enough to be carried from room to room but can also be held in a vice and used as a bench bender
- Loading arm has pre-set rollers for speed of operation and formers with guides for 15mm and 22mm tubes

ITEM NO	TYPE	CAPACITY
0050155	T218M	15mm / 22 mm

RECORD MINI TUBE BENDER



- Designed for bending small diameter copper, stainless steel, aluminium and steel tubes
- Particularly suitable for the hydraulic engineer, vehicle mechanic and tool maker

ITEM NO	TYPE	CAPACITY
0050153	T210	3/4/6 mm

RECORD COPPER FORMER AND GUIDE PACK



- TCOP15-35: formers/guides 15mm, 22mm, 28mm and 35mm for copper

ITEM NO	TYPE	CAPACITY
0050163	TCOP	15/22/28/35 mm

RECORD FORMER AND GUIDE SET FOR UNIVERSAL BENDER



- Comes complete with a metal carrying case
- They are suitable for the CT223/32 machines which are designed to bend conduit

ITEM NO	TYPE	CAPACITY
0050170	T3F226M	16/20/25/32 mm

RECORD BACK NUT WRENCH



- Specially designed double ended wrenches to fit 13mm/0.5in and 19mm/0.75in lavatory basin and bath nuts
- Designed for use in situations where access is restricted

ITEM NO	TYPE	CAPACITY
0050128	T6552	13/19 mm

RECORD BOLT CUTTER



- The bolt cutter consists of two drop-forged steel handles, which open and close the jaws through a compound action
- This action means that every pound of force applied to the handles is amplified to produce 80lbs of force between the jaws
- The jaws are dropforged from a special steel and machined to precise specifications
- This produces a resilient body and rigid cutting edge.

ITEM NO	TYPE
0050008	TBC924E
0051092	T924 Fastener Kit

KNEE PADS

IRWIN PROFESSIONAL KNEE PAD



- Absorb shock with foam cushion under the cap
- Breathable perforated neoprene straps
- Double straps for comfort and safety
- Do not restrict blood flow during use

ITEM NO	TYPE
0090027	Gel
0090028	All Terrain
0090029	Swivel Flexible

TOOL BOXES

IRWIN PROFESSIONAL FOAM TOOLBOX



- Made out of a heavy-duty structural foam
- Unlike most plastic or metal tool boxes this box will stand years of use and abuse
- Lid access storage which secures small parts
- Comfortable grip with rubberised handle
- Easier lifting made possible by extra handle grips on sides
- Rainproof design. All the hardware has been attached without penetrating interior space
- Rust-resistant metal latches provide secure closure
- Padlock ready with a built-in eye
- Easy access on both sides for IRWIN set cases or frequently used tools
- 3/4 length removable tray allows for storage of tall objects
- Industrial strength structural foam construction withstands temperatures below zero, and is exceptionally strong - can easily be used as a convenient step-up

ITEM NO	TYPE
0090001	Pro Structural Foam

IRWIN PROFESSIONAL LARGE TOOL ORGANISER



- Large capacity storage
- Top opening for quick and easy access
- False bottom provides separate storage for important items
- Durable plastic bottom is water resistant
- Reinforced handle features extra strength rivets

ITEM NO	TYPE
0090006	Pro Large Tool Organiser

IRWIN PROFESSIONAL UTILITY ORGANISER



- Enough capacity to carry a range of tools and accessories
- Pockets and compartments designed to provide better organisation
- Bottom made of tough wear resistant plastic
- Reinforced rivets throughout for added durability

ITEM NO	TYPE
0090009	Pro Utility Organiser

IRWIN PROFESSIONAL SOFT SIDE TOOL ORGANISER



- Small, lightweight and strong
- Zip fastening for security
- Padded handle features reinforced stitching for extra strength
- Extra wide opening provides easy access to all tools

ITEM NO	TYPE
0090010	Pro Soft Side Tool Organiser

IRWIN PROFESSIONAL SOFT SIDE TOOL ORGANISER WITH ZIPPER



- Long enough to carry saws and levels as well as having space and pockets for other tools
- Size: 60cm x 26cm x 40cm
- Pockets and compartments designed to provide better organisation

ITEM NO	TYPE
0090002	Pro Soft Side Tool Org with Zipper

STRAITLINE

STRAITLINE HEAVY DUTY CHALK LINE



- Strong durable reels with high-strength cord and a high chalk capacity
- Chalk is available in a range of colours and refill sizes
- Gear ratio 6:1 for faster line retraction
- Larger aggressive hook for greater anchorage
- Strong polymer line: 2 x stronger for added durability
- Clutch for easy line release
- Lock holds line in place
- Impact resistant die cast plates
- 3.5 x stronger than plastic reels
- Metal handle, 25% stronger for durability

ITEM NO	TYPE
0509272	HPP Chalk Line

STRAITLINE MINIREEL SET



- Perfect tool for roofers and concrete workers who have to snap chalk lines
- Shock resistant case
- Comfortable heavy duty steel handle
- 180 feet of heavy duty braided line
- Large steel pull ring
- Fast rewind

ITEM NO	TYPE
0509208	T64490