
Lenovo 7Y37A01088 interface cards/adapter Internal SAS, SATA



Brand : Lenovo

Product code: 7Y37A01088

Product name : 7Y37A01088

ThinkSystem 430-8i SAS/SATA 12Gb HBA

Lenovo 7Y37A01088 interface cards/adapter Internal SAS, SATA:

The 430-8i and 430-16i internal HBAs offer improved performance over the previous generation N2215 HBA for System x servers, with a faster processor and more memory.

Rigorous testing of the ThinkSystem HBAs by Lenovo through the ServerProven program ensures a high degree of confidence in storage subsystem compatibility and reliability. Providing an additional peace of mind, the controller is covered under Lenovo warranty.
Lenovo 7Y37A01088. Host interface: PCIe, Output interface: SAS, SATA, Expansion card form factor: Low-profile. Product colour: Black, Green. Data transfer rate (max): 12 Gbit/s

Ports & interfaces	
Host interface *	PCIe
Output interface *	SAS, SATA
Expansion card form factor	Low-profile
Expansion card standard	PCIe 3.0
External mini-SAS ports	8

Design	
Internal *	✔
Product colour	Black, Green
Features	
Data transfer rate (max)	12 Gbit/s
Logistics data	
Harmonized System (HS) code	84733020

0889488433490

889488433490

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date