



## PUSH ON TERMINALS (INSULATED AND NON INSULATED)



For Insulated Disconnect Terminals without copper sleeve please add **NTG** to the end of part number i.e. **DVPO 1 6.3F NTG**

These adaptors are to suit all 6.3mm (0.250") Series push on terminals.

### Male/Female Piggyback Adaptors

Vinyl insulated



Part Number	Conductor Size mm <sup>2</sup>	Colour
<b>DVPOA 1-6.3</b>	0.25-1.65	Red
<b>DVPOA 2-6.3</b>	1.04-2.63	Blue
<b>DVPOA 5-6.3</b>	2.63-6.64	Yellow

#### Suitable crimping tools:

**Red** DHC 15, DHC 15Y, DHCR 1, DHCR 15, DBMT 1, 3 & 4.

**Blue** DHC 15, DHC 15Y, DHCR 2, DHCR 15, DBMT 1, 3 & 4.

**Yellow** DHC 15, DHC 15Y, DHCR 5, DHCR 15, DBMT 1, 3 & 4.

### Interlocking Nylon Disconnectors (Non Twin Grip)

Fully insulated



Part Number	To Suit Width mm <sup>2</sup>	Male/Female
<b>DVFPO 1-6.3FIT</b>	6.3	Female
<b>DVFPO 1-6.3MIT</b>	6.3	Male
<b>DVFPO 2-6.3FIT</b>	6.3	Female
<b>DVFPO 2-6.3MIT</b>	6.3	Male
<b>DVFPO 5-6.3FIT</b>	6.3	Female
<b>DVFPO 5-6.3MIT</b>	6.3	Male

#### Suitable crimping tools:

DHCR 15, DHCR HS.

### Push-on Terminal Type PVC Insulating Covers



Part Number	Dimensions mm	
	A	C
<b>DVC 2.8</b>	2.8	4.0 x 2.4
<b>DVC 4.g</b>	2.4	5.2 x 2.0
<b>DVC 6.3 1</b>	2.8	8.0 x 2.0
<b>DVC 6.3 2</b>	5.6 x 2.0	8.0 x 2.0
<b>DVC 9.5</b>	4.8	10.3 x 4.0

#### For use with:

DVC 2.8	2.8 Push On (0.110")
DVC 6 3 1	6.3 Push On (0.250")
DVC 6 3 2	6.3 Push On (0.250")
DVC 9.5	9.5 Push On (0.375")

Non insulated




Part Number	Conductor Size mm <sup>2</sup>
<b>DPOA 1 6.3</b>	0.25-1.65
<b>DPOA 2 6.3</b>	1.04-2.63
<b>DPOA 5 6.3</b>	2.63-6.64

#### Suitable crimping tools:

DHCF 15, DHCRF 15, DBMT 1, 3 & 4.


### Female Nylon Flag Disconnectors



Part Number	Conductor Size mm <sup>2</sup>	Colour
<b>DNFPO 1-6.3 FLAG</b>	0.25-1.65	Red
<b>DNFPO 2-6.3 FLAG</b>	1.04-2.63	Blue
<b>DNFPO 1-4.8 FLAG</b>	0.25-1.65	Red
<b>DNFPO 2-4.8 FLAG</b>	1.04-2.63	Blue

Suitable crimping tool: DHCR-FL

### Flag Terminal Type PVC Insulating Covers



Part Number	Width mm
<b>DVC6.3 FLAG</b>	6.3

### Female Flag Disconnector



Part Number	To suit Width mm
<b>DPO1-6.3 FLAG</b>	6.3

Non Crimp Adaptor

Part Number
<b>DPOA 6.3</b>

