

# **QUALITEK®**

## Lead Free NC601 Cored Solder Wire No-Clean

### For all Lead Free Alloys

#### NC601 (Colophony free No-Clean)

Containing a very effective activator, NC601 wets and spreads like and RA yet leaves virtually no post-soldering residue. This results in a visibly clean solder connection. NC601 conforms to J-STD-004 / J-STD-006.

Qualitek® is a trademark of Qualitek International, Inc.

PHYSICAL & CHEMICAL CHARACTERISTICS (FLUX EXTRACT)

|                                      | NC601   |
|--------------------------------------|---|
| Color & Appearance                   | Amber Solid   |
| Softening Point, C?(Flux Extract)    | 75?   |
| Acid Number (mgKOH/g sample)         | 350-370   |
| Silver Chromate(Qualitative Halides) | No Detection  |
| Classification Per J-STD-004         | ORL0  |
| Surface Insulation Resistance        | $>1.0 \times 10^9$  |
| Shelf Life                           | Indefinite  |
| Residue Removal                      | Not Required.  May be removed with hot DI water  Residues may be removed with a stiff brush |

#### STANDARD PACKAGING

Qualitek flux-core wire and solid wire are packed in 250gm, 500gm, 1 pound, 1 kilogram, and 5 pound spools. We also offer 50 pound to 250 pound Quali-packs in rugged fiber containers.

### STANDARD FLUX CORE PERCENTAGE\*







#### STANDARD WIRE DIAMETERS

| DIAMETER/INCH  | 0.125 | 0.092 | 0.062 | 0.050 | 0.040 | 0.032 | 0.025 | 0.020 | 0.015 | 0.010 |
|----------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| DIAMETER/MM    | 3.17  | 2.3   | 1.57  | 1.27  | 1.01  | 0.81  | 0.63  | 0.50  | 0.38  | 0.25  |
| STD.WIRE GAUGE | 11    | 13    | 16    | 18    | 19    | 21    | 23    | 25    | 28    | 31    |

<sup>\*</sup>NC601Only available at 2.2% flux for lead free alloys.

TEL: +44 (0) 151 334 0888 FAX: +44 (0) 151 346 1408 E-mail: <a href="mailto:sales@qualitek-europe.com">sales@qualitek-europe.com</a> Internet: <a href="mailto:www.qualitek.com">www.qualitek.com</a> 9 Apex Court, Bassendale Road. Wirral International Business Park, Bromborough, Wirral, CH62 3RE



WORLDWIDE BRANCHES: UNITED KINGDOM - MEXICO - CHINA - PHILIPPINES - SINGAPORE-USA

This data is based on information that the manufacturer believed to be reliable and offered in good faith. Qualitek International, Inc. makes no warranties expressed or implied as to its accuracy and assumes no responsibilities and liabilities arising out of its use by others as conditions and methods of use of the products is beyond the control of Qualitek International, Inc. The user must determine the suitability of the product before using it on a commercial basis. The warranties extend only to the conformity of the product to the physical descriptions. In no event will Qualitek International, Inc. be responsible for special, incidental and consequential damages whether the claim is in contract, negligence or otherwise.

Rev. 081799-wiresolder2

Consult MSDS for health and safety information