



SAFETY DATA SHEET
GRAINFILLER

Page: 1

Compilation date: 25/09/2012

Revision date: 06/01/2020

Revision No: 4

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: GRAINFILLER

Product code: GRTE

Synonyms: GRAINFILLER

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: Rustins Ltd
Waterloo Road
Cricklewood
London
NW2 7TX
United Kingdom

Tel: +44 (0)208 450 4666

Fax: +44 (0)208 452 2008

Email: rustins@rustins.co.uk

1.4. Emergency telephone number

Emergency tel: .+44(0)2084504666 (Office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: This product has no classification under CLP.

2.2. Label elements

Label elements:

Precautionary statements: P101: If medical advice is needed, have product container or label at hand.
P102: Keep out of reach of children.
P103: Read label before use.
P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P262: Do not get in eyes, on skin, or on clothing.
P270: Do not eat, drink or smoke when using this product.
P281: Use personal protective equipment as required.

[cont...]

SAFETY DATA SHEET

GRAINFILLER

Page: 2

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

NAPHTHA (PETROLEUM) HYDROTREATED HEAVY

EINECS	CAS	PBT / WEL	CLP Classification	Percent
265-150-3	64742-48-9	-	-	7.246%

NAPHTHA (PETROLEUM), HYDROTREATED HEAVY

-	64742-48-9	-	Aquatic Chronic 3: H412; Flam. Liq. 3: H226	3.248%
---	------------	---	---	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

Inhalation: Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

[cont...]

SAFETY DATA SHEET

GRAINFILLER

Page: 3

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Wash the spillage site with large amounts of water.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid the formation or spread of dust in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is exhaust ventilation of the area.

Respiratory protection: Respiratory protective device with particle filter.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: Various

Odour: Paraffinic.

[cont...]

SAFETY DATA SHEET

GRAINFILLER

Page: 4

Evaporation rate: No data available.

Oxidising: No data available.

Solubility in water: Insoluble

Also soluble in: Most organic solvents.

Viscosity: Highly viscous

Boiling point/range°C: >35

Melting point/range°C: No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: 23 - 55

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available.

Vapour pressure: No data available.

Relative density: 1.97 @ 20 C

pH: Approx. 7

VOC g/l: No data available.

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

[cont...]

SAFETY DATA SHEET

GRAINFILLER

Page: 5

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Insoluble in water. Volatile. Absorbed only slowly into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1263

14.2. UN proper shipping name

Shipping name: PAINT

including paint, lacquer, enamel, stain, shellac, varnish, polish, liquid filler and liquid lacquer base

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: I

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: Yes

[cont...]

SAFETY DATA SHEET

GRAINFILLER

Page: 6

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: D/E

Transport category: 1

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H226: Flammable liquid and vapour.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.