



Standard Crimping Tools



CT15

- Ratchet crimping tool for red, blue and yellow pre-insulated terminals.
- Adjustable tensioner.
- Replaceable jaws.
- Indents on jaws identify which jaw has been used.
- Ergonomically designed handles reduce operator fatigue.
- Length 225mm.
- Weight 0.51kgs.



UCT15

- Ratchet crimping tool for un-insulated terminals 0.5 to 6.0mm².
- Adjustable tensioner.
- Replaceable jaws.
- Ergonomically designed handles reduce operator fatigue.
- Length 225mm.
- Weight 0.51kgs.



CT1.5-16

- Ratchet crimping tool for smaller copper tube terminals.
- Suitable for volume use on terminals up to 6.0mm² and occasional use on terminals up to 16mm².
- For volume use of 10mm² and 16mm² terminals use tool no. CT10-16.
- Adjustable tensioner.
- Replaceable jaws.
- Ergonomically designed handles reduce operator fatigue.
- Length 225mm.
- Weight 0.51kgs.



CEFT1, 2 and 3

- CEFT1 - for cord end ferrules 0.5 to 6.0mm².
- CEFT2 - for cord end ferrules 4 to 16mm².
- CEFT3 - for cord end ferrules 16 to 35mm².
- Adjustable tensioner.
- Replaceable jaws.
- Ergonomically designed handles reduce operator fatigue.
- Polished jaws mean that ferrules release easily after crimping.
- Length CEFT1 and CEFT2 205mm, CEFT3 226mm
- Weight CEFT1 and CEFT2 0.39kgs, CEFT3 0.54kgs.



CT10-16


- Ratchet crimping tool specifically designed for crimping 10 and 16mm² copper tube terminals.
- Ideal for IEE specification earthing bond work.
- Adjustable tensioner.
- Ergonomically designed handles reduce operator fatigue.
- Length 242mm.
- Weight 0.54kgs.



CT FLAG

- Ratchet crimping tool for red and blue insulated flag terminals.
- Adjustable tensioner.
- Replaceable jaws.
- Indents on jaws identify which jaw has been used.
- Ergonomically designed handles reduce operator fatigue.
- Length 242mm.
- Weight 0.54kgs.

Ergo Crimping Tools



ECT 15

- New ergonomic tool for red, blue and yellow pre-insulated terminals.
- Extra long computer designed handles and new ratchet system reduces crimping effort to a minimum.
- Reduces risk of Repetitive Strain Injuries and cuts operator fatigue.
- Adjustable tensioner.
- Replaceable jaws.
- Indents on jaws identify which jaws has been used.
- Length 258mm.
- Weight 0.65kgs.



EUCT 15

- New ergonomic tool for un-insulated terminals 0.5 to 6.0mm².
- Extra long computer designed handles and new ratchet system reduces crimping effort to a minimum.
- Reduces risk of Repetitive Strain Injuries and cuts operator fatigue.
- Adjustable tensioner.
- Replaceable jaws.
- Length 258mm.
- Weight 0.65kgs.



ECEFT 4

- New ergonomic tool for cord end ferrules. 0.5 to 10mm².
- Extra long computer designed handles and new ratchet system reduces crimping effort to a minimum.
- Reduces risk of Repetitive Strain Injuries and cuts operator fatigue.
- Adjustable tensioner.
- Replaceable jaws.
- Length 258mm.
- Weight 0.65kgs.



ECEFT 5

- New ergonomic tool for cord end ferrules. 16 to 35mm².
- Extra long computer designed handles and new ratchet system reduces crimping effort to a minimum.
- Reduces risk of Repetitive Strain Injuries and cuts operator fatigue.
- Adjustable tensioner.
- Replaceable jaws.
- Length 258mm.
- Weight 0.65kgs.

Heavy Duty Crimping Tools

CT 50

- Heavy duty crimping tool for 6 to 50mm² copper tube terminals.
- Hexagon crimping.
- Multiple rotating dies built in to head, easy to select correct size.
- Longer handles minimize the effort required to produce a perfect crimp.
- Length 390mm.
- Weight 1.10kgs.




CT 120

- Heavy duty crimping tool for 16 to 120mm² copper tube terminals.
- Crimp size easily selected using screw adjustment.
- Extremely popular tool due to its extended size range.
- Length 645mm.
- Weight 3.50kgs.



CT 150

- Heavy duty crimping tool for 25 to 150mm² copper tube terminals.
- Hexagon crimping.
- Multiple rotating dies built in to head, easy to select correct size.
- Longer handles minimize the effort required to produce a perfect crimp.
- Length 650mm.
- Weight 2.90kgs.



Cable Cutters



PCC 38

- Low cost cable cutter for cutting aluminium and copper non-armoured cables up to 38mm².
- The specially designed shape of the blades means the tool cuts without distortion leaving a perfect finish for crimping or insertion.
- Soft feel insulated handles.
- Length 210mm.
- Weight 0.30kgs.



PCC 80

- Cable cutter for copper and aluminium non-armoured cables up to 80mm².
- Precision ground blades for ease of operation and long service life.
- Cushion handles reduce operator fatigue.
- Length 320mm.
- Weight 0.73kgs.



PCC 250

- Cable cutter for copper and aluminium non-armoured cables up to 250mm².
- Precision ground blades for ease of operation and long service life.
- Extra long forged aluminium handles reduce operator effort required but maintain light weight.
- Length 600mm.
- Weight 1.54kgs.

PCC 400A

- Lightweight cutter for copper and aluminium non-armoured cables up to 400mm².
- Precision ground blades for ease of operation and long service life.
- Compound cutting design reduces operator effort required to a minimum.
- Extensive use of forged aluminium ensures that the tool is remarkably light but also extremely durable.
- Length 700mm.
- Weight 1.57kgs.



Ratchet Cable Cutters



PRCC 240

- Cable cutter for copper and aluminium non-armoured cables up to 240mm².
- Ratchet design gives a large capacity tool that can fit in any toolbox.
- Precision ground blades for ease of operation and long service life.
- Safety lock and part cycle release functions.
- Soft feel insulated handles.
- Length 250mm
- Weight 0.65kgs



PRCC 380

- Cable cutter for copper and aluminium non-armoured cables up to 380mm².
- Ratchet design gives a large capacity tool that can fit in any toolbox.
- Precision ground blades for ease of operation and long service life.
- Safety lock and part cycle release functions.
- Ergonomically designed handles for ease of use.
- Length 285mm
- Weight 0.85kgs



PRCC 500

- Cable cutter for copper and aluminium non-armoured cables up to 500mm².
- Ratchet design gives a large capacity tool that can fit in any toolbox.
- Precision ground blades for ease of operation and long service life.
- Safety lock and part cycle release functions.
- Soft feel insulated handles.
- Length 285mm
- Weight 0.85kgs

Telecom Tool



PRTC 500

- Specially designed cutter for use with telecomms cables up to 2700 pairs capacity.
- Ratchet design gives a large capacity tool that can fit in any toolbox.
- Precision ground blades for ease of operation and long service life.
- Safety lock and part cycle release functions.
- Ergonomically designed handles for ease of use.
- Length 285mm
- Weight 0.85kgs

Wire Strippers.



PWS A

- Automatic wire stripper for stripping wires from 0.2 to 2.5mm².
- Simple to use and extremely durable.
- Automatically strips and removes insulation in one operation.
- Returns to initial position ready for next wire after each stripping operation.
- Length 170mm
- Weight 0.34kgs



PWS B

- Automatic wire stripper for stripping wires from 1.0 to 8.0mm².
- Simple to use and extremely durable.
- Automatically strips and removes insulation in one operation.
- Returns to initial position ready for next wire after each stripping operation.
- Length 170mm
- Weight 0.34kgs

Cable Tie Tensioning Tools



TT 1

- Automatic cable tie tensioner and cutter. For cable ties from 2.2mm to 4.8mm wide.
- This tool is very durable due to its quality construction and metal body.
- Suitable for continuous use.
- Length 160mm
- Weight 0.30kgs



TT 3

- Cable tie tensioning tool. Manually cuts ties from 3.6 to 9mm width.
- A simple but efficient tool.
- Much in demand due to its budget price.
- Length 195mm
- Weight 0.32kgs



TT 4


- Automatic cable tie tensioner and cutter for cable ties up to 13mm width.
- Manufactured to meet the increasing demand for the installation of heavy duty cable ties.
- Length 200mm
- Weight 0.32kgs



Sue



Mick



Michelle

VISIT OUR WEB SITE: www.partex.co.uk