


Parts Information:  
**Geared Hand Winch with Brake & Cable**  
**540kg Capacity**  
**Model No: GWC1200B**



Item	Part No.	Description
1	NLN6.S	NYLOC NUT M6 ZINC DIN 985 (SINGLE)
2	GWC1200B.02	BOLT M6x16
3	GWC1200B.03	CABLE ANCHOR
4	GWW1200B.04	DRUM ASSEMBLY
5	GWW1200B.05	RETAINING SLEEVE
6	GWW1200B.06	PINION-JAW
7	GWW1200B.07	BOLT (M6x30)
8	GWW1200B.08	BASE
9	GWW1200B.09	BOLT (M10x105)
10	SWM12.S	SPRING WASHER M12 ZINC (SINGLE)
11	SN12.S	STEEL NUT M12 ZINC DIN934(SINGLE)
12	GWW1200B.12	TORSION SPRING-JAW
13	GWW1200B.13	PAWL
14	GWW1200B.14	PULLING SPRING
15	GWW1200B.15	CIRCLIP (8mm)
16	GWW1200B.16	BRAKE PINION
17	GWW1200B.17	BRAKE DISC
18	GWW1200B.18	COVER-RATCHET WHEEL

Item	Part No.	Description
19	GWW2000B.21	HANDLE ASSEMBLY
20	GWW1200B.20	SCREW, SOCKET HEAD CAP (M6x8)
21	SS612.S	HEX HEAD SET SCREW M6x12mm SINGLE
22	GWW1200B.22	SPACER
23	GWW1200B.23	BRAKE NUT
24	GWW1200B.24	RACHET WHEEL
25	GWW1200B.25	RETAINING RING
26	GWW1200B.26	RETAINING DISC
27	GWW1200B.27	BUSH (LARGE)
28	GWW1200B.28	CIRCLIP (26mm) (NLA)
29	SWM6.S	SPRING WASHER M6 ZINC (SINGLE)
30	SN6.S	STEEL NUT M6 ZINC DIN934 (SINGLE)
31	GWW1200B.31	CIRCLIP (20mm)
32	GWW1200B.32	BUSH (SMALL)
34	GWW1200B.34	RETAINING PINION
36	FWM10.S	FLAT WASHER M10 SINGLE
38	NLN10.S	NYLOC NUT M10 ZINC (SINGLE)
40	GWC1200B.40	CABLE (4mm x 10mtr)

**NOTE:** It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

**IMPORTANT:** No liability is accepted for incorrect use of product.

**WARRANTY:** Guarantee is 12 months from purchase date, proof of which will be required for any claim.