


Parts Information:
Geared Hand Winch with Brake 900kg Capacity
Model No: GWE2000B



Item	Part No.	Description
1	GWW2000B.01	COVER
3	GWW2000B.03	DRUM ASSEMBLY
4	GWW2000B.04	SLEEVE
5	GWW2000B.05	GEAR PINION (2nd)
6	GWW2000B.06	RETAINING SLEEVE
9	GWW2000B.09	PINION-JAW
10	GWW2000B.10	BOLT (M6x32)
11	GWW2000B.11	BASE
12	GWW2000B.12	PINION
13	GWW2000B.13	SPRING-JAW
14	FWM10.S	FLAT WASHER M10 SINGLE
15	GWW2000B.15	JAW
16	NLN10.S	NYLOC NUT M10 ZINC (SINGLE)
17	GWW2000B.17	PULLING SPRING
18	SWM8.S	SPRING WASHER M8 ZINC (SINGLE)
19	GWW2000B.19	COVER-RATCHET
20	NLN6.S	NYLOC NUT M6 ZINC DIN 985 (SINGLE)
21	GWW2000B.21	HANDLE ASSEMBLY
22	GWW2000B.22	SCREW (M6x8)
23	GWW2000B.23	BOLT (M6x12)
24	GWW2000B.24	BOLT (M6x16)

Item	Part No.	Description
25	SWM8.S	SPRING WASHER M8 ZINC (SINGLE)
26	GWW2000B.26	SPACER
27	GWW2000B.27	FRICTION NUT
28	GWW2000B.28	FRICTION COPPER DISC
29	GWW2000B.29	RATCHET ASSEMBLY
30	GWW2000B.30	RETAINING RING
31	SN12.S	STEEL NUT M12 ZINC DIN934(SINGLE)
32	GWW2000B.32	DISC
33	SWM12.S	SPRING WASHER M12 ZINC (SINGLE)
34	GWW2000B.34	BUSH (LARGE)
35	GWW2000B.35	RETAINING PINION
36	SN6.S	STEEL NUT M6 ZINC DIN934 (SINGLE)
37	SWM6.S	SPRING WASHER M6 ZINC (SINGLE)
38	GWW2000B.38	CIRCLIP (26mm)
39	GWW2000B.39	BUSH HOLDER
40	GWW2000B.40	GEAR-SMALL
41	GWW2000B.41	GEAR PINION
42	GWW2000B.42	GEAR-LARGE
43	GWW2000B.43	WASHER
48	GWW2000B.48	BOLT (M10x132)

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.