




Parts Information:
Air Staple Gun 13-32mm Capacity
Model No: SA789.V2



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk



Parts Information:
Air Staple Gun 13-32mm Capacity
Model No: SA789.V2

Item	Part No.	Description
1	SA789.V2-01	DEFLECTOR
2	SA789.V2-02	HEX BOLT (M5x22)
3	SA789.V2-03	SPRING WASHER (5mm)
4	SA789.V2-04	WASHER (5mm)
5	SA789.V2-05	AIR CAP
6	SA789.V2-06	SEAL
7	SA789.V2-07	INTERNAL LINING
8	SA789.V2-08	O-RING (23.6x1.5)
9	SA789.V2-09	SPRING
10	SA789.V2-10	GASKET
11	SA789.V2-11	O-RING (9.5x2.65)
12	SA789.V2-12	HEAD VALVE PISTON
13	SA789.V2-13	O-RING (31.5x2.4)
14	SA789.V2-14	O-RING (24.5x3.5)
15	SA789.V2-15	O-RING (14x2.65)
16	SA789.V2-16	COLLAR
17	SA789.V2-17	O-RING (21x3)
18	SA789.V2-18	DRIVER BLADE UNIT
19	SA789.V2-19	RETAINING RING
20	SA789.V2-20	O-RING (41.2x2.65)
21	SA789.V2-21	LINING RING
22	SA789.V2-22	O-RING (30x2.65)
23	SA789.V2-23	RING
24	SA789.V2-24	CYLINDER
25	SA789.V2-25	GASKET
26	SA789.V2-26	BUMPER
27	SA789.V2-27	BODY
28	SA789.V2-28	BASE BUNG
29	SA789.V2-29	SWITCH UNIT
30	SA789.V2-30	TRIGGER PLATE
31	SA789.V2-31	SPRING PIN (2.5x16)
32	SA789.V2-32	O-RING (1.8x1.8)
33	SA789.V2-33	TRIGGER
34	SA789.V2-34	PIN

Item	Part No.	Description
35	SA789.V2-35	SAFETY GUIDE
36	SA789.V2-36	SPRING PIN (3x25)
37	SA789.V2-37	SAFETY
38	SA789.V2-38	SET PLATE
39	SA789.V2-39	SPRING SEAT
40	SA789.V2-40	SPRING
41	SA789.V2-41	WASHER (4mm)
42	SA789.V2-42	HEX BOLT (M4x8)
43	SA789.V2-43	SAFETY COVER
44	SA789.V2-44	WORKING CONTACT ELEMENT
45	SA789.V2-45	HEX BOLT (M4x14)
46	SA789.V2-46	DRIVER GUIDE
47	SA789.V2-47	MAGAZINE
48	SA789.V2-48	SPRING
49	SA789.V2-49	SPRING HOLDER
50	SA789.V2-50	PUSHER
51	SA789.V2-51	O-RING (2.5x1.8)
52	NLN4.S	NYLOC NUT M4 ZINC DIN 985 (SINGLE)
53	SA789.V2-53	TAIL COVER
54	SA789.V2-54	PIN
55	SA789.V2-55	HEX BOLT (M4x35)
56	SA789.V2-56	PIN
57	SA789.V2-57	CLICK LEVER
58	SA789.V2-58	SPRING
59	SA789.V2-59	MAGAZINE
60	SA789.V2-60	HEX BOLT (M4x12)
61	SA789.V2-61	TAIL HANGER
62	SA789.V2-62	HEX BOLT (M4x8)
63	NLN5.S	NYLOC NUT M5 ZINC DIN 985 (SINGLE)
64	SA789.V2-64	HEX BOLT (M5x18)
65	SA789.V2-65	O-RING (33x1.65)
66	SA789.V2-66	END CAP
67	SA789.V2-67	AIR COUPLING
68	SA789.V2-68	HAND GRIP

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk