



INSTRUCTIONS FOR
RETRACTING AIR HOSE REELS
 MODEL NO: **SA894.V3 & SA895.V3**

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.



Refer to instruction manual



Wear eye protection

1. SAFETY

- WARNING! DO NOT** dismantle the hose reel casing. To do so may result in damage to the appliance and/or personal injury and will invalidate the warranty. Internal maintenance, which will require the opening of the casing, must only be undertaken by an authorised service agent.
- ✓ Familiarise yourself with the application and limitations of the air hose reel, as well as the specific hazards.
- WARNING!** Disconnect the air hose reel from the air supply before changing accessories, servicing or performing any maintenance.
- ✓ Maintain the air hose reel in good condition (use an authorised service agent).
- ✓ Replace or repair damaged parts. *Use recommended parts only. Unauthorised parts may be dangerous and will invalidate the warranty.*
- ✓ Locate and fix the air hose reel in a suitable working area. **DO NOT** position the hose in direct sun light, or in areas of extreme heat or cold. Ensure there is adequate lighting.
- WARNING!** Ensure maximum air pressure is not exceeded.
- ✓ Keep extended air hose away from heat, oil and sharp edges. Check hose for wear before each use, and ensure all connections are secure.
- ✓ Keep the unwound air hose at a safe distance from the working area and free from wet, damp, oily surfaces.
- WARNING!** Always wear approved eye or face protection when operating the air hose reel.
- ✓ Maintain correct balance and footing. Ensure the floor is not slippery and wear non-slip shoes.
- ✓ Remove ill fitting clothing. Remove ties, watches, rings, and other loose jewellery and contain and/or tie back long hair.
- ✓ Keep children and unauthorised persons away from the working area.
- ✗ **DO NOT** operate the air hose reel if any parts are damaged or missing as this may cause failure and/or personal injury.
- ✗ **DO NOT** exceed the rated capacity of the air hose reel.
- ✗ **DO NOT** use the air hose reel for any purpose other than that for which it is designed.
- ✗ **DO NOT** pull the hose from the air supply.
- ✗ **DO NOT** operate the air hose reel when you are tired or under the influence of alcohol, drugs or intoxicating medication.
- ✗ **DO NOT** direct air from the air hose at yourself or others.
- ✓ When not in use ensure the air supply is turned off and tools disconnected. Disconnect from the air supply and retract the hose into case.

2. INTRODUCTION

Hard wearing, composite cased retracting air hose reels supplied with heavy duty polyurethane hose. Reels feature ratchet or free running operation and are supplied with wall/ceiling mounting brackets.

3. SPECIFICATION

Model no: SA894.V3
 Hose length: 15mtr
 Hose size ID/OD: 8/12mm
 Maximum pressure: 150psi
 Inlet/outlet: 1/4" BSP

Model no: SA895.V3
 Hose length: 10mtr
 Hose size ID/OD: 10/15mm
 Maximum pressure: 150psi
 Inlet/outlet: 3/8" BSP



4. MOUNTING AND ASSEMBLY

- WARNING!** Ensure the hose is disconnected from the air supply. **DO NOT** position the hose in direct sunlight or in areas of extreme heat or cold.
- 4.1. To wall mount the reel first remove the wall mounting bracket from the reel by releasing and withdrawing the two bracket pivots. (Refer to item 11 on the parts diagram. To release the pivots remove the casing screws which pass directly through each pivot. (The pivots are each retained by two screws.)
- WARNING! DO NOT** remove any other casing screws.
- 4.2. Fix the bracket in an appropriate position ensuring that the wall and the mounting screws and plugs will adequately support the weight of the reel and the tension of the hose as it is pulled from the reel.
- 4.3. Reattach the reel to the bracket ensuring the pivots are correctly inserted and retained by the casing screws.
- 4.4. Ensure that the hose can be pulled out to, and reeled back from, work sites without rubbing the sides of the cable entry.

5. OPERATION

- 5.1. **Extending the hose.**
As the hose is pulled out from the reel the action of the ratchet mechanism can be heard alternating between the usual clicking sound and a short period of silence. If the tension on the hose is released whilst the ratchet is clicking the hose will remain extended. If the tension on the hose is released during silent operation the hose will retract. To stop the hose retracting pull it out again a little until you hear the ratchet clicking.
- 5.2. **Retracting the hose.**
To release the hose and allow it to automatically rewind, pull the hose out from the locked position until the clicking stops and then release the tension on the hose. **DO NOT** let go of the hose but keep hold of it and guide the end back to the reel.
- WARNING!** The reel tension is factory set, if any adjustment is required contact an authorised service agent. **DO NOT** remove any of the black spring cover screws.

6. MAINTENANCE

- WARNING!** Before attempting maintenance or inspection vent any pressure remaining in the hose.
- 6.1. To ensure reliable operation, clean the hose and casing regularly. **DO NOT** spray or wet the product, but clean with a cloth and warm water. **DO NOT** use solvents or detergents, as these may cause permanent damage.
- 6.2. The hose reel does not require special maintenance as it is lubricated for life. If the product needs to be opened, consult your nearest authorised service agent.
- WARNING: DO NOT** attempt to loosen, or remove, any casing screws.
- 6.3. Replacement of the supply hose should be carried out by skilled personnel only. Consult your nearest authorised service agent.
- 6.4. **Storage.**
Should you wish to store the air hose, ensure it is clean and dry. Place the item in a dark, safe, dry, childproof location, where the temperature will remain reasonably stable. **DO NOT** store in a nylon, or plastic, bag as this will encourage condensation.

Environmental Protection



Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain off any fluids (if applicable) into approved containers and dispose of the product and the fluids according to local regulations.

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of this product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.



Sole UK Distributor, Sealey Group.
Kempson Way, Suffolk Business Park,
Bury St. Edmunds, Suffolk.
IP32 7AR



01284 757500



01284 703534



www.sealey.co.uk



sales@sealey.co.uk