


Parts Information: Compressor 100ltr Belt Drive 3hp with Cast Cylinders & Wheels Model No: SAC2103B.V2



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR I.B 01284 757500 01284 703534 sales@sealey.co.uk (Care)

www.sealey.co.uk

Page 1 of 4



Parts Information: Compressor 100ltr Belt Drive 3hp with Cast Cylinders & Wheels Model No: SAC2103B.V2

Item	Part No.	Description	Item	Part No.	Description
1	SAC3020041000	PUMP UNIT	25	SAC7230010000	RISLAN HOSE (SOLD PER 1 METER)
2	SAC5010940008	BASE PLATE	26	SAC7238810000	INFEED HOSE
3	SAC5140100008	HANDLE	27	SAC4170130000	BELT GUARD KIT
4	SAC5159151008	TANK 100ltr (SO)	28	SAC7260030000	WHEEL,CASTOR (100x8x29x132)
5	SS830.S	HEX HEAD SET SCREW M8x30mm SINGLE	29	SAC7260470000	WHEEL,FIXED (196x20x52)(SO)
6	SS1045.S	HEX HEAD SET SCREW M10x45mm SINGLE	30	SAC7330010000	WHEEL SPACER
7	HHB1280.S	HEX HEAD BOLT M12x80mm SINGLE	31	V/M51	V-BELT (ID-1295) M51
8	SS835.S	HEX HEAD SET SCREW M8x35mm SINGLE	32	SAC4151600000	MOTOR C/W PULLEY
9	SFS1020.S	HEX HEAD FLANGE BOLT M10x20 SINGLE	33	SAC7458860000	BELT GUARD SUPPORT
10	MSP512.S	MACHINE SCREW PAN HEAD PHILLIPS	34	SAC7459260000	BELT GUARD SUPPORT
		M5x12mm	35	SAC7459670000	BELT GUARD SUPPORT
11	SN12.S	STEEL NUT M12 ZINC DIN934(SINGLE)	50	SAC4057700000	PRESSURE SWITCH KIT
12	SN8.S	STEEL NUT M8 ZINC DIN934 (SINGLE)	51	SAC7023050000	LOCK NUT
13	SN10.S	STEEL NUT M10 ZINC DIN934(SINGLE)	52	SAC7081090000	JOINT 1/4"
14	FWM8.S	FLAT WASHER M8 SINGLE	53	SAC7088060000	CONNECTOR
15	RW625.S	REPAIR WASHER M6x25 (SINGLE)	54	SAC7090090000	PLUG 1/4"
16	FWM12.S	FLAT WASHER M12 SINGLE	55	SAC7100640000	PRESSURE REDUCER
17	RW1235.S	REPAIR WASHER M12x35 (SINGLE)	56	SAC7110240000	PRESSURE GAUGE 240psi, 40mm OD, REAR
18	SAC7080140000	ELBOW 1/8"			FIT
19	SAC7081040000	JOINT 1/2"	57	SAC9700001789	PRESSURE GAUGE 230 psi, 50mm
20	SAC7090030000	PLUG 1/2	58	SAC7250360000	PRESSURE SWITCH 20Amp
21	SAC7130150000	TAP 1/2" M/F	59	SAC7329050000	INFEED CABLE
22	SAC7130160000	TAP 3/8"	100	SAC4080500000	SCREW KIT
23	SAC7190190000	NON-RETURN VALVE	101	SAC4083760000	RUBBER FOOT KIT
24	SAC7192090000	SAFETY VALVE	102	SAC4083060000	PIVOT WHEEL KIT

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

01284 703534

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR


sales@sealey.co.uk

(Cris)

www.sealey.co.uk



Parts Information: Compressor 100ltr Belt Drive 3hp with Cast Cylinders & Wheels Model No: SAC2103B.V2



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR 1: 01284 757500 01284 703534 sales@sealey.co.uk (Surger)

www.sealey.co.uk



Parts Information: Compressor 100ltr Belt Drive 3hp with Cast Cylinders & Wheels Model No: SAC2103B.V2

Item	Part No.	Description
1	SAC9105450240	CON-ROD
11	SAC4080070000	PISTON RING SET
14	SAC7041410000	RING
15	SAC7050110000	PISTON PIN (15x55)
16	SAC7051510000	KEY (5x7.5)
17	B/6205	BEARING 6205
18	B/6206	BEARING 6206
26	SAC7090090000	PLUG 1/4"
27	SAC7180060000	OIL SIGHT GLASS
29	SAC7201010000	FLYWHEEL
31	SAC7220090000	PISTON
32	SAC9100270270	AFTERCOOLER
34	SAC9105450010	CRANKCASE

Item	Part No.	Description
35	SAC9105450250	CRANKSHAFT
36	SAC9105450060	CYLINDER
37	SAC9105450070	FRONT COVER
38	SAC9105450080	REAR COVER
39	SAC9105450090	BOTTOM COVER
44	SAC9105450180	HEAD
45	SAC7153140000	COVER
46	SAC9700001377	VENT PLUG
100	SAC4231260000	VALVE PLATE KIT
101	SAC4291070000	PISTON KIT
102	SAC4250130000	INTAKE FILTER KIT
103	SAC4081990000	KIT OF ACCESSORIES
104	SAC4080480000	SCREW KIT

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. **IMPORTANT**: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

01284 703534

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR

sales@sealey.co.uk

💮 www.sealey.co.uk

SAC2103B.V2 Issue 2 PL 8/09/17