


Parts Information: Compressor 50ltr Belt Drive 3hp with Cast Cylinders & Wheels Model No: SAC1503B



Item	Part No.	Description
1	SAC5010990008	BASE PLATE
2	SAC5159140008	TANK 50ltr
3	SS825.S	HEX HEAD SET SCREW M8x25mm SINGLE
4	SS1045.S	HEX HEAD SET SCREW M10x45mm SINGLE
5	HHB1280.S	HEX HEAD BOLT M12x80mm SINGLE
6	SFS1020.S	HEX HEAD FLANGE BOLT M10x20 SINGLE
7	MSP512.S	MACHINE SCREW PAN HEAD PHILLIPS M5x12mm
8	SAC7012170000	SCREW (M5x8)
9	SN12.S	STEEL NUT M12 ZINC DIN934(SINGLE)
10	SN8.S	STEEL NUT M8 ZINC DIN934 (SINGLE)
11	SN10.S	STEEL NUT M10 ZINC DIN934(SINGLE)
12	FWM8.S	FLAT WASHER M8 SINGLE
13	RW625.S	REPAIR WASHER M6x25 (SINGLE)
14	FWM12.S	FLAT WASHER M12 SINGLE
15	RW619.S	REPAIR WASHER M6x19 (SINGLE)
16	RW1235.S	REPAIR WASHER M12x35 (SINGLE)
17	SAC7080130000	ELBOW (3/8"BSP FEMALE-1/2"BSP MALE
18	SAC7080160000	ELBOW 1/2"BSP MALE X2
19	SAC7090030000	PLUG 1/2
20	SAC7090080000	PLUG
21	SAC7130160000	DRAIN VALVE 3/8"BSP MALE
22	SAC7190090000	NON-RETURN VALVE
23	SAC7192090000	SAFETY VALVE 10bar 3/8"BSP MALE
24	SAC7230010000	RISLAN HOSE (SOLD PER 1 METER)

Item	Part No.	Description
25	SAC7234620000	DELIVERY PIPE
26	SAC4170010000	BELT GUARD KIT
27	SAC7260360000	WHEEL,CASTOR(63x7x22x83)
28	SAC7260470000	WHEEL,FIXED (196x20x52)
29	SAC7330010000	WHEEL SPACER
30	SAC7360020000	END PLUG
31	V/A47	V-BELT (ID-1200) A47
32	SAC1127380796	MOTOR (BLACK FAN COVER TWO CAPACITORS)
33	SAC7409570000	MOTOR PULLEY 160MM - SINGLE BELT (STANDA
34	SAC7458510000	BELT GUARD SUPPORT
35	SAC9101880000	PUMP UNIT
40	SAC4057620000	PRESSURE SWITCH KIT 16/20Amp 12Bar 175Ps
41	SAC7023050000	LOCK NUT
42	SAC7081090000	UNION 1/4"BSP M-1/4"BSP M L:25mm
43	SAC7088060000	CONNECTOR
44	SAC7090090000	PLUG 1/4"
45	SAC7100640000	PRESSURE REDUCER
46	SAC7110240000	PRESSURE GAUGE 240psi, 43mm OD, REAR FIT
47	SAC9700001789	PRESSURE GAUGE 230 psi, 50mm OD, rear fi
48	SAC7130570000	COUPLING BODY 1/4"BSP MALE
49	SAC7250360000	PRESSURE SWITCH 20Amp
	SAC7329010000	POWER CABLE (NOT SHOWN)

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

🙊 sales@sealey.co.uk

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.


01284 703534

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR U.B 01284 757500

🐑 www.sealey.co.uk



Parts Information: Compressor 50ltr Belt Drive 3hp with Cast Cylinders & Wheels Model No: SAC1503B



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR I. 01284 757500 01284 703534 sales@sealey.co.uk

🐑 www.sealey.co.uk

SAC1503B Issue 2 PL 26/01/18



Parts Information: Compressor 50ltr Belt Drive 3hp with Cast Cylinders & Wheels Model No: SAC1503B

Item	Part No.	Description
1	SAC9700001075	CRANKCASE
2	SAC9700001076	CRANKCASE COVER
3	SAC9700000531	SCREW (M5x12)
4	SAC9700001077	CRANKCASE BASE SEAL
5	SAC9100270140	CRANKSHAFT
6	B/6203	BEARING 6203
7	B/6204	BEARING 6204
8	SAC9100270150	OIL SEAL
9	SAC9100270160	FRONT COVER
10	SAC9100270170	REAR COVER
11	SAC9100280010	O-RING 46.2x39.6x3.3 (FRONT COVER SEAL)
12	SAC7011420000	SCREW (M6x16)
13	SAC9100280020	KEY
14	SAC9100270010	CONNECTION ROD
15	SAC9100270020	GUDGEON PIN
16	SAC9100270030	PISTON
17	SAC4080120000	KIT OF PISTON RINGS (3)
18	SAC9100270070	SEEGER RING (OGIVE)
19	SAC9100270080	CYLINDER(TWIN)
20	SAC7012220000	SCREW
21	SAC9100280070	OIL SIGHT GLASS
22	SAC9100270180	GASKET, CYLINDER BASE
23	SAC9100270190	GASKET
24	SAC9100270090	VALVE PLATE (CAST WITH HOLE FOR REEDS)
25	SAC9100270200	GASKET

ltom	Part No.	Description
Item		Description
26	SAC9100280090	VALVE
27	SAC9100270210	GASKET
28	SAC9100270100	CYLINDER HEAD
29	SAC7458340000	PLATE
30	SAC7210010000	FILTER ELEMENT
31	SAC9100270240	INTAKE FILTER
32	SAC7012100000	RD HEAD S/T SCREW M3.8 X 15
33	SCB855.S	SOCKET CAP BOLT ZINC M8X55
34	SAC9100270220	COVER
35	MSP512.S	MACHINE SCREW PAN HEAD PHILLIPS M5x12mm
36	SS616.S	HEX HEAD SET SCREW M6x16mm SINGLE
37	SAC1129700300	BREATHER PLUG
38	RW825.S	REPAIR WASHER M8x25 (SINGLE)
39	SAC9100270230	FLYWHEEL
40	SS825.S	HEX HEAD SET SCREW M8x25mm SINGLE
41	SAC7031010000	TOOTHED WASHER
42	SAC9100270270	AFTERCOOLER
43	FWM8.S	FLAT WASHER M8 SINGLE
44	SAC9100270280	GASKET
45	SAC7080160000	ELBOW 1/2"BSP MALE X2
46	SAC9700000693	PLUG 3/8"
100	SAC9700003272	VALVE PLATE ASS'Y
101	SAC9700000078	GASKET KIT
102	SAC9700010170	PISTON GROUP

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. **IMPORTANT**: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

01284 703534

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR

sales@sealey.co.uk

www.sealey.co.uk

01284 757500