


Parts Information:

Transmission Jack 1.5tonne Vertical Model No: 1500TR



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. There may be alternative versions of this product, please contact us should you require this information.

IMPORTANT: No liability is accepted for incorrect use of product. Spare parts must be fitted by a competent person

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk





Parts Information:

Transmission Jack 1.5tonne Vertical Model No: 1500TR

| Item | Part No. | Description |
|------|------------|----------------------|
| 1 | 1500TR.01 | Forked Saddle Ass'y |
| 2 | 1500TR.02 | Dust Seal |
| 3 | SA316.60 | O-Ring |
| 4 | 1500TR.04 | Cylinder Head Ass'y. |
| 5 | SB-6.0 | Steel Ball 6.0mm |
| 6 | 1500TR.06 | O-Ring |
| 7 | 1500TR.07 | Release Rod 12 |
| 8 | 1500TR.08 | Bush |
| 9 | 1500TR.09 | Spring |
| 10 | 1500TR.10 | Release Knob |
| 11 | GSM58.S | Grub Screw M5x8 |
| 12 | 800TTJ.227 | Spring Pin M4 X 25 |
| 13 | 1500TR.13 | O-Ring |
| 14 | 1500TR.14 | O-Ring |
| 15 | 1500TR.15 | Oil Filler Plug |
| 16 | 1500TR.16 | Oil Reservoir Ass'y |
| 17 | 1500TR.17 | Cylinder |
| 18 | 1500TR.18 | Piston |
| 19 | 1500TR.19 | Piston Screw |
| 20 | 2200HL.45 | O-Ring |
| 21 | 1500TR.21 | Screw |
| 22 | SB-9.5 | Steel Ball 9.5mm |
| 23 | 1500TR.23 | Retaining Ring |
| 24 | FWM20.S | Flat Washer M20 |

| Item | Part No. | Description |
|------|------------|-----------------------------|
| 25 | 1500TR.25 | Bush |
| 26 | 1500TR.26 | Spring |
| 27 | 1500TR.27 | Pump Cylinder |
| 28 | 1500TR.28 | Pump Rod |
| 29 | 1500TR.29 | Cup Seal |
| 30 | 1500TR.30 | O-Ring |
| 31 | 1500TR.31 | Screw |
| 32 | 1500TR.32 | O-Ring |
| 33 | 1500TR.33 | Spring |
| 34 | 1500TR.34 | Taper Valve |
| 35 | 1500TR.35 | Retaining Ring |
| 36 | 1500TR.36 | Bush |
| 37 | 1500TR.37 | Pump Pedal |
| 38 | 1500TR.38 | R Ring |
| 39 | 1500TR.39 | Screw |
| 40 | FWM12.S | Flat Washer M12 |
| 41 | 1500TR.41 | Pump Base Ass'y |
| 42 | 1500TR.42 | Leg Ass'y |
| 43 | SN12.SD | Domed Nut M12 |
| 44 | SWM12.S | Spring Washer M12 |
| 45 | 1500TR.45 | Wheel, Swivel Castor |
| 46 | SS1230.S | Hex Head Set Screw M12 X 30 |
| 47 | SN12.S | Steel Nut M12 |
| 48 | HHB12140.S | Hex Head Bolt M12 x 140mm |

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. There may be alternative versions of this product, please contact us should you require this information.

IMPORTANT: No liability is accepted for incorrect use of product. Spare parts must be fitted by a competent person

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

01284 757500



01284 703534



sales@sealey.co.uk

